
BROCHURE

Lug Express

Fast delivery on custom, made-to-order
Color-Keyed® lugs

Color-Keyed®



Lug Express

350+ made-to-order Color-Keyed® lugs — ready to ship in 5 days or less!

Need lugs in a hurry? Meet the new Lug Express program from ABB Installation Products.

Global supply chain issues and delays with raw materials have made it tough to get what you need when you need it — particularly if what you need isn't a standard, "off-the-shelf," stocked product. Long lead times can cost businesses staggering sums in downtime.

That's why ABB Installation Products has established the Lug Express program — so you can get customized, made-to-order (MTO) lugs in quantities of 25 to 200 ready to ship in just five business days.

Other manufacturers may be moving away from small quantity orders for MTO lugs, but ABB Installation Products has your back with high-quality Color-Keyed lugs built stateside in our Ormond Beach, Florida manufacturing facility.

Lug Express lug options

- Copper or aluminum
- #1 AWG–750 kcmil
- Single or double hole for bolt size #8–1"
- Any functional hole spacing for two-hole lugs
- Long or short barrel
- Standard or narrow tongue
- Bend configurations (15°, 30°, 45°, 60° or 90°)
- Belled ends
- Tin plated



Get your equipment that requires unique terminations **up and running fast** with Lug Express.



See how we do it

Watch a video on the Lug Express program and see how your custom, MTO lugs are made in our state-of-the-art Ormond Beach manufacturing facility.

 [ABB Lug Express video](#)

Get started now

The following pages show standard lugs and splices available through the Lug Express program. You can also visit the ABB Lug Express portal and see how easy it is to start configuring the custom lugs you need.

 [ABB Lug Express portal](#)

5 days
 **to ship or less**



Color-Keyed®

Lug Express

Copper lugs

Copper lugs — One-hole, standard barrel, straight

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54148R	Tin	1	3/8	Round	Yes	Green
LE54150BT	Tin		1/2	Standard	Yes	
LE54208BT	Tin		None	Standard	Yes	
LE54155BT	Tin	1/0	None	Standard	Yes	Pink
LE25630695920	Tin	2/0	3/16	Standard	Yes	Black
LE54158NT	Tin		3/16	Narrow	Yes	
LE54260BT	Tin		None	Standard	Yes	
LE54111NT	Tin	3/0	3/8	Narrow	Yes	Orange
LE5416510	Tin		3/8	Standard	Yes	
LE54265BT	Tin		None	Standard	Yes	
LE54167BE	Tin	4/0	1/4	Standard	No	Purple
LE54168NT	Tin		3/16	Narrow	Yes	
LE54112NT	Tin		3/8	Narrow	Yes	
LE54170BT	Tin		None	Standard	Yes	
LE58161BE	Tin	4/0 flex	1/4	Standard	No	Yellow
LE58163NT	Tin		3/8	Narrow	Yes	
LE54173NT	Tin	250	3/16	Narrow	Yes	
LE54174NT	Tin		3/8	Narrow	Yes	
LE58168NT05	Tin	250 flex	3/16	Narrow	Yes	White
LE5816812	Tin		3/4	Standard	Yes	
LE58171BT PFM250	Plain		None	Standard	Yes	
LE54178NT	Tin	300	3/16	Narrow	Yes	
LE54179NT	Tin		3/8	Narrow	Yes	
LE54280NTBT	Tin		None	Narrow	Yes	
LE54114PF	Plain		1/2	Standard	Yes	
LE5817110	Tin	300 flex	5/8	Standard	Yes	Red
LE5411505	Tin	350	3/16	Standard	Yes	
LE54115NT06	Tin		3/8	Narrow	Yes	
LE54115NT	Tin		1/2	Narrow	Yes	
LE54115PF	Plain		1/2	Standard	Yes	
LE58177NT05	Tin	350 flex	3/16	Narrow	Yes	Blue
LE58177NT06	Tin		3/8	Narrow	Yes	
LE5817406	Tin		3/8	Standard	Yes	
LE5411605TL16	Tin	400	3/16	Standard	Yes	
LE5411606	Tin		3/8	Standard	Yes	
LE5418512	Tin		3/4	Standard	Yes	
LE54116BT	Tin		None	Standard	Yes	
LE54283NTBT	Tin		None	Narrow	Yes	
LE54116PF	Plain		1/4	Standard	Yes	
LE54118NT06	Tin	500	3/8	Narrow	Yes	Brown
LE54118NT	Tin		1/2	Narrow	Yes	
LE5818006	Tin	500 weld	3/8	Standard	Yes	Green
LE5818008	Tin		1/2	Standard	Yes	
LE5412008PFNM	Plain	600	1/2	Standard	Yes	-
LE54122TB	Tin	700	5/8	Standard	Yes	Pink
LE58182NT08	Tin	1325/24	1/2	Narrow	Yes	
LE54123NT08	Tin	750	1/2	Narrow	Yes	Black
LE5412308PF	Plain		1/2	Standard	Yes	
LE54123BT PFM600	Plain		None	Standard	Yes	



Lug Express

Copper lugs

Copper lugs — One-hole, standard barrel, 45° bend

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54147UF	Tin	1	3/16	Standard	Yes	Green
LE54148UF	Tin		3/8	Standard	Yes	
LE54150UF	Tin		1/2	Standard	Yes	
LE54152UF	Tin	1/0	1/4	Standard	Yes	Pink
LE54109UF	Tin		3/8	Standard	Yes	
LE54155UF	Tin		1/2	Standard	Yes	
LE54157NTUF03	Tin	2/0	10	Narrow	Yes	Black
LE54157UF	Tin		1/4	Standard	Yes	
LE54158NTUF	Tin		3/16	Narrow	Yes	
LE54158UF	Tin		3/16	Standard	Yes	
LE54160UF	Tin		1/2	Standard	Yes	
LE54111UF	Tin	3/0	3/8	Standard	Yes	Orange
LE54165UF	Tin		1/2	Standard	Yes	
LE54112UF	Tin	4/0	3/8	Standard	Yes	Purple
LE54170UF	Tin		1/2	Standard	Yes	
LE58162NTUF	Tin	4/0 flex	3/16	Narrow	Yes	Yellow
LE58162UF	Tin		3/16	Standard	Yes	
LE58163UF	Tin		3/8	Standard	Yes	
LE58165UF	Tin		1/2	Standard	Yes	
LE54113UF	Tin	250	1/2	Standard	Yes	
LE54275UFBT	Tin		None	Standard	Yes	
LE54114UF	Tin	300	1/2	Standard	Yes	White
LE54115UF	Tin	350	1/2	Standard	Yes	Red
LE54116UF06	Tin	400	3/8	Standard	Yes	Blue
LE54185UF	Tin		5/8	Standard	Yes	
LE58177UF06	Tin	400 flex	3/8	Standard	Yes	-
LE58177UF	Tin		1/2	Standard	Yes	
LE54118UF	Tin	500	1/2	Standard	Yes	Brown



Copper lugs — One-hole, standard barrel, 90° bend

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54108NTUB	Tin	1	1/4	Narrow	Yes	Green
LE54150UB	Tin		1/2	Standard	Yes	
LE54155UB	Tin	1/0	1/2	Standard	Yes	Pink
LE54160UB	Tin	2/0	1/2	Standard	Yes	Black
LE54110UBPFNM	Plain		3/8	Standard	Yes	-
LE54167UB	Tin	4/0	1/4	Standard	Yes	Purple
LE58161UB	Tin	4/0 flex	1/4	Standard	Yes	Yellow
LE58163NTUB	Tin		3/8	Narrow	Yes	
LE58163UB	Tin		3/8	Standard	Yes	
LE58165UB	Tin		1/2	Standard	Yes	
LE54172NTUB	Tin	250	1/4	Narrow	Yes	
LE54174UB	Tin		3/8	Standard	Yes	
LE54113UB	Tin		1/2	Standard	Yes	



Lug Express

Copper lugs

Copper lugs — One-hole, standard barrel, 90° bend

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE58168UB	Tin	250 flex	½	Standard	Yes	White
LE54178UB	Tin	300	⅝	Standard	Yes	
LE54179UB	Tin		¾	Standard	Yes	
LE54114UB	Tin		½	Standard	Yes	
LE54181UB12	Tin		¾	Standard	Yes	
LE54115NTUB06	Tin	350	¾	Narrow	Yes	Red
LE54116UB06	Tin	400	¾	Standard	Yes	Blue
LE54185UB	Tin		⅝	Standard	Yes	
LE54185UB12	Tin		¾	Standard	Yes	
LE58177UB	Tin	400 flex	½	Standard	Yes	-
LE54118UB	Tin	500	½	Standard	Yes	Brown
LE58180UB	Tin	500 flex	⅝	Standard	Yes	Green
LE54120UB08	Tin	600	½	Standard	Yes	
LE54120UB	Tin		⅝	Standard	Yes	

Copper lugs — Two-hole, standard barrel, straight

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE542080310	Tin	1	10	⅝	Standard	Yes	Green
LE542080412	Tin		¾	¾	Standard	Yes	
LE54208NT	Tin		¾	¾	Narrow	Yes	
LE542080628	Tin		¾	1¼	Standard	Yes	
LE542550410	Tin	1/0	¾	⅝	Standard	Yes	
LE542550416	Tin		¾	1	Standard	Yes	
LE54255	Tin		⅝	⅞	Standard	Yes	
LE54255NT0410	Silver		¾	⅝	Narrow	Yes	
LE542100410	Tin	2/0	¾	⅝	Standard	Yes	Black
LE54261NT0412	Tin		¾	¾	Narrow	Yes	
LE542100416	Tin		¾	1	Standard	Yes	
LE54210NT	Tin		¾	1	Narrow	Yes	
LE54261NT0410	Silver		¾	⅝	Narrow	Yes	
LE542660412	Tin	3/0	¾	¾	Standard	Yes	Orange
LE542660416	Tin		¾	1	Standard	Yes	
LE54265BE	Tin		½	1¼	Standard	No	
LE54265NH	Tin		½	1¼	Standard	Yes	
LE582650412	Tin	4/0 flex	¾	¾	Standard	Yes	Yellow
LE54214NT0410	Tin	250	¾	⅝	Narrow	Yes	
LE542130416	Tin		¾	1	Standard	Yes	
LE542830828PFM250	Plain		½	1¼	Standard	Yes	
LE542140516	Tin	300	⅝	1	Standard	Yes	White
LE542140617	Tin		¾	1½	Standard	Yes	
LE58277PFM350	Plain	350	½	1¼	Standard	Yes	-
LE542160516	Tin	400	⅝	1	Standard	Yes	Blue
LE542830828	Tin		½	1¼	Standard	Yes	

Lug Express

Copper lugs

Copper lugs — Two-hole, standard barrel, straight

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54289PFM500	Plain	500	½	1¼	Standard	Yes	Brown
LE54286NT	Tin		½	1¼	Narrow	Yes	
LE54223NT	Tin	600	½	1¼	Narrow	Yes	Green
LE54223PFM600	Plain		½	1¼	Standard	Yes	
LE58281NT0616	Tin	1325/24	¾	1	Narrow	Yes	Pink
LE58284	Tin	646	½	1¼	Standard	No	Black

Copper lugs — Two-hole, standard barrel, 45° bend

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54208NTUF	Tin	1	¾	¾	Narrow	Yes	Green
LE54261NTUF0410	Tin	2/0	¾	⅝	Narrow	Yes	Black
LE54210UF	Tin		¾	1	Standard	Yes	
LE54214UF	Tin	250	¾	1	Standard	Yes	Yellow
LE54286UF	Tin	500	½	1¼	Standard	Yes	Brown
LE54223UF	Plain	600	½	1¼	Standard	Yes	Green
LE58281UF	Tin	1325/24	½	1¼	Standard	Yes	Black

Copper lugs — Two-hole, standard barrel, 90° bend

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54208NTUB	Tin	1	¾	¾	Narrow	Yes	Green
LE54208UB	Tin		¾	¾	Standard	Yes	
LE54210UB	Tin	2/0	¾	1	Standard	Yes	Black
LE54212UB	Tin	4/0	¾	1	Standard	Yes	Purple
LE54216UB	Tin	400	¾	1	Standard	Yes	Blue
LE54286UB	Tin	500	½	1¼	Standard	Yes	Brown
LE54220UB	Tin	600	¾	1	Standard	Yes	Green
LE54220UB0628	Tin		¾	1¼	Standard	Yes	
LE54289UB	Tin		½	1¼	Standard	Yes	

Lug Express

Copper lugs

Copper lugs — One-hole, long barrel, straight

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54947BEPH	Tin	1	#10	Standard	Yes	Green
LE54947BE04	Tin		¼	Standard	No	
LE54947BE08	Tin		½	Standard	No	
LE54946BE	Tin	1/0	#10	Standard	No	Pink
LE54949BE04	Tin		¼	Standard	No	
LE54949BEPH	Tin		⅜	Standard	Yes	
LE54909BEPH	Tin		¾	Standard	Yes	
LE54910BE05	Tin	2/0	⅜	Standard	No	Black
LE54910BEPH	Tin		¾	Standard	Yes	
LE54951BEPH	Tin		½	Standard	Yes	
LE54965BE04	Tin	3/0	¼	Standard	No	Orange
LE54965BE06PH	Tin		¾	Standard	Yes	
LE54965BEPH	Tin		½	Standard	Yes	
LE54965BEBT	Tin		None	Standard	No	
LE54970BE06	Tin	4/0	¾	Standard	No	Purple
LE54970BE06PH	Tin		¾	Standard	Yes	
LE54913BE05	Tin	250	⅜	Standard	No	Yellow
LE54913BE06PH	Tin		¾	Standard	Yes	
LE54913BENT06	Tin		¾	Narrow	No	
LE54913BEPH	Tin		½	Standard	Yes	
LE54913BE10	Tin		⅝	Standard	No	
LE54913BE10PH	Tin		⅝	Standard	Yes	
LE54868BEBT	Tin		None	Standard	No	
LE54914BENTPH	Tin	300	½	Narrow	Yes	White
LE54914BE10	Tin		⅝	Standard	No	
LE54914BENT10PH	Tin		⅝	Narrow	Yes	
LE54915BEPH	Tin	350	½	Standard	Yes	Red
LE54915BE10PH	Tin		⅝	Standard	Yes	
LE54916BE06	Tin	400	¾	Standard	No	Blue
LE54918BENTPH	Tin	500	½	Narrow	Yes	Brown
LE54918BEPH	Tin		½	Standard	Yes	
LE54918BEBT	Tin		None	Standard	No	
LE54921BENTPH	Tin	600	½	Narrow	Yes	Green
LE54921BEPH	Tin		½	Standard	Yes	
LE54979BE	Tin	700	½	Standard	No	Pink
LE54979BENTPH	Tin		½	Narrow	Yes	
LE58984BENT08PH	Tin	1600/24	½	Narrow	Yes	Black
LE58984BEPH	Tin		⅝	Standard	Yes	



Lug Express

Copper lugs

Copper lugs — One-hole, long barrel, 45° bend

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54909BEUF	Tin	1/0	¾	Standard	No	Pink
LE54950BEUF	Tin		½	Standard	No	
LE54970BEUF	Tin	4/0	½	Standard	No	Purple
LE54913BEUF06	Tin	250	¾	Standard	No	Yellow
LE54914BEUFPH	Tin	300	½	Standard	Yes	White
LE54916BEUF	Tin	400	½	Standard	No	Blue
LE54874BEUFBT	Tin		None	Standard	No	
LE54918BEUF	Tin	500	½	Standard	No	Brown




Copper lugs — One-hole, long barrel, 90° bend

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54910BEUB	Tin	2/0	¾	Standard	No	Black
LE54951BEUB	Tin		½	Standard	No	
LE54965BEUB	Tin	3/0	½	Standard	No	Orange
LE54970BEUB06	Tin	4/0	¾	Standard	No	Purple
LE54970BEUB	Tin		½	Standard	No	
LE54913BEUB06	Tin	250	¾	Standard	No	Yellow
LE54913BEUB	Tin		½	Standard	No	
LE54914BEUB06PH	Tin	300	¾	Standard	Yes	White
LE54915BEUB	Tin	350	½	Standard	No	Red
LE54874BEUBBT	Tin	400	None	Standard	No	Blue
LE54918BEUB	Tin	500	½	Standard	No	Brown




Lug Express Copper lugs

Copper lugs — Two-hole, long barrel, straight



Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54809BE	Tin	1	3/4	3/8	Standard	No	Green
LE54812BE	Tin		3/4	3/4	Standard	No	
LE54812BEPH	Tin		3/4	3/4	Standard	Yes	
LE54858BEPH	Tin		5/16	7/8	Standard	Yes	
LE54857BEPH	Tin		1/2	1 1/4	Standard	Yes	
LE54859BEPH	Tin	1/0	3/4	3/8	Standard	Yes	Pink
LE54860BEPH	Tin		5/16	7/8	Standard	Yes	
LE54814BEPH	Tin	2/0	3/4	3/4	Standard	Yes	Black
LE54862BE0514PH	Tin		5/16	7/8	Standard	Yes	
LE54815BE	Tin	3/0	3/4	3/4	Standard	No	Orange
LE54816BEPH	Tin		3/8	1	Standard	Yes	
LE54818BEPH	Tin	4/0	3/8	1 1/4	Standard	Yes	Purple
LE54866BE0822	Tin		1/2	1 3/8	Standard	No	
LE54866BE0816PF	Plain		1/2	1	Standard	No	
LE54868BENTO616	Tin	250	3/8	1	Narrow	No	Yellow
LE54868BENTO616PH	Tin		3/8	1	Narrow	Yes	
LE54819BENT	Tin	300	3/8	1	Narrow	No	White
LE54872BENTO616	Tin	350	3/8	1	Narrow	No	Red
LE54872BENT	Tin		1/2	1 1/4	Narrow	No	
LE54872BENTPH	Tin		1/2	1 1/4	Narrow	Yes	
LE54874BENT	Tin	400	1/2	1 1/4	Narrow	No	Blue
LE54876BENT	Tin	500	1/2	1 1/4	Narrow	No	Brown
LE54876BENTPH	Tin		1/2	1 1/4	Narrow	Yes	
LE54878BENTPH	Tin	600	1/2	1 1/4	Narrow	Yes	Green
LE54879BENTO616PH	Tin	700	3/8	1	Narrow	Yes	Pink
LE54880BENT	Tin	750	1/2	1 1/4	Narrow	No	Black
LE54880BENTPH	Tin		1/2	1 1/4	Narrow	Yes	


Copper lugs — Two-hole, long barrel, 45° bend



Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54809BEUF	Tin	1	3/4	3/8	Standard	No	Green
LE54818BEUF0616	Tin	4/0	3/8	1	Standard	No	Purple
LE54866BEUF	Tin		1/2	1 1/4	Standard	No	
LE54868BEUF0616PH	Tin	250	3/8	1	Standard	Yes	Yellow
LE54868BEUF	Tin		1/2	1 1/4	Standard	No	
LE54819BEUF	Tin	300	3/8	1	Standard	No	White
LE54876BEUF	Tin	500	1/2	1 1/4	Standard	No	Brown
LE54878BEUF	Tin	600	1/2	1 1/4	Standard	No	Green


Lug Express Copper lugs

Copper lugs — Two-hole, long barrel, 90° bend



Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54809BENTUBPH	Tin	1	3/4	3/8	Narrow	Yes	Green
LE54809BEUBPH	Tin	1	3/4	3/8	Standard	Yes	
LE54858BEUB	Tin	1	5/16	7/8	Standard	No	
LE54857BEUB0616	Tin	1	3/8	1	Standard	No	
LE54860BEUB0828	Tin	1/0	1/2	1 1/4	Standard	No	Pink
LE54862BEUB	Tin	2/0	1/2	1 1/4	Standard	No	Black
LE54816BEUB	Tin	3/0	3/8	1	Standard	No	Orange
LE54876BEUB	Tin	500	1/2	1 1/4	Standard	No	Brown
LE54878BEUB	Tin	600	1/2	1 1/4	Standard	No	Green
LE58884BEUB	Tin	1600/24	1/2	1 1/4	Standard	No	Black

Copper lugs — One-hole, standard barrel, straight, bell-ended



Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54147BS	Tin	1	5/16	Standard	Yes	Green
LE54148BS	Tin		3/8	Standard	Yes	
LE54152BS	Tin	1/0	1/4	Standard	Yes	Pink
LE54153BS	Tin		5/16	Standard	Yes	
LE54160BS	Tin	2/0	1/2	Standard	Yes	Black
LE54162BS	Tin	3/0	1/4	Standard	Yes	Orange
LE54112BS	Tin	4/0	3/8	Standard	Yes	Purple
LE58163BS	Tin	4/0 flex	3/8	Standard	Yes	Yellow
LE58165BS	Tin		1/2	Standard	Yes	
LE58168BE06BS	Tin	250 flex	3/8	Standard	Yes	White
LE54114BS	Tin	300	1/2	Standard	Yes	
LE54185313BS06	Tin	400	3/8	Standard	Yes	Blue
LE54122BS	Tin	600	5/8	Standard	Yes	Green
LE58184BS	Tin	1600/24	5/8	Standard	Yes	Black

Lug Express

Copper lugs

Copper lugs — Two-hole, standard barrel, straight, bell-ended

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54210BS	Tin	2/0	3/8	1	Standard	Yes	Black
LE542660410BS	Tin	3/0	1/4	3/4	Standard	Yes	Orange
LE542660412BS	Tin		1/4	3/4	Standard	Yes	Orange
LE54265BS	Tin		1/2	1 1/4	Standard	Yes	Orange
LE582650612BS	Tin	4/0 flex	3/8	3/4	Standard	Yes	Yellow
LE58265NT0616BS	Tin		3/8	1	Narrow	Yes	Yellow
LE54280BEBS	Tin	300	1/2	1 1/4	Standard	No	White
LE58277NT0616BS	Tin	350 flex	3/8	1	Narrow	Yes	-
LE54223PFM600BS	Plain	600	1/2	1 1/4	Standard	Yes	Black
LE582810616PHBS	Tin	1325/24	3/8	1	Standard	Yes	Pink

Copper lugs — Two-hole, standard barrel, 45° bend, bell-ended

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54208UFBS	Tin	1	1/4	3/4	Standard	Yes	Green

Copper lugs — One-hole, long barrel, straight, bell-ended

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54913BEBS	Tin	250	1/2	Standard	No	Yellow
LE54921BEBS	Tin	600	1/2	Standard	No	Green
LE54979BEBS	Tin	700	1/2	Standard	No	Pink
LE54922BEBS	Tin	750	1/2	Standard	No	Black
LE58984BEBS	Tin	1600/24	3/8	Standard	No	Black

Lug Express

Copper lugs

Copper lugs — Two-hole, long barrel, straight, bell-ended

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54857BEBS	Tin	1	1/2	1 1/4	Standard	No	Green
LE54814BEBS	Tin	2/0	1/4	3/4	Standard	No	Black
LE54862BE0616BS	Tin		3/8	1	Standard	No	Black
LE54862BEBS	Tin		1/2	1 1/4	Standard	No	Black
LE54864BEBS	Tin	3/0	1/2	1 1/4	Standard	No	Orange
LE54866BEBS	Tin	4/0	1/2	1 1/4	Standard	No	Purple
LE54868BE0616BS	Tin	250	3/8	1	Standard	No	Yellow
LE54876BE0616BS	Tin	500	3/8	1	Standard	No	Brown

Copper lugs — Two-hole, long barrel, 90° bend, bell-ended

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54809BEUBBS	Tin	1	1/4	3/4	Standard	No	Green


Copper stacking lugs — One-hole, standard barrel, straight, top

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54108T	Tin	1	1/4	Standard	Yes	Green
LE54147T	Tin		5/16	Standard	Yes	Green
LE54148T	Tin		3/8	Standard	Yes	Green
LE54153T	Tin	1/0	5/16	Standard	Yes	Pink
LE54109T	Tin		3/8	Standard	Yes	Pink
LE54158T	Tin	2/0	5/16	Standard	Yes	Black
LE54160T	Tin		1/2	Standard	Yes	Black
LE54168T	Tin	4/0	5/16	Standard	Yes	Purple
LE54170T	Tin		1/2	Standard	Yes	Purple
LE58163T	Tin	4/0 flex	3/8	Standard	Yes	Yellow
LE54113T	Tin	250	1/2	Standard	Yes	Yellow
LE5816806T	Tin	250 flex	3/8	Standard	Yes	White
LE58168T	Tin		1/2	Standard	Yes	White
LE54187T	Tin	500	3/8	Standard	Yes	Brown

Lug Express Copper lugs


Copper stacking lugs — One-hole, standard barrel, 90° bend, top

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54157NTUB06T	Tin	2/0	3/8	Narrow	Yes	Black




Copper stacking lugs — Two-hole, standard barrel, straight, top

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54212T	Tin	4/0	3/8	1	Standard	Yes	Purple
LE54214T	Tin	300	3/8	1	Standard	Yes	White



Copper stacking lugs — One-hole, standard barrel, straight, bottom


Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54108B	Tin	1	1/4	Standard	Yes	Green
LE54147B	Tin		5/16	Standard	Yes	Green
LE54147NT	Tin		5/16	Narrow	Yes	Green
LE54148B	Tin		3/8	Standard	Yes	Green
LE54153B	Tin	1/0	5/16	Standard	Yes	Pink
LE54109B	Tin		3/8	Standard	Yes	Pink
LE54158B	Tin	2/0	5/16	Standard	Yes	Black
LE54160B	Tin		1/2	Standard	Yes	Black
LE54163B	Tin	3/0	5/16	Standard	Yes	Orange
LE54168B	Tin	4/0	5/16	Standard	Yes	Purple
LE54167BCK	Tin		1/2	Standard	Yes	Purple
LE54170B	Tin		1/2	Standard	Yes	Purple
LE58163NTB	Tin	4/0 flex	3/8	Narrow	Yes	Yellow
LE54174B	Tin	250	3/8	Standard	Yes	Yellow
LE54113B	Tin		1/2	Standard	Yes	Yellow
LE5816806B	Tin	250 flex	3/8	Standard	Yes	White
LE58168NT06B	Tin		3/8	Narrow	Yes	White
LE5817406B	Tin	350 flex	3/8	Standard	Yes	Blue
LE58177B	Tin		1/2	Standard	Yes	Blue



Lug Express Copper lugs


Copper stacking lugs — One-hole, standard barrel, 45° bend, bottom

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54148UFB	Tin	1	3/8	Standard	Yes	Green
LE54160UFB	Tin	2/0	1/2	Standard	Yes	Black
LE54165UFB	Tin	3/0	1/2	Standard	Yes	Orange
LE58165UFB	Tin	4/0 flex	1/2	Standard	Yes	Yellow
LE54113UFB	Tin	250	1/2	Standard	Yes	Yellow
LE58168UFB	Tin	250 flex	1/2	Standard	Yes	White




Copper stacking lugs — One-hole, standard barrel, 90° bend, bottom

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54147UBB	Tin	1	5/16	Standard	Yes	Green
LE54157NTUB06B	Tin	2/0	3/8	Narrow	Yes	Black
LE54162NTUBB	Tin	3/0	1/4	Narrow	Yes	Orange
LE54111UBB	Tin		3/8	Standard	Yes	Orange
LE54112UBB	Tin	4/0	3/8	Standard	Yes	Purple
LE58163UBB	Tin	4/0 flex	3/8	Standard	Yes	Yellow



Copper stacking lugs — Two-hole, standard barrel, straight, bottom

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Hole spacing (in.)	Tongue	Peep hole	Ink marking
LE54211B	Tin	3/0	3/8	1	Standard	Yes	Orange
LE54212B	Tin	4/0	3/8	1	Standard	Yes	Purple
LE54214B	Tin	250	3/8	1	Standard	Yes	Yellow




Lug Express

Copper lugs


Copper stacking lugs — One-hole, long barrel, straight, top

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54965BE06T	Tin	3/0	$\frac{3}{8}$	Standard	No	Orange
LE54965BE10	Tin		$\frac{5}{8}$	Standard	No	




Copper stacking lugs — One-hole, long barrel, straight, bottom

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54965BE06B	Tin	3/0	$\frac{3}{8}$	Standard	No	Orange
LE54913BE06B	Tin	250	$\frac{3}{8}$	Standard	No	Yellow
LE54921BEB	Tin	600	$\frac{1}{2}$	Standard	No	Green



Copper stacking lugs — One-hole, long barrel, 45° bend, bottom

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54913BEUF06B	Tin	250	$\frac{3}{8}$	Standard	No	Yellow




Lug Express

Copper lugs and splices


Copper stacking lugs — One-hole, long barrel, 90° bend, bottom

Catalog no.	Plating	Wire size (AWG or kcmil)	Bolt size (in.)	Tongue	Peep hole	Ink marking
LE54970BEUBB	Tin	4/0	$\frac{1}{2}$	Standard	No	Purple
LE54913BEUB06B	Tin	250	$\frac{3}{8}$	Standard	No	Yellow



Copper splices — Standard barrel

Catalog no.	Plating	Wire size (AWG or kcmil)	Ink marking
LE54009TB	Tin	1/0	Pink
LE54510PF	Plain	2/0	Black
LE54011	Tin	3/0	Orange



Copper parallel splices

Catalog no.	Plating	Wire size (AWG or kcmil)	Ink marking
LE540010	Tin	83–119	–
LE540010PFM10	Plain		1/0
LE540020PFM20	Plain	119–150	2/0
LE540030PFM30	Plain	150–190	3/0
LE540040PFM40	Plain	190–231	4/0
LE540250PFM250	Plain	231–300	250
LE540300PFM350	Plain	300–380	350
LE540500	Tin	478–600	–
LE540500PFM500	Plain		500






ABB Installation Products Inc.

Electrification Business
860 Ridge Lake Blvd.
Memphis, TN 38120

electrification.us.abb.com

ABB has made every attempt to ensure the accuracy and reliability of the contents of this document. However, all content is provided for general informational purposes only, and ABB makes no guaranty or warranty, express or implied, as to the accuracy of any technical content, or that the information contained in this publication will be error free and all such guarantees or warranties are expressly disclaimed. ABB may change or modify

the contents at any time, without prior notice. We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction or utilization of its contents — in whole or in parts — is forbidden without prior written consent of ABB.
© 2022 ABB Installation Products Inc.
and/or its affiliated companies.
All rights reserved.