



Catalog

Durable efficiency Vandal-resistant bulkheads by ABB

Lighting

Presentation	2
Product overview	6
Lighting offer	
Sextan Vandal-resistant	9
Sextan Premium Vandal-resistant	10
Sextan Premium Wall-mounted	11
Atoll C320	13
Squad	15
Alium	17
H350	19
Option	21
Dune	23
Lips - Rim	25
Lips - Band	26
Lips - Slotted Visor	27
Havana	29
Axiome	31
Eo	33
Index	34

Symbol overview




ABB lighting Presentation

ABB lighting

For the past 80 years ABB lighting products have been designed and manufactured in Lyon, France in strict conformity with French and European quality standards (CE, NF).

The key factor to this success was the company's ability to listen carefully to the requirements of wholesalers, installers, and architects, and design products in line with the needs of the commercial and residential sector.

Key points and philosophy

ABB lighting has its focus on lighting solutions for commercial and residential buildings. This strategy enables it to come up constantly with innovative products dedicated to the needs of stakeholders in this specific market segment.

The added values derive from three factors, which are the main focus of every product development.

Design

The design gives to the product the esthetical aspect absolutely necessary to melt the product into the environment. The light source should be invisible.

Performance

To ensure brilliant features, the cutting edge LED chips are selected and electronic drivers are designed for our products.

Quality

All the materials and devices used in the product manufacturing are top quality to ensure premium solutions. Each product includes an optical system to have the best quality of light, and to reduce glare.



Lighting

General skills

Basic concept

CRI: Color Rendering Index

CRI describes the ability of a light source to reproduce the colors of objects in comparison with an ideal or natural light source. CRI is always between 0 and 100. Natural light has the best CRI possible i.e 100.

Color of temperature

Color temperature refers to a characterization of the spectral properties of a light source. Low color temperature is the warmest, the most orange light while high color temperature is the coldest, the bluest light. The standard unit of measurement for color temperature is Kelvin (K).

Luminous flux

In lighting, the luminous flux is the quantity of light emitted in all directions around the source. This is the measure of the perceived power of light. Units: Lumen (lm).

Lux

The Lux (symbol: lx) is the standard unit of luminance and luminous emittance, measuring luminous flux per unit area. This is the quantity of light on a surface.

Efficiency

This is the performance of a light source, the quantity of electricity (W) needed to produce a lumen. Unit: lm/W.

The technologies

There are different ways to obtain light. Throughout history the light sources have changed, and different technologies have evolved.

Incandescent

In spite of a perfect quality of light, this light source is outdated because of a very low efficiency. This solution has been banned by European regulations.

Halogen

Working on the same technological principle than the incandescent lamp, this solution has a better efficiency due to the halogen gas contained in the bulb. However, this isn't enough for it to be regarded as an environmentally friendly solution.

Fluorescent

Compact fluorescent lamps allow up to 80 % energy saving in comparison to the incandescent technology. Available in different color temperature and with ballast integrated or not, CFL is a good alternative for green lighting solution.

LED

The future of lighting. The performances of this technology makes it possible to reduce the carbon foot print of the building and achieve substantial cost saving.



LED

Cutting edge technology

LED vision

In order to drive innovation ABB has established two of its own laboratories in Lyon, where products are developed and tested against high French and European standards. The facilities are located in close proximity to the manufacturing plant, in order to ensure the quickest reaction time for our customers.

Our LED products are using the last generation of LEDs to offer the best performance for your application. The LEDs are fixed into an aluminum diffuser to optimize heat dissipation and improve life time. Thanks to a special polycarbonate dedicated to LED, the transmission and the uniformity across the diffuser is state-of-the-art. These features make it a premium solution for LED lighting.

Because LED is very sensitive to high temperatures, a special driver with a self-protected system is designed: in case of an increase of the operating temperature, a thermal protection adapt the nominal current to protect the LED and extend the life time.

LED advantage

Eco friendly

Using cutting edge LED technology, to reduce the carbon footprint and the total cost of ownership of the building.

Heat management

Aluminum-based heat sink for optimized heat dissipation.

Maintenance savings

Very long life time up to 50 000 hours (70 % lumen maintenance at to 25 °C).

Instant light

100 % of the light output is available instantly even in low temperature conditions.

Clever electronic devices

Integrated driver designed internally to perfectly protect and run the LED chip.



LED

The future of lighting

Why using LED?

LED, a cutting edge technology

Today, LED (Light-Emitting Diode) is established as a global lighting source and gives a concrete answer to reduce the CO₂ emission and carbon footprint of a building, and to decrease total cost of ownership. Historically used for ambiance and decorative lighting, LED chips reach today incredible technical features. The quality of light (Color rendering Index, CRI), efficiency and cost enable a generalization of the applications from ambiance to general lighting.

LED, no maintenance

In the ABB strategy, quality is always in the focus. Using the last generation of LED chips, we ensure the highest quality, which means a long life time, luminous flux stability, color temperature homogeneity, CRI, and heat radiation. Drivers, which are necessary to supply constant current to the LED, are designed internally in order to drive the LED chip at its optimal current. This way the LEDs do not only save you money through reduced energy consumption, but also through reduced maintenance expenses.

The perfect technology for presence detector and timer

Compact fluorescent lamps (CFL) showed, in some applications their limits. In fact, used on a timer or on a presence detector, the LED appears to be the most adapted solution. Indeed, unlike to the LED and because of the high sensibility to switch cycles, the life time of CFL will decrease dramatically. The electronic systems implemented by ABB are conceived to protect the LED technology. In fact electronic devices are added to the driver in order to protect the LED against overheating and create an innovative solution to be used in the most extreme conditions.



Product overview



Range		Sextan	Sextan Premium	Sextan Premium Wall-mounted	Atoll C320	Squad
Dimensions		ø350 x 102 mm	ø350 x 102 mm	372 x 168 x 102 mm 372 x 112 x 166 mm	320 x 320 x 103 mm	ø350 x 110 mm
IK rating		IK10	IK10	IK02	IK10	IK10
IP rating		IP55	IP55	IP44	IP54	IP65
Vandal-resistant		✓	✓	—	✓	✓
Glow wire test		850°C	850°C	850°C	850°C	850°C
Sources	Separate electronic ballast	✓	✓	✓	✓	✓
	LED	✓	✓	—	✓	✓
	E27	✓	✓	✓	✓	✓
Installation	Indoor	✓	✓	✓	✓	✓
	Outdoor	✓	✓	✓	✓	✓
	Wall-mounted	✓	✓	✓	✓	✓
	Ceiling-mounted	✓	✓	—	✓	✓
Material	Ring	Polycarbonate	Aluminium	—	Polycarbonate	Polycarbonate
	Body	—	—	Aluminium	—	—
		✓	✓	—	✓	—
Page		9	10	11	13	15



	Alium	H350	Option	Dune	Lips	Havana	Axiome	Eo
	ø300 x 116 mm	ø350 x 105 mm	ø300 x 116 mm	ø245 x 97 mm	378 x 157 x 95 mm	165 x 285 x 97 mm	ø260 x 98 mm ø320 x 100 mm	445 x 64 x 90 mm
	IK10	IK10	IK10	IK10	IK07	IK02	IK10	IK07
	IP44	IP65	IP44	IP44	IP54	IP54	IP54	IP24
	✓	✓	✓	✓	✓	—	✓	—
	650°C	650°C	650°C	650°C	650°C	650°C	650°C	650°C
	✓	✓	✓	✓	✓	✓	✓	—
	—	—	✓	—	—	—	✓	—
	✓	✓	✓	✓	✓	✓	✓	—
	✓	✓	✓	✓	✓	✓	✓	✓
	✓	✓	✓	✓	✓	✓	✓	—
	✓	✓	✓	✓	✓	✓	✓	✓
	✓	✓	✓	✓	—	—	✓	—
	Aluminium	—	Polypropylène	Polycarbonate	—	Polycarbonate	Polycarbonate	—
	—	—	—	—	Polycarbonate	—	—	—
	—	—	—	—	—	—	—	—
	17	19	21	23	25	29	31	33

Sextan

Saving energy never shined so bright

A great combination of aesthetics, robustness and efficiency – always fitting your application. The Sextan range provides a comprehensive solution for single rooms or whole building concepts – indoors and outdoors. Due to its very low power consumption and the long-lasting LED lights (up to 50 000 hours) or CFL lamps (up to 15 000 hours), the Sextan helps to reduce the carbon footprint and the maintenance costs of a building. On other hand, the Sextan solution offers a unique design in various colors and even a vandal-resistant model for use in public buildings.



Sextan Vandal-resistant




Sextan Premium Wall-mounted



Features:

- High level solution for upper commercial and residential segment
- Classic version: polycarbonate body and diffuser
- Premium version: aluminum body and polycarbonate diffuser
- IP44 or IP55 for an indoor and outdoor use
- Vandal resistant thanks to IK10 rating and theft proof screw (except wall-mounted version)
- Easy installation with built-in driver and rapid connector
- Available in different colors and finishes
- DALI version available for 2 x 26 W.

Sextan Vandal-resistant Polycarbonate



Sextan - White



Sextan - Grey


Ordering details

Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
Sextan						
E27 Lamp not included	1x 100W or 1x 70W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Grey	2CFL871700R0001 2CFL871730R0001	1 1
CFL - TC-DEL	1x 18W	G24q-2	640	<input type="checkbox"/> White <input checked="" type="checkbox"/> Grey	2CFL871704R0001 2CFL871734R0001	1 1
	2x 18W	G24q-2	1250	<input type="checkbox"/> White <input checked="" type="checkbox"/> Grey	2CFL871705R0001 2CFL871735R0001	1 1
	1x 26W	G24q-3	950	<input type="checkbox"/> White <input checked="" type="checkbox"/> Grey	2CFL871706R0001 2CFL871736R0001	1 1
	2x 26W	G24q-3	1870	<input type="checkbox"/> White <input checked="" type="checkbox"/> Grey	2CFL871707R0001 2CFL871737R0001	1 1
	CFL - TC-TEL	1x 32W	GX24q-3	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Grey	2CFL871708R0001 2CFL871738R0001
LED	15W	-	1080	<input type="checkbox"/> White <input checked="" type="checkbox"/> Grey	Available 2015/04 Available 2015/04	1 1
	24W	-	1800	<input type="checkbox"/> White <input checked="" type="checkbox"/> Grey	Available 2015/04 Available 2015/04	1 1
Sextan 						
CFL - TC-DEL	2x 26W	G24q-3	1870	<input type="checkbox"/> White <input checked="" type="checkbox"/> Grey	2CFL871709R0001 2CFL871739R0001	1 1

Technical data

Photometric specifications	
CRI (Color Rendering Index)	> 80
Color temperature	4000 K
LED lifetime	50000h
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	Polycarbonate
IK rating	IK10
IP rating	IP55
Glow wire test	850°C
Electrical specifications	
Power supply	230 V / 50-60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.

Sextan Premium Vandal-resistant Aluminium




Ordering details

Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
Sextan						
E27 Lamp not included	1x 100W or 1x 70W HAL	E27	-	<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	2CFL871790R0001 2CFL871950R0001 2CFL871760R0001 2CFL871960R0001	1
CFL - TC-DEL	1x 18W	G24q-2	640	<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	2CFL871794R0001 2CFL871954R0001 2CFL871764R0001 2CFL871964R0001	1
				<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	2CFL871795R0001 2CFL871955R0001 2CFL871765R0001 2CFL871965R0001	1
				<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	2CFL871796R0001 2CFL871956R0001 2CFL871766R0001 2CFL871966R0001	1
	2x 18W	G24q-2	1250	<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	2CFL871797R0001 2CFL871957R0001 2CFL871767R0001 2CFL871967R0001	1
				<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	2CFL871798R0001 2CFL871958R0001 2CFL871768R0001 2CFL871968R0001	1
				<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	2CFL871799R0001 2CFL871959R0001 2CFL871769R0001 2CFL871969R0001	1
CFL - TC-TEL	1x 32W	GX24q-3	-	<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	2CFL871798R0001 2CFL871958R0001 2CFL871768R0001 2CFL871968R0001	1
				<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	2CFL871798R0001 2CFL871958R0001 2CFL871768R0001 2CFL871968R0001	1
LED	15W	-	-	<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	Available 2015/04 Available 2015/04 Available 2015/04 Available 2015/04	1
				<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	Available 2015/04 Available 2015/04 Available 2015/04 Available 2015/04	1
LED	24W	-	-	<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	Available 2015/04 Available 2015/04 Available 2015/04 Available 2015/04	1
				<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	Available 2015/04 Available 2015/04 Available 2015/04 Available 2015/04	1
Sextan 						
CFL - TC-DEL	2x 26W	G24q-3	1870	<input checked="" type="checkbox"/> Anthracite <input type="checkbox"/> Alu-Silver <input type="checkbox"/> White <input checked="" type="checkbox"/> Stainless steel	2CFL871799R0001 2CFL871959R0001 2CFL871769R0001 2CFL871969R0001	1

Technical data


Photometric specifications	
CRI (Color Rendering Index)	> 80
Color temperature	4000 K
LED lifetime	50000h
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	Aluminium
IK rating	IK10
IP rating	IP55
Glow wire test	850°C
Electrical specifications	
Power supply	230 V / 50-60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.


Sextan Premium Wall-mounted



H/B version - Stainless steel



D/H version - Stainless steel



Ordering details

Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
Sextan Premium Wall-mounted - H/B						
CFL - TC-SEL	1x 9W	2G7	-	<input type="checkbox"/> White <input type="checkbox"/> Anthracite <input type="checkbox"/> Stainless steel	2CFL871501R0001 2CFL871531R0001 2CFL871521R0001	1
CFL - TC-DEL	1x 13W	G24q-1	-	<input type="checkbox"/> White <input type="checkbox"/> Anthracite <input type="checkbox"/> Stainless steel	2CFL871502R0001 2CFL871532R0001 2CFL871522R0001	1
	1x 18W	G24q-2	-	<input type="checkbox"/> White <input type="checkbox"/> Anthracite <input type="checkbox"/> Stainless steel	2CFL871503R0001 2CFL871533R0001 2CFL871523R0001	1
	1x 26W	G24q-3	900	<input type="checkbox"/> White <input type="checkbox"/> Anthracite <input type="checkbox"/> Stainless steel	2CFL871504R0001 2CFL871534R0001 2CFL871524R0001	1



Sextan Premium Wall-mounted - D/H

CFL - TC-SEL	1x 9W	2G7	-	<input type="checkbox"/> White <input type="checkbox"/> Anthracite <input type="checkbox"/> Stainless steel	2CFL871601R0001 2CFL871631R0001 2CFL871621R0001	1
CFL - TC-DEL	1x 13W	G24q-1	-	<input type="checkbox"/> White <input type="checkbox"/> Anthracite <input type="checkbox"/> Stainless steel	2CFL871602R0001 2CFL871632R0001 2CFL871622R0001	1
	1x 18W	G24q-2	-	<input type="checkbox"/> White <input type="checkbox"/> Anthracite <input type="checkbox"/> Stainless steel	2CFL871603R0001 2CFL871633R0001 2CFL871623R0001	1
	1x 26W	G24q-3	750	<input type="checkbox"/> White <input type="checkbox"/> Anthracite <input type="checkbox"/> Stainless steel	2CFL871604R0001 2CFL871634R0001 2CFL871624R0001	1

Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	-
Mechanical specifications	
Body material	Aluminium
Diffuser material	Opal glass
IK rating	IK02
IP rating	IP44
Glow wire test	850°C
Electrical specifications	
Power supply	230 V / 50 – 60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.

Sextan Premium Wall-mounted - H/B

Sextan Premium Wall-mounted - D/H

Atoll C320 Square design

Atoll C320 is an esthetical solution for corridor lighting. Thanks to the square design and the back lighting effect, Atoll C320 is definitely an innovative solution without any compromise between design, visual comfort and efficiency.



Atoll C320



Features:

- Wall or ceiling mounted
- IP54 for an indoor and outdoor use
- Vandal resistant thanks to IK10 rating, and theft proof screw
- Polycarbonate body and diffuser
- Available in 4 different colors
- Square shape with back lighting effect
- DALI version available for 2 x 26 W.

Atoll C320



Ordering details


Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
Atoll C320						
E27 Lamp not included	2x 60W or 2x 42W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input type="checkbox"/> Anthracite	2CFL870000R0001 2CFL870010R0001 2CFL870020R0001 2CFL870030R0001	1
CFL - TC-SEL	2x 9W	2G7	580	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input type="checkbox"/> Anthracite	2CFL870004R0001 2CFL870014R0001 2CFL870024R0001 2CFL870034R0001	1
CFL - TC-DEL	2x 13W	G24q-1	860	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input type="checkbox"/> Anthracite	2CFL870009R0001 2CFL870095R0001 2CFL870096R0001 2CFL870097R0001	1
	2x 18W	G24q-2	1150	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input type="checkbox"/> Anthracite	2CFL870005R0001 2CFL870015R0001 2CFL870025R0001 2CFL870035R0001	1
	2x 26W	G24q-3	1730	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input type="checkbox"/> Anthracite	2CFL870006R0001 2CFL870016R0001 2CFL870026R0001 2CFL870036R0001	1
LED	15W	-	920	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input type="checkbox"/> Anthracite	2CFL870280R0001 2CFL870281R0001 2CFL870291R0001 2CFL870296R0001	1
	24W	-	1580	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input type="checkbox"/> Anthracite	2CFL870246R0001 2CFL870256R0001 2CFL870266R0001 2CFL870276R0001	1
Atoll C320 						
CFL - TC-DEL	2x 26W	G24q-3	1730	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input type="checkbox"/> Anthracite	2CFL870062R0001 2CFL870067R0001 2CFL870072R0001 2CFL870077R0001	1



Atoll C320 - White




Atoll C320 - Black



Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	50000h
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Opal Polycarbonate
Ring material	Polycarbonate
IK rating	IK10
IP rating	IP54
Glow wire test	850°C
Electrical specifications	
Power supply	230 V / 50-60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.

Squad

Vandal resistant solution for industrial area

Squad combines a timeless design with excellent technical properties. Thanks to its IP65, and IK10 rating, plus theft protected screws, this is a vandal resistant solution for indoor and outdoor use.



Squad



Features:

- Round and conventional design for an industrial use
- Wall mounted or ceiling installation
- Polycarbonate body and diffuser
- Available in black and white
- IP65 for an indoor and outdoor use
- Vandal resistant thanks to IK10 rating, and theft proof screw
- DALI version available for 2 x 26 W.

Squad



Squad - White


Ordering details

Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty	
Squad							
E27 Lamp not included	1x 100W or 1x 70W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879403R0001 2CFL879404R0001	1 1	
CFL - TC-DEL	1x 18W	G24q-2	660	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879462R0001 2CFL879463R0001	1 1	
	2x 18W	G24q-2	1420	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879440R0001 2CFL879441R0001	1 1	
	1x 26W	G24q-3	990	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879464R0001 2CFL879465R0001	1 1	
	2x 26W	G24q-3	1910	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879444R0001 2CFL879445R0001	1 1	
	LED	15W	-	1250	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL876436R0001 2CFL876437R0001	1 1
		24W	-	2030	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL876445R0001 2CFL876450R0001	1 1
Squad 							
CFL - TC-DEL	2x 26W	G24q-3	1910	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879454R0001 2CFL879455R0001	1 1	

Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	50000h
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	Polycarbonate
IK rating	IK10
IP rating	IP65
Glow wire test	850°C
Electrical specifications	
Power supply	230 V / 50-60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.

Alium

Architectural solution, aluminium body

Alium is a range of contemporary bulkheads with an elegant combination of aluminium body and polycarbonate diffuser. The mix between two different materials makes Alium a perfect solution for residential and commercial building.



Alium



Features:

- Architectural solution thanks to the elegant mix between aluminum and polycarbonate
- Aluminum body and polycarbonate diffuser
- Twist and look diffuser for an easy maintenance
- IP44 for indoor and outdoor use
- Vandal resistant
- Available in 2 designs.



Alium - Anthracite



Alium Grid - Anthracite


Ordering details

Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
Alium						
E27 Lamp not included	1x 100W or 1x 70W HAL	E27	-	■ Anthracite	2CFL878870R0001	1
CFL - TC-SEL	2x 9W	2G7	720	■ Anthracite	2CFL878316R0001	1
CFL - TC-DEL	2x 13W	G24q-1	990	■ Anthracite	2CFL878320R0001	1
	1x 18W	G24q-2	660	■ Anthracite	2CFL878322R0001	1
	1x 26W	G24q-3	790	■ Anthracite	2CFL878324R0001	1
CFL - TC-TEL	1x 32W	GX24q-3	-	■ Anthracite	2CFL878310R0001	1
LED	15W	-	1100	■ Anthracite	2CFL878259R0001	1
	24W	-	1800	■ Anthracite	2CFL878260R0001	1
Alium Grid						
E27 Lamp not included	1x 100W or 1x 70W HAL	E27	-	■ Anthracite	2CFL878840R0001	1
CFL - TC-SEL	2x 9W	2G7	590	■ Anthracite	2CFL878315R0001	1
CFL - TC-DEL	2x 13W	G24q-1	-	■ Anthracite	2CFL878319R0001	1
	1x 18W	G24q-2	410	■ Anthracite	2CFL878321R0001	1
	1x 26W	G24q-3	610	■ Anthracite	2CFL878323R0001	1
CFL - TC-TEL	1x 32W	GX24q-3	-	■ Anthracite	2CFL878309R0001	1
LED	15W	-	1100	■ Anthracite	2CFL878259R0001	1
	24W	-	1800	■ Anthracite	2CFL878260R0001	1

Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	50000h
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	Aluminium
IK rating	IK10
IP rating	IP44
Glow wire test	650°C
Electrical specifications	
Power supply	230 V / 50-60 Hz
Electrical class	Class II

Main dimensions mm




All our products are delivered with the light source, unless the opposite is indicated.

H350

Timeless design

Its design makes it fit into every environment, and so do its technical features – an IP65, and IK10 rating make sure, that once installed the H350 illuminates its surroundings over a long period of time.



H350



Features:

- IP65 for an indoor and outdoor use
- Vandal resistant thanks to IK10 rating, and theft proof screw
- Unique design
- Polycarbonate body and diffuser.

H350



H350 - White


Ordering details

Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
E27 Lamp not included 	1x 100W or 70W HAL	E27	-	<input type="checkbox"/> White	2CFL874001R0001	1
	2x 70W or 53W HAL	E27	-	<input type="checkbox"/> White	2CFL874000R0001	1
CFL - TC-DEL 	1x 18W	G24q-2	760	<input type="checkbox"/> White	2CFL874002R0001	1
	2x 18W	G24q-2	1440	<input type="checkbox"/> White	2CFL874003R0001	1
	1x 26W	G24q-3	1100	<input type="checkbox"/> White	2CFL874004R0001	1
	2x 26W	G24q-3	2230	<input type="checkbox"/> White	2CFL874005R0001	1
CFL - TC-TEL 	1x 32W	GX24q-3	1270	<input type="checkbox"/> White	2CFL874006R0001	1
LED 	15W	-	1050	<input type="checkbox"/> White	2CFL874018R0001	1
	24W	-	1725	<input type="checkbox"/> White	2CFL874020R0001	1

Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	50000h
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	-
IK rating	IK10
IP rating	IP65
Glow wire test	650°C
Electrical specifications	
Power supply	230 V / 50 – 60 Hz
Electrical class	Class II

Main dimensions mm




All our products are delivered with the light source, unless the opposite is indicated.

Option

Good value for money

Option is a basic solution for corridors and stairwells of residential and commercial building. Good value for money solution for the medium residential and commercial segment.



Option



Features:

- Good value for money solution for medium residential and commercial segment
- Vandal resistant thanks to IK10 rating and theft proof screws
- IP44 for indoor and outdoor use
- Polycarbonate body and diffuser
- Available in black and white.

Option



Option - Black


Ordering details

Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
E27 Lamp not included	1x 100W or 1x 70W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL878847R0001 2CFL878848R0001	1 1
CFL - TC-SEL	1x 9W	2G7	510	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL878341R0001 2CFL878342R0001	1 1
	2x 9W	2G7	880	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL878335R0001 2CFL878336R0001	1 1
CFL - TC-DEL	1x 13W	G24q-1	770	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL878365R0001 2CFL878366R0001	1 1
	2x 13W	G24q-1	1310	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL878347R0001 2CFL878348R0001	1 1
	1x 18W	G24q-2	1020	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL878353R0001 2CFL878354R0001	1 1
	1x 26W	G24q-3	1200	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL878359R0001 2CFL878360R0001	1 1
CFL - TC-TEL	1x 32W	GX24q-3	1530	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL878863R0001 2CFL878864R0001	1 1
LED	15W	-	1100	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	Available 2015/04 Available 2015/04	1 1
	24W	-	1800	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	Available 2015/04 Available 2015/04	1 1

Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	50000h
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	Polycarbonate
IK rating	IK10
IP rating	IP44
Glow wire test	650°C
Electrical specifications	
Power supply	230 V / 50-60 Hz
Electrical class	Class II

Main dimensions mm




All our products are delivered with the light source, unless the opposite is indicated.

Dune

Multifaceted solution

Due to its concept, consisting of a base unit and a single ring, it is very easy to install. The minimum diameter (245 mm) and the visor option give the Dune range a very qualitative aspect and make it an aesthetic solution for indoor and outdoor application.



Dune



Dune Visor



Dune Casquette



Features:

- Architectural solution, small diameter (245 mm) for an easy installation
- Polycarbonate body and diffuser
- IP54 indoor and outdoor use
- Vandal resistant
- The different designs are available in black and white.

Dune



Ordering details

Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
Dune						
E27 Lamp not included	1x 75W or 1x 46W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879012R0001 2CFL879017R0001	1 1
CFL - TC-SEL	1x 9W	2G7	400	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879043R0001 2CFL879044R0001	1 1
	2x 9W	2G7	700	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879045R0001 2CFL878046R0001	1 1
CFL - TC-DEL	1x 13W	G24q-1	410	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879047R0001 2CFL879048R0001	1 1
	LED	19W	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL876106R0001 2CFL876107R0001	1 1



Dune - White



Dune Visor - White



Dune Casquette - White


Dune Visor						
E27 Lamp not included	1x 75W or 1x 46W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879063R0001 2CFL879064R0001	1 1
CFL - TC-SEL	1x 9W	2G7	230	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879253R0001 2CFL879254R0001	1 1
	2x 9W	2G7	370	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879255R0001 2CFL879256R0001	1 1
CFL - TC-DEL	1x 13W	G24q-1	280	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879257R0001 2CFL879258R0001	1 1
	LED	19W	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL876146R0001 2CFL876147R0001	1 1

Dune Casquette						
E27 Lamp not included	1x 75W or 1x 46W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879259R0001 2CFL879260R0001	1 1
CFL - TC-SEL	1x 9W	2G7	310	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879267R0001 2CFL879268R0001	1 1
	2x 9W	2G7	500	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879269R0001 2CFL879270R0001	1 1
CFL - TC-DEL	1x 13W	G24q-1	380	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879271R0001 2CFL879272R0001	1 1
	LED	19W	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL876166R0001 2CFL876167R0001	1 1

Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	50000h
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	Polycarbonate
IK rating	IK10
IP rating	IP44
Glow wire test	650°C
Electrical specifications	
Power supply	230 V / 50-60 Hz
Electrical class	Class II

Main dimensions mm




All our products are delivered with the light source, unless the opposite is indicated.

Lips

Wall mounted fixture

Lips is a range of wall mounted fixtures. Thanks to a declination of three different designs, Lips has a lot of various applications. With a polycarbonate body, and diffuser.



Lips Rim



Lips Slotted Visor



Lips Band



Features:

- Wall mounted fixtures
- Polycarbonate body and polycarbonate opal diffuser
- Available in 4 colors and 3 different designs: Rim, Slotted Visor and Band.

Lips Rim



Lips Rim - White

Ordering details


Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
E27 Lamp not included 	1x 55W or 1x 42W HAL	E27	-	<input type="checkbox"/> White	2CFL878600R0001	1
				<input checked="" type="checkbox"/> Black	2CFL878603R0001	1
				<input checked="" type="checkbox"/> Titanium	2CFL878606R0001	1
CFL - TC-SEL 	1x 9W	2G7	290	<input checked="" type="checkbox"/> Anthracite	2CFL878609R0001	1
				<input type="checkbox"/> White	2CFL879542R0001	1
				<input checked="" type="checkbox"/> Black	2CFL879544R0001	1
CFL - TC-DEL 	1x 13W	24Gq-3	430	<input checked="" type="checkbox"/> Titanium	2CFL879548R0001	1
				<input checked="" type="checkbox"/> Anthracite	2CFL879554R0001	1
				<input type="checkbox"/> White	2CFL879543R0001	1
	1x 18W	24Gq-2	580	<input checked="" type="checkbox"/> Black	2CFL879547R0001	1
				<input checked="" type="checkbox"/> Titanium	2CFL879549R0001	1
				<input checked="" type="checkbox"/> Anthracite	2CFL879557R0001	1
	1x 26W	24Gq-3	860	<input type="checkbox"/> White	2CFL879603R0001	1
				<input checked="" type="checkbox"/> Black	2CFL879608R0001	1
				<input checked="" type="checkbox"/> Titanium	2CFL879613R0001	1
				<input checked="" type="checkbox"/> Anthracite	2CFL879618R0001	1
				<input type="checkbox"/> White	2CFL879604R0001	1
				<input checked="" type="checkbox"/> Black	2CFL879609R0001	1
				<input checked="" type="checkbox"/> Titanium	2CFL879614R0001	1
				<input checked="" type="checkbox"/> Anthracite	2CFL879619R0001	1



Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	-
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	
IK rating	IK07
IP rating	IP54
Glow wire test	650°C
Electrical specifications	
Power supply	230 V / 50 – 60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.

Lips Band



Lips Band - White

Ordering details


Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
E27 Lamp not included	1x 55W or 1x 42W HAL	E27	-	<input type="checkbox"/> White	2CFL878602R0001	1
				<input checked="" type="checkbox"/> Black	2CFL878605R0001	1
				<input checked="" type="checkbox"/> Titanium	2CFL878608R0001	1
				<input checked="" type="checkbox"/> Anthracite	2CFL878611R0001	1
CFL - TC-SEL	1x 9W	2G7	220	<input type="checkbox"/> White	2CFL879578R0001	1
				<input checked="" type="checkbox"/> Black	2CFL879580R0001	1
				<input checked="" type="checkbox"/> Titanium	2CFL879582R0001	1
				<input checked="" type="checkbox"/> Anthracite	2CFL879584R0001	1
CFL - TC-DEL	1x 13W	24Gq-3	330	<input type="checkbox"/> White	2CFL879579R0001	1
				<input checked="" type="checkbox"/> Black	2CFL879581R0001	1
				<input checked="" type="checkbox"/> Titanium	2CFL879583R0001	1
				<input checked="" type="checkbox"/> Anthracite	2CFL879585R0001	1
	1x 18W	24Gq-2	440	<input type="checkbox"/> White	2CFL879663R0001	1
				<input checked="" type="checkbox"/> Black	2CFL879668R0001	1
				<input checked="" type="checkbox"/> Titanium	2CFL879673R0001	1
				<input checked="" type="checkbox"/> Anthracite	2CFL879678R0001	1
	1x 26W	24Gq-3	670	<input type="checkbox"/> White	2CFL879664R0001	1
				<input checked="" type="checkbox"/> Black	2CFL879669R0001	1
				<input checked="" type="checkbox"/> Titanium	2CFL879674R0001	1
				<input checked="" type="checkbox"/> Anthracite	2CFL879579R0001	1



Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	-
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	
IK rating	IK07
IP rating	IP54
Glow wire test	650°C
Electrical specifications	
Power supply	230 V / 50 – 60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.

Lips Slotted Visor



Lips Slotted Visor - White

Ordering details


Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
E27 Lamp not included	1x 55W or 1x 42W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input checked="" type="checkbox"/> Anthracite	2CFL878601R0001 2CFL878604R0001 2CFL878607R0001 2CFL878610R0001	1
CFL - TC-SEL	1x 9W	2G7	210	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input checked="" type="checkbox"/> Anthracite	2CFL879564R0001 2CFL879566R0001 2CFL879570R0001 2CFL879572R0001	1
CFL - TC-DEL	1x 13W	24Gq-3	320	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input checked="" type="checkbox"/> Anthracite	2CFL879565R0001 2CFL879569R0001 2CFL879571R0001 2CFL879573R0001	1
	1x 18W	24Gq-2	420	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input checked="" type="checkbox"/> Anthracite	2CFL879633R0001 2CFL879638R0001 2CFL879643R0001 2CFL879648R0001	1
	1x 26W	24Gq-3	630	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black <input type="checkbox"/> Titanium <input checked="" type="checkbox"/> Anthracite	2CFL879634R0001 2CFL879639R0001 2CFL879644R0001 2CFL879649R0001	1



Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	-
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	
IK rating	IK07
IP rating	IP54
Glow wire test	650°C
Electrical specifications	
Power supply	230 V / 50 – 60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.

Havana

Oval architectural solution

Havana's distinctive oval shape makes it an eye-catcher especially in the outdoor area, i. e. entrance, facade, or balcony. The combination between the aluminum body and the glass diffuser together with the oval shape makes Havana a very qualitative architectural solution.



Havana



Features:

- Oval shape
- Architectural solution: Aluminum body and glass diffuser
- IP54 and IK02
- Black or white finish.

Havana



Havana - White



Havana - Black


Ordering details

Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
E27 Lamp not included	1x 75W or 1x 52W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879205R0001 2CFL879207R0001	1 1
CFL - TC-SEL	1x 9W	2G7	310	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879237R0001 2CFL879238R0001	1 1
	2x 9W	2G7	610	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879239R0001 2CFL879240R0001	1 1
CFL - TC-DEL	1x 13W	G24q-1	470	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879221R0001 2CFL879222R0001	1 1
	1x 18W	G24q-2	620	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879223R0001 2CFL879224R0001	1 1
LED	20W	-	800	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL879247R0001 2CFL879248R0001	1 1

Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	50000h
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Glass (Polycarbonate for LED version)
Ring material	Aluminium
IK rating	IK02
IP rating	IP54
Glow wire test	650°C
Electrical specifications	
Power supply	230 V / 50 – 60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.

Axiome

The eco-design solution

Axiome is a range of functional and versatile fixtures fulfilling all the requirements of installers when it comes to easy installation and electrical connection. This is a solution coming from an innovative eco-design with specific focus on reducing installation time. Available in two sizes with different lights sources.



Axiome



Features:

- Basic solution
- Polycarbonate diffuser
- IP54
- IK10 and torx screws
- Easy to install – Only two parts (body and diffuser) – Rapid connector
- Available in two diameter Ø 260 mm (T1) and Ø 320 mm (T2).

Axiome



Axiome T1 - White



Axiome T2 - White



Ordering details

Lamps	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
Axiome T1						
E27 Lamp not included	1x 55W or 1x 42W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL873000R0001 Available 2015/10	1 1
CFL - TC-DEL	1x 18W	G24q-2	490	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL873012R0001 Available 2015/10	1 1
	1x 26W	G24q-3	810	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL873010R0001 Available 2015/10	1 1
LED	12W	-	900	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL873022R0001 Available 2015/10	1 1
Axiome T2						
E27 Lamp not included	2x 55W or 2x 42W HAL	E27	-	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL873050R0001 Available 2015/10	1 1
CFL - TC-SEL	2x 18W	G24q-2	1150	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL873064R0001 Available 2015/10	1 1
	2x 26W	G24q-3	1330	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL873060R0001 Available 2015/10	1 1
LED	11W	-	900	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL873085R0001 Available 2015/10	1 1
	15W	-	1200	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL873090R0001 Available 2015/10	1 1
	20W	-	1500	<input type="checkbox"/> White <input checked="" type="checkbox"/> Black	2CFL873095R0001 Available 2015/10	1 1

Technical data

Photometric specifications	
CRI (Color Rendering Index)	>80
Color temperature	4000K
LED lifetime	50000h
Mechanical specifications	
Body material	Polypropylene
Diffuser material	Polycarbonate
Ring material	-
IK rating	IK10
IP rating	IP54
Glow wire test	650°C
Electrical specifications	
Power supply	230 V / 50-60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.

Eo

Perfect light for bathroom and kitchen

Eo is a range of batten to be used for kitchen or bathroom applications. Specially designed to be installed in dust and dirty environment.



SlimEo

Eo



Features:

- For bathroom or kitchen application
- Easy to install
- Electronic ballast
- Polycarbonate body and diffuser
- Switch on the side of the body for a manual use
- Available with shaver socket.

Eo



Ordering details

Version	Power	Caps	Luminous flux (Fixture) lm	Finition color	Order code	Pkg qty
Eo - Without lamp						
Standard	1x 75W	S19	-	<input type="checkbox"/> White <input type="checkbox"/> Brown	2CFL855211R0001 2CFL855231R0001	1 1
With lightswitch	1x 75W	S19	-	<input type="checkbox"/> White <input type="checkbox"/> Brown	2CFL855213R0001 2CFL855233R0001	1 1
With socket 16A	1x 75W	S19	-	<input type="checkbox"/> White <input type="checkbox"/> Brown	2CFL855214R0001 2CFL855234R0001	1 1
With lightswitch and socket 16A	1x 75W	S19	-	<input type="checkbox"/> White <input type="checkbox"/> Brown	2CFL855215R0001 2CFL855235R0001	1 1
With shaver socket	1x 75W	S19	-	<input type="checkbox"/> White <input type="checkbox"/> Brown	2CFL855217R0001 2CFL855237R0001	1 1
with transformer 230V/20A and shaver socket	1x 75W	S19	-	<input type="checkbox"/> White <input type="checkbox"/> Brown	2CFL855218R0001 2CFL855238R0001	1 1
Eo - With lamp						
Standard	1x TC-SEL 11W	2G7	-	<input type="checkbox"/> White	2CFL855281R0001	1
With lightswitch	1x TC-SEL 11W	2G7	-	<input type="checkbox"/> White	2CFL855283R0001	1
With socket 16A	1x TC-SEL 11W	2G7	-	<input type="checkbox"/> White	2CFL855284R0001	1
with transformer 230V/20A and shaver socket	1x TC-SEL 11W	2G7	-	<input type="checkbox"/> White	2CFL855285R0001	1
SlimEo - With lamp						
Standard	1x T16 13W	G5	-	<input type="checkbox"/> White	2CFL855451R0001	1
	1x T26 18W	G13	-	<input type="checkbox"/> White	2CFL855442R0001	1
	1x T26 36W	G13	-	<input type="checkbox"/> White	2CFL855462R0001	1
With lightswitch	1x T16 13W	G5	-	<input type="checkbox"/> White	2CFL855453R0001	1
	1x T26 18W	G13	-	<input type="checkbox"/> White	2CFL855446R0001	1
	1x T26 36W	G13	-	<input type="checkbox"/> White	2CFL855466R0001	1



Eo - White





SlimEo - White

Technical data

Photometric specifications	
CRI (Color Rendering Index)	-
Color temperature	-
LED lifetime	-
Mechanical specifications	
Body material	Polycarbonate
Diffuser material	Polycarbonate
Ring material	-
IK rating	IK07
IP rating	IP24
Glow wire test	650°C
Electrical specifications	
Power supply	230 V / 50-60 Hz
Electrical class	Class II

Main dimensions mm



All our products are delivered with the light source, unless the opposite is indicated.

Index

Type classification

Description	Lamp	Power W	Cap	Luminous flux lm	Finition color	Order code	Page	
Alium	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Anthracite	2CFL878870R0001	17	
	CFL - TC-SEL	2x 9W	2G7	720	Anthracite	2CFL878316R0001	17	
	CFL - TC-DEL	2x 13W	G24q-1	990	Anthracite	2CFL878320R0001	17	
	CFL - TC-DEL	1x 18W	G24q-2	660	Anthracite	2CFL878322R0001	17	
	CFL - TC-DEL	1x 26W	G24q-3	790	Anthracite	2CFL878324R0001	17	
	CFL - TC-TEL	1x 32W	GX24q-3	-	Anthracite	2CFL878310R0001	17	
	LED	15W	-	1100	Anthracite	2CFL878259R0001	17	
	LED	24W	-	1800	Anthracite	2CFL878260R0001	17	
Alium Grid	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Anthracite	2CFL878840R0001	17	
	CFL - TC-SEL	2x 9W	2G7	590	Anthracite	2CFL878315R0001	17	
	CFL - TC-DEL	2x 13W	G24q-1	-	Anthracite	2CFL878319R0001	17	
	CFL - TC-DEL	1x 18W	G24q-2	410	Anthracite	2CFL878321R0001	17	
	CFL - TC-DEL	1x 26W	G24q-3	610	Anthracite	2CFL878323R0001	17	
	CFL - TC-TEL	1x 32W	GX24q-3	-	Anthracite	2CFL878309R0001	17	
	LED	15W	-	1100	Anthracite	2CFL878259R0001	17	
	LED	24W	-	1800	Anthracite	2CFL878260R0001	17	
Atoll C320	E27 (Lamp not included)	2x 60W or 2x 42W HAL	E27	-	White	2CFL870000R0001	13	
	E27 (Lamp not included)	2x 60W or 2x 42W HAL	E27	-	Black	2CFL870010R0001	13	
	E27 (Lamp not included)	2x 60W or 2x 42W HAL	E27	-	Titanium	2CFL870020R0001	13	
	E27 (Lamp not included)	2x 60W or 2x 42W HAL	E27	-	Anthracite	2CFL870030R0001	13	
	CFL - TC-SEL	2x 9W	2G7	580	White	2CFL870004R0001	13	
	CFL - TC-SEL	2x 9W	2G7	580	Black	2CFL870014R0001	13	
	CFL - TC-SEL	2x 9W	2G7	580	Titanium	2CFL870024R0001	13	
	CFL - TC-SEL	2x 9W	2G7	580	Anthracite	2CFL870034R0001	13	
	CFL - TC-DEL	2x 13W	G24q-1	860	White	2CFL870094R0001	13	
	CFL - TC-DEL	2x 13W	G24q-1	860	Black	2CFL870095R0001	13	
	CFL - TC-DEL	2x 13W	G24q-1	860	Titanium	2CFL870096R0001	13	
	CFL - TC-DEL	2x 13W	G24q-1	860	Anthracite	2CFL870097R0001	13	
	CFL - TC-DEL	2x 18W	G24q-2	1150	White	2CFL870005R0001	13	
	CFL - TC-DEL	2x 18W	G24q-2	1150	Black	2CFL870015R0001	13	
	CFL - TC-DEL	2x 18W	G24q-2	1150	Titanium	2CFL870025R0001	13	
	CFL - TC-DEL	2x 18W	G24q-2	1150	Anthracite	2CFL870035R0001	13	
	CFL - TC-DEL	2x 26W	G24q-3	1730	White	2CFL870006R0001	13	
	CFL - TC-DEL	2x 26W	G24q-3	1730	Black	2CFL870016R0001	13	
	CFL - TC-DEL	2x 26W	G24q-3	1730	Titanium	2CFL870026R0001	13	
	CFL - TC-DEL	2x 26W	G24q-3	1730	Anthracite	2CFL870036R0001	13	
	LED	15W	-	920	White	2CFL870280R0001	13	
	LED	15W	-	920	Black	2CFL870281R0001	13	
	LED	15W	-	920	Titanium	2CFL870291R0001	13	
	LED	15W	-	920	Anthracite	2CFL870296R0001	13	
	LED	24W	-	1580	White	2CFL870246R0001	13	
	LED	24W	-	1580	Black	2CFL870256R0001	13	
	LED	24W	-	1580	Titanium	2CFL870266R0001	13	
	LED	24W	-	1580	Anthracite	2CFL870276R0001	13	
	Atoll C320 DALI	CFL - TC-DEL	2x 26W	G24q-3	1730	White	2CFL870062R0001	13
		CFL - TC-DEL	2x 26W	G24q-3	1730	Black	2CFL870067R0001	13
		CFL - TC-DEL	2x 26W	G24q-3	1730	Titanium	2CFL870072R0001	13
		CFL - TC-DEL	2x 26W	G24q-3	1730	Anthracite	2CFL870077R0001	13
E27 (Lamp not included)		1x 55W or 1x 42W HAL	E27	-	White	2CFL873000R0001	31	
Axioeme T1	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Black	Available 2015/10	31	
	CFL - TC-DEL	1x 18W	G24q-2	490	White	2CFL873012R0001	31	
	CFL - TC-DEL	1x 18W	G24q-2	490	Black	Available 2015/10	31	
	CFL - TC-DEL	1x 26W	G24q-3	810	White	2CFL873010R0001	31	
	CFL - TC-DEL	1x 26W	G24q-3	810	Black	Available 2015/10	31	
	LED	12W	-	900	White	2CFL873022R0001	31	
	LED	12W	-	900	Black	Available 2015/10	31	
	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	White	2CFL873050R0001	31	
Axioeme T2	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Black	Available 2015/10	31	
	CFL - TC-SEL	2x 18W	G24q-2	1150	White	2CFL873064R0001	31	
	CFL - TC-SEL	2x 18W	G24q-2	1150	Black	Available 2015/10	31	
	CFL - TC-SEL	2x 26W	G24q-3	1330	White	2CFL873060R0001	31	
	CFL - TC-SEL	2x 26W	G24q-3	1330	Black	Available 2015/10	31	
	LED	11W	-	900	White	2CFL873085R0001	31	
	LED	11W	-	900	Black	Available 2015/10	31	
	LED	15W	-	1200	White	2CFL873090R0001	31	
	LED	15W	-	1200	Black	Available 2015/10	31	
	LED	20W	-	1500	White	2CFL873095R0001	31	
	LED	20W	-	1500	Black	Available 2015/10	31	
	Dune	E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	White	2CFL879012R0001	23
E27 (Lamp not included)		1x 75W or 1x 46W HAL	E27	-	Black	2CFL879017R0001	23	
CFL - TC-SEL		1x 9W	2G7	400	White	2CFL879043R0001	23	
CFL - TC-SEL		1x 9W	2G7	400	Black	2CFL879044R0001	23	
CFL - TC-SEL		2x 9W	2G7	700	White	2CFL879045R0001	23	
CFL - TC-SEL		2x 9W	2G7	700	Black	2CFL878046R0001	23	
CFL - TC-DEL		1x 13W	G24q-1	410	White	2CFL879047R0001	23	
CFL - TC-DEL		1x 13W	G24q-1	410	Black	2CFL879048R0001	23	
LED		19W	-	930	White	2CFL876106R0001	23	
LED		19W	-	930	Black	2CFL876107R0001	23	
Dune Casquette		E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	White	2CFL879259R0001	23
		E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	Black	2CFL879260R0001	23
	CFL - TC-SEL	1x 9W	2G7	310	White	2CFL879267R0001	23	
	CFL - TC-SEL	1x 9W	2G7	310	Black	2CFL879268R0001	23	

Index

Type classification

Description	Lamp	Power W	Cap	Luminous flux lm	Finition color	Order code	Page
	CFL - TC-SEL	2x 9W	2G7	500	White	2CFL879269R0001	23
	CFL - TC-SEL	2x 9W	2G7	500	Black	2CFL879270R0001	23
	CFL - TC-DEL	1x 13W	G24q-1	380	White	2CFL879271R0001	23
	CFL - TC-DEL	1x 13W	G24q-1	380	Black	2CFL879272R0001	23
	LED	19W	-	770	White	2CFL876166R0001	23
	LED	19W	-	770	Black	2CFL876167R0001	23
Dune Visor	E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	White	2CFL879063R0001	23
	E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	Black	2CFL879064R0001	23
	CFL - TC-SEL	1x 9W	2G7	230	White	2CFL879253R0001	23
	CFL - TC-SEL	1x 9W	2G7	230	Black	2CFL879254R0001	23
	CFL - TC-SEL	2x 9W	2G7	370	White	2CFL879255R0001	23
	CFL - TC-SEL	2x 9W	2G7	370	Black	2CFL879256R0001	23
	CFL - TC-DEL	1x 13W	G24q-1	280	White	2CFL879257R0001	23
	CFL - TC-DEL	1x 13W	G24q-1	280	Black	2CFL879258R0001	23
	LED	19W	-	620	White	2CFL876146R0001	23
	LED	19W	-	620	Black	2CFL876147R0001	23
Eo - With lamp	Standard	1x TC-SEL 11W	2G7	-	White	2CFL855281R0001	33
	With lightswitch	1x TC-SEL 11W	2G7	-	White	2CFL855283R0001	33
	With socket 16A	1x TC-SEL 11W	2G7	-	White	2CFL855284R0001	33
	with transformer 230V/20A and shaver socket	1x TC-SEL 11W	2G7	-	White	2CFL855285R0001	33
Eo - Without lamp	Standard	1x 75W	S19	-	White	2CFL855211R0001	33
	Standard	1x 75W	S19	-	Brown	2CFL855231R0001	33
	With lightswitch	1x 75W	S19	-	White	2CFL855213R0001	33
	With lightswitch	1x 75W	S19	-	Brown	2CFL855233R0001	33
	With socket 16A	1x 75W	S19	-	White	2CFL855214R0001	33
	With socket 16A	1x 75W	S19	-	Brown	2CFL855234R0001	33
	With lightswitch and socket 16A	1x 75W	S19	-	White	2CFL855215R0001	33
	With lightswitch and socket 16A	1x 75W	S19	-	Brown	2CFL855235R0001	33
	With shaver socket	1x 75W	S19	-	White	2CFL855217R0001	33
	With shaver socket	1x 75W	S19	-	Brown	2CFL855237R0001	33
	with transformer 230V/20A and shaver socket	1x 75W	S19	-	White	2CFL855218R0001	33
	with transformer 230V/20A and shaver socket	1x 75W	S19	-	Brown	2CFL855238R0001	33
H350	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	White	2CFL874001R0001	19
	E27 (Lamp not included)	2x 70W or 53W HAL	E27	-	White	2CFL874000R0001	19
	CFL - TC-DEL	1x 18W	G24q-2	760	White	2CFL874002R0001	19
	CFL - TC-DEL	2x 18W	G24q-2	1440	White	2CFL874003R0001	19
	CFL - TC-DEL	1x 26W	G24q-3	1100	White	2CFL874004R0001	19
	CFL - TC-DEL	2x 26W	G24q-3	2230	White	2CFL874005R0001	19
	CFL - TC-TEL	1x 32W	GX24q-3	1270	White	2CFL874006R0001	19
	LED	15W	-	1050	White	2CFL874018R0001	19
	LED	24W	-	1725	White	2CFL874020R0001	19
Havana	E27 (Lamp not included)	1x 75W or 1x 52W HAL	E27	-	White	2CFL879205R0001	29
	E27 (Lamp not included)	1x 75W or 1x 52W HAL	E27	-	Black	2CFL879207R0001	29
	CFL - TC-SEL	1x 9W	2G7	310	White	2CFL879237R0001	29
	CFL - TC-SEL	1x 9W	2G7	310	Black	2CFL879238R0001	29
	CFL - TC-SEL	2x 9W	2G7	610	White	2CFL879239R0001	29
	CFL - TC-SEL	2x 9W	2G7	610	Black	2CFL879240R0001	29
	CFL - TC-DEL	1x 13W	G24q-1	470	White	2CFL879221R0001	29
	CFL - TC-DEL	1x 13W	G24q-1	470	Black	2CFL879222R0001	29
	CFL - TC-DEL	1x 18W	G24q-2	620	White	2CFL879223R0001	29
	CFL - TC-DEL	1x 18W	G24q-2	620	Black	2CFL879224R0001	29
	LED	20W	-	800	White	2CFL879247R0001	29
	LED	20W	-	800	Black	2CFL879248R0001	29
Lips Band	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	White	2CFL878602R0001	26
	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Black	2CFL878605R0001	26
	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Titanium	2CFL878608R0001	26
	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Anthracite	2CFL878611R0001	26
	CFL - TC-SEL	1x 9W	2G7	220	White	2CFL879578R0001	26
	CFL - TC-SEL	1x 9W	2G7	220	Black	2CFL879580R0001	26
	CFL - TC-SEL	1x 9W	2G7	220	Titanium	2CFL879582R0001	26
	CFL - TC-SEL	1x 9W	2G7	220	Anthracite	2CFL879584R0001	26
	CFL - TC-DEL	1x 13W	24Gq-3	330	White	2CFL879579R0001	26
	CFL - TC-DEL	1x 13W	24Gq-3	330	Black	2CFL879581R0001	26
	CFL - TC-DEL	1x 13W	24Gq-3	330	Titanium	2CFL879583R0001	26
	CFL - TC-DEL	1x 13W	24Gq-3	330	Anthracite	2CFL879585R0001	26
	CFL - TC-DEL	1x 18W	24Gq-2	440	White	2CFL879663R0001	26
	CFL - TC-DEL	1x 18W	24Gq-2	440	Black	2CFL879668R0001	26
	CFL - TC-DEL	1x 18W	24Gq-2	440	Titanium	2CFL879673R0001	26
	CFL - TC-DEL	1x 18W	24Gq-2	440	Anthracite	2CFL879678R0001	26
	CFL - TC-DEL	1x 26W	24Gq-3	670	White	2CFL879664R0001	26
	CFL - TC-DEL	1x 26W	24Gq-3	670	Black	2CFL879669R0001	26
	CFL - TC-DEL	1x 26W	24Gq-3	670	Titanium	2CFL879674R0001	26
	CFL - TC-DEL	1x 26W	24Gq-3	670	Anthracite	2CFL879579R0001	26
Lips Rim	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	White	2CFL878600R0001	25
	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Black	2CFL878603R0001	25
	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Titanium	2CFL878606R0001	25
	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Anthracite	2CFL878609R0001	25
	CFL - TC-SEL	1x 9W	2G7	290	White	2CFL879542R0001	25
	CFL - TC-SEL	1x 9W	2G7	290	Black	2CFL879544R0001	25

Index

Type classification

Description	Lamp	Power W	Cap	Luminous flux lm	Finition color	Order code	Page	
Lips Rim	CFL - TC-SEL	1x 9W	2G7	290	Titanium	2CFL879548R0001	25	
	CFL - TC-SEL	1x 9W	2G7	290	Anthracite	2CFL879554R0001	25	
	CFL - TC-DEL	1x 13W	24Gq-3	430	White	2CFL879543R0001	25	
	CFL - TC-DEL	1x 13W	24Gq-3	430	Black	2CFL879547R0001	25	
	CFL - TC-DEL	1x 13W	24Gq-3	430	Titanium	2CFL879549R0001	25	
	CFL - TC-DEL	1x 13W	24Gq-3	430	Anthracite	2CFL879557R0001	25	
	CFL - TC-DEL	1x 18W	24Gq-2	580	White	2CFL879603R0001	25	
	CFL - TC-DEL	1x 18W	24Gq-2	580	Black	2CFL879608R0001	25	
	CFL - TC-DEL	1x 18W	24Gq-2	580	Titanium	2CFL879613R0001	25	
	CFL - TC-DEL	1x 18W	24Gq-2	580	Anthracite	2CFL879618R0001	25	
	CFL - TC-DEL	1x 26W	24Gq-3	860	White	2CFL879604R0001	25	
	CFL - TC-DEL	1x 26W	24Gq-3	860	Black	2CFL879609R0001	25	
	CFL - TC-DEL	1x 26W	24Gq-3	860	Titanium	2CFL879614R0001	25	
	CFL - TC-DEL	1x 26W	24Gq-3	860	Anthracite	2CFL879619R0001	25	
	Lips Slotted Visor	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	White	2CFL878601R0001	27
		E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Black	2CFL878604R0001	27
		E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Titanium	2CFL878607R0001	27
		E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Anthracite	2CFL878610R0001	27
		CFL - TC-SEL	1x 9W	2G7	210	White	2CFL879564R0001	27
		CFL - TC-SEL	1x 9W	2G7	210	Black	2CFL879566R0001	27
CFL - TC-SEL		1x 9W	2G7	210	Titanium	2CFL879570R0001	27	
CFL - TC-SEL		1x 9W	2G7	210	Anthracite	2CFL879572R0001	27	
CFL - TC-DEL		1x 13W	24Gq-3	320	White	2CFL879565R0001	27	
CFL - TC-DEL		1x 13W	24Gq-3	320	Black	2CFL879569R0001	27	
CFL - TC-DEL		1x 13W	24Gq-3	320	Titanium	2CFL879571R0001	27	
CFL - TC-DEL		1x 13W	24Gq-3	320	Anthracite	2CFL879573R0001	27	
CFL - TC-DEL		1x 18W	24Gq-2	420	White	2CFL879633R0001	27	
CFL - TC-DEL		1x 18W	24Gq-2	420	Black	2CFL879638R0001	27	
CFL - TC-DEL		1x 18W	24Gq-2	420	Titanium	2CFL879643R0001	27	
CFL - TC-DEL		1x 18W	24Gq-2	420	Anthracite	2CFL879648R0001	27	
CFL - TC-DEL		1x 26W	24Gq-3	630	White	2CFL879634R0001	27	
CFL - TC-DEL		1x 26W	24Gq-3	630	Black	2CFL879639R0001	27	
CFL - TC-DEL		1x 26W	24Gq-3	630	Titanium	2CFL879644R0001	27	
CFL - TC-DEL		1x 26W	24Gq-3	630	Anthracite	2CFL879649R0001	27	
Option	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	White	2CFL878847R0001	21	
	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Black	2CFL878848R0001	21	
	CFL - TC-SEL	1x 9W	2G7	510	White	2CFL878341R0001	21	
	CFL - TC-SEL	1x 9W	2G7	510	Black	2CFL878342R0001	21	
	CFL - TC-SEL	2x 9W	2G7	880	White	2CFL878335R0001	21	
	CFL - TC-SEL	2x 9W	2G7	880	Black	2CFL878336R0001	21	
	CFL - TC-DEL	1x 13W	G24q-1	770	White	2CFL878365R0001	21	
	CFL - TC-DEL	1x 13W	G24q-1	770	Black	2CFL878366R0001	21	
	CFL - TC-DEL	2x 13W	G24q-1	1310	White	2CFL878347R0001	21	
	CFL - TC-DEL	2x 13W	G24q-1	1310	Black	2CFL878348R0001	21	
	CFL - TC-DEL	1x 18W	G24q-2	1020	White	2CFL878353R0001	21	
	CFL - TC-DEL	1x 18W	G24q-2	1020	Black	2CFL878354R0001	21	
	CFL - TC-DEL	1x 26W	G24q-3	1200	White	2CFL878359R0001	21	
	CFL - TC-DEL	1x 26W	G24q-3	1200	Black	2CFL878360R0001	21	
	CFL - TC-TEL	1x 32W	GX24q-3	1530	White	2CFL878863R0001	21	
	CFL - TC-TEL	1x 32W	GX24q-3	1530	Black	2CFL878864R0001	21	
	LED	15W	-	1100	White	Available 2015/04	21	
	LED	15W	-	1100	Black	Available 2015/04	21	
	LED	24W	-	1800	White	Available 2015/04	21	
	LED	24W	-	1800	Black	Available 2015/04	21	
Sextan	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	White	2CFL871700R0001	9	
	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Grey	2CFL871730R0001	9	
	CFL - TC-DEL	1x 18W	G24q-2	640	White	2CFL871704R0001	9	
	CFL - TC-DEL	1x 18W	G24q-3	640	Grey	2CFL871734R0001	9	
	CFL - TC-DEL	2x 18W	G24q-2	1250	White	2CFL871705R0001	9	
	CFL - TC-DEL	2x 18W	G24q-3	1250	Grey	2CFL871735R0001	9	
	CFL - TC-DEL	1x 26W	G24q-3	950	White	2CFL871706R0001	9	
	CFL - TC-DEL	1x 26W	G24q-4	950	Grey	2CFL871736R0001	9	
	CFL - TC-DEL	2x 26W	G24q-3	1870	White	2CFL871707R0001	9	
	CFL - TC-DEL	2x 26W	G24q-4	1870	Grey	2CFL871737R0001	9	
	CFL - TC-TEL	1x 32W	GX24q-3	-	White	2CFL871708R0001	9	
	CFL - TC-TEL	1x 32W	GX24q-3	-	Grey	2CFL871738R0001	9	
	LED	15W	-	1080	White	Available 2015/04	9	
	LED	15W	-	1080	Grey	Available 2015/04	9	
	LED	24W	-	1800	White	Available 2015/04	9	
	LED	24W	-	1800	Grey	Available 2015/04	9	
	Sextan DALI	CFL - TC-DEL	2x 26W	G24q-3	1870	White	2CFL871709R0001	9
		CFL - TC-DEL	2x 26W	G24q-3	1870	Grey	2CFL871739R0001	9
	Sextan Premium	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Anthracite	2CFL871790R0001	10
		E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Alu-Silver	2CFL871950R0001	10
E27 (Lamp not included)		1x 100W or 1x 70W HAL	E27	-	White	2CFL871760R0001	10	
E27 (Lamp not included)		1x 100W or 1x 70W HAL	E27	-	Stainless steel	2CFL871960R0001	10	
CFL - TC-DEL		1x 18W	G24q-2	640	Anthracite	2CFL871794R0001	10	
CFL - TC-DEL		1x 18W	G24q-2	640	Alu-Silver	2CFL871954R0001	10	
CFL - TC-DEL		1x 18W	G24q-2	640	White	2CFL871764R0001	10	
CFL - TC-DEL		1x 18W	G24q-2	640	Stainless steel	2CFL871964R0001	10	
CFL - TC-DEL		2x 18W	G24q-2	1250	Anthracite	2CFL871795R0001	10	
CFL - TC-DEL		2x 18W	G24q-2	1250	Alu-Silver	2CFL871955R0001	10	

Index

Type classification

Description	Lamp	Power W	Cap	Luminous flux lm	Finint color	Order code	Page
	CFL - TC-DEL	2x 18W	G24q-2	1250	White	2CFL871765R0001	10
	CFL - TC-DEL	2x 18W	G24q-2	1250	Stainless steel	2CFL871965R0001	10
	CFL - TC-DEL	1x 26W	G24q-3	950	Anthracite	2CFL871796R0001	10
	CFL - TC-DEL	1x 26W	G24q-3	950	Alu-Silver	2CFL871956R0001	10
	CFL - TC-DEL	1x 26W	G24q-3	950	White	2CFL871766R0001	10
	CFL - TC-DEL	1x 26W	G24q-3	950	Stainless steel	2CFL871966R0001	10
	CFL - TC-DEL	2x 26W	G24q-3	1870	Anthracite	2CFL871797R0001	10
	CFL - TC-DEL	2x 26W	G24q-3	1870	Alu-Silver	2CFL871957R0001	10
	CFL - TC-DEL	2x 26W	G24q-3	1870	White	2CFL871767R0001	10
	CFL - TC-DEL	2x 26W	G24q-3	1870	Stainless steel	2CFL871967R0001	10
	CFL - TC-TEL	1x 32W	GX24q-3	-	Anthracite	2CFL871798R0001	10
	CFL - TC-TEL	1x 32W	GX24q-3	-	Alu-Silver	2CFL871958R0001	10
	CFL - TC-TEL	1x 32W	GX24q-3	-	White	2CFL871768R0001	10
	CFL - TC-TEL	1x 32W	GX24q-3	-	Stainless steel	2CFL871968R0001	10
	LED	15W	-	-	Anthracite	Available 2015/04	10
	LED	15W	-	-	Alu-Silver	Available 2015/04	10
	LED	15W	-	-	White	Available 2015/04	10
	LED	15W	-	-	Stainless steel	Available 2015/04	10
	LED	24W	-	-	Anthracite	Available 2015/04	10
	LED	24W	-	-	Alu-Silver	Available 2015/04	10
	LED	24W	-	-	White	Available 2015/04	10
	LED	24W	-	-	Stainless steel	Available 2015/04	10
Sextan Premium DALI	CFL - TC-DEL	2x 26W	G24q-3	1870	Anthracite	2CFL871799R0001	10
	CFL - TC-DEL	2x 26W	G24q-3	1870	Alu-Silver	2CFL871959R0001	10
	CFL - TC-DEL	2x 26W	G24q-3	1870	White	2CFL871769R0001	10
	CFL - TC-DEL	2x 26W	G24q-3	1870	Stainless steel	2CFL871969R0001	10
Sextan Premium Wall-mounted - D/H	CFL - TC-SEL	1x 9W	2G7	-	White	2CFL871601R0001	11
	CFL - TC-SEL	1x 9W	2G7	-	Anthracite	2CFL871631R0001	11
	CFL - TC-SEL	1x 9W	2G7	-	Stainless steel	2CFL871621R0001	11
	CFL - TC-DEL	1x 13W	G24q-1	-	White	2CFL871602R0001	11
	CFL - TC-DEL	1x 13W	G24q-1	-	Anthracite	2CFL871632R0001	11
	CFL - TC-DEL	1x 13W	G24q-1	-	Stainless steel	2CFL871622R0001	11
	CFL - TC-DEL	1x 18W	G24q-2	-	White	2CFL871603R0001	11
	CFL - TC-DEL	1x 18W	G24q-2	-	Anthracite	2CFL871633R0001	11
	CFL - TC-DEL	1x 18W	G24q-2	-	Stainless steel	2CFL871623R0001	11
	CFL - TC-DEL	1x 26W	G24q-3	750	White	2CFL871604R0001	11
	CFL - TC-DEL	1x 26W	G24q-3	750	Anthracite	2CFL871634R0001	11
	CFL - TC-DEL	1x 26W	G24q-3	750	Stainless steel	2CFL871624R0001	11
Sextan Premium Wall-mounted - H/B	CFL - TC-SEL	1x 9W	2G7	-	White	2CFL871501R0001	11
	CFL - TC-SEL	1x 9W	2G7	-	Anthracite	2CFL871531R0001	11
	CFL - TC-SEL	1x 9W	2G7	-	Stainless steel	2CFL871521R0001	11
	CFL - TC-DEL	1x 13W	G24q-1	-	White	2CFL871502R0001	11
	CFL - TC-DEL	1x 13W	G24q-1	-	Anthracite	2CFL871532R0001	11
	CFL - TC-DEL	1x 13W	G24q-1	-	Stainless steel	2CFL871522R0001	11
	CFL - TC-DEL	1x 18W	G24q-2	-	White	2CFL871503R0001	11
	CFL - TC-DEL	1x 18W	G24q-2	-	Anthracite	2CFL871533R0001	11
	CFL - TC-DEL	1x 18W	G24q-2	-	Stainless steel	2CFL871523R0001	11
	CFL - TC-DEL	1x 26W	G24q-3	900	White	2CFL871504R0001	11
	CFL - TC-DEL	1x 26W	G24q-3	900	Anthracite	2CFL871534R0001	11
	CFL - TC-DEL	1x 26W	G24q-3	900	Stainless steel	2CFL871524R0001	11
SlimEo - With lamp	Standard	1x T16 13W	G5	-	White	2CFL855451R0001	33
	Standard	1x T26 18W	G13	-	White	2CFL855442R0001	33
	Standard	1x T26 36W	G13	-	White	2CFL855462R0001	33
	With lightswitch	1x T16 13W	G5	-	White	2CFL855453R0001	33
	With lightswitch	1x T26 18W	G13	-	White	2CFL855446R0001	33
	With lightswitch	1x T26 36W	G13	-	White	2CFL855466R0001	33
Squad	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	White	2CFL879403R0001	15
	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Black	2CFL879404R0001	15
	CFL - TC-DEL	1x 18W	G24q-2	660	White	2CFL879462R0001	15
	CFL - TC-DEL	1x 18W	G24q-2	660	Black	2CFL879463R0001	15
	CFL - TC-DEL	2x 18W	G24q-2	1420	White	2CFL879440R0001	15
	CFL - TC-DEL	2x 18W	G24q-2	1420	Black	2CFL879441R0001	15
	CFL - TC-DEL	1x 26W	G24q-3	990	White	2CFL879464R0001	15
	CFL - TC-DEL	1x 26W	G24q-3	990	Black	2CFL879465R0001	15
	CFL - TC-DEL	2x 26W	G24q-3	1910	White	2CFL879444R0001	15
	CFL - TC-DEL	2x 26W	G24q-3	1910	Black	2CFL879445R0001	15
	LED	15W	-	1250	White	2CFL876436R0001	15
	LED	15W	-	1250	Black	2CFL876437R0001	15
	LED	24W	-	2030	White	2CFL876445R0001	15
	LED	24W	-	2030	Black	2CFL876450R0001	15
Squad DALI	CFL - TC-DEL	2x 26W	G24q-3	1910	White	2CFL879454R0001	15
	CFL - TC-DEL	2x 26W	G24q-3	1910	Black	2CFL879455R0001	15

Index

Order code classification

Order code	Description	Lamp	Power W	Cap	Luminous flux lm	Finition color	Page
2CFL878870R0001	Alium	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Anthracite	17
2CFL855211R0001	Eo - Without lamp	Standard	1x 75W	S19	-	White	33
2CFL855213R0001	Eo - Without lamp	With lightswitch	1x 75W	S19	-	White	33
2CFL855214R0001	Eo - Without lamp	With socket 16A	1x 75W	S19	-	White	33
2CFL855215R0001	Eo - Without lamp	With lightswitch and socket 16A	1x 75W	S19	-	White	33
2CFL855217R0001	Eo - Without lamp	With shaver socket	1x 75W	S19	-	White	33
2CFL855218R0001	Eo - Without lamp	with transformer 230V/20A and shaver socket	1x 75W	S19	-	White	33
2CFL855231R0001	Eo - Without lamp	Standard	1x 75W	S19	-	Brown	33
2CFL855233R0001	Eo - Without lamp	With lightswitch	1x 75W	S19	-	Brown	33
2CFL855234R0001	Eo - Without lamp	With socket 16A	1x 75W	S19	-	Brown	33
2CFL855235R0001	Eo - Without lamp	With lightswitch and socket 16A	1x 75W	S19	-	Brown	33
2CFL855237R0001	Eo - Without lamp	With shaver socket	1x 75W	S19	-	Brown	33
2CFL855238R0001	Eo - Without lamp	with transformer 230V/20A and shaver socket	1x 75W	S19	-	Brown	33
2CFL855281R0001	Eo - With lamp	Standard	1x TC-SEL 11W	2G7	-	White	33
2CFL855283R0001	Eo - With lamp	With lightswitch	1x TC-SEL 11W	2G7	-	White	33
2CFL855284R0001	Eo - With lamp	With socket 16A	1x TC-SEL 11W	2G7	-	White	33
2CFL855285R0001	Eo - With lamp	with transformer 230V/20A and shaver socket	1x TC-SEL 11W	2G7	-	White	33
2CFL855442R0001	SlimEo - With lamp	Standard	1x T26 18W	G13	-	White	33
2CFL855446R0001	SlimEo - With lamp	With lightswitch	1x T26 18W	G13	-	White	33
2CFL855451R0001	SlimEo - With lamp	Standard	1x T16 13W	G5	-	White	33
2CFL855453R0001	SlimEo - With lamp	With lightswitch	1x T16 13W	G5	-	White	33
2CFL855462R0001	SlimEo - With lamp	Standard	1x T26 36W	G13	-	White	33
2CFL855466R0001	SlimEo - With lamp	With lightswitch	1x T26 36W	G13	-	White	33
2CFL870000R0001	Atoll C320	E27 (Lamp not included)	2x 60W or 2x 42W HAL	E27	-	White	13
2CFL870004R0001	Atoll C320	CFL - TC-SEL	2x 9W	2G7	580	White	13
2CFL870005R0001	Atoll C320	CFL - TC-DEL	2x 18W	G24q-2	1150	White	13
2CFL870006R0001	Atoll C320	CFL - TC-DEL	2x 26W	G24q-3	1730	White	13
2CFL870010R0001	Atoll C320	E27 (Lamp not included)	2x 60W or 2x 42W HAL	E27	-	Black	13
2CFL870014R0001	Atoll C320	CFL - TC-SEL	2x 9W	2G7	580	Black	13
2CFL870015R0001	Atoll C320	CFL - TC-DEL	2x 18W	G24q-2	1150	Black	13
2CFL870016R0001	Atoll C320	CFL - TC-DEL	2x 26W	G24q-3	1730	Black	13
2CFL870020R0001	Atoll C320	E27 (Lamp not included)	2x 60W or 2x 42W HAL	E27	-	Titanium	13
2CFL870024R0001	Atoll C320	CFL - TC-SEL	2x 9W	2G7	580	Titanium	13
2CFL870025R0001	Atoll C320	CFL - TC-DEL	2x 18W	G24q-2	1150	Titanium	13
2CFL870026R0001	Atoll C320	CFL - TC-DEL	2x 26W	G24q-3	1730	Titanium	13
2CFL870030R0001	Atoll C320	E27 (Lamp not included)	2x 60W or 2x 42W HAL	E27	-	Anthracite	13
2CFL870034R0001	Atoll C320	CFL - TC-SEL	2x 9W	2G7	580	Anthracite	13
2CFL870035R0001	Atoll C320	CFL - TC-DEL	2x 18W	G24q-2	1150	Anthracite	13
2CFL870036R0001	Atoll C320	CFL - TC-DEL	2x 26W	G24q-3	1730	Anthracite	13
2CFL870062R0001	Atoll C320 DALI	CFL - TC-DEL	2x 26W	G24q-3	1730	White	13
2CFL870067R0001	Atoll C320 DALI	CFL - TC-DEL	2x 26W	G24q-3	1730	Black	13
2CFL870072R0001	Atoll C320 DALI	CFL - TC-DEL	2x 26W	G24q-3	1730	Titanium	13
2CFL870077R0001	Atoll C320 DALI	CFL - TC-DEL	2x 26W	G24q-3	1730	Anthracite	13
2CFL870094R0001	Atoll C320	CFL - TC-DEL	2x 13W	G24q-1	860	White	13
2CFL870095R0001	Atoll C320	CFL - TC-DEL	2x 13W	G24q-1	860	Black	13
2CFL870096R0001	Atoll C320	CFL - TC-DEL	2x 13W	G24q-1	860	Titanium	13
2CFL870097R0001	Atoll C320	CFL - TC-DEL	2x 13W	G24q-1	860	Anthracite	13
2CFL870246R0001	Atoll C320	LED	24W	-	1580	White	13
2CFL870256R0001	Atoll C320	LED	24W	-	1580	Black	13
2CFL870266R0001	Atoll C320	LED	24W	-	1580	Titanium	13
2CFL870276R0001	Atoll C320	LED	24W	-	1580	Anthracite	13
2CFL870280R0001	Atoll C320	LED	15W	-	920	White	13
2CFL870281R0001	Atoll C320	LED	15W	-	920	Black	13
2CFL870291R0001	Atoll C320	LED	15W	-	920	Titanium	13
2CFL870296R0001	Atoll C320	LED	15W	-	920	Anthracite	13
2CFL871501R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-SEL	1x 9W	2G7	-	White	11
2CFL871502R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-DEL	1x 13W	G24q-1	-	White	11
2CFL871503R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-DEL	1x 18W	G24q-2	-	White	11
2CFL871504R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-DEL	1x 26W	G24q-3	900	White	11
2CFL871521R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-SEL	1x 9W	2G7	-	Stainless steel	11
2CFL871522R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-DEL	1x 13W	G24q-1	-	Stainless steel	11
2CFL871523R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-DEL	1x 18W	G24q-2	-	Stainless steel	11
2CFL871524R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-DEL	1x 26W	G24q-3	900	Stainless steel	11
2CFL871531R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-SEL	1x 9W	2G7	-	Anthracite	11
2CFL871532R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-DEL	1x 13W	G24q-1	-	Anthracite	11
2CFL871533R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-DEL	1x 18W	G24q-2	-	Anthracite	11
2CFL871534R0001	Sextan Premium Wall-mounted - H/B	CFL - TC-DEL	1x 26W	G24q-3	900	Anthracite	11
2CFL871601R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-SEL	1x 9W	2G7	-	White	11
2CFL871602R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-DEL	1x 13W	G24q-1	-	White	11
2CFL871603R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-DEL	1x 18W	G24q-2	-	White	11
2CFL871604R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-DEL	1x 26W	G24q-3	750	White	11
2CFL871621R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-SEL	1x 9W	2G7	-	Stainless steel	11
2CFL871622R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-DEL	1x 13W	G24q-1	-	Stainless steel	11
2CFL871623R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-DEL	1x 18W	G24q-2	-	Stainless steel	11
2CFL871624R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-DEL	1x 26W	G24q-3	750	Stainless steel	11
2CFL871631R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-SEL	1x 9W	2G7	-	Anthracite	11
2CFL871632R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-DEL	1x 13W	G24q-1	-	Anthracite	11
2CFL871633R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-DEL	1x 18W	G24q-2	-	Anthracite	11
2CFL871634R0001	Sextan Premium Wall-mounted - D/H	CFL - TC-DEL	1x 26W	G24q-3	750	Anthracite	11

Index

Order code classification

Order code	Description	Lamp	Power W	Cap	Luminous flux lm	Finition color	Page
2CFL871700R0001	Sextan	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	White	9
2CFL871704R0001	Sextan	CFL - TC-DEL	1x 18W	G24q-2	640	White	9
2CFL871705R0001	Sextan	CFL - TC-DEL	2x 18W	G24q-2	1250	White	9
2CFL871706R0001	Sextan	CFL - TC-DEL	1x 26W	G24q-3	950	White	9
2CFL871707R0001	Sextan	CFL - TC-DEL	2x 26W	G24q-3	1870	White	9
2CFL871708R0001	Sextan	CFL - TC-TEL	1x 32W	GX24q-3	-	White	9
2CFL871709R0001	Sextan DALI	CFL - TC-DEL	2x 26W	G24q-3	1870	White	9
2CFL871730R0001	Sextan	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Grey	9
2CFL871734R0001	Sextan	CFL - TC-DEL	1x 18W	G24q-3	640	Grey	9
2CFL871735R0001	Sextan	CFL - TC-DEL	2x 18W	G24q-3	1250	Grey	9
2CFL871736R0001	Sextan	CFL - TC-DEL	1x 26W	G24q-4	950	Grey	9
2CFL871737R0001	Sextan	CFL - TC-DEL	2x 26W	G24q-4	1870	Grey	9
2CFL871738R0001	Sextan	CFL - TC-TEL	1x 32W	GX24q-3	-	Grey	9
2CFL871739R0001	Sextan DALI	CFL - TC-DEL	2x 26W	G24q-3	1870	Grey	9
2CFL871760R0001	Sextan Premium	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	White	10
2CFL871764R0001	Sextan Premium	CFL - TC-DEL	1x 18W	G24q-2	640	White	10
2CFL871765R0001	Sextan Premium	CFL - TC-DEL	2x 18W	G24q-2	1250	White	10
2CFL871766R0001	Sextan Premium	CFL - TC-DEL	1x 26W	G24q-3	950	White	10
2CFL871767R0001	Sextan Premium	CFL - TC-DEL	2x 26W	G24q-3	1870	White	10
2CFL871768R0001	Sextan Premium	CFL - TC-TEL	1x 32W	GX24q-3	-	White	10
2CFL871769R0001	Sextan Premium DALI	CFL - TC-DEL	2x 26W	G24q-3	1870	White	10
2CFL871790R0001	Sextan Premium	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Anthracite	10
2CFL871794R0001	Sextan Premium	CFL - TC-DEL	1x 18W	G24q-2	640	Anthracite	10
2CFL871795R0001	Sextan Premium	CFL - TC-DEL	2x 18W	G24q-2	1250	Anthracite	10
2CFL871796R0001	Sextan Premium	CFL - TC-DEL	1x 26W	G24q-3	950	Anthracite	10
2CFL871797R0001	Sextan Premium	CFL - TC-DEL	2x 26W	G24q-3	1870	Anthracite	10
2CFL871798R0001	Sextan Premium	CFL - TC-TEL	1x 32W	GX24q-3	-	Anthracite	10
2CFL871799R0001	Sextan Premium DALI	CFL - TC-DEL	2x 26W	G24q-3	1870	Anthracite	10
2CFL871950R0001	Sextan Premium	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Alu-Silver	10
2CFL871954R0001	Sextan Premium	CFL - TC-DEL	1x 18W	G24q-2	640	Alu-Silver	10
2CFL871955R0001	Sextan Premium	CFL - TC-DEL	2x 18W	G24q-2	1250	Alu-Silver	10
2CFL871956R0001	Sextan Premium	CFL - TC-DEL	1x 26W	G24q-3	950	Alu-Silver	10
2CFL871957R0001	Sextan Premium	CFL - TC-DEL	2x 26W	G24q-3	1870	Alu-Silver	10
2CFL871958R0001	Sextan Premium	CFL - TC-TEL	1x 32W	GX24q-3	-	Alu-Silver	10
2CFL871959R0001	Sextan Premium DALI	CFL - TC-DEL	2x 26W	G24q-3	1870	Alu-Silver	10
2CFL871960R0001	Sextan Premium	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Stainless steel	10
2CFL871964R0001	Sextan Premium	CFL - TC-DEL	1x 18W	G24q-2	640	Stainless steel	10
2CFL871965R0001	Sextan Premium	CFL - TC-DEL	2x 18W	G24q-2	1250	Stainless steel	10
2CFL871966R0001	Sextan Premium	CFL - TC-DEL	1x 26W	G24q-3	950	Stainless steel	10
2CFL871967R0001	Sextan Premium	CFL - TC-DEL	2x 26W	G24q-3	1870	Stainless steel	10
2CFL871968R0001	Sextan Premium	CFL - TC-TEL	1x 32W	GX24q-3	-	Stainless steel	10
2CFL871969R0001	Sextan Premium DALI	CFL - TC-DEL	2x 26W	G24q-3	1870	Stainless steel	10
2CFL873000R0001	Axiome T1	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	White	31
2CFL873010R0001	Axiome T1	CFL - TC-DEL	1x 26W	G24q-3	810	White	31
2CFL873012R0001	Axiome T1	CFL - TC-DEL	1x 18W	G24q-2	490	White	31
2CFL873022R0001	Axiome T1	LED	12W	-	900	White	31
2CFL873050R0001	Axiome T2	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	White	31
2CFL873060R0001	Axiome T2	CFL - TC-SEL	2x 26W	G24q-3	1330	White	31
2CFL873064R0001	Axiome T2	CFL - TC-SEL	2x 18W	G24q-2	1150	White	31
2CFL873085R0001	Axiome T2	LED	11W	-	900	White	31
2CFL873090R0001	Axiome T2	LED	15W	-	1200	White	31
2CFL873095R0001	Axiome T2	LED	20W	-	1500	White	31
2CFL874000R0001	H350	E27 (Lamp not included)	2x 70W or 53W HAL	E27	-	White	19
2CFL874001R0001	H350	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	White	19
2CFL874002R0001	H350	CFL - TC-DEL	1x 18W	G24q-2	760	White	19
2CFL874003R0001	H350	CFL - TC-DEL	2x 18W	G24q-2	1440	White	19
2CFL874004R0001	H350	CFL - TC-DEL	1x 26W	G24q-3	1100	White	19
2CFL874005R0001	H350	CFL - TC-DEL	2x 26W	G24q-3	2230	White	19
2CFL874006R0001	H350	CFL - TC-TEL	1x 32W	GX24q-3	1270	White	19
2CFL874018R0001	H350	LED	15W	-	1050	White	19
2CFL874020R0001	H350	LED	24W	-	1725	White	19
2CFL876106R0001	Dune	LED	19W	-	930	White	23
2CFL876107R0001	Dune	LED	19W	-	930	Black	23
2CFL876146R0001	Dune Visor	LED	19W	-	620	White	23
2CFL876147R0001	Dune Visor	LED	19W	-	620	Black	23
2CFL876166R0001	Dune Casquette	LED	19W	-	770	White	23
2CFL876167R0001	Dune Casquette	LED	19W	-	770	Black	23
2CFL876436R0001	Squad	LED	15W	-	1250	White	15
2CFL876437R0001	Squad	LED	15W	-	1250	Black	15
2CFL876445R0001	Squad	LED	24W	-	2030	White	15
2CFL876450R0001	Squad	LED	24W	-	2030	Black	15
2CFL878046R0001	Dune	CFL - TC-SEL	2x 9W	2G7	700	Black	23
2CFL878259R0001	Alium	LED	15W	-	1100	Anthracite	17
2CFL878259R0001	Alium Grid	LED	15W	-	1100	Anthracite	17
2CFL878260R0001	Alium	LED	24W	-	1800	Anthracite	17
2CFL878260R0001	Alium Grid	LED	24W	-	1800	Anthracite	17
2CFL878309R0001	Alium Grid	CFL - TC-TEL	1x 32W	GX24q-3	-	Anthracite	17
2CFL878310R0001	Alium	CFL - TC-TEL	1x 32W	GX24q-3	-	Anthracite	17
2CFL878315R0001	Alium Grid	CFL - TC-SEL	2x 9W	2G7	590	Anthracite	17
2CFL878316R0001	Alium	CFL - TC-SEL	2x 9W	2G7	720	Anthracite	17
2CFL878319R0001	Alium Grid	CFL - TC-DEL	2x 13W	G24q-1	-	Anthracite	17
2CFL878320R0001	Alium	CFL - TC-DEL	2x 13W	G24q-1	990	Anthracite	17

Index

Order code classification

Order code	Description	Lamp	Power W	Cap	Luminous flux lm	Finition color	Page
2CFL878321R0001	Alium Grid	CFL - TC-DEL	1x 18W	G24q-2	410	Anthracite	17
2CFL878322R0001	Alium	CFL - TC-DEL	1x 18W	G24q-2	660	Anthracite	17
2CFL878323R0001	Alium Grid	CFL - TC-DEL	1x 26W	G24q-3	610	Anthracite	17
2CFL878324R0001	Alium	CFL - TC-DEL	1x 26W	G24q-3	790	Anthracite	17
2CFL878335R0001	Option	CFL - TC-SEL	2x 9W	2G7	880	White	21
2CFL878336R0001	Option	CFL - TC-SEL	2x 9W	2G7	880	Black	21
2CFL878341R0001	Option	CFL - TC-SEL	1x 9W	2G7	510	White	21
2CFL878342R0001	Option	CFL - TC-SEL	1x 9W	2G7	510	Black	21
2CFL878347R0001	Option	CFL - TC-DEL	2x 13W	G24q-1	1310	White	21
2CFL878348R0001	Option	CFL - TC-DEL	2x 13W	G24q-1	1310	Black	21
2CFL878353R0001	Option	CFL - TC-DEL	1x 18W	G24q-2	1020	White	21
2CFL878354R0001	Option	CFL - TC-DEL	1x 18W	G24q-2	1020	Black	21
2CFL878359R0001	Option	CFL - TC-DEL	1x 26W	G24q-3	1200	White	21
2CFL878360R0001	Option	CFL - TC-DEL	1x 26W	G24q-3	1200	Black	21
2CFL878365R0001	Option	CFL - TC-DEL	1x 13W	G24q-1	770	White	21
2CFL878366R0001	Option	CFL - TC-DEL	1x 13W	G24q-1	770	Black	21
2CFL878600R0001	Lips Rim	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	White	25
2CFL878601R0001	Lips Slotted Visor	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	White	27
2CFL878602R0001	Lips Band	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	White	26
2CFL878603R0001	Lips Rim	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Black	25
2CFL878604R0001	Lips Slotted Visor	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Black	27
2CFL878605R0001	Lips Band	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Black	26
2CFL878606R0001	Lips Rim	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Titanium	25
2CFL878607R0001	Lips Slotted Visor	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Titanium	27
2CFL878608R0001	Lips Band	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Titanium	26
2CFL878609R0001	Lips Rim	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Anthracite	25
2CFL878610R0001	Lips Slotted Visor	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Anthracite	27
2CFL878611R0001	Lips Band	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Anthracite	26
2CFL878840R0001	Alium Grid	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Anthracite	17
2CFL878847R0001	Option	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	White	21
2CFL878848R0001	Option	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Black	21
2CFL878863R0001	Option	CFL - TC-TEL	1x 32W	GX24q-3	1530	White	21
2CFL878864R0001	Option	CFL - TC-TEL	1x 32W	GX24q-3	1530	Black	21
2CFL879012R0001	Dune	E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	White	23
2CFL879017R0001	Dune	E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	Black	23
2CFL879043R0001	Dune	CFL - TC-SEL	1x 9W	2G7	400	White	23
2CFL879044R0001	Dune	CFL - TC-SEL	1x 9W	2G7	400	Black	23
2CFL879045R0001	Dune	CFL - TC-SEL	2x 9W	2G7	700	White	23
2CFL879047R0001	Dune	CFL - TC-DEL	1x 13W	G24q-1	410	White	23
2CFL879048R0001	Dune	CFL - TC-DEL	1x 13W	G24q-1	410	Black	23
2CFL879063R0001	Dune Visor	E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	White	23
2CFL879064R0001	Dune Visor	E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	Black	23
2CFL879205R0001	Havana	E27 (Lamp not included)	1x 75W or 1x 52W HAL	E27	-	White	29
2CFL879207R0001	Havana	E27 (Lamp not included)	1x 75W or 1x 52W HAL	E27	-	Black	29
2CFL879221R0001	Havana	CFL - TC-DEL	1x 13W	G24q-1	470	White	29
2CFL879222R0001	Havana	CFL - TC-DEL	1x 13W	G24q-1	470	Black	29
2CFL879223R0001	Havana	CFL - TC-DEL	1x 18W	G24q-2	620	White	29
2CFL879224R0001	Havana	CFL - TC-DEL	1x 18W	G24q-2	620	Black	29
2CFL879237R0001	Havana	CFL - TC-SEL	1x 9W	2G7	310	White	29
2CFL879238R0001	Havana	CFL - TC-SEL	1x 9W	2G7	310	Black	29
2CFL879239R0001	Havana	CFL - TC-SEL	2x 9W	2G7	610	White	29
2CFL879240R0001	Havana	CFL - TC-SEL	2x 9W	2G7	610	Black	29
2CFL879247R0001	Havana	LED	20W	-	800	White	29
2CFL879248R0001	Havana	LED	20W	-	800	Black	29
2CFL879253R0001	Dune Visor	CFL - TC-SEL	1x 9W	2G7	230	White	23
2CFL879254R0001	Dune Visor	CFL - TC-SEL	1x 9W	2G7	230	Black	23
2CFL879255R0001	Dune Visor	CFL - TC-SEL	2x 9W	2G7	370	White	23
2CFL879256R0001	Dune Visor	CFL - TC-SEL	2x 9W	2G7	370	Black	23
2CFL879257R0001	Dune Visor	CFL - TC-DEL	1x 13W	G24q-1	280	White	23
2CFL879258R0001	Dune Visor	CFL - TC-DEL	1x 13W	G24q-1	280	Black	23
2CFL879259R0001	Dune Casquette	E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	White	23
2CFL879260R0001	Dune Casquette	E27 (Lamp not included)	1x 75W or 1x 46W HAL	E27	-	Black	23
2CFL879267R0001	Dune Casquette	CFL - TC-SEL	1x 9W	2G7	310	White	23
2CFL879268R0001	Dune Casquette	CFL - TC-SEL	1x 9W	2G7	310	Black	23
2CFL879269R0001	Dune Casquette	CFL - TC-SEL	2x 9W	2G7	500	White	23
2CFL879270R0001	Dune Casquette	CFL - TC-SEL	2x 9W	2G7	500	Black	23
2CFL879271R0001	Dune Casquette	CFL - TC-DEL	1x 13W	G24q-1	380	White	23
2CFL879272R0001	Dune Casquette	CFL - TC-DEL	1x 13W	G24q-1	380	Black	23
2CFL879403R0001	Squad	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	White	15
2CFL879404R0001	Squad	E27 (Lamp not included)	1x 100W or 1x 70W HAL	E27	-	Black	15
2CFL879440R0001	Squad	CFL - TC-DEL	2x 18W	G24q-2	1420	White	15
2CFL879441R0001	Squad	CFL - TC-DEL	2x 18W	G24q-2	1420	Black	15
2CFL879444R0001	Squad	CFL - TC-DEL	2x 26W	G24q-3	1910	White	15
2CFL879445R0001	Squad	CFL - TC-DEL	2x 26W	G24q-3	1910	Black	15
2CFL879454R0001	Squad DALI	CFL - TC-DEL	2x 26W	G24q-3	1910	White	15
2CFL879455R0001	Squad DALI	CFL - TC-DEL	2x 26W	G24q-3	1910	Black	15
2CFL879462R0001	Squad	CFL - TC-DEL	1x 18W	G24q-2	660	White	15
2CFL879463R0001	Squad	CFL - TC-DEL	1x 18W	G24q-2	660	Black	15
2CFL879464R0001	Squad	CFL - TC-DEL	1x 26W	G24q-3	990	White	15
2CFL879465R0001	Squad	CFL - TC-DEL	1x 26W	G24q-3	990	Black	15
2CFL879542R0001	Lips Rim	CFL - TC-SEL	1x 9W	2G7	290	White	25
2CFL879543R0001	Lips Rim	CFL - TC-DEL	1x 13W	24Gq-3	430	White	25

Index

Order code classification

Order code	Description	Lamp	Power W	Cap	Luminous flux lm	Finition color	Page
2CFL879544R0001	Lips Rim	CFL - TC-SEL	1x 9W	2G7	290	Black	25
2CFL879547R0001	Lips Rim	CFL - TC-DEL	1x 13W	24Gq-3	430	Black	25
2CFL879548R0001	Lips Rim	CFL - TC-SEL	1x 9W	2G7	290	Titanium	25
2CFL879549R0001	Lips Rim	CFL - TC-DEL	1x 13W	24Gq-3	430	Titanium	25
2CFL879554R0001	Lips Rim	CFL - TC-SEL	1x 9W	2G7	290	Anthracite	25
2CFL879557R0001	Lips Rim	CFL - TC-DEL	1x 13W	24Gq-3	430	Anthracite	25
2CFL879564R0001	Lips Slotted Visor	CFL - TC-SEL	1x 9W	2G7	210	White	27
2CFL879565R0001	Lips Slotted Visor	CFL - TC-DEL	1x 13W	24Gq-3	320	White	27
2CFL879566R0001	Lips Slotted Visor	CFL - TC-SEL	1x 9W	2G7	210	Black	27
2CFL879569R0001	Lips Slotted Visor	CFL - TC-DEL	1x 13W	24Gq-3	320	Black	27
2CFL879570R0001	Lips Slotted Visor	CFL - TC-SEL	1x 9W	2G7	210	Titanium	27
2CFL879571R0001	Lips Slotted Visor	CFL - TC-DEL	1x 13W	24Gq-3	320	Titanium	27
2CFL879572R0001	Lips Slotted Visor	CFL - TC-SEL	1x 9W	2G7	210	Anthracite	27
2CFL879573R0001	Lips Slotted Visor	CFL - TC-DEL	1x 13W	24Gq-3	320	Anthracite	27
2CFL879578R0001	Lips Band	CFL - TC-SEL	1x 9W	2G7	220	White	26
2CFL879579R0001	Lips Band	CFL - TC-DEL	1x 13W	24Gq-3	330	White	26
2CFL879579R0001	Lips Band	CFL - TC-DEL	1x 26W	24Gq-3	670	Anthracite	26
2CFL879580R0001	Lips Band	CFL - TC-SEL	1x 9W	2G7	220	Black	26
2CFL879581R0001	Lips Band	CFL - TC-DEL	1x 13W	24Gq-3	330	Black	26
2CFL879582R0001	Lips Band	CFL - TC-SEL	1x 9W	2G7	220	Titanium	26
2CFL879583R0001	Lips Band	CFL - TC-DEL	1x 13W	24Gq-3	330	Titanium	26
2CFL879584R0001	Lips Band	CFL - TC-SEL	1x 9W	2G7	220	Anthracite	26
2CFL879585R0001	Lips Band	CFL - TC-DEL	1x 13W	24Gq-3	330	Anthracite	26
2CFL879603R0001	Lips Rim	CFL - TC-DEL	1x 18W	24Gq-2	580	White	25
2CFL879604R0001	Lips Rim	CFL - TC-DEL	1x 26W	24Gq-3	860	White	25
2CFL879608R0001	Lips Rim	CFL - TC-DEL	1x 18W	24Gq-2	580	Black	25
2CFL879609R0001	Lips Rim	CFL - TC-DEL	1x 26W	24Gq-3	860	Black	25
2CFL879613R0001	Lips Rim	CFL - TC-DEL	1x 18W	24Gq-2	580	Titanium	25
2CFL879614R0001	Lips Rim	CFL - TC-DEL	1x 26W	24Gq-3	860	Titanium	25
2CFL879618R0001	Lips Rim	CFL - TC-DEL	1x 18W	24Gq-2	580	Anthracite	25
2CFL879619R0001	Lips Rim	CFL - TC-DEL	1x 26W	24Gq-3	860	Anthracite	25
2CFL879633R0001	Lips Slotted Visor	CFL - TC-DEL	1x 18W	24Gq-2	420	White	27
2CFL879634R0001	Lips Slotted Visor	CFL - TC-DEL	1x 26W	24Gq-3	630	White	27
2CFL879638R0001	Lips Slotted Visor	CFL - TC-DEL	1x 18W	24Gq-2	420	Black	27
2CFL879639R0001	Lips Slotted Visor	CFL - TC-DEL	1x 26W	24Gq-3	630	Black	27
2CFL879643R0001	Lips Slotted Visor	CFL - TC-DEL	1x 18W	24Gq-2	420	Titanium	27
2CFL879644R0001	Lips Slotted Visor	CFL - TC-DEL	1x 26W	24Gq-3	630	Titanium	27
2CFL879648R0001	Lips Slotted Visor	CFL - TC-DEL	1x 18W	24Gq-2	420	Anthracite	27
2CFL879649R0001	Lips Slotted Visor	CFL - TC-DEL	1x 26W	24Gq-3	630	Anthracite	27
2CFL879663R0001	Lips Band	CFL - TC-DEL	1x 18W	24Gq-2	440	White	26
2CFL879664R0001	Lips Band	CFL - TC-DEL	1x 26W	24Gq-3	670	White	26
2CFL879668R0001	Lips Band	CFL - TC-DEL	1x 18W	24Gq-2	440	Black	26
2CFL879669R0001	Lips Band	CFL - TC-DEL	1x 26W	24Gq-3	670	Black	26
2CFL879673R0001	Lips Band	CFL - TC-DEL	1x 18W	24Gq-2	440	Titanium	26
2CFL879674R0001	Lips Band	CFL - TC-DEL	1x 26W	24Gq-3	670	Titanium	26
2CFL879678R0001	Lips Band	CFL - TC-DEL	1x 18W	24Gq-2	440	Anthracite	26
Available 2015/04	Option	LED	15W	-	1100	White	21
Available 2015/04	Option	LED	15W	-	1100	Black	21
Available 2015/04	Option	LED	24W	-	1800	White	21
Available 2015/04	Option	LED	24W	-	1800	Black	21
Available 2015/04	Sextan	LED	15W	-	1080	White	9
Available 2015/04	Sextan	LED	15W	-	1080	Grey	9
Available 2015/04	Sextan	LED	24W	-	1800	White	9
Available 2015/04	Sextan	LED	24W	-	1800	Grey	9
Available 2015/04	Sextan Premium	LED	15W	-	-	Anthracite	10
Available 2015/04	Sextan Premium	LED	15W	-	-	Alu-Silver	10
Available 2015/04	Sextan Premium	LED	15W	-	-	White	10
Available 2015/04	Sextan Premium	LED	15W	-	-	Stainless steel	10
Available 2015/04	Sextan Premium	LED	24W	-	-	Anthracite	10
Available 2015/04	Sextan Premium	LED	24W	-	-	Alu-Silver	10
Available 2015/04	Sextan Premium	LED	24W	-	-	White	10
Available 2015/04	Sextan Premium	LED	24W	-	-	Stainless steel	10
Available 2015/10	Axiome T1	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Black	31
Available 2015/10	Axiome T1	CFL - TC-DEL	1x 18W	G24q-2	490	Black	31
Available 2015/10	Axiome T1	CFL - TC-DEL	1x 26W	G24q-3	810	Black	31
Available 2015/10	Axiome T1	LED	12W	-	900	Black	31
Available 2015/10	Axiome T2	E27 (Lamp not included)	1x 55W or 1x 42W HAL	E27	-	Black	31
Available 2015/10	Axiome T2	CFL - TC-SEL	2x 18W	G24q-2	1150	Black	31
Available 2015/10	Axiome T2	CFL - TC-SEL	2x 26W	G24q-3	1330	Black	31
Available 2015/10	Axiome T2	LED	11W	-	900	Black	31
Available 2015/10	Axiome T2	LED	15W	-	1200	Black	31
Available 2015/10	Axiome T2	LED	20W	-	1500	Black	31

Contact us

Germany

Busch-Jaeger Elektro GmbH

Freisenbergstraße 2
58513 Lüdenscheid / Germany
Tel: 02351 956-1600
Fax: 02351 956-1700
E-mail: info.bje@de.abb.com
www.BUSCH-JAEGER.de

ABB Stotz-Kontakt / Striebel & John

Vertriebsgesellschaft mbH
Eppelheimer Strasse 82
69123 Heidelberg / Germany
Tel: +49 6221 701 1117
Fax: +49 6221 701 1760

Netherlands

Thomas & Betts Netherlands BV VanLien Emergency Lighting

Visiting address:
Oosteinde 3
2991 LG Barendrecht / Netherlands
Tel: +31 (0)180 641 888
Fax Sales: +31 (0)180 641 889
Fax Purchase: +31 (0)180 641 887
E-mail: info@vanlien.nl
www.vanlien.nl

Austria

ABB AG Low Voltage Products Zentrale

Clemens-Holzmeister-Straße 4
1109 Wien, Österreich / Austria
Tel: +43 (0)1 60109 6203
Fax: +43 (0)1 60109 8600
www.abb.at/lowvoltage

Kunden Center

Lagerhausstraße 30
5071 Wals bei Salzburg / Austria
Tel: +43 (0)662 850150 6530
Fax: +43 (0)662 850150 6548
E-Mail: abb.lpvs@at.abb.com

Dubai

Thomas&Betts

Office 724 – Building 6WA West Wing
Dubai Airport Free Zone
Dubai
UAE
www.tnb.com

Spain

Asea Brown Boveri, S.A. Fábrica Niessen

Pol. Ind. de Aranguren, 6
20180 OIARTZUN / Spain
Tel: 943 260 101
Fax: 943 260 240
www.abb.es/niessen

France

L'Ébénoïd

817, rue Nicéphore Niépce
Bâtiment B
Parc des Lumières
ZAC de la Fouillouse
F-69808 Saint Priest Cedex / France
Tel: +33 (0)4 72 11 39 90
Fax: +33 (0)4 72 11 39 99
www.lebenoid.fr

Note

We reserve the right to make technical changes or modify the contents of this document without prior notice.
ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright© 2015 ABB - All rights reserved