



EC DECLARATION OF CONFORMITY

(supplier's name) We ABB SACE S.p.A

(address) VIALE VICENZA, 61

36063 - MAROSTICA (VI)

declare under our sole responsibility that the product : _____

SENDZIMIR TRUNKINGS H50

(name,type or model,lot,batch or serial number,possibly sources and numbers of items)

ARTICLES : IN ATTACHED

to which this declaration relates is in conformity with the following standard(s) or other
normative/documents CEI 23-31

RELEASE FROM IMQ INSTITUTE BY D.A.T. N° E7253 E N°E7254

(title and/or number and date of issue of the standard(s) or other normative document(s))

following the provisions of the Directive(s) 73/23 CEE MODIFIED BY 93/68 CEE

MAROSTICA, 11/03/2002

(Place and date of issue)

02

(last two digits of the year in which the mark was affixed)

ABB SACE S.p.A
TECHNICAL MANAGER
ENZO RIZZI

(seal, name and signature of authorized person)

Mod. 379 - 12/94 - 900

1SLT000014D00

Industrial metal trunkings

Sendzimir trunkings H 50



Article	Trunking base (mm)	Length (mm)	Colour	Weight (kg/m)	Unit/pack-metres
---------	--------------------	-------------	--------	---------------	------------------

Punched cable trunking IP20*

06 312	100	3000	Galvanised	1.32	36
06 313	150	3000	Galvanised	1.61	36
06 314	200	3000	Galvanised	2.37	18
06 315	300	3000	Galvanised	3.12	18
06 316	400	3000	Galvanised	4.64	18
06 317	500	3000	Galvanised	5.53	18

Cable trunking IP40*

06 332	100	3000	Galvanised	1.39	36
06 333	150	3000	Galvanised	1.70	36
06 334	200	3000	Galvanised	2.50	18
06 335	300	3000	Galvanised	3.29	18
06 336	400	3000	Galvanised	4.89	18
06 337	500	3000	Galvanised	5.82	18

Cover for cable trunking IP20 and IP40

07 242	100	3000	Galvanised	0.69	48
07 243	150	3000	Galvanised	0.92	48
07 244	200	3000	Galvanised	1.16	36
07 245	300	3000	Galvanised	2.16	36
07 246	400	3000	Galvanised	2.79	30
07 247	500	3000	Galvanised	3.48	24

* Degree of protection refers to feeders with mounted cover

Article	For trunking base (mm)	Colour	Unit/pack-pieces
---------	------------------------	--------	------------------

90° flat corner

Base			
06 352	100	Galvanised	8
06 353	150	Galvanised	8
06 354	200	Galvanised	4
06 355	300	Galvanised	4
06 356	400	Galvanised	2
06 357	500	Galvanised	2
Cover			
06 362	100	Galvanised	8
06 363	150	Galvanised	8
06 364	200	Galvanised	4
06 365	300	Galvanised	4
06 366	400	Galvanised	2
06 367	500	Galvanised	2

Except in specifically indicated cases, the accessories cover must be ordered separately.

Industrial metal trunkings

Sendzimir trunkings H 50



Article	For trunking base (mm)	Colour	Unit/pack-pieces
---------	------------------------	--------	------------------

45° flat corner

Base			
06 372	100	Galvanised	8
06 373	150	Galvanised	4
06 374	200	Galvanised	4
06 375	300	Galvanised	4
06 376	400	Galvanised	2
06 377	500	Galvanised	2
Cover			
06 382	100	Galvanised	8
06 383	150	Galvanised	4
06 384	200	Galvanised	4
06 385	300	Galvanised	4
06 386	400	Galvanised	2
06 387	500	Galvanised	2

Flat tee

Base			
06 392	100	Galvanised	4
06 393	150	Galvanised	4
06 394	200	Galvanised	4
06 395	300	Galvanised	2
06 396	400	Galvanised	2
06 397	500	Galvanised	2
Cover			
06 402	100	Galvanised	4
06 403	150	Galvanised	4
06 404	200	Galvanised	4
06 405	300	Galvanised	2
06 406	400	Galvanised	2
06 407	500	Galvanised	2

Except in specifically indicated cases, the accessories cover must be ordered separately.

Industrial metal trunkings

Sendzimir trunkings H 50



Article	For trunking base (mm)	Colour	Unit/pack-pieces
---------	------------------------	--------	------------------

Flat cross

Base			
06 412	100	Galvanised	4
06 413	150	Galvanised	4
06 414	200	Galvanised	2
06 415	300	Galvanised	2
06 416	400	Galvanised	2
06 417	500	Galvanised	2

Cover			
06 422	100	Galvanised	4
06 423	150	Galvanised	4
06 424	200	Galvanised	2
06 425	300	Galvanised	2
06 426	400	Galvanised	2
06 427	500	Galvanised	2

90° vertical inside riser

Base			
06 462	100	Galvanised	6
06 463	150	Galvanised	4
06 464	200	Galvanised	4
06 465	300	Galvanised	2
06 466	400	Galvanised	2
06 467	500	Galvanised	2

Cover			
06 472	100	Galvanised	6
06 473	150	Galvanised	4
06 474	200	Galvanised	4
06 475	300	Galvanised	2
06 476	400	Galvanised	2
06 477	500	Galvanised	2

Except in specifically indicated cases, the accessories cover must be ordered separately.

Industrial metal trunkings

Sendzimir trunkings H 50



FLCM8091-92



FLCM8093-94

Article	For trunking base (mm)	Colour	Unit/pack-pieces
---------	------------------------	--------	------------------

45° vertical inside riser

Base			
06 482	100	Galvanised	6
06 483	150	Galvanised	4
06 484	200	Galvanised	3
06 485	300	Galvanised	2
06 486	400	Galvanised	2
06 487	500	Galvanised	2
Cover			
06 492	100	Galvanised	6
06 493	150	Galvanised	4
06 494	200	Galvanised	3
06 495	300	Galvanised	2
06 496	400	Galvanised	2
06 497	500	Galvanised	2


90° vertical outside riser

Base			
06 502	100	Galvanised	6
06 503	150	Galvanised	4
06 504	200	Galvanised	4
06 505	300	Galvanised	2
06 506	400	Galvanised	2
06 507	500	Galvanised	2
Cover			
06 512	100	Galvanised	6
06 513	150	Galvanised	4
06 514	200	Galvanised	4
06 515	300	Galvanised	2
06 516	400	Galvanised	2
06 517	500	Galvanised	2

Except in specifically indicated cases, the accessories cover must be ordered separately.

Industrial metal trunkings

Sendzimir trunkings H 50



Article	For trunking base (mm)	Colour	Unit/pack-pieces
---------	------------------------	--------	------------------

45° vertical outside riser

Base			
06 522	100	Galvanised	6
06 523	150	Galvanised	4
06 524	200	Galvanised	3
06 525	300	Galvanised	2
06 526	400	Galvanised	2
06 527	500	Galvanised	2

Cover			
06 532	100	Galvanised	6
06 533	150	Galvanised	4
06 534	200	Galvanised	3
06 535	300	Galvanised	2
06 536	400	Galvanised	2
06 537	500	Galvanised	2

End cap

06 542	100	Galvanised	4
06 543	150	Galvanised	4
06 544	200	Galvanised	4
06 545	300	Galvanised	4
06 546	400	Galvanised	4
06 547	500	Galvanised	4

Left 90° vertical outside riser

Complete with cover.			
06 562	100	Galvanised	2
06 563	150	Galvanised	2
06 564	200	Galvanised	2
06 565	300	Galvanised	2
06 566	400	Galvanised	1
06 567	500	Galvanised	1

Except in specifically indicated cases, the accessories cover must be ordered separately.

Industrial metal trunkings

Sendzimir trunkings H 50



Article	For trunking base (mm)	Colour	Unit/pack-pieces
---------	------------------------	--------	------------------

Right 90° vertical outside riser

Complete with base.

06 572	100	Galvanised	2
06 573	150	Galvanised	2
06 574	200	Galvanised	2
06 575	300	Galvanised	2
06 576	400	Galvanised	1
06 577	500	Galvanised	1

Vertical tee corner with level gradient

Complete with base.

06 582	100	Galvanised	3
06 583	150	Galvanised	2
06 584	200	Galvanised	2
06 585	300	Galvanised	2
06 586	400	Galvanised	1
06 587	500	Galvanised	1

Industrial metal trunkings

Sendzimir trunkings H 50



Article	Reduction from (mm)	Colour	Unit/pack-pieces
---------	---------------------	--------	------------------

Left reducer

06 602	50	Galvanised	4
06 603	100	Galvanised	4
06 604	150	Galvanised	4
06 605	200	Galvanised	4

Right reducer

06 612	50	Galvanised	4
06 613	100	Galvanised	4
06 614	150	Galvanised	4
06 615	200	Galvanised	4

Article	For trunking base (mm)	Colour	Unit/pack-pieces
---------	------------------------	--------	------------------

Integral mechanical joint

Guarantees electric continuity. Complete with screws and nuts.

06 632	100	Galvanised	48
06 633	150	Galvanised	36
06 634	200	Galvanised	24
06 635	300	Galvanised	24
06 636	400	Galvanised	8
06 637	500	Galvanised	8

Industrial metal trunkings

Sendzimir trunkings H 50



Article	Length (mm)	Colour	Unit/pack-pieces
Mechanical joint for trunkings			
Guarantees electric continuity. Every joint supplied with 2 plates, screws and nuts.			
06 642	180		30

Mechanical joint for accessories			
Guarantees electric continuity. Every joint supplied with 2 plates, screws and nuts.			
06 643	80		30


Adjustable vertical joint			
Guarantees electric continuity. Every joint supplied with 2 plates, screws and nuts.			
06 644			10

Flange for fastening to switchboard			
Supplied with 2 plates, screws and nuts.			
06 646		Galvanised	25

Article	Length (mm)	Colour	Unit/pack-metres
Galvanised divider profile			
06 652	2000	Galvanised	20

Industrial metal trunkings

Sendzimir trunkings H 50



Article	Description	Unit/pack-pieces
Screw and nut		
07 848	Round-headed M6x10 screw with nut	100
Earth staple		
07 850	Staple complete with 2 M6x10 screws	50

Overall dimensions pages 11/36 - 11/53