



Blocco porta della cella ad interruttore chiuso e impedimento alla chiusura
Lock for compartment door with circuit-breaker closed and prevention of closing
Verrriegelung der Schaltfeldtür bei eingeschaltetem Leistungsschalter und Einschaltsperr
Verrouillage porte du compartiment avec disjoncteur fermé et empêchement à la fermeture
Bloqueo de la puerta de la celda con interruptor cerrado e impedimento al cierre




Indicazioni di foratura per portella
 Drilling information for door
 Angabe der Bohrungen für die Schaltfeldtür
 Indications de perçage pour porte
 Indicaciones de taladrado para puerta



	A (mm)
E1 III-IV	180
E2 III-IV	180
E3 III-IV	234
E4 III	270
E4 IV	360
E6 III	360
E6 IV	486


A

Distanza minima tra interruttori e parete quadro
 Minimum distance between circuit-breakers and switchboard wall
 Mindestabstand zwischen Leistungsschaltern und Schaltanlagenwand
 Distance minimale entre disjoncteurs et paroi tableau
 Distancia mínima entre interruptores y pared del cuadro




B

APERTO
 OPEN
 AUS-STELLUNG
 OUVERT
 ABIERTO




BIANCO
 WHITE
 WEISS
 BLANC
 BLANCO

C




D




E


F




G




H




I




L




M




N




O




P



Q



R



S

