


NOTES:

1. **WARNING:** This drawing does not illustrate completely the installation methods required for hazardous locations. Prior to any installation in a Classified Hazardous Location, verify installation methods by the Control Drawing referenced on the product's name tag and national and local codes.
2. Up to 32 devices may be connected on the RS-485 buss, for up to a total combined distance of 4000 feet.
3. Units must be daisy-chained; No Star Configurations.



REF: N/A

| | | | | | | | |
|--|-----------|--------|----------|--|---------|-----|--------|
| | TOTALFLOW | ACTION | DOC TYPE | TITLE | DWG NO. | REV | SHEET |
| | Products | L21012 | UD | NGC PORT1 RS-485 TO B&B CONVERTER RS-232 WIRING DIAGRAM | 2103670 | AA | 1 OF 1 |