




SACE Tmax XT

Parte fissa di interruttore rimovibile XT1
Fixed part for plug-in circuit breakers XT1
Festteil für Leistungsschalter in ausfahrbarer Ausführung XT1
Partie fixe pour disjoncteur débrochable XT1
Parte fija para interruptor extraíble XT1
插入式断路器固定部分 XT1




D

XT1/III-IV




E


XT1/III-IV




F

XT1/III-IV/Example for adapters






J




K

XT1-P/III-IV/Fc Cu/MC




L

XT1-P/III-IV/Fc-CuAl



M

XT1-P/III-IV/Fc-CuAl EXT



P-EF 6 Nm

P-ES 6 Nm

P-FC Cu Al 5 Nm, 7 Nm

P-MC 6 Nm, 7 Nm

P-EXT FC Cu Al 13,5 Nm, 6 Nm

P-FC Cu 7 Nm

P-HR/VR 6 Nm

	FC Cu		Mc		FC CuAl			
	MAX	MIN	MAX	MIN	INTERNAL		EXTERNAL	
					MAX	MIN	MAX	MIN
Stranded	70 mm ²	2,5 mm ²	35 mm ²	2,5 mm ²	50 mm ²	1,5 mm ²	95 mm ²	35 mm ²
Flexible	50 mm ²	2,5 mm ²	25 mm ²	2,5 mm ²	50 mm ²	1,5 mm ²	X	

	A
MCCB	7.5
MCP	6

		A		B	C	D	E
		50mm	70mm				
XT1 WITH FLANGE CON MOSTRINA	III	124	144	55	81	21	40,5
	IV	124	144	55	106	21	40,5
	OPTIONAL FLANGE III-IV	129	149	73	57	30	28,5

		A		B	C	D	E
		50mm	70mm				
XT1 WITHOUT FLANGE SENZA MOSTRINA	III-IV	129	149	43	47	15	23,5
	III	121	141	47	73	17	36,5
	IV	121	141	47	98	17	36,5