



M2AA 090
(* Except 090_LD)

S = $\begin{cases} \text{Ø10} - \text{Special IM 3001/*11} \\ \text{M8} - \text{Special IM 3601/*11} \end{cases}$

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador

VC223: Flange ring FT 115 / Aro brida FT 115 // VC224: Flange ring FF 115 / Aro brida FF 115

Motor Dimension Print	Motor Type : M2AA 090 (*)	Document Nº : 3GZE 500 092-931.005
Description : Motor flange mounted special (2-pieces) IM3001/*11 or IM3601/*11 Motor con brida (2 piezas) IM3001/*11 o IM3601/*11		
Unit : Discret Automation & Motion - Fábrica Motores Date : 2012-12-03	Issued by : ERM/ A. Caubera Approved by : ERM/ G. Blanes	Replaces : Replaced by :
Asea Brown Boveri, S.A.	Customer Reference :	ABB