Relion® 650 series

Line distance protection REL650
Commissioning Manual

Power and productivity
for a better world™

Document ID: 1MRK 506 331-UEN
Issued: June 2012
Revision: -
Product version: 1.2

© Copyright 2012 ABB. All rights reserved

Copyright

This document and parts thereof must not be reproduced or copied without written permission from ABB, and the contents thereof must not be imparted to a third party, nor used for any unauthorized purpose.

The software and hardware described in this document is furnished under a license and may be used or disclosed only in accordance with the terms of such license.

Trademarks

ABB and Relion are registered trademarks of the ABB Group. All other brand or product names mentioned in this document may be trademarks or registered trademarks of their respective holders.

Warranty

Please inquire about the terms of warranty from your nearest ABB representative.

ABB AB

Substation Automation Products

SE-721 59 Västerås

Sweden

Telephone: +46 (0) 21 32 50 00

Facsimile: +46 (0) 21 14 69 18

http://www.abb.com/substationautomation

Conformity

This product complies with the directive of the Council of the European Communities on the approximation of the laws of the Member States relating to electromagnetic compatibility (EMC Directive 2004/108/EC) and concerning electrical equipment for use within specified voltage limits (Low-voltage directive 2006/95/EC). This conformity is the result of tests conducted by ABB in accordance with the product standards EN 50263 and EN 60255-26 for the EMC directive, and with the product standards EN 60255-1 and EN 60255-27 for the low voltage directive. The product is designed in accordance with the international standards of the IEC 60255 series.

Disclaimer

The data, examples and diagrams in this manual are included solely for the concept or product description and are not to be deemed as a statement of guaranteed properties. All persons responsible for applying the equipment addressed in this manual must satisfy themselves that each intended application is suitable and acceptable, including that any applicable safety or other operational requirements are complied with. In particular, any risks in applications where a system failure and/or product failure would create a risk for harm to property or persons (including but not limited to personal injuries or death) shall be the sole responsibility of the person or entity applying the equipment, and those so responsible are hereby requested to ensure that all measures are taken to exclude or mitigate such risks.

This document has been carefully checked by ABB but deviations cannot be completely ruled out. In case any errors are detected, the reader is kindly requested to notify the manufacturer. Other than under explicit contractual commitments, in no event shall ABB be responsible or liable for any loss or damage resulting from the use of this manual or the application of the equipment.

Safety information

Dangerous voltages can occur on the connectors, even though the auxiliary voltage has been disconnected.

Non-observance can result in death, personal injury or substantial property damage.

Only a competent electrician is allowed to carry out the electrical installation.

National and local electrical safety regulations must always be followed.

The frame of the IED has to be carefully earthed.

Whenever changes are made in the IED, measures should be taken to avoid inadvertent tripping.

The IED contains components which are sensitive to electrostatic discharge. Unnecessary touching of electronic components must therefore be avoided.

Table of contents

Section 1 Introduction....9
This manual....9
Intended audience....9
Product documentation....10
Product documentation set....10
Document revision history....11
Related documents....11
Symbols and conventions....12
Symbols....12
Document conventions....13

Section 2 Available functions....15
Main protection functions....15
Back-up protection functions....16
Control and monitoring functions....17
Communication....20
Basic IED functions....21

Section 3 Starting up....23
Factory and site acceptance testing....23
Commissioning checklist....23
Checking the power supply....24
Energizing the IED....24
Checking the IED operation....24
IED start-up sequence....24
Setting up communication between PCM600 and the IED....25
Writing an application configuration to the IED....29
Checking CT circuits....30
Checking VT circuits....31
Checking the RTXP test switch....31
Checking binary input and output circuits....32
Binary input circuits....32
Binary output circuits....32
Checking optical connections....32

Section 4 Establishing connection and verifying the IEC 61850 station communication....33
Setting the station communication....33
Verifying the communication....33

Table of contents

Section 5 Testing IED operation....35
Preparing the IED to verify settings....35
Activating test mode....37
Preparing the connection to the test equipment....37
Connecting the test equipment to the IED....38
Releasing the function to be tested....39
Verifying analog primary and secondary measurement....39
Testing protection functionality....41

Section 6 Testing functionality....43
Testing disturbance report....43
Introduction....43
Disturbance report settings....43
Identifying the function to test in the technical reference manual....43
Testing impedance protection functions....44
Five zone distance protection, quadrilateral and mho characteristic ZQMPDIS....44
Quadrilateral characteristics....44
Mho characteristics....47
Measuring the operating limit of set values with shaped load encroachment characteristics....48
Measuring the operate time of distance protection zones....49
Completing the test....49
Phase selection with load encroachment, quadrilateral characteristic FDPSPDIS....49
Measuring the operate limit of set values....52
Completing the test....52
Faulty phase identification with load encroachment FMPSPDIS....52
Phase preference logic PPLPHIZ....53
Completing the test....54
Power swing detection ZMRPSB....54
Verifying the settings....55
Testing the power swing detection function ZMRPSB....56
Testing the *tR1* timer....56
Completing the test....57
Automatic switch onto fault logic, voltage and current based ZCVPSOF....57
External activation of ZCVPSOF....57
Automatic initiation of ZCVPSOF....57
Completing the test....58
Testing current protection functions....58

Instantaneous phase overcurrent protection 3-phase output PHPIOC 58
Measuring the operate limit of set values....58
Completing the test....59
Instantaneous phase overcurrent protection phase segregated output SPTPIOC 59
Completing the test....59
Four step phase overcurrent protection 3-phase output OC4PTOC....60
Verifying the settings....60
Completing the test....61
Four step phase overcurrent protection phase segregated output OC4SPTOC 61
Verifying the settings....61
Completing the test....62
Instantaneous residual overcurrent protection EFPIOC 63
Measuring the operate limit of set values....63
Completing the test....63
Four step residual overcurrent protection, zero or negative sequence direction EF4PTOC 63
Four step directional residual overcurrent protection 64
Four step non-directional residual overcurrent protection....64
Completing the test....64
Sensitive directional residual overcurrent and power protection SDEPSDE 65
Measuring the operate and time limit for set values....65
Completing the test....70
Thermal overload protection, one time constant, Celsius/ Fahrenheit LCPTTR/LFPTTR....70
Testing the protection without external temperature compensation (NonComp)....70
Completing the test....71
Breaker failure protection, phase segregated activation and output CCRBRF....71
Checking the phase current operate value, *IP>*....72
Checking the residual (earth fault) current operate value *IN>* set below *IP>*....72
Checking the re-trip and back-up times....72
Verifying the re-trip mode....73
Verifying the back-up trip mode....73
Verifying the case *RetripMode* = *Contact*....74
Verifying the function mode *Current&Contact*....75
Completing the test....76

Table of contents

Breaker failure protection, phase segregated activation and output CSPRBRF....76
Checking the phase current operate value, IP>....76
Checking the residual (EF) current operate value *IN>* set below IP>....77
Checking the re-trip and back-up times....77
Verifying the *RetripMode*....77
Verifying the case *RetripMode* = *No CB Pos Check*....78
Verifying the function mode *Current&Contact*....78
Checking the case with fault current below set value *I>BlkCont*....79
Checking the phase current operate value, *IP>*....79
Completing the test....80
Stub protection STBPTOC....80
Measuring the operate limit of set values....80
Completing the test....81
Pole discordance protection CCRPLD....81
Verifying the settings....81
Completing the test....81
Broken conductor check BRCPTOC....82
Measuring the operate and time limit of set values....82
Completing the test....82
Directional underpower protection GUPPDUP....83
Verifying the settings....83
Completing the test....84
Directional overpower protection GOPPDOP....85
Verifying the settings....85
Completing the test....86
Testing voltage protection functions....86
Two step undervoltage protection UV2PTUV....86
Verifying the setting....86
Completing the test....87
Two step overvoltage protection OV2PTOV....87
Verifying the settings....87
Completing the test....87
Two step residual overvoltage protection ROV2PTOV....87
Verifying the settings....88
Completing the test....88
Loss of voltage check LOVPTUV....88
Measuring the operate limit of set values....88
Completing the test....89
Testing frequency protection functions....89
Underfrequency protection SAPTUF....89
Verifying the settings....89

Completing the test....90
Overfrequency protection SAPTOF 90
Verifying the settings....91
Completing the test....91
Rate-of-change frequency protection SAPFRC 92
Verifying the settings....92
Completing the test....92
Testing secondary system supervision functions....93
Current circuit supervision CCSRDIF 93
Verifying the settings....93
Completing the test....93
Fuse failure supervision SDDRFUF....93
Checking that the binary inputs and outputs operate as expected 94
Measuring the operate value for the negative sequence function 94
Measuring the operate value for the zero-sequence function 95
Checking the operation of the du/dt and di/dt based function 95
Completing the test....96
Testing control functions....97
Synchrocheck, energizing check, and synchronizing SESRSYN....97
Testing the synchronizing function....99
Testing the synchrocheck check....100
Testing the energizing check....103
Testing the voltage selection....105
Completing the test....105
Autorecloser for 3-phase operation SMBRREC 105
Preparation of the verification 107
Switching the autorecloser for 3-phase operation function to *On* and *Off*....108
Verifying the autorecloser for 3-phase operation function SMBRREC 108
Checking the reclosing conditions 109
Completing the test....110
Autorecloser for 1/3-phase operation STBRREC 110
Preparation of the verification....112
Switching the auto-reclosing function *On* and *Off*....113
Verifying the auto-reclosing function....113
Checking the reclosing conditions....114
Checking the influence of the INHIBIT signal....114
Check closing onto a fault....114

Checking the influence of CB not ready for reclosing.....114
Checking the influence of synchrocheck (at three-phase reclosing).....115
Restoring equipment.....115
Completing the test.....115
Testing scheme communication functions.....115
Scheme communication logic with delta based blocking scheme signal transmit ZCPSCH 115
Testing permissive underreaching.....116
Testing permissive overreaching.....116
Testing blocking scheme.....117
Testing delta blocking scheme.....117
Checking of unblocking logic.....118
Completing the test.....118
Current reversal and WEI logic for distance protection 3-phase ZCRWPSCH 118
Current reversal logic.....119
Weak-end infeed logic at permissive schemes.....119
Testing conditions.....119
Completing the test.....120
Current reversal and WEI logic for distance protection, phase segregated ZCWSPSCH 120
Current reversal logic.....120
Weak-end infeed logic at permissive schemes.....121
Testing conditions.....121
Completing the test.....122
Local acceleration logic ZCLCPLAL.....122
Verifying the settings.....122
Completing the test.....123
Scheme communication logic for residual overcurrent protection ECPSCH 123
Testing the directional comparison logic function.....123
Completing the test.....125
Current reversal and weak-end infeed logic for residual overcurrent protection ECRWPSCH 125
Testing the current reversal logic.....125
Testing the weak-end infeed logic.....126
Completing the test.....127
Testing logic functions.....128
Tripping logic, common 3-phase output SMPPTRC 128
Three-phase operating mode.....128
Circuit breaker lockout.....128
Completing the test.....129
Tripping logic phase segregated output SPTPTRC 129

1ph/3ph operating mode....129
Circuit breaker lockout....130
Completing the test....131
Testing monitoring functions....131
Event counter CNTGGIO....131
Fault locator LMBRFLO....131
Measuring the operate limit....132
Completing the test....133
Testing metering functions....133
Pulse counter PCGGIO....133
Exit test mode....133

Section 7 Commissioning and maintenance of the fault clearing system....135
Commissioning and maintenance of the fault clearing system....135
Commissioning tests....135
Periodic maintenance tests....135
Visual inspection....136
Maintenance tests....136

Section 8 Troubleshooting 141
Fault tracing....141
Identifying hardware errors....141
Identifying runtime errors....141
Identifying communication errors....141
Checking the communication link operation....142
Checking the time synchronization....142
Running the display test....142
Indication messages....143
Internal faults....143
Warnings....144
Additional indications....144
Correction procedures....144
Changing and setting the password....144
Identifying IED application problems....145
Inspecting the wiring....145

Section 9 Glossary....149

Section 1 Introduction

1.1 This manual

The commissioning manual contains instructions on how to commission the IED. The manual can also be used by system engineers and maintenance personnel for assistance during the testing phase. The manual provides procedures for checking of external circuitry and energizing the IED, parameter setting and configuration as well as verifying settings by secondary injection. The manual describes the process of testing an IED in a substation which is not in service. The chapters are organized in chronological order in which the IED should be commissioned.

1.2 Intended audience

This manual addresses the personnel responsible for commissioning, maintenance and taking the IED in and out of normal service.

The commissioning personnel must have a basic knowledge of handling electronic equipment. The commissioning and maintenance personnel must be well experienced in using protection equipment, test equipment, protection functions and the configured functional logics in the IED.

1.3 Product documentation

1.3.1 Product documentation set



Figure 1: The intended use of manuals in different lifecycles

The engineering manual contains instructions on how to engineer the IEDs using the different tools in PCM600. The manual provides instructions on how to set up a PCM600 project and insert IEDs to the project structure. The manual also recommends a sequence for engineering of protection and control functions, LHMI functions as well as communication engineering for IEC 60870-5-103, IEC 61850 and DNP3.

The installation manual contains instructions on how to install the IED. The manual provides procedures for mechanical and electrical installation. The chapters are organized in chronological order in which the IED should be installed.

The commissioning manual contains instructions on how to commission the IED. The manual can also be used by system engineers and maintenance personnel for assistance during the testing phase. The manual provides procedures for checking of external circuitry and energizing the IED, parameter setting and configuration as

well as verifying settings by secondary injection. The manual describes the process of testing an IED in a substation which is not in service. The chapters are organized in chronological order in which the IED should be commissioned.

The operation manual contains instructions on how to operate the IED once it has been commissioned. The manual provides instructions for monitoring, controlling and setting the IED. The manual also describes how to identify disturbances and how to view calculated and measured power grid data to determine the cause of a fault.

The service manual contains instructions on how to service and maintain the IED. The manual also provides procedures for de-energizing, de-commissioning and disposal of the IED.

The application manual contains application descriptions and setting guidelines sorted per function. The manual can be used to find out when and for what purpose a typical protection function can be used. The manual can also be used when calculating settings.

The technical manual contains application and functionality descriptions and lists function blocks, logic diagrams, input and output signals, setting parameters and technical data sorted per function. The manual can be used as a technical reference during the engineering phase, installation and commissioning phase, and during normal service.

The communication protocol manual describes a communication protocol supported by the IED. The manual concentrates on vendor-specific implementations.

The point list manual describes the outlook and properties of the data points specific to the IED. The manual should be used in conjunction with the corresponding communication protocol manual.

1.3.2 Document revision history

Document revision/date	History
-/June 2012	First release

1.3.3 Related documents

Documents related to REL650	Identity number
Application manual	1MRK 506 329-UEN
Technical manual	1MRK 506 330-UEN
Commissioning manual	1MRK 506 331-UEN
Product Guide, configured	1MRK 506 332-BEN
Type test certificate	1MRK 506 332-TEN
Application notes for Circuit Breaker Control	1MRG006806

650 series manuals	Identity number
Communication protocol manual, DNP3	1MRK 511 257-UEN
Communication protocol manual, IEC 61850–8–1	1MRK 511 258-UEN
Communication protocol manual, IEC 60870-5-103	1MRK 511 259-UEN
Cyber Security deployment guidelines	1MRK 511 268-UEN
Point list manual, DNP3	1MRK 511 260-UEN
Engineering manual	1MRK 511 261-UEN
Operation manual	1MRK 500 095-UEN
Installation manual	1MRK 514 015-UEN

1.4 Symbols and conventions

1.4.1 Symbols

The electrical warning icon indicates the presence of a hazard which could result in electrical shock.

The warning icon indicates the presence of a hazard which could result in personal injury.

The caution icon indicates important information or warning related to the concept discussed in the text. It might indicate the presence of a hazard which could result in corruption of software or damage to equipment or property.

The information icon alerts the reader of important facts and conditions.

The tip icon indicates advice on, for example, how to design your project or how to use a certain function.

Although warning hazards are related to personal injury, it is necessary to understand that under certain operational conditions, operation of damaged equipment may result in degraded process performance leading to personal injury or death. Therefore, comply fully with all warning and caution notices.

1.4.2 Document conventions

A particular convention may not be used in this manual.

- Abbreviations and acronyms in this manual are spelled out in the glossary. The glossary also contains definitions of important terms.
- Push button navigation in the LHMI menu structure is presented by using the push button icons.
  To navigate between the options, use and .
- HMI menu paths are presented in bold.
  Select **Main menu/Settings**.
- LHMI messages are shown in Courier font.
  To save the changes in non-volatile memory, select `Yes` and press .
- Parameter names are shown in italics.
  The function can be enabled and disabled with the *Operation* setting.
- The ^ character in front of an input or output signal name in the function block symbol given for a function, indicates that the user can set an own signal name in PCM600.
- The * character after an input or output signal name in the function block symbol given for a function, indicates that the signal must be connected to another function block in the application configuration to achieve a valid application configuration.

Section 2 Available functions

Note that not all functions included in the tables below have commissioning information available.

2.1 Main protection functions

IEC 61850/ Function block name	ANSI	Function description	Line Distance			
			REL650	REL650 (A01) 3Ph/1CB	REL650 (A11) 1Ph/1CB	REL650 (B01) 3Ph/2CB
Impedance protection						
ZQMPDIS	21	Five zone distance protection, quadrilateral and mho characteristic	1	1	1	1
FDPSPDIS	21	Phase selection with load enchroachment, quadrilateral characteristic	1	1	1	1
FMPSPDIS	21	Faulty phase identification with load enchroachment for mho	1	1	1	1
ZDARDIR	21	Additional distance protection directional function for earth faults	1	1	1	1
ZDNRDIR	21	Directional impedance quadrilateral and mho	1	1	1	1
PPLPHIZ		Phase preference logic	0–1	1	1	1
ZMRPSB	68	Power swing detection	0–1	1	1	1
ZCVPSOF		Automatic switch onto fault logic, voltage and current based	1	1	1	1

2.2 Back-up protection functions

IEC 61850/ Function block name	ANSI	Function description	Line Distance			
			REL650	REL650 (A01) 3Ph/1CB	REL650 (A11) 1Ph/1CB	REL650 (B01) 3Ph/2CB
Current protection						
PHPIOC	50	Instantaneous phase overcurrent protection, 3–phase output	0–1	1		1
SPTPIOC	50	Instantaneous phase overcurrent protection, phase segregated output	0–1		1	
OC4PTOC	51	Four step phase overcurrent protection, 3–phase output	0–1	1		1
OC4SPTOC	51/67	Four step phase overcurrent protection, phase segregated output	0–1		1	
EFPIOC	50N	Instantaneous residual overcurrent protection	0–1	1	1	1
EF4PTOC	51N/67N	Four step residual overcurrent protection, zero/ negative sequence direction	0–1	1	1	1
SDEPSDE	67N	Sensitive directional residual overcurrent and power protection	0–1	1	1	1
UC2PTUC	37	Time delayed 2-step undercurrent protection	0–1	1	1	1
LCPTTR	26	Thermal overload protection, one time constant, Celsius	0–1	1	1	1
LFPTTR	26	Thermal overload protection, one time constant, Fahrenheit	0–1	1	1	1
CCRBRF	50BF	Breaker failure protection, 3–phase activation and output	0–2	1		2
CSPRBRF	50BF	Breaker failure protection, phase segregated activation and output	0–1		1	
STBPTOC	50STB	Stub protection	0–1	1	1	1
CCRPLD	52PD	Pole discordance protection	0–2	1	1	2
BRCPTOC	46	Broken conductor check	0–1	1	1	1
GUPPDUP	37	Directional underpower protection	0–1	1	1	1
GOPPDOP	32	Directional overpower protection	0–1	1	1	1
DNSPTOC	46	Negative sequence based overcurrent function	0–1	1	1	1
Voltage protection						
UV2PTUV	27	Two step undervoltage protection	0–1	1	1	1
OV2PTOV	59	Two step overvoltage protection	0–1	1	1	1
ROV2PTOV	59N	Two step residual overvoltage protection	0–1	1	1	1
LOVPTUV	27	Loss of voltage check	0–1	1	1	1
Frequency protection						

Table continues on next page

IEC 61850/ Function block name	ANSI	Function description	Line Distance			
			REL650	REL650 (A01) 3Ph/1CB	REL650 (A11) 1Ph/1CB	REL650 (B01) 3Ph/2CB
SAPTUF	81	Underfrequency function	0–2	2	2	2
SAPTOF	81	Overfrequency function	0–2	2	2	2
SAPFRC	81	Rate-of-change frequency protection	0–2	2	2	2

2.3 Control and monitoring functions

IEC 61850/Function block name	ANSI	Function description	Line Distance			
			REL650	REL650 (A01) 3Ph/1CB	REL650 (A11) 1Ph/1CB	REL650 (B01) 3Ph/2CB
Control						
SESRSYN	25	Synchrocheck, energizing check, and synchronizing	0–2	1	1	2
SMBRREC	79	Autorecloser for 3–phase operation	0–2	1		2
STBRREC	79	Autorecloser for 1/3–phase operation	0–1		1	
QCBAY		Bay control	1	1	1	1
LOCREM		Handling of LR-switch positions	1	1	1	1
LOCREMCTRL		LHMI control of Permitted Source To Operate (PSTO)	1	1	1	1
CBC1		Circuit breaker for 1CB	0–1	1	1	
CBC2		Circuit breaker for 2CB	0–1			1
SLGGIO		Logic Rotating Switch for function selection and LHMI presentation	15	15	15	15
VSGGIO		Selector mini switch extension	20	20	20	20
DPGGIO		IEC 61850 generic communication I/O functions double point	16	16	16	16
SPC8GGIO		Single point generic control 8 signals	5	5	5	5
AUTOBITS		AutomationBits, command function for DNP3.0	3	3	3	3
I103CMD		Function commands for IEC60870-5-103	1	1	1	1
I103IEDCMD		IED commands for IEC60870-5-103	1	1	1	1
I103USRCMD		Function commands user defined for IEC60870-5-103	4	4	4	4
I103GENCMD		Function commands generic for IEC60870-5-103	50	50	50	50

Table continues on next page

IEC 61850/Function block name	ANSI	Function description	Line Distance			
			REL650	REL650 (A01) 3Ph/1CB	REL650 (A11) 1Ph/1CB	REL650 (B01) 3Ph/2CB
I103POSCMD		IED commands with position and select for IEC60870-5-103	50	50	50	50
Secondary system supervision						
CCSRDIF	87	Current circuit supervision	0–2	1	1	2
SDDRFUF		Fuse failure supervision	0–3	1	1	3
TCSSCBR		Breaker close/trip circuit monitoring	3	3	3	3
Logic						
SMPPTRC	94	Tripping logic, common 3–phase output	1–2	1		2
SPTPTRC	94	Tripping logic, phase segregated output	1		1	
TMAGGIO		Trip matrix logic	12	12	12	12
OR		Configurable logic blocks, OR gate	283	283	283	283
INVERTER		Configurable logic blocks, Inverter gate	140	140	140	140
PULSETIMER		Configurable logic blocks, Pulse timer	40	40	40	40
GATE		Configurable logic blocks, Controllable gate	40	40	40	40
XOR		Configurable logic blocks, exclusive OR gate	40	40	40	40
LOOPDELAY		Configurable logic blocks, loop delay	40	40	40	40
TIMERSET		Configurable logic blocks, timer function block	40	40	40	40
AND		Configurable logic blocks, AND gate	280	280	280	280
SRMEMORY		Configurable logic blocks, set-reset memory flip-flop gate	40	40	40	40
RSMEMORY		Configurable logic blocks, reset-set memory flip-flop gate	40	40	40	40
FXDSIGN		Fixed signal function block	1	1	1	1
B16I		Boolean 16 to Integer conversion	16	16	16	16
B16IFCVI		Boolean 16 to Integer conversion with logic node representation	16	16	16	16
IB16A		Integer to Boolean 16 conversion	16	16	16	16
IB16FCVB		Integer to Boolean 16 conversion with logic node representation	16	16	16	16
Monitoring						
CVMMXN		Measurements	6	6	6	6
CMMXU		Phase current measurement	10	10	10	10
VMMXU		Phase-phase voltage measurement	6	6	6	6
CMSQI		Current sequence component measurement	6	6	6	6
VMSQI		Voltage sequence measurement	6	6	6	6
VNMMXU		Phase-neutral voltage measurement	6	6	6	6
AISVBAS		Function block for service values presentation of the analog inputs	1	1	1	1

Table continues on next page

IEC 61850/Function block name	ANSI	Function description	Line Distance			
			REL650	REL650 (A01) 3Ph/1CB	REL650 (A11) 1Ph/1CB	REL650 (B01) 3Ph/2CB
TM_P_P2		Function block for service values presentation of primary analog inputs 600TRM	1	1	1	1
AM_P_P4		Function block for service values presentation of primary analog inputs 600AIM	1	1	1	1
TM_S_P2		Function block for service values presentation of secondary analog inputs 600TRM	1	1	1	1
AM_S_P4		Function block for service values presentation of secondary analog inputs 600AIM	1	1	1	1
CNTGGIO		Event counter	5	5	5	5
DRPRDRE		Disturbance report	1	1	1	1
AxRADR		Analog input signals	4	4	4	4
BxRBDR		Binary input signals	6	6	6	6
SPGGIO		IEC 61850 generic communication I/O functions	64	64	64	64
SP16GGIO		IEC 61850 generic communication I/O functions 16 inputs	16	16	16	16
MVGGIO		IEC 61850 generic communication I/O functions	16	16	16	16
MVEXP		Measured value expander block	66	66	66	66
LMBRFLO		Fault locator	1	1	1	1
SPVNZBAT		Station battery supervision	0–1	1	1	1
SSIMG	63	Insulation gas monitoring function	0–2	1	1	2
SSIML	71	Insulation liquid monitoring function	0–2	1	1	2
SSCBR		Circuit breaker condition monitoring	0–2	1	1	2
I103MEAS		Measurands for IEC60870-5-103	1	1	1	1
I103MEASUSR		Measurands user defined signals for IEC60870-5-103	3	3	3	3
I103AR		Function status auto-recloser for IEC60870-5-103	1	1	1	1
I103EF		Function status earth-fault for IEC60870-5-103	1	1	1	1
I103FLTPROT		Function status fault protection for IEC60870-5-103	1	1	1	1
I103IED		IED status for IEC60870-5-103	1	1	1	1
I103SUPERV		Supervison status for IEC60870-5-103	1	1	1	1
I103USRDEF		Status for user defined signals for IEC60870-5-103	20	20	20	20

Table continues on next page

IEC 61850/Function block name	ANSI	Function description	Line Distance			
			REL650	REL650 (A01) 3Ph/1CB	REL650 (A11) 1Ph/1CB	REL650 (B01) 3Ph/2CB
Metering						
PCGGIO		Pulse counter logic	16	16	16	16
ETPMMTR		Function for energy calculation and demand handling	3	3	3	3

2.4 Communication

IEC 61850/Function block name	ANSI	Function description	Line Distance			
			REL650	REL650 (A01) 3Ph/1CB	REL650 (A11) 1Ph/1CB	REL650 (B01) 3Ph/2CB
Station communication						
IEC61850-8-1		IEC 61850 communication protocol	1	1	1	1
DNPGEN		DNP3.0 for TCP/IP communication protocol	1	1	1	1
RS485DNP		DNP3.0 for EIA-485 communication protocol	1	1	1	1
CH1TCP		DNP3.0 for TCP/IP communication protocol	1	1	1	1
CH2TCP		DNP3.0 for TCP/IP communication protocol	1	1	1	1
CH3TCP		DNP3.0 for TCP/IP communication protocol	1	1	1	1
CH4TCP		DNP3.0 for TCP/IP communication protocol	1	1	1	1
OPTICALDNP		DNP3.0 for optical serial communication	1	1	1	1
MSTSERIAL		DNP3.0 for serial communication protocol	1	1	1	1
MST1TCP		DNP3.0 for TCP/IP communication protocol	1	1	1	1
MST2TCP		DNP3.0 for TCP/IP communication protocol	1	1	1	1
MST3TCP		DNP3.0 for TCP/IP communication protocol	1	1	1	1
MST4TCP		DNP3.0 for TCP/IP communication protocol	1	1	1	1
RS485GEN		RS485	1	1	1	1
OPTICALPROT		Operation selection for optical serial	1	1	1	1
RS485PROT		Operation selection for RS485	1	1	1	1

Table continues on next page

IEC 61850/Function block name	ANSI	Function description	Line Distance			
			REL650	REL650 (A01) 3Ph/1CB	REL650 (A11) 1Ph/1CB	REL650 (B01) 3Ph/2CB
DNPFREC		DNP3.0 fault records for TCP/IP communication protocol	1	1	1	1
OPTICAL103		IEC60870-5-103 Optical serial communication	1	1	1	1
RS485103		IEC60870-5-103 serial communication for RS485	1	1	1	1
GOOSEINTLKRCV		Horizontal communication via GOOSE for interlocking	59	59	59	59
GOOSEBINRCV		GOOSE binary receive	4	4	4	4
ETHFRNT ETHLAN1 GATEWAY		Ethernet configuration of front port, LAN1 port and gateway	1	1	1	1
GOOSEDPRCV		GOOSE function block to receive a double point value	32	32	32	32
GOOSEINTRCV		GOOSE function block to receive an integer value	32	32	32	32
GOOSEMVRCV		GOOSE function block to receive a measurand value	16	16	16	16
GOOSESPRCV		GOOSE function block to receive a single point value	64	64	64	64
Scheme communication						
ZCPSCH	85	Scheme communication logic with delta based blocking scheme signal transmit	0–1	1	1	1
ZCRWPSCH	85	Current reversal and WEI logic for distance protection, 3–phase	0–1	1		1
ZCWSPSCH	85	Current reversal and WEI logic for distance protection, phase segregated	0–1		1	
ZCLCPLAL		Local acceleration logic	1	1	1	1
ECPSCH	85	Scheme communication logic for residual overcurrent protection	0–1	1	1	1
ECRWPSCH	85	Current reversal and weak-end infeed logic for residual overcurrent protection	0–1	1	1	1

2.5 Basic IED functions

IEC 61850/Function block name	Function description	
Basic functions included in all products		
INTERRSIG	Self supervision with internal event list	1
SELFSUPEVLST	Self supervision with internal event list	1
TIMESYNCHGEN	Time synchronization	1

Table continues on next page

IEC 61850/Function block name	Function description	
SNTP	Time synchronization	1
DTSBEGIN, DTSEND, TIMEZONE	Time synchronization, daylight saving	1
IRIG-B	Time synchronization	1
SETGRPS	Setting group handling	1
ACTVGRP	Parameter setting groups	1
TESTMODE	Test mode functionality	1
CHNGLCK	Change lock function	1
TERMINALID	IED identifiers	1
PRODINF	Product information	1
SYSTEMTIME	System time	1
RUNTIME	IED Runtime comp	1
PRIMVAL	Primary system values	1
SMAI_20_1 - SMAI_20_12	Signal matrix for analog inputs	2
3PHSUM	Summation block 3 phase	12
GBASVAL	Global base values for settings	6
ATHSTAT	Authority status	1
ATHCHCK	Authority check	1
SPACOMMMAP	SPA communication mapping	1
FTPACCS	FTP access with password	1
DOSFRNT	Denial of service, frame rate control for front port	1
DOSLAN1	Denial of service, frame rate control for LAN1	1
DOSSCKT	Denial of service, socket flow control	1
SAFEFILECOPY	Safe file copy function	1
SPATD	Date and time via SPA protocol	1
BCSCONF	Basic communication system	1

Section 3 Starting up

3.1 Factory and site acceptance testing

Testing the proper IED operation is carried out at different occasions, for example:

- Acceptance testing
- Commissioning testing
- Maintenance testing

This manual describes the workflow and the steps to carry out the commissioning testing.

Factory acceptance testing (FAT) is typically done to verify that the IED and its corresponding configuration meet the requirements of the utility or industry. This test is the most complex and in depth, as it is done to familiarize the user with a new product or to verify a new configuration. The complexity of this testing depends on several factors, such as:

- New IED type
- New configuration
- Modified configuration

Site acceptance testing (SAT or commissioning testing) is typically done to verify that the installed IED is correctly set and connected to the power system. SAT requires that the acceptance testing has been performed and that the application configuration is verified.

Maintenance testing is a periodic verification that the IED is healthy and has correct settings, depending on changes in the power system. There are also other types of maintenance testing.

3.2 Commissioning checklist

Before starting up commissioning at site, check that the following items are available.

- Single line diagram
- Protection block diagram
- Circuit diagram
- Setting list and configuration
- RJ-45 Ethernet cable (CAT 5)
- Three-phase test kit or other test equipment depending on the complexity of the configuration and functions to be tested.

- PC with PCM600 installed along with the connectivity packages corresponding to the IEDs to be tested.
- Administration rights on the PC, to set up IP addresses
- Product documentation (engineering manual, installation manual, commissioning manual, operation manual, technical manual and communication protocol manual)

3.3 Checking the power supply

Check that the auxiliary supply voltage remains within the permissible input voltage range under all operating conditions. Check that the polarity is correct before powering the IED.

3.4 Energizing the IED

3.4.1 Checking the IED operation

Check all connections to external circuitry to ensure correct installation, before energizing the IED and carrying out the commissioning procedures.

Energize the power supply of the IED to start it up. This could be done in a number of ways, from energizing a whole cubicle to energizing a single IED. Set the IED time if no time synchronization source is configured. Check the self-supervision function in **Main menu/Diagnostics/Internal events** or **Main menu/Diagnostics/IED status/General** menu in local HMI to verify that the IED is functioning properly.

3.4.2 IED start-up sequence

The following sequence is expected when the IED is energized.

- The green Ready LED starts flashing instantly and the ABB logo is shown on the LCD.
- After approximately 30 seconds, "Starting" is shown on the LCD.
- Within 90 seconds, the main menu is shown on the LCD and the green Ready LED shows a steady light, which indicates a successful startup.

The startup time depends on the size of the application configuration. Application configurations with less functionality have shorter startup times.

If the green Ready LED continues to flash after startup, the IED has detected an internal error. Navigate via **Main menu/Diagnostics/IED status/General** to investigate the error description.

3.5 Setting up communication between PCM600 and the IED

The communication between the IED and PCM600 is independent of the communication protocol used within the substation or to the NCC.

The communication media is always Ethernet and the used protocol is TCP/IP.

Each IED has an RJ-45 Ethernet interface connector on the front and on the rear side. The Ethernet connector can be used for communication with PCM600.

When an Ethernet-based station protocol is used, PCM600 communication can use the same Ethernet port and IP address.

To connect PCM600 to the IED, two basic variants must be considered.

- Direct point-to-point link between PCM600 and the IED front port.
- Indirect link via a station LAN or from remote via a network.

The physical connection and the IP address must be configured in both cases to enable communication.

The communication procedures are the same in both cases.

1. If needed, set the IP address for the IEDs.
2. Set up the PC or workstation for a direct link (point-to-point), or
3. Connect the PC or workstation to the LAN/WAN network.
4. Configure the IED IP addresses in the PCM600 project for each IED to match the IP addresses of the physical IEDs.

Setting up IP addresses

The IP address and the corresponding mask must be set via the LHMI for each available Ethernet interface in the IED. Each Ethernet interface has a default factory IP address when the IED is delivered. This is not given when an additional Ethernet interface is installed or an interface is replaced.

- The default IP address for the IED front port is 10.1.150.3 and the corresponding subnetwork mask is 255.255.255.0, which can be set via the local HMI path **Main menu/Configuration/Communication/TCP-IP configuration/1:ETHFRNT**.
- The default IP address for the IED rear port is 192.168.1.10 and the corresponding subnetwork mask is 255.255.255.0, which can be set via the local HMI path **Main menu/Configuration/Communication/TCP-IP configuration/1:ETHLAN1** and **Rear OEM - port CD**.

The front and rear port IP addresses cannot belong to the same subnet or communication will fail. It is recommended to change the

IP address of the front port, if the front and rear port are set to the same subnet.

Setting up the PC or workstation for point-to-point access to IEDs front port

A special cable is needed to connect two physical Ethernet interfaces together without a hub, router, bridge or switch in between. The Tx and Rx signal wires must be crossed in the cable to connect Tx with Rx on the other side and vice versa. These cables are known as cross over cables. The maximum length should be about 2 m. The connector type is RJ-45.



Figure 2: Point-to-point link between IED and PCM600 using a null-modem cable

The following description is an example valid for standard PCs using Microsoft Windows operating system. The example is taken from a Laptop with one Ethernet interface.

Administrator rights are required to change the PC communication setup. Some PCs have the feature to automatically detect that Tx signals from the IED are received on the Tx pin on the PC. Thus, a straight (standard) Ethernet cable can be used.

When a PC is connected to the IED and the setting *DHCPServer* is set to *On* via the local HMI path **Main menu/Configuration/Communication/TCP-IP configuration/1:ETHFRNT/DHCPServer**, the IEDs DHCP server for the front port assigns an IP address for the PC. The PC must be configured to obtain its IP address automatically as described in the following procedure.

1. Select **Network Connections** in the PC.



Figure 3: Select: Network connections

2. Select **Properties** in the status window.



Figure 4: Right-click Local Area Connection and select Properties

3. Select the TCP/IP protocol from the list of configured components using this connection and click **Properties**.



IEC09000357-1-en.vsd

Figure 5: Select the TCP/IP protocol and open Properties

4. Select **Obtain an IP address automatically** if the parameter *DHCPServer* is set to *On* in the IED.



IEC09000358-1-en.vsd

Figure 6: Select: Obtain an IP address automatically

5. Select **Use the following IP address** and define *IP address* and *Subnet mask* if the front port is used and if the *IP address* is not set to be obtained automatically by the IED, see Figure 7. The IP address must be different from the IP address chosen for the IED.



Figure 7: Select: Use the following IP address

6. Close all open windows and start PCM600.

Setting up the PC to access the IED via a network

This task depends on the used LAN/WAN network.

The PC and IED must belong to the same subnetwork for this set-up to work.

3.6 Writing an application configuration to the IED

Ensure that the IED includes the correct application configuration according to project specifications.

The application configuration is created using PCM600 and then written to the IED. Establish a connection between PCM600 and the IED when an application configuration must be written to the IED.

After writing an application configuration to the IED, the IED makes an application restart or a complete IED restart, when necessary.

The IED does not restart after reconfiguring IEC61850 (regardless of whether the protocol is enabled or disabled).

Be sure to set the correct technical key in both the IED and PCM600 to prevent writing an application configuration to a wrong IED.

See the engineering manual for information on how to create or modify an application configuration and how to write to the IED.

3.7 Checking CT circuits

Check that the wiring is in strict accordance with the supplied connection diagram.

- Primary injection test to verify the current ratio of the CT, the correct wiring up to the protection IED and correct phase sequence connection (that is L1, L2, L3.)
- CT secondary loop resistance measurement to confirm that the current transformer secondary loop DC resistance is within specification and that there are no high resistance joints in the CT winding or wiring.
- Earthing check of the individual CT secondary circuits to verify that each three-phase set of main CTs is properly connected to the station earth and only at one electrical point.
- Insulation resistance check.

CT and VT connectors are pre-coded, and the CT and VT connector markings are different. For more information, see the installation manual.

Both the primary and the secondary sides must be disconnected from the line and the IED when plotting the excitation characteristics.

3.8 Checking VT circuits

Check that the wiring is in strict accordance with the supplied connection diagram.

Correct possible errors before continuing to test the circuitry.

Test the circuitry.

- Polarity check
- VT circuit voltage measurement (primary injection test)
- Earthing check
- Phase relationship
- Insulation resistance check

The polarity check verifies the integrity of circuits and the phase relationships. The check must be performed as close to the IED as possible.

The primary injection test verifies the VT ratio and the wiring all the way from the primary system to the IED. Injection must be performed for each phase-to-neutral circuit and each phase-to-phase pair. In each case, voltages in all phases and neutral are measured.

3.9 Checking the RTXP test switch

The RTXP test switch is designed to provide the means of safe testing of the IED. This is achieved by the electromechanical design of the test switch and test plug handle. When the test plug handle is inserted, it first blocks the trip and alarm circuits then it short circuits the CT secondary circuit and opens the VT secondary circuits making the IED available for secondary injection.

When pulled out, the test handle is mechanically stopped in half withdrawn position. In this position, the current and voltage enter the protection, but the alarm and trip circuits are still isolated. Before removing the test handle, check that no trip or alarms are present in the IED.

Not until the test handle is completely removed, the trip and alarm circuits are restored for operation.

By pulling in all cables, verify that the contact sockets have been crimped correctly and that they are fully inserted. Never do this with current circuits in service.

Current circuit

1. Verify that the contacts are of current circuit type.
2. Verify that the short circuit jumpers are located in the correct slots.

Voltage circuit

1. Verify that the contacts are of voltage circuit type.
2. Check that no short circuit jumpers are located in the slots dedicated for voltage.

Trip and alarm circuits

1. Check that the correct types of contacts are used.

3.10 Checking binary input and output circuits

3.10.1 Binary input circuits

Preferably, disconnect the binary input connector from the binary input cards. Check all connected signals so that both input level and polarity are in accordance with the IED specifications.

3.10.2 Binary output circuits

Preferably, disconnect the binary output connector from the binary output cards. Check all connected signals so that both load and polarity are in accordance with IED specifications.

3.11 Checking optical connections

Check that the Tx and Rx optical connections are correct.

An IED equipped with optical connections requires a minimum depth of 180 mm for plastic fiber cables and 275 mm for glass fiber cables. Check the allowed minimum bending radius from the optical cable manufacturer.

Section 4 Establishing connection and verifying the IEC 61850 station communication

4.1 Setting the station communication

To enable IEC 61850 station communication:

- The IEC 61850-8-1 station communication functionality must be on in the local HMI. Navigate to **Main menu/Configuration/Communication/Station communication/1:IEC61850-8-1** and set the *Operation* parameter to *On*.
- To enable GOOSE communication the *Operation* parameter for the corresponding GOOSE function blocks (GOOSEBINRCV and GOOSEINTLKRCV) must be set to *On* in the application configuration.
- To enable GOOSE communication via the front port the parameter *GOOSE* in **Main menu/Configuration/Communication/Station communication/ IEC61850-8-1** must be set to *Front*. To enable GOOSE communication via rear port the parameter *GOOSE* must be set to *LAN1*.

4.2 Verifying the communication

Connect your PC to the substation network and ping the connected IED and the Substation Master PC, to verify that the communication is working (up to the transport layer).

The best way to verify the communication up to the application layer is to use protocol analyzer ITT600 connected to the substation bus, and monitor the communication.

Section 5 Testing IED operation

5.1 Preparing the IED to verify settings

If a test switch is included, start preparation by making the necessary connections to the test switch. This means connecting the test equipment according to a specific and designated IED terminal diagram.

Put the IED into the test mode to facilitate the test of individual functions and prevent unwanted operation caused by other functions. The test switch should then be connected to the IED.

Verify that analog input signals from the analog input module are measured and recorded correctly by injecting currents and voltages required by the specific IED.

To make testing even more effective, use PCM600. PCM600 includes the Signal monitoring tool, which is useful in reading the individual currents and voltages, their amplitudes and phase angles. In addition, PCM600 contains the Disturbance handling tool. The content of reports generated by the Disturbance handling tool can be configured which makes the work more efficient. For example, the tool may be configured to only show time tagged events and to exclude analog information and so on.

Check the disturbance report settings to ensure that the indications are correct.

For test functions and test and signal parameter names, see the technical manual. The correct initiation of the disturbance recorder is made on start and/or release or trip from a function. Also check that the wanted recordings of analogue (real and calculated) and binary signals are achieved.

The IEDs in the 650 series can have between 1 and 4 individual parameter setting groups prepared with full sets of different parameters for all functions. The purpose of these groups is to be able to handle different power system load conditions to optimize the parameters settings of the different functions for these different power systems conditions (for example summer/winter and day/night).

Parameters can be entered into different setting groups. Make sure to test functions for the same parameter setting group. If needed, repeat the tests for all different setting groups used. The difference between testing the first parameter setting group and the remaining is that there is no need for testing the connections.

During testing, observe that the right testing method, that corresponds to the actual parameters set in the activated parameter setting group, is used.

In the local HMI the sensitive directional earth fault protection SDEPSDE parameter group 4 is active indicated by the * next to #4 and the test of the SDEPSDE must be performed according to the instructions given for the setting *OpMode* and setting value *3I03U0cosfi*.

Set and configure the function(s) before testing. Most functions are highly flexible and permit a choice of functional and tripping modes. The various modes are checked at the factory as part of the design verification. In certain cases, only modes with a high probability of coming into operation need to be checked when commissioned to verify the configuration and settings.

Requirements for testing the function.

- Calculated settings
- Valid configuration diagram for the IED
- Valid terminal diagram for the IED
- Technical manual
- Three-phase test equipment

Content of the technical manual.

- Application and functionality summaries
- Function blocks
- Logic diagrams
- Input and output signals
- A list of setting parameters
- Technical data for the function

The test equipment should be able to provide a three-phase supply of currents and three-phase voltage. The magnitude and angle of currents (and voltages) should be possible to vary. Check that the IED is prepared for test before starting the test session. Consider the logic diagram of the function when performing the test.

The response from a test can be viewed in different ways.

- Binary output signals
- Service values in the local HMI (logical signal or phasors)
- A PC with PCM600 (configuration software) in debug mode

Do not switch off the auxiliary power supply to the IED before changes, for example, setting parameter or local/remote control state changes are saved.

A mechanism for limiting the number of writings per time period is included in the IED to prevent the flash memory to be worn out due to too many writings. As a consequence it may take up to an hour to save changes. If the auxiliary power is interrupted before a change is saved, that change is lost.

5.2 Activating test mode

Put the IED into the test mode before testing. The test mode blocks all protection functions and some of the control functions in the IED, and the individual functions to be tested can be unblocked to prevent unwanted operation caused by other functions. In this way, it is possible to test slower back-up measuring functions without the interference from faster measuring functions. Test mode is indicated when the yellow StartLED flashes.

Procedure

1. Select **Main menu/Tests/IED test mode/1:TESTMODE**
2. Set parameter *TestMode* to *On*.
3. Save the changes.
   As a consequence, the yellow startLED starts flashing as a reminder and remains flashing until the test mode is switched off.

5.3 Preparing the connection to the test equipment

The IED can be equipped with a test switch of type RTXP8, RTXP18 or RTXP24. The test switch and its associated test plug handle (RTXH8, RTXH18 or RTXH24) are a part of the COMBITEST system, which provides secure and convenient testing of the IED.

When using the COMBITEST, preparations for testing are automatically carried out in the proper sequence, that is, for example, blocking of tripping circuits, short circuiting of CT's, opening of voltage circuits, making IED terminals available for secondary injection. Terminals 1 and 8, 1 and 18 as well as 1 and 12 of the test switches RTXP8, RTXP18 and RTXP24 respectively are not disconnected as they supply DC power to the protection IED.

The RTXH test-plug handle leads may be connected to any type of test equipment or instrument. When a number of protection IEDs of the same type are tested, the test-plug handle only needs to be moved from the test switch of one protection IED to the test switch of the other, without altering the previous connections.

Use COMBITEST test system to prevent unwanted tripping when the handle is withdrawn, since latches on the handle secure it in the half withdrawn position. In this position, all voltages and currents are restored and any re-energizing transients are given a chance to decay before the trip circuits are restored. When the latches are released, the handle can be completely withdrawn from the test switch, restoring the trip circuits to the protection IED.

If a test switch is not used, perform measurement according to the provided circuit diagrams.

Never disconnect the secondary connection of a current transformer circuit without first short-circuiting the transformer's secondary winding. Operating a current transformer with the secondary winding open will cause a massive potential build up that may damage the transformer and cause personal injury.

5.4 Connecting the test equipment to the IED

Connect the test equipment according to the IED specific connection diagram and the needed input and output signals for the function under test. An example of a connection is shown in figure 8.

Connect the current and voltage terminals. Pay attention to the current polarity. Make sure that the connection of input and output current terminals and the connection of the residual current conductor is correct. Check that the input and output logical signals in the logic diagram for the function under test are connected to the corresponding binary inputs and outputs of the IED under test.

To ensure correct results, make sure that the IED as well as the test equipment are properly earthed before testing.



Figure 8: Connection example of the test equipment to the IED when test equipment is connected to the transformer input module

5.5 Releasing the function to be tested

Release or unblock the function to be tested. This is done to ensure that only the function or the chain of functions to be tested are in operation and that other functions are prevented from operating. Release the tested function(s) by setting the corresponding *Blocked* parameter under Function test modes to *No* in the local HMI.

When testing a function in this blocking feature, remember that not only the actual function must be activated, but the whole sequence of interconnected functions (from measuring inputs to binary output contacts), including logic must be activated. Before starting a new test mode session, scroll through every function to ensure that only the function to be tested (and the interconnected ones) have the parameters *Blocked* and eventually *EvDisable* set to *No* and *Yes* respectively. Remember that a function is also blocked if the BLOCK input signal on the corresponding function block is active, which depends on the configuration. Ensure that the logical status of the BLOCK input signal is equal to 0 for the function to be tested. Event function blocks can also be individually blocked to ensure that no events are reported to a remote station during the test. This is done by setting the parameter *EvDisable* to *Yes*.

Any function is blocked if the corresponding setting in the local HMI under **Main menu/Tests/Function test modes** menu remains *On*, that is, the parameter *Blocked* is set to *Yes* and the parameter *TestMode* under **Main menu/Tests/IED test mode** remains active. All functions that were blocked or released in a previous test mode session, that is, the parameter *Test mode* is set to *On*, are reset when a new test mode session is started.

Procedure

1. Click the **Function test modes** menu.
   The Function test modes menu is located in the local HMI under **Main menu/Tests/Function test modes**.
2. Browse to the function instance that needs to be released.
3. Set parameter *Blocked* for the selected function to *No*.

5.6 Verifying analog primary and secondary measurement

Verify that the connections are correct and that measuring and scaling is done correctly. This is done by injecting current and voltage to the IED.

Apply input signals as needed according to the actual hardware and the application configuration.

1. Inject a symmetrical three-phase voltage and current at rated value.
2. Compare the injected value with the measured values.
   The voltage and current phasor menu in the local HMI is located under **Main menu/Measurements/Analog primary values** and **Main menu/ Measurements/Analog secondary values**.
3. Compare the frequency reading with the set frequency and the direction of the power.
   The frequency and active power are located under **Main menu/Tests/ Function status/Monitoring/CVMMXN/1:CVMMXN/Outputs**. Then navigate to the bottom of the list to find the frequency.

   Check both analog primary and secondary values, because then the CT and VT ratios entered into the IED are also checked.

   These checks shall be repeated for Analog primary values.
4. Inject an unsymmetrical three-phase voltage and current, to verify that phases are correctly connected.

If some setting deviates, check the analog input settings under

Main menu/Configuration/Analog modules

Measured values such as current and voltages as well as active, reactive and apparent power, power factor phase angles as well as positive and negative and zero sequence currents and voltages are available in the local HMI under **Main menu/Tests/Function status/Monitoring**.

Navigate to the measurement function that contains the quantity to be checked.

Table 1: Measurement functions

Function	Quantity	Description
CMMXU	IL1 to IL3	amplitude, range and angle
CMSQI	$3I_0$; I1 and I2	amplitude, range and angle
CVMMXN	S; P; Q; PF; Ilag; Ilead; U; I and f	amplitude, range and angle
VMMXU	UL12 to UL31 i.e. phase-to-phase	amplitude, range and angle
VMSQI	$3U_0$; U1 and U2	amplitude, range and angle
VNMMXU	UL1 to UL3 i.e. phase-to-neutral	amplitude, range and angle

Also the Signal Monitoring tool in PCM600 can be used to read the measured values. In many cases it is more convenient to use PCM600 since, among many things, reports on measured values can be exported from the Signal Monitoring tool to other tools (for example, MS Excel) for further analysis.

5.7 Testing protection functionality

Each protection function must be tested individually by secondary injection.

- Verify operating levels (trip) and timers.
- Verify alarm and blocking signals.
- Use the disturbance handling tool in PCM600 to evaluate that the protection function has received the correct data and responded correctly (signaling and timing).
- Use the event viewer tool in PCM600 to check that only expected events have occurred.

Section 6 Testing functionality

6.1 Testing disturbance report

6.1.1 Introduction

The following sub-functions are included in the disturbance report function:

- Disturbance recorder
- Event list
- Event recorder
- Fault locator
- Trip value recorder
- Indications

If the disturbance report is set on, then its sub-functions are also set up and so it is not possible to only switch these sub-functions off. The disturbance report function is switched off (parameter *Operation* = *Off*) in PCM600 or the local HMI under **Main menu/Settings/IED Settings/Monitoring/Disturbance report/1:DRPRDRE**.

6.1.2 Disturbance report settings

When the IED is in test mode, the disturbance report can be made active or inactive. If the disturbance recorder is turned on during test mode, recordings will be made. When test mode is switched off all recordings made during the test session are cleared.

Setting *OpModeTest* for the control of the disturbance recorder during test mode are located on the local HMI under **Main menu/Settings/IED Settings/Monitoring/Disturbance report/1:DRPRDRE**.

6.2 Identifying the function to test in the technical reference manual

Use the technical manual to identify function blocks, logic diagrams, input and output signals, setting parameters and technical data.

6.3 Testing impedance protection functions

6.3.1 Five zone distance protection, quadrilateral and mho characteristic ZQMPDIS

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for ZQMPDIS are available on the local HMI under **Main menu/Tests/Function status/Impedance/ZQMPDIS(21,Z<)/1:ZQMPDIS**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.3.1.1 Quadrilateral characteristics

Consider releasing Zone 1, the Phase selection with load encroachment, quadrilateral characteristic FDPSPDIS and the Tripping logic SMPPTRC.

Measure operating characteristics during constant current conditions. Keep the measured current as close as possible to its rated value or lower. But make sure it is higher than the set minimum operating current.

Ensure that the maximum continuous current to the IED does not exceed four times its rated value, if the measurement of the operating characteristics runs under constant voltage conditions.

The test procedure has to take into consideration that the shaped load encroachment characteristic is active. It is therefore necessary to check the setting. To verify the settings with the shaped load encroachment characteristic the test should be carried out according to figures 9 and 10 and tables 2 and 3.

To verify the settings the following fault types should be tested:

- One phase-to-phase fault
- One phase-to-earth fault

The shape of the operating characteristic depends on the values of the setting parameters.

Phase-to-phase faults

The angles a (angle on blinder in second quadrant for forward direction), b (load angle determining the load impedance area), c (angle to blinder in fourth quadrant for forward direction), d (line angle) and e (angle for earth compensation factor KN) in the figures below are adjusted with the parameters *ArgNegRes*, *ArgLd*, *ArgDir*, *LineAng* and *KNAng* respectively.



Figure 9: Distance protection characteristic with test points for phase-to-phase measurements

Table 2: Test points for phase-to-phase loops L1-L2 (Ohm/phase)

Test point	Reach	Set value	Comments
1	X	Z · Sin (LineAng)	
	R	0	
2	X	0	
	F	RLdFw	When RLdFw < 0,5 * RFPP
	R	0,5 * RFPP	When RLdFw > 0,5 * RFPP
3	X	0.8 · Z · Sin (LineAng)	
	R	0.8 · Z · Cos (LineAng) + RFPP/2	
4	X	0.8 · Z · Sin (LineAng)	Can be limited by 0,5 * RFPP setting
	R	-0.8 · Z · Sin (LineAng) · tan (ArgNegRes-90)	
5	X	0.5 · RFPP · tan (ArgLd)	Only when RLdFw < 0,5 * RFPP
	R	0.5 · RFPP	
6	X	-0.5 RLdFw · tan (ArgDir)	
	R	0.5 · RLdFw	
7	X	0.5 · Z · Sin (LineAng)	Time measurement
	R	0	

Table 2 is used in conjunction with figure 9.

Phase-to-earth fault



Figure 10: Distance protection characteristic with test points for phase-to-earth measurements

Table 3 is used in conjunction with figure 10.

Table 3: Test points for phase-to-earthL3-E (Ohm/Loop)

Test point	Reach	Value	Comments
1	X	Z · Sin (LineAng) + KNMag · Z · Sin (LineAng + KNAng)	
	R	0	
2	X	0	
	R	RLdFw	When RLdFw < RFPE
	R	RFPE	When RLdFw > RFPE
3	X	0.8 (Z · Sin (LineAng) + KNMag · Z · Sin (LineAng + KNAng))	
	R	0.8(Z · Cos (LineAng) + KNMag · Z · Cos (LineAng + KNAng)) + RFPE	
4	X	0.8 (Z · Sin (LineAng) + KNMag · Z · Sin (LineAng + KNAng))	Can be limited by RFPE
	R	-(0.8 (Z · Sin (LineAng) + KNMag · Z · Sin (LineAng + KNAng)) · tan (ArgNegRes-90)	
5	X	RFPE · tan (ArgLd)	Only when RLdFw < RFPE
	R	RFPE	
6	X	-0.5 RLdFw · tan (ArgDir)	
	R	0.5 RLdFw	
7	X	0.5 (Z · Sin (LineAng) + KNMag · Z · Sin (LineAng + KNAng))	Time measurement
	R	0	

6.3.1.2 Mho characteristics

Phase-to-phase faults



Figure 11: Proposed test points for phase-to-phase fault

Table 4: Test points for phase-to-phase (ohms / phase)

Test points	reach	Value	Comments
1	X	ZPP · sin(ZAngPP)	
	R	ZPP · sin(ZAngPP)	
2	X	0,5· (ZPP· sin(ZAngPP)	
	R	0,5·ZPP + ΔR = 0,5·ZPP·(1+cos(ZAngPP))	
3	X	0,5·ZPP·sin(ZAngPP)	
	R	0,5·ZPP - ΔR = 0,5·ZPP(1-cos(ZAngPP))	

Change the magnitude and angle of phase-to-phase voltage to achieve impedances at test points 1, 2 and 3. For each test point, observe that the output signals, START and STLx are activated where x refers to the actual phase to be tested. After the timer *tPP* for the actual zone has elapsed, also the signals TRIP and TRx shall be activated.

Phase-to-earth faults

For simplicity, the same test points as for phase-to-phase faults are proposed, but considering new impedance values.



Figure 12: Proposed test points for phase-to-earth faults

Table 5: Test points for phase-to-phase loops L1-L2 (Ohm/Loop)

Test points	Reach	Value	Comments
1	X	ZPE · sin(ZAngPE)	
	R	ZPE · cos(ZAngPE)	
2	X	0,5·ZPE · sin(ZAngPE)	
	R	0,5·ZPE + ΔR = 0,5·ZPE · (1 - cos(ZAngPE))	
3	X	0,5·ZPE·sin(ZangPE)	
	R	0,5·ZPE - ΔR = 0,5·ZPE · (1 - cos(ZAngPE))	

Check also in the same way as for phase-to-earth fault for each test point that the output signals START and STLx are activated where x refers to the actual phase to be tested. After the timer *tPE* for the zone has elapsed, also the signals TRIP and TRx shall be activated.

6.3.1.3 Measuring the operating limit of set values with shaped load encroachment characteristics

1. Subject the IED to healthy normal load conditions for at least two seconds.
2. Apply the fault condition and slowly decrease the measured impedance to find the operating value of the phase-to-phase fault L1-L2 for zone 1 according to test point 1 in figure 9 and table 2. Compare the result of the measurement with the set value.
3. Repeat steps 1 to 2 to find the operating value for the remaining test points.

Observe that the zones that are not tested have to be blocked and the zone that is tested has to be released.

4. Repeat steps 1 to 3 to find the operating value for the phase-to-earth fault L3-E according to figure 10 and table 3

Test point 6 is intended to test the directional line of impedance protection. Since directionality is a common function for all 5 measuring zones, it is only necessary to test point 6 once, in the forward direction. Directional functionality testing (trip inside, no-trip outside) should always be carried for all impedance zones set with directionality (forward or reverse).

6.3.1.4 Measuring the operate time of distance protection zones

1. Subject the IED to healthy normal load conditions for at least two seconds.
2. Apply the fault condition to find the operating time for the phase-to-phase fault according to test point 7 in figure 9 and table 2 for zone 1. Compare the result of the measurement with the setting *t1PP*.
3. Repeat steps 1 to 2 to find the operating time for the phase-to-earth fault according to test point 7 in figure 10 and table 3. Compare the result of the measurement with the setting *t1PE*.
4. Repeat steps 1 to 2 to find the operating time for all other used measuring zones. Observe that the zones that are not tested have to be blocked and the zone that is tested has to be released.

6.3.1.5 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Impedance/ZQMPDIS(21,Z<)/1:ZQMPDIS** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.3.2 Phase selection with load encroachment, quadrilateral characteristic FDPSPDIS

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for FDPSPDIS are available on the local HMI under **Main menu/Tests/Function status/Impedance/FDPSPDIS/1:FDPSPDIS**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The phase selectors operate on the same measuring principles as the impedance measuring zones. So it is necessary to follow the same principles as for distance protection, when performing the secondary injection tests.

Measure operating characteristics during constant current conditions. Keep the measured current as close as possible to the rated value of its associated input transformer, or lower. But ensure that it is higher than the set minimum operating current.

Ensure that the maximum continuous current to the IED does not exceed four times its rated value, if the measurement of the operating characteristics runs under constant voltage conditions.

To verify the settings the operating points according to figures 13 and 14 should be tested. See also tables 6 and 7 for information.



Figure 13: Operating characteristic for phase selection function, forward direction single-phase faults

Table 6: Test points for phase-earth loop L3-E (Ohm/loop)

Test point	Reach	Value	Comments
1	X	[X1+XN]	XN=(X_0-X_1)/3
	R	0	
2	X	0	
	R	RLdFw	When RLdFW < RFFwPE
	R	RFFwPE	When RLdFwPE > RFFwPE
3	X	0.85·[X1+XN]	R≈0.491·(X1+XN)+RFFwPE
	R	0.85·[X1+XN]·1/tan(60°)+RFFwPE	

Table continues on next page

Test point	Reach	Value	Comments
4	X	0.85·[X1+XN]	Can be limited by RFFwPE
	R	-0.85·[X1+XN]· tan (AngNegRes-90°)	
5	X	RFFwPE·tan (ArgLd)	Only when RLdFw < RFFwPE
	R	RFFwPE	
6	X	-0.5·RLdFw·tan (ArgDir)	
	R	0.5·RLdFw	

Table 6 is used together with figure 13.



Figure 14: Operating characteristic for phase selection function, forward direction phase-to-phase faults

Table 7: Test points for phase-to-phase loops L1–L2 (Ohm/phase)

Test point	Reach	Value	Comments
1	X	X1	
	R	0	
2	X	0	
	R	RLdFw	When RLdFw < 0,5·RFFwPP
	R	0,5·RFFwPP	When RLdFw > 0,5·RFFwPP
3	X	0.85·X1	R=0.491·X1+0.5 RFFwPP
	R	0.85·X1·1/tan(60°)+0.5 RFFwPP	

Table continues on next page

Test point	Reach	Value	Comments
4	X	0.85·X1	Can be limited by RFFwPP
	R	-0.85·X1·tan (AngNegRes-90°)	
5	X	0.5·RFFwPP·tan (ArgLd)	Only when RLdFW < RFFwPP
	R	0.5·RFFwPP	
6	X	-0.5·RLdFw·tan (ArgDir)	
	R	0.5·RLdFw	

Table 7 is used together with figure 14.

6.3.2.1 Measuring the operate limit of set values

1. Supply the IED with healthy conditions for at least two seconds.
2. Apply the fault condition and slowly decrease the measured impedance to find the operate value for of the phase-to-earth loop L3, test point 1, according to figure 13. Compare the result of the measurement with the expected value according to table 6.
   The corresponding binary signals that inform about the operation of the phase selection measuring elements are available in the local HMI under **Main menu/Tests/Function status/Impedance/FDPSPDIS**.
3. Repeat steps 1 to 2 to find the operate values for the remaining test points according to figure 13 and table 6.

4. Repeat steps 1 to 3 to find the operate value for the phase-to-phase fault in L1 — L2 according to figure 14 and table 7.

6.3.2.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Impedance/FDPSPDIS/1:FDPSPDIS** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.3.3 Faulty phase identification with load encroachment FMPSPDIS

There is no specific test routine for this function. The function is tested in conjunction with other impedance (mho) functions.

6.3.4 Phase preference logic PPLPHIZ

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for PPLHPIZ are available on the local HMI under **Main menu/Tests/Function status/Impedance/PPLHPIZ/1:PPLHPIZ**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The Phase preference logic function PPLPHIZ is tested with a three-phase testing equipment for distance protections. PPLPHIZ is tested in co-operation with the Five zone distance protection, quadrilateral and mho characteristic function ZQMPDIS . The distance protection and the phase preference logic shall be set to values according to the real set values to be used. The test is made by means of injection of voltage and current where the amplitude of both current and voltage and the phase angle between the voltage and current can be controlled.

During the test the following binary signals (outputs) shall be monitored:

- Trip signal from distance protection
- Start signal from phase preference logic

1. Connect the test set for injection of voltage and current.
2. Inject voltages and currents corresponding to a phase-to-phase to earth fault within zone 1 of the distance protection function. In the test one of the current inputs (one of the faulted phases) is disconnected. The remaining current is the fault current out on the protected line. All combinations of two phase-to-earth faults with one phase current are tested. The result shall be according to table 8. It should be checked that the fault will give phase-to-phase voltage, phase-to-earth voltage, zero-sequence voltage and phase current so that the conditions set for the logic are fulfilled.

Table 8: Operation at different combinations of faults and operation mode

OperMode	Fault type/Faulted phase current to the IED					
	L1L2N/IL1	L1L2N/IL2	L2L3N/IL2	L2L3N/IL3	L3L3N/IL1	L3L1N/IL3
No Filter	Trip	Trip	Trip	Trip	Trip	Trip
No Pref	Trip	Trip	Trip	Trip	Trip	Trip
1231c	Trip	No Trip	Trip	No Trip	No Trip	Trip
1321c	No Trip	Trip	No Trip	Trip	Trip	No Trip
123a	Trip	No Trip	Trip	No Trip	Trip	No Trip
132a	Trip	No Trip	No Trip	Trip	Trip	No Trip
213a	No Trip	Trip	Trip	No Trip	Trip	No Trip
231a	No Trip	Trip	Trip	No Trip	No Trip	Trip
312a	Trip	No Trip	No Trip	Trip	No Trip	Trip
321a	No Trip	Trip	No Trip	Trip	No Trip	Trip

6.3.4.1 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No*, under **Main menu/Tests/Function test modes/<Function group>/<Function>/<1:Function>** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.3.5 Power swing detection ZMRPSB

The aim is to verify that the settings of the Power swing detection function ZMRPSB is according to the setting table and to verify that ZMRPSB operates as expected.

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for ZMRPSB are available on the local HMI under **Main menu/Tests/Function status/Impedance/ZMRPSB(68)/1:ZMRPSB**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

Before starting this process, all impedance measuring zones shall be set and in operation. Test the outer resistive boarder in forward and reverse direction, *RLdOutFw* and *RLdOutRv* and the inner reactive boarder in forward and reverse direction *X1InFw* and *X1InRv*. See figure 15.

The corresponding resistive boarder for the inner resistive boundary and outer resistive boundary is calculated automatically from the setting of *kLdRFw* and *kLdRRv*.

The inner zone of ZMRPSB must cover all zones by at least 10% margin.

The test is mainly divided into two parts, one which aim is to verify that the settings are in accordance to the selective plane and a second part to verify the operation of ZMRPSB. The proposed test points for validation of the settings are numbered according to figure 15

Test of the interactions or combinations that are not configured are not considered in this instruction.



Figure 15: Operating principle and characteristic of the power swing detection function (settings parameters in italic)

Where:

RLdInFw = *RLdOutFw* · *kLdRFw*

RLdInRv = *RLdOutRv* · *kLdRRv*

X1OutFw = *X1InFw* + (*RLdOutFw* - RLdInFw)

X1OutRv = *X1InRv* + (*RLdOutFw* - RLdInFw)

6.3.5.1 Verifying the settings

Preconditions

The following output signal shall be configured to binary output available: ZOUT, measured impedance within outer impedance boundary.

1. Keep the measured current as close as possible to its rated value or lower. Keep it constant during the test, but ensure that it is higher than the set minimum operating current.
2. Ensure that the maximum continuous current to the IED does not exceed four times its rated value, if the measurement of the operating characteristics runs under constant voltage conditions.
3. Make the necessary connections and settings of the test equipment for test of point 1 according to figure 15.
4. Decrease the measured three-phase impedance slowly and observe the operation value for the signal ZOUT.
5. Compare the operation value with the set value.
6. Do the necessary change of the setting of the test equipment and repeat step 4 and step 5 for point 2, 3 and 4 according to figure 15.

6.3.5.2 Testing the power swing detection function ZMRPSB

Preconditions

The following output signals shall be configured to binary outputs: ZOUT, measured impedance within outer impedance boundary, ZIN, measured impedance within inner impedance boundary and START, power swing detection.

1. Slowly decrease the measured impedance in all three phases until the START signal gets activated.
2. Increase the measured voltages to their rated values.
3. Decrease instantaneously voltages in all three phases to the values, which are approximately 20% lower than the voltage that gives the set value *R1LIn* at the predefined test current.
4. The START signal must not appear.
5. Increase the measured voltages to their rated values.

6.3.5.3 Testing the *tR1* timer

Preconditions

- The input I0CHECK, residual current ($3I_0$) detection used to inhibit the start output must be configured to the output signal STPE on the FDPSPDIS function.
- The input BLKI02, block inhibit of the start output for subsequent residual current detection is connected to FALSE.

1. Program the test equipment for a single-phase to earth fault and energize FDPSPDIS and check that the input BLOCK on the power swing detection function ZMRPSB is activated.
2. Make a test sequence so that a single-phase to earth fault occurs after that the trajectory of the impedance has passed the outer and inner boundary of ZMRPSB during power swing. Use the result from test of ZMRPSB above to

determine when the fault shall be applied. The earth-fault must be activated before *tR1* has elapsed.
3. Start the sequence and observe that the START signal will not be activated.

6.3.5.4 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Impedance/ZMRPSB(68)/1:ZMRPSB** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.3.6 Automatic switch onto fault logic, voltage and current based ZCVPSOF

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for ZCVPSOF are available on the local HMI under **Main menu/Tests/Function status/Impedance/ZCVPSOF/1:ZCVPSOF**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

Automatic switch onto fault logic, voltage and current based function ZCVPSOF is checked using secondary injection tests together with the Scheme communication logic for distance or overcurrent protection function ZCPSCH and with the dead line detection function (DLD), which is embedded in ZCVPSOF. ZCVPSOF is activated either by the external input BC, or by the internal DLD. SDDRFUF is done with a pre-fault condition where the phase voltages and currents are at zero. A reverse three-phase fault with zero impedance and a three-phase fault with an impedance corresponding to the whole line is applied. This fault shall cause an instantaneous trip and result in a TRIP indication.

6.3.6.1 External activation of ZCVPSOF

1. Activate the switch onto fault BC input.
   During normal operating conditions, the BC input is de-energized.
2. Apply a three-phase fault condition corresponding to a fault at approximately 45% of the line or with an impedance at 50% of used zone setting and current greater than 30% of I_r.
3. Check that the correct trip outputs, external signals and indication are obtained.

6.3.6.2 Automatic initiation of ZCVPSOF

1. Deactivate the switch onto fault BC input.
2. Set current and voltage inputs to 0 for at least 1 second.
3. Apply a three-phase fault condition corresponding to a fault at approximately 45% of the line or with an impedance at 50% of used zone setting and current greater than 30% of I_r.
4. Check that the correct trip outputs, external signals and indication are obtained.

6.3.6.3 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Impedance/ZCVPSOF/1:ZCVPSOF** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4 Testing current protection functions

6.4.1 Instantaneous phase overcurrent protection 3-phase output PHPIOC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for PHPIOC are available on the local HMI under **Main menu/Tests/Function status/Current/PHPIOC(50,I>>)/1:PHPIOC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

To verify the settings the following fault type should be tested:

- Phase-to-earth fault

Ensure that the maximum continuous current, supplied from the current source used for the test of the IED, does not exceed four times the rated current value of the IED.

6.4.1.1 Measuring the operate limit of set values

1. Inject a phase current into the IED with an initial value below that of the setting.
2. Increase the injected current until the TRIP signal appears.
3. Switch the fault current off.

Observe: Do not exceed the maximum permitted overloading of the current circuits in the IED.

4. Compare the measured operating current with the set value.

6.4.1.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/PHPIOC(50,I>>)/1:PHPIOC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.2 Instantaneous phase overcurrent protection phase segregated output SPTPIOC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for SPTPIOC are available on the local HMI under **Main menu/Tests/Function status/Current/SPTPIOC(50,I>>)/1:SPTPIOC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

To verify the settings the following fault type should be tested:

- Phase-to-earth fault

Ensure that the maximum continuous current, supplied from the current source used for the test of the IED, does not exceed four times the rated current value of the IED.

1. Inject a phase current into the IED with an initial value below that of the setting.
2. Increase the injected current in the Ln phase until the TRLn (n=1-3) signal appears.
3. Switch the fault current off. Observe to not exceed the maximum permitted overloading of the current circuits in the IED.
4. Compare the measured operating current with the set value.

6.4.2.1 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/SPTPIOC(50,I>>)/1:SPTPIOC** for the

function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.3 Four step phase overcurrent protection 3-phase output OC4PTOC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for OC4PTOC are available on the local HMI under **Main menu/Tests/Function status/Current/OC4PTOC(51_67,4I>)/1:OC4PTOC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.4.3.1 Verifying the settings

1. Connect the test set for current injection to the appropriate IED phases.
   If there is any configuration logic that is used to enable or block any of the four available overcurrent steps, make sure that the step under test is enabled (for example, end fault protection).
   Connect the symmetrical three-phase injection current into phases L1, L2 and L3.
2. Connect the test set for the appropriate three-phase voltage injection to the IED phases L1, L2 and L3. The protection shall be fed with a symmetrical three-phase voltage.
3. Set the injected polarizing voltage slightly larger than the set minimum polarizing voltage (default is 5% of *UBase*) and set the injection current to lag the appropriate voltage by an angle of 55° if forward directional function is selected.
   If *1 out of 3* currents for operation is chosen: The voltage angle of phase L1 is the reference.
   If reverse directional function is selected, set the injection current to lag the polarizing voltage by an angle equal to 235° (equal to 55° + 180°).
4. Increase the injected current and note the operate value of the tested step of the function.
5. Decrease the current slowly and note the reset value.
6. If the test has been performed by injection of current in phase L1, repeat the test, injecting current into phases L2 and L3 with polarizing voltage connected to phases L2, respectively L3 (*1 out of 3* currents for operation).
7. If the test has been performed by injection of current in phases L1 – L2, repeat the test, injecting current into phases L2 – L3 and L3 – L1 with the appropriate phase angle of injected currents.
8. Block higher set stages when testing lower set stages by following the procedure described below.
9. Connect a trip output contact to a timer.

10. Set the injected current to 200% of the operate level of the tested stage, switch on the current and check the time delay.
    For inverse time curves, check the operate time at a current equal to 110% of the operate current for *txMin*.
11. Check that all trip and start contacts operate according to the configuration (signal matrixes)
12. Reverse the direction of the injected current and check that the protection does not operate.
13. Repeat the above described tests for the higher set stages.
14. Finally check that start and trip information is stored in the event menu.

Verification of the non-directional phase overcurrent function is done as instructed above, without applying any polarizing voltage.

6.4.3.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/OC4PTOC(51_67,4I>)/1:OC4PTOC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.4 Four step phase overcurrent protection phase segregated output OC4SPTOC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for OC4SPTOC are available on the local HMI under **Main menu/Tests/Function status/Current/OC4SPTOC(51_67,4I>)/1:OC4SPTOC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.4.4.1 Verifying the settings

1. Connect the test set for appropriate current injection to the appropriate IED phases.
   If there is any configuration logic that is used to enable/block any of the four available overcurrent steps, make sure that the step under test is enabled, for example end fault protection. Connect the symmetrical three-phase injection current into phases L1, L2 and L3.
2. Connect the test set for the appropriate three-phase voltage injection to the IED phases L1, L2 and L3.

Make sure that the protection is fed with a symmetrical three-phase voltage.

3. Set the injected polarizing voltage slightly larger than the set minimum polarizing voltage (default is 5% of *UBase*) and set the injection current to lag the appropriate voltage by an angle of about 55° if forward directional function is selected.
   If reverse directional function is selected, set the injection current to lag the polarizing voltage by an angle equal to 235° (equal to 55° + 180°).
4. Increase the injected current and note the operated value of the tested step of the function.
5. Decrease the current slowly and note the reset value.
6. If the test has been performed by injection of current in phase L1, repeat the test when injecting current into phases L2 and L3 with polarizing voltage connected to phases L2 respectively L3 (1 of 3 currents for operation).
7. If the test has been performed by injection of current in phases L1 – L2, repeat the test when injecting current into phases L2 – L3 and L3 – L1 with appropriate phase angle of injected currents.
8. Block higher set stages when testing lower set stages according to below.
9. Connect a trip output contact to a timer.
10. Set the injected current to 200% of the operate level of the tested stage, switch on the current and check the time delay.
    For inverse time curves, check the operate time at a current equal to 110% of the operate current for tnMin.
11. Check that all trip and start contacts operate according to the configuration (signal matrixes).
12. Reverse the direction of the injected current and check that the protection does not operate.
13. Repeat the above-described tests for the higher set stages.
14. Finally check that start and trip information is stored in the event menu.

Check of the non-directional phase over-current function. This is done in principle as instructed above, without applying any polarizing voltage.

6.4.4.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/OC4SPTOC(51_67,4I>)/1:OC4SPTOC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.5 Instantaneous residual overcurrent protection EFPIOC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for EFPIOC are available on the local HMI under **Main menu/Tests/Function status/Current/EFPIOC(50N,IN>>)/1:EFPIOC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

To verify the settings the following fault type should be tested:

- Phase-to-earth fault

Ensure that the maximum continuous current, supplied from the current source used for the test of the IED, does not exceed four times the rated current value of the IED.

6.4.5.1 Measuring the operate limit of set values

1. Inject a phase current into the IED with an initial value below that of the setting.
2. Increase the injected current in the Ln or in the neutral (summated current input) phase until the TRIP signal appears.
3. Switch the fault current off.
   Observe to not exceed the maximum permitted overloading of the current circuits in the IED
4. Compare the measured operating current with the set value.

6.4.5.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/EFPIOC(50N,IN>>)/1:EFPIOC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.6 Four step residual overcurrent protection, zero or negative sequence direction EF4PTOC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for EF4PTOC are available on the local HMI under **Main menu/Tests/Function status/Current/EF4PTOC(51N67N,4IN>)/**

X:EF4PTOC. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.4.6.1 Four step directional residual overcurrent protection

1. Connect the test set for single current injection to the appropriate IED terminals. Connect the injection current and voltage to terminals L1 and neutral.
2. Set the injected polarizing voltage slightly larger than the set minimum polarizing voltage (default 1% of Ur) and set the injection current to lag the voltage by an angle equal to the set reference characteristic angle (*AngleRCA*), if the forward directional function is selected.
   If reverse directional function is selected, set the injection current to lag the polarizing voltage by an angle equal to RCA+ 180°.
3. Increase the injected current and note the value at which the studied step of the function operates.
4. Decrease the current slowly and note the reset value.
5. If the test has been performed by injection of current in phase L1, repeat the test, injecting current into terminals L2 and L3 with a polarizing voltage connected to terminals L2, respectively L3.
6. Block lower set steps when testing higher set steps according to the instructions that follow.
7. Connect a trip output contact to a timer.
8. Set the injected current to 200% of the operate level of the tested step, switch on the current and check the time delay.
   For inverse time curves, check the operate time at a current equal to 110% of the operate current for *txMin*.
9. Check that all trip and start contacts operate according to the configuration (signal matrixes)
10. Reverse the direction of the injected current and check that the step does not operate.
11. Check that the protection does not operate when the polarizing voltage is zero.
12. Repeat the above described tests for the higher set steps.
13. Finally, check that start and trip information is stored in the event menu.

6.4.6.2 Four step non-directional residual overcurrent protection

1. Do as described in "Four step directional residual overcurrent protection", but without applying any polarizing voltage.

6.4.6.3 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/EF4PTOC(51N67N,4IN>)/X:EF4PTOC**

for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.7 Sensitive directional residual overcurrent and power protection SDEPSDE

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for SDEPSDE are available on the local HMI under **Main menu/Tests/Function status/Current/SDEPSDE(67N,IN<->)/1:SDEPSDE**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.4.7.1 Measuring the operate and time limit for set values

Operation mode $3I_0 \cdot \cos\varphi$

Procedure

1. Set the polarizing voltage to 1.2 · *UNRel>* and the phase angle between voltage and current to the set characteristic angle (*RCADir*), the current lagging the voltage.
   Take setting *RCAComp* into consideration if not equal to *0*.
2. Measure that the operate current of the set directional element is equal to the *INcosPhi>* setting.
   The I Dir (I_0 cos(Angle)) function activates the START and STDIRIN output.
3. Measure with angles φ = RCADir +/- 45° that the measuring element operates when I_0 cos (*RCADir* - φ) = I_0cos(+/-45) = *INcosPhi>*.
4. Compare the result with the set value.
   Take the set characteristic into consideration, see figure 16 and figure 17.
5. Measure the operate time of the timer by injecting a current two times the set *INcosPhi>* value and the polarizing voltage 1.2 · *UNRel>*.

$$Tinv = kSN \cdot Sref / 3I_{0test} \cdot \cos(\varphi)$$

(Equation 1)

6. Compare the result with the expected value.
   The expected value depends on whether definite or inverse time was selected.
7. Set the polarizing voltage to zero and increase until the boolean output signal UNREL is activated, which is visible in the Application Configuration in PCM600 when the IED is in online mode. Compare the voltage with the set value *UNRel>*.
8. Continue to test another function or complete the test by setting the test mode to *Off*.



Figure 16: Characteristic with ROADir restriction



Figure 17: Explanation of RCAcomp

Operation mode $3I_0 \cdot 3U_0 \cdot \cos\varphi$

1. Set the polarizing voltage to 1.2 · *UNRel>* and the phase angle between voltage and current to the set characteristic angle (*RCADir*), the current lagging the voltage.
2. Measure that the operate power is equal to the *SN>* setting for the set directional element.
   Note that for operation, both the injected current and voltage must be greater than the set values *INRel>* and *UNRel>* respectively.
   The function activates the START and STDIRIN outputs.
3. Measure with angles φ = *RCADir* +/- 45° that the measuring element operates when $3I_0 \cdot 3U_0 \cdot \cos$ (*RCADir* - φ) = 3I0 · 3U0 · cos(+/-45) = *SN>*.
4. Compare the result with the set value. Take the set characteristic into consideration, see figure 16 and figure 17.
5. Measure the operate time of the timer by injecting 1.2 · *UNRel>* and a current to get two times the set *SN>* operate value.

$$Tinv = kSN \cdot Sref / 3I_{0test} \cdot 3U_{0test} \cdot \cos(\varphi)$$

(Equation 2)

6. Compare the result with the expected value.
   The expected value depends on whether definite or inverse time was selected.
7. Continue to test another function or complete the test by setting the test mode to *Off*.

Operation mode $3I_0$ and φ

1. Set the polarizing voltage to 1.2 · *UNRel>* and the phase angle between voltage and current to the set characteristic angle (*RCADir*), the current lagging the voltage.
2. Measure that the operate power is equal to the *INDir>* setting for the set directional element.

   Note that for operation, both the injected current and voltage must be greater than the set values *INRel>* and *UNRel>* respectively.

   The function activates the START and STDIRIN output.
3. Measure with angles φ around *RCADir +/- ROADir*.
4. Compare the result with the set values, refer to figure 18 for example characteristic.
5. Measure the operate time of the timer by injecting a current to get two times the set *SN_>* operate value.

$$Tinv = kSN \cdot Sref / 3I_{0test} \cdot 3U_{0test} \cdot \cos(\varphi)$$

(Equation 3)

6. Compare the result with the expected value.
   The expected value depends on whether definite or inverse time was selected.
7. Continue to test another function or complete the test by setting the test mode to *Off*.



Figure 18: Example characteristic

Non-directional earth fault current protection

Procedure

1. Measure that the operate current is equal to the *INNonDir>* setting.
   The function activates the START and STDIRIN output.
2. Measure the operate time of the timer by injecting a current of 200% of the operate value.
3. Compare the result with the expected value.
   The expected value depends on whether definite time *tINNonDir* or inverse time was selected.
4. Continue to test another function or complete the test by setting the test mode to *Off*.

Residual overvoltage release and protection

Procedure

1. Measure that the operate voltage is equal to the *UN>* setting.
   The function activates the START and STUN signals.
2. Measure the operate time by injecting a voltage 1.2 timers set *UN>* operate value.
3. Compare the result with the set *tUN* operate value.
4. Inject a voltage 0.8 · *UNRel>* and a current high enough to operate the directional function at the chosen angle.
5. Increase the voltage until the directional function is released.
6. Compare the measured value with the set *UNRel>* operate value.

6.4.7.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/SDEPSDE(67N,IN<->)/1:SDEPSDE** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.8 Thermal overload protection, one time constant, Celsius/ Fahrenheit LCPTTR/LFPTTR

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for LCPTTR/LFPTTR are available on the local HMI under , **Main menu/Tests/Function status/Current/LCPTTR(26,T>)/1:LCPTTR**, **Main menu/Tests/Function status/Current/LFPTTR(26,T>)/1:LFPTTR**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

Check that the input logical signal BLOCK is logical zero and that on the local HMI, the logical signal TRIP, START and ALARM are equal to logical zero.

6.4.8.1 Testing the protection without external temperature compensation (NonComp)

1. Quickly set the measured current (fault current) in one phase to about 300% of *IRef* (to minimise the trip time), and switch the current off.
2. Reset the thermal memory on the local HMI under **Main menu/Clear/Clear temperature constant/LFPTTR(26,8>)/1:LFPTTR**, **Main menu/Clear/Clear temperature constant/LCPTTR(26,8>)/1:LCPTTR**
3. Switch the fault current on and take note of the temperature, available on the local HMI under **Main menu/Tests/Function status/Current/LFPTTR(26,8>)/1:LFPTTR/Outputs/TEMP**, **Main menu/Tests/Function status/Current/LCPTTR(26,8>)/1:LCPTTR/Outputs/TEMP**
4. Check the time until the alarm limit has reached the *AlarmTemp* level during injection.
   Monitor the signal ALARM until it appears on the corresponding binary output or on the local HMI.
5. Compare the measured temperature with the setting.
6. Measure the LCPTTR/LFPTTRprotection trip time.
   Use the TRIP signal from the configured binary output to stop the timer.
7. Take the TEMP readings.
   Compare with the setting of *TripTemp*.
8. Activate the BLOCK binary input.

The signals ALARM, START and TRIP should disappear.

9. Reset the BLOCK binary input.
10. Check the reset limit (TdReset).
    Monitor the signal START until it disappears on the corresponding binary output or on the local HMI, take the TEMP readings and compare with the setting of *ReclTemp*.
11. Compare the measured trip time with the setting according to the formula.
12. Reset the thermal memory.
13. Continue to test another function or end the test by changing the test mode setting to *Off*.

6.4.8.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/LCPTTR(26,T>)/1:LCPTTR**, **Main menu/Tests/Function test modes/Current/LFPTTR(26,T>)/1:LFPTTR** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.9 Breaker failure protection, phase segregated activation and output CCRBRF

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for CCRBRF are available on the local HMI under **Main menu/Tests/Function status/Current/CCRBRF(50BF)/1:CCRBRF**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The Breaker failure protection, 3-phase activation and output function CCRBRF should normally be tested in conjunction with some other function that provides a start signal. An external START signal can also be used.

To verify the settings in the most common back-up trip mode *1 out of 3*, it is sufficient to test phase-to-earth faults.

At mode *2 out of 4* the phase current setting, *IP>* can be checked by single-phase injection where the return current is connected to the summated current input. The value of residual (earth fault) current IN set lower than *IP>* is easiest checked in back-up trip mode *1 out of 4*.

6.4.9.1 Checking the phase current operate value, *IP>*

Check the current level *IP>* where setting *FunctionMode=Current* and setting *BuTripMode=1 out of 3* or *2 out of 4* as set under **Main menu/Settings/IED Settings/Current/CCRBRF(50BF)/1:CCRBRF**.

1. Apply the fault condition, including START of CCRBRF, with a current below set *IP>*.
2. Repeat the fault condition and increase the current in steps until a trip occurs.
3. Compare the result with the set *IP>*.
4. Disconnect AC and START input signals.

Note! If *NoI>check* or *Retrip off* is set, only back-up trip can be used to check set *IP>*.

6.4.9.2 Checking the residual (earth fault) current operate value *IN>* set below *IP>*

Check the low set *IN>* current where setting *FunctionMode = Current* and setting *BuTripMode = 1 out of 4* as set under **Main menu/Settings/IED Settings/Current/CCRBRF(50BF)/1:CCRBRF**.

1. Apply the fault condition, including START of CCRBRF, with a current just below set *IN>Pickup_N*.
2. Repeat the fault condition and increase the current in steps until trip appears.
3. Compare the result with the set *IN>*.
4. Disconnect AC and START input signals.

6.4.9.3 Checking the re-trip and back-up times

The check of the set times can be made in connection with the check of operate values above.

Choose the applicable function and trip mode, such as *FunctionMode = Current* and setting *RetripMode = No* CBPos. Check as set under **Main menu/Settings/IED Settings/Current/CCRBRF(50BF)/1:CCRBRF**.

1. Apply the fault condition, including start of CCRBRF, well above the set current value. Measure time from START of CCRBRF.
2. Check the re-trip *t1* and back-up trip times *t2*.
3. Disconnect AC and START input signals.

6.4.9.4 Verifying the re-trip mode

Choose the mode below, which corresponds to the actual case.

In the cases below it is assumed that *FunctionMode = Current* as set under **Main menu/Settings/IED Settings/Current/CCRBRF(50BF)/1:CCRBRF**.

Checking the case without re-trip, *RetripMode = Retrip Off*

1. Set *RetripMode = Retrip Off*.
2. Apply the fault condition, including start of CCRBRF, well above the set current value.
3. Verify that no re-trip, but back-up trip is achieved after set time.
4. Disconnect AC and START input signals.

Checking the re-trip with current check, *RetripMode = CB Pos Check*

1. Set *RetripMode = CB Pos Check*.
2. Apply the fault condition, including start of CCRBRF, well above the set current value.
3. Verify that re-trip is achieved after set time *t1* and back-up trip after time *t2*
4. Apply the fault condition, including start of CCRBRF, with current below set current value.
5. Verify that no re-trip, and no back-up trip is obtained.
6. Disconnect AC and START input signals.

Checking re-trip without current check, *RetripMode = No CBPos Check*

1. Set *RetripMode = No CBPos Check*.
2. Apply the fault condition, including start of CCRBRF, without any current.
3. Verify that re-trip is achieved after set time *t1*, and back-up trip after time *t2*.
4. Apply the fault condition, including start of CCRBRF, with current below set current value.
5. Verify that re-trip is achieved after set time *t1*, but no back-up trip is obtained.
6. Disconnect AC and START input signals.

6.4.9.5 Verifying the back-up trip mode

In the cases below it is assumed that *FunctionMode = Current* is selected.

Checking that back-up tripping is not achieved at normal CB tripping

Use the actual tripping modes. The case below applies to re-trip with current check.

1. Apply the fault condition, including start of CCRBRF, with phase current well above set value *IP*.
2. Interrupt the current, with a margin before back-up trip time, *t2*. It may be made at issue of re-trip command.
3. Check that re-trip is achieved, if selected, but no back-up trip is obtained.
4. Disconnect AC and START input signals.

The normal mode *BuTripMode = 1 out of 3* should have been verified in the tests above. In applicable cases the modes *1 out of 4* and *2 out of 4* can be checked. Choose the mode below, which corresponds to the actual case.

Checking the case *BuTripMode = 1 out of 4*

It is assumed that the earth-fault current setting *IN>* is below phase current setting *IP>*.

1. Set *BuTripMode = 1 out of 4*.
2. Apply the fault condition, including start of CCRBRF, with one-phase current below set *IP>* but above *IN>*. The residual earth-fault should then be above set *IN>*.
3. Verify that back-up trip is achieved after set time. If selected, re-trip should also appear.
4. Disconnect AC and START input signals.

Checking the case *BuTripMode = 2 out of 4*

The earth-fault current setting *IN>* may be equal to or below phase-current setting *IP>*.

1. Set *BuTripMode = 2 out of 4*.
2. Apply the fault condition, including start of CCRBRF, with one-phase current above set *IP>* and residual (earth fault) above set *IN>*.
3. Verify that back-up trip is achieved after set time. If selected, re-trip should also appear.
4. Apply the fault condition, including start of CCRBRF, with at least one-phase current below set *IP>* and residual (earth fault) above set *IN>*. The current may be arranged by feeding three- (or two-) phase currents with equal phase angle (I0-component) below *IP>*, but of such value that the residual (earth fault) current ($3I_0$) will be above set value *IN>*.
5. Verify that back-up trip is not achieved.
6. Disconnect AC and START input signals.

6.4.9.6 Verifying the case *RetripMode = Contact*

It is assumed that re-trip without current check is selected, *RetripMode = Contact*.

1. Set *FunctionMode = Contact*
2. Apply input signal for CB closed to input CBCLDL1, CBCLD2 or CBCDL3.
3. Apply input signal, for start of CCRBRF.
4. Verify that phase selection re-trip and back-up trip are achieved after set times.
5. Disconnect the start signal. Keep the CB closed signal.
6. Apply input signal, for start of CCRBRF.
7. Arrange disconnection of CB closed signal well before set back-up trip time *t2*.
8. Verify that back-up trip is not achieved.
9. Disconnect injected AC and START input signals.

6.4.9.7 Verifying the function mode *Current&Contact*

To be made only when *FunctionMode = Current&Contact* is selected.

Checking the case with fault current above set value *IP>*

The operation shall be as in *FunctionMode = Current*.

1. Set *FunctionMode = Current&Contact*.
2. Leave the inputs for CB close inactivated. These signals should not influence.
3. Apply the fault condition, including start of CCRBRF, with current above the set *IP>* value.
4. Check that the re-trip, if selected, and back-up trip commands are achieved.
5. Disconnect injected AC and START input signals.

Checking the case with fault current below set value *I>BlkCont*

The case shall simulate a case where the fault current is very low and operation will depend on CB position signal from CB auxiliary contact. It is suggested that re-trip without current check is used, setting *RetripMode = No CBPos Check*.

1. Set *FunctionMode = Current&Contact*.
2. Apply input signal for CB closed to relevant input or inputs CBCLDL1 (2 or 3)
3. Apply the fault condition with input signal(s) for start of CCRBRF. The value of current should be below the set value *I>BlkCont*
4. Verify that phase selection re-trip (if selected) and back-up trip are achieved after set times. Failure to trip is simulated by keeping the signal(s) CB closed activated.
5. Disconnect the AC and the START signal(s). Keep the CB closed signal(s).
6. Apply the fault and the start again. The value of current should be below the set value *I>BlkCont*.
7. Arrange disconnection of BC closed signal(s) well before set back-up trip time *t2*. It simulates a correct CB tripping.
8. Verify that back-up trip is not achieved. Re-trip can appear for example, due to selection “Re-trip without current check”.
9. Disconnect injected AC and START input signals.

6.4.9.8 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/CCRBRF(50BF)/X:CCRBRF** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.10 Breaker failure protection, phase segregated activation and output CSPRBRF

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for CSPRBRF are available on the local HMI under **Main menu/Tests/Function status/Current/CSPRBRF(50BF)/1:CSPRBRF**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

Breaker failure protection, phase segregated activation and output CSPRBRFshould normally be tested in conjunction with some other function that provides a start signal. An external START signal can also be used.

To verify the settings in the most common back-up trip mode *1 out of 3* it is sufficient to test phase-to-earth-faults.

At mode *2 out of 4* the Phase current setting, *IP>* can be checked by single phase injection where the return current is connected to the summed current input. The value of residual (EF) current IN set lower than *IP>* is most easily checked in backup trip mode *1 out of 4*.

6.4.10.1 Checking the phase current operate value, IP>

Check the current level *IP>* where setting *FunctionMode = Current* and setting *BuTripMode = 1 out of 3* or *2 out of 4* as set under **Main menu/Settings/IED Settings/Current/CSPRBRF(50BF)/1:CSPRBRF**.

1. Apply the fault condition, including START of CSPRBRF, with a current below set *IP>*.
2. Repeat the fault condition and increase the current in steps until a trip occurs.
3. Compare the result with the set *IP>*.
4. Disconnect AC and START input signals.

If “No I> check” or “*Retrip off*” is set, only back-up trip can be used to check set *IP>*.

6.4.10.2 Checking the residual (EF) current operate value *IN>* set below IP>

Check the low set *IN>* current where setting *FunctionMode = Current* and setting *BuTripMode = 1 out of 4* as set under **Main menu/Settings/IED Settings/Current/CSPRBRF(50BF)1:CSPRBRF**.

1. Apply the fault condition, including start of CSPRBRF , with a current just below set *IN>*.
2. Repeat the fault condition and increase the current in steps until trip appears.
3. Compare the result with the set *IN>*.
4. Disconnect AC and start input signals.

6.4.10.3 Checking the re-trip and back-up times

The check of the set times can be made in connection with the check of operate values above. Choose the applicable function and trip mode, such as *FunctionMode = Current* and setting *RetripMode = No CBPos Check* as set under **Main menu/Settings/IED Settings/CSPRBRF(50BF)/Current/1:CSPRBRF**.

1. Apply the fault condition, including start of CSPRBRF, well above the set current value. Measure time from start of CSPRBRF.
2. Check the re-trip *t1* and back-up trip times *t2*.
3. Disconnect AC and start input signals.

6.4.10.4 Verifying the *RetripMode*

1. Choose the mode below, which corresponds to the actual case. In the cases below it is assumed that *FunctionMode = Current* as set under **Main menu/Settings/IED Settings/Current/CSPRBRF(50BF)/1:CSPRBRF**
2. Continue with the cases shown below.

Checking the re-trip with current check, *RetripMode = CB Pos Check*

1. Set *RetripMode = CB Pos Check* check.
2. Apply the fault condition, including start of CSPRBRF, well above the set current value.
3. Verify that retrip is achieved after set time *t1* and back-up trip after time *t2*
4. Apply the fault condition, including start of CSPRBRF, with current below set current value.
5. Verify that no re-trip, and no back-up trip is obtained.
6. Disconnect AC and start input signals.

Checking the case without re-trip, *RetripMode = Retrip Off*

1. *Set RetripMode = Retrip Off*.
2. Apply the fault condition, including start of CSPRBRF , well above the set current value.
3. Verify that no re-trip, but back-up trip is achieved after set time.
4. Disconnect AC and start input signals.

Checking re-trip without current check, *RetripMode = No CBPos Check*

1. Set *RetripMode = No CBPos Check*.
2. Apply the fault condition, including start of CSPRBRF, well above the set current value.
3. Verify that re-trip is achieved after set time *t1*, and back-up trip after time *t2*.
4. Apply the fault condition, including start of CSPRBRF, with current below set current value.
5. Verify that re-trip is achieved after set time *t1*, but no back-up trip is obtained.
6. Disconnect AC and start input signals.

6.4.10.5 Verifying the case *RetripMode = No CB Pos Check*

It is assumed that re-trip without current check is selected, *RetripMode = No CB Pos Check*.

1. Set *FunctionMode = Contact*.
2. Apply input signal for CB closed to input CBCLD.
3. Apply input signal, for start of CSPRBRF.
4. Verify that re-trip and back-up trip are achieved after set times.
5. Disconnect the start signal. Keep the CB closed signal.
6. Apply input signal, for start of CSPRBRF.
7. Arrange disconnection of CB closed signal well before set back-up trip time *t2*.
8. Verify that back-up trip is not achieved.
9. Disconnect injected AC and start input signals.

6.4.10.6 Verifying the function mode *Current&Contact*

- To be made only when *FunctionMode = Current&Contact* is selected.
- Checking the case with fault current above set value *IP>*.
- The operation shall be as in *FunctionMode = Current&Contact*.

1. Set *FunctionMode* = *Current&Contact*.
2. Leave the inputs for CB close inactivated. These signals should not influence.
3. Apply the fault condition, including start of CSPRBRF, with current above the set *IP>* value.
4. Check that the re-trip, if selected, and back-up trip commands are achieved.
5. Disconnect injected AC and start input signals.

6.4.10.7 Checking the case with fault current below set value *I>BlkCont*

The case shall simulate a case where the fault current is very low and operation will depend on CB position signal from CB auxiliary contact. It is suggested that retrip without current check is used; setting *RetripMode* = *No CBPos Check*.

1. Set *FunctionMode* = *Current & Contact* check.
2. Apply input signal for CB closed to relevant input or inputs CBCLDL1, CBCLDL2, or CBCLDL3
3. Apply the fault condition with input signal(s) for start of CSPRBRF. The value of current should be below the set value *I>BlkCont*.
4. Verify that phase selection re-trip (if selected) and back-up trip are achieved after set times. Failure to trip is simulated by keeping the signal(s) CB closed activated.
5. Disconnect the AC and the start signal(s). Keep the CB closed signal(s).
6. Apply the fault and the start again. The value of current should be below the set value *I>BlkCont*.
7. Arrange disconnection of BC closed signal(s) well before set back-up trip time *t2*. It simulates a correct CB tripping.
8. Verify that back-up trip is not achieved. Re-trip can appear for example, due to selection "Re-trip without current check".
9. Disconnect injected AC and start of input signals.

6.4.10.8 Checking the phase current operate value, *IP>*

Check the low set *IP>* current where setting *FunctionMode* = *Current* and setting *BuTripMode* = *1 out of 3* or *2 out of 4* as set under **Main menu/Settings/IED Settings/Current/CSPRBRF(50BF)/1:CSPRBRF**.

1. Apply the fault condition, including start of CSPRBRP, with a current just below set *IP>*.
2. Repeat the fault condition and increase the current in steps until trip appears.
3. Compare the result with the set *IP>*.
4. Disconnect AC and start input signals.

If *NoI> check* or *Retrip off* is set, only back-up trip can be used to check set *IP>*.

6.4.10.9 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/CSPRBRF(50BF)/1:CSPRBRF** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.11 Stub protection STBPTOC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Logical signals for STBPTOC protection are available on the local HMI under**Main menu/Tests/Function status/Current/STBPTOC(50STB)/1:STBPTOC/Inputs or Outputs**

Values of the logical signals for STBPTOC are available on the local HMI under **Main menu/Tests/Function status/Current/STBPTOC(50STB,I>)/1:STBPTOC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.4.11.1 Measuring the operate limit of set values

1. Check that the input logical signals BLOCK and RELEASE and the output logical signal TRIP are all logical zero.
2. Activate the input RELEASE on the STBPTOC function block
3. For a short while inject a current (fault current) in one phase to about 110% of the set operating current, and switch the current off.
   Observe to not exceed the maximum permitted overloading of the current circuits in the IED.
4. Switch the fault current on and measure the operating time of STBPTOC.
   Use the TRIP signal from the configured binary output to stop the timer. The operation should be instantaneously.
5. Activate the input BLOCK on the STBPTOC function block.
6. Switch on the fault current (110% of the setting).
   No TRIP signal should appear.
7. Switch off the fault current.
8. For a short while inject a current (fault current) in same phase to about 90% of the set operating current, and switch the current off.
9. Switch the fault current on.
   No TRIP signal should appear.
10. Switch off the fault current.
11. Reset the RELEASE binary input.
12. Switch the fault current on.

No TRIP signal should appear.
13. Switch the fault current off.

6.4.11.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/STBPTOC(50STB,I>)/1:STBPTOC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.12 Pole discordance protection CCRPLD

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for CCRPLD are available on the local HMI under **Main menu/Tests/Function status/Current/CCRPLD(52PD)/X:CCRPLD**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.4.12.1 Verifying the settings

1. When CCRPLD is set for external, set setting *ContSel* to *On* under **Main menu/Settings/IED Settings/Current/CCRPLD/1:CCRPLD** to activate the logic that detects pole discordance when external pole discordance signaling is used (input EXTPDIND) in the application configuration.
2. Activate the input EXTPDIND on CCRPLD function block, and measure the operating time of CCRPLD.
3. Compare the measured time with the set value *tTrip*.
4. Reset the EXTPDIND input.
5. When CCRPLD is set for unsymmetrical current detection with CB monitoring, set setting *CurrSel* under **Main menu/Settings/IED Settings/Current/CCRPLD/1:CCRPLD** to *On*.
   Use the TRIP signal from the configured binary output to stop the timer.
6. Repeat point 4 and 5 using OPENCMD instead of CLOSECMD. Set all three currents to 110% of *CurrRelLevel*. Activate CLOSECMD.
   NO TRIP signal should appear due to symmetrical condition.

6.4.12.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/CCRPLD(52PD)/X:CCRPLD** for the

function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.13 Broken conductor check BRCPTOC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for BRCPTOC are available on the local HMI under **Main menu/Tests/Function status/Current/BRCPTOC(46,lub)/X:BRCPTOC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.4.13.1 Measuring the operate and time limit of set values

1. Check that the input logical signal BLOCK to the BRCPTOC function block is logical zero and note on the local HMI that the output signal TRIP from the BRCPTOC function block is equal to the logical 0.
2. Set the measured current (fault current) in one phase to about 110% of the set operating current *IP>*.
   Observe to not exceed the maximum permitted overloading of the current circuits in the terminal.
3. Switch on the fault current and measure the operating time of BRCPTOC.
   TRIP is controlled by Gate 13 in the configuration.
   Use the TRIP signal from the configured binary output to stop the timer.
4. Compare the measured time with the set value *tOper*.
5. Activate the BLOCK binary input.
6. Switch on the fault current (110% of the setting) and wait longer than the set value *tOper*.
   No TRIP signal should appear.
7. Switch off the fault current.
8. Set the measured current (fault current) in same phase to about 90% of the set operating current *IP>*. Switch off the current.
9. Switch on the fault current and wait longer than the set value *tOper*.
   No TRIP signal should appear.
10. Switch off the fault current.

6.4.13.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/BRCPTOC(46,lub)/X:BRCPTOC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.14 Directional underpower protection GUPPDUP

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for GUPPDUP are available on the local HMI under **Main menu/Tests/Function status/Current/GUPPDUP(37,P<)/1:GUPPDUP**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.4.14.1 Verifying the settings

The underpower protection shall be set to values according to the real set values to be used.

The test is made by means of injection of voltage and current where the amplitude of both current and voltage and the phase angle between the voltage and current can be controlled. During the test, the analog outputs of active and reactive power shall be monitored.

1. Connect the test set for injection of voltage and current corresponding to the mode to be used in the application. If a three-phase test set is available this could be used for all the modes. If a single-phase current/voltage test set is available the test set should be connected to a selected input for one-phase current and voltage.
   Use the formulas stated in Table 9 for the different calculation modes used. The set mode *Mode* can be found on the local HMI under **Main menu/ Settings/IED Settings/Current/GUPPDUP(37,P<)/1:GUPPDUP/General**.

Table 9: Calculation modes

Set value: *Mode*	Formula used for complex power calculation
L1, L2, L3	$\bar{S} = \bar{U}_{L1} \cdot \bar{I}_{L1}^{*} + \bar{U}_{L2} \cdot \bar{I}_{L2}^{*} + \bar{U}_{L3} \cdot \bar{I}_{L3}^{*}$ (Equation 4)
Arone	$\bar{S} = \bar{U}_{L1L2} \cdot \bar{I}_{L1}^{*} - \bar{U}_{L2L3} \cdot \bar{I}_{L3}^{*}$ (Equation 5)
PosSeq	$\bar{S} = 3 \cdot \bar{U}_{PosSeq} \cdot \bar{I}_{PosSeq}^{*}$ (Equation 6)
L1L2	$\bar{S} = \bar{U}_{L1L2} \cdot (\bar{I}_{L1}^{*} - \bar{I}_{L2}^{*})$ (Equation 7)

Table continues on next page

Set value: *Mode*	Formula used for complex power calculation
L2L3	$\bar{S} = \bar{U}_{L2L3} \cdot (\bar{I}_{L2}^{*} - \bar{I}_{L3}^{*})$ (Equation 8)
L3L1	$\bar{S} = \bar{U}_{L3L1} \cdot (\bar{I}_{L3}^{*} - \bar{I}_{L1}^{*})$ (Equation 9)
L1	$\bar{S} = 3 \cdot \bar{U}_{L1} \cdot \bar{I}_{L1}^{*}$ (Equation 10)
L2	$\bar{S} = 3 \cdot \bar{U}_{L2} \cdot \bar{I}_{L2}^{*}$ (Equation 11)
L3	$\bar{S} = 3 \cdot \bar{U}_{L3} \cdot \bar{I}_{L3}^{*}$ (Equation 12)

2. Adjust the injected current and voltage to the set values in % of *IBase* and *UBase* (converted to secondary current and voltage). The angle between the injected current and voltage shall be set equal to the set direction *Angle1*, angle for stage 1 (equal to 0° for low forward power protection and equal to 180° for reverse power protection). Check that the monitored active power is equal to 100% of rated power and that the reactive power is equal to 0% of rated power.
3. Change the angle between the injected current and voltage to *Angle1* + 90°. Check that the monitored active power is equal to 0% of rated power and that the reactive power is equal to 100% of rated power.
4. Change the angle between the injected current and voltage back to 0°. Decrease the current slowly until the START1 signal, start of stage 1, is activated.
5. Increase the current to 100% of *IBase*.
6. Switch the current off and measure the time for activation of TRIP1, trip of stage 1.
7. If a second stage is used, repeat steps 2 to 6 for the second stage.

6.4.14.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/GUPPDUP(37,P<)/1:GUPPDUP** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.4.15 Directional overpower protection GOPPDOP

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for GOPPDOP are available on the local HMI under **Main menu/Tests/Function status/Current/GOPPDOP(32,P>)/X:GOPPDOP**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.4.15.1 Verifying the settings

The overpower protection shall be set to values according to the real set values to be used. The test is made by means of injection of voltage and current where the amplitude of both current and voltage and the phase angle between the voltage and current can be controlled. During the test the analog outputs of active and reactive power shall be monitored.

1. Connect the test set for injection of voltage and current corresponding to the mode to be used in the application. If a three phase test set is available this could be used for all the modes. If a single phase current/voltage test set is available the test set should be connected to a selected input for one phase current and voltage.
   Use the formulas stated in Table 9 for the different calculation modes used. The set mode *Mode* can be found under **Main menu/Settings/IED Settings/ Current/GOPPDOP(32,P>)/1:GOPPDOP/General**.
2. Adjust the injected current and voltage to the set rated values in % of *IBase* and *UBase* (converted to secondary current and voltage). The angle between the injected current and voltage shall be set equal to the set direction *Angle1*, angle for stage 1 (equal to 0° for low forward power protection and equal to 180° for reverse power protection). Check that the monitored active power is equal to 100% of rated power and that the reactive power is equal to 0% of rated power.
3. Change the angle between the injected current and voltage to *Angle1* + 90°. Check that the monitored active power is equal to 0% of rated power and that the reactive power is equal to 100% of rated power.
4. Change the angle between the injected current and voltage back to *Angle1* value. Increase the current slowly from 0 until the START1 signal, start of stage 1, is activated. Check the injected power and compare it to the set value *Power1*, power setting for stage 1 in % of *Sbase*.
5. Increase the current to 100% of *IBase* and switch the current off.
6. Switch the current on and measure the time for activation of TRIP1, trip of stage 1.
7. If a second stage is used, repeat steps 2 to 6 for the second stage.

6.4.15.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Current/GOPPDOP(32,P>)/X:GOPPDOP** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.5 Testing voltage protection functions

6.5.1 Two step undervoltage protection UV2PTUV

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for UV2PTUV are available on the local HMI under **Main menu/Tests/Function status/Voltage/UV2PTUV(27,2U<)/1:UV2PTUV**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.5.1.1 Verifying the setting

Verification of START value and time delay to operate for Step1

1. Check that the IED settings are appropriate, especially the START value, the definite time delay and the *1 out of 3* operation mode.
2. Supply the IED with three-phase voltages at their rated values.
3. Slowly decrease the voltage in one of the phases, until the START signal appears.
4. Note the operate value and compare it with the set value.
5. Increase the measured voltage to rated load conditions.
6. Check that the START signal resets.
7. Instantaneously decrease the voltage in one phase to a value about 20% lower than the measured operate value.
8. Measure the time delay for the TRIP signal, and compare it with the set value.

Extended testing

1. The test above can now be repeated for step 2.
2. The tests above can be repeated for *2 out of 3* and for *3 out of 3* operation mode.
3. The tests above can be repeated to check security, that is, the START and operate signals, that are not supposed to appear, - do not.
4. The tests above can be repeated to check the time to reset.
5. The tests above can be repeated to test the inverse time characteristic.

6.5.1.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Voltage/UV2PTUV(27,2U<)/1:UV2PTUV** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.5.2 Two step overvoltage protection OV2PTOV

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for OV2PTOV are available on the local HMI under **Main menu/Tests/Function status/Voltage/OV2PTOV(59,2U>)/1:OV2PTOV**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.5.2.1 Verifying the settings

1. Apply single-phase voltage below the set value *U1>*.
2. Slowly increase the voltage until the ST1 signal appears.
3. Note the operate value and compare it with the set value.
4. Switch the applied voltage off.
5. Set and apply about 20% higher voltage than the measured operate value for one phase.
6. Measure the time delay for the TR1 signal and compare it with the set value.
7. Repeat the test for step 2.

6.5.2.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Voltage/OV2PTOV(59,2U>)/1:OV2PTOV** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.5.3 Two step residual overvoltage protection ROV2PTOV

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for ROV2PTOV are available on the local HMI under **Main menu/Tests/Function status/Voltage/ROV2PTOV(59N,2UN>)/**

1:ROV2PTOV. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.5.3.1 Verifying the settings

1. Apply the single-phase voltage either to a single-phase voltage input or to a residual voltage input with the start value below the set value *U1>*.
2. Slowly increase the value until ST1 appears.
3. Note the operate value and compare it with the set value.
4. Switch the applied voltage off.
5. Set and apply about 20% higher voltage than the measured operate value for one phase.
6. Measure the time delay for the TR1 signal and compare it with the set value.
7. Repeat the test for step 2.

6.5.3.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Voltage/ROV2PTOV(59N,2UN>)/1:ROV2PTOV** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.5.4 Loss of voltage check LOVPTUV

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for LOVPTUV are available on the local HMI under **Main menu/Tests/Function status/Voltage/LOVPTUV(27,U<)/1:LOVPTUV**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.5.4.1 Measuring the operate limit of set values

1. Check that the input logical signals BLOCK, CBOPEN and VTSU are logical zero.
2. Supply a three-phase rated voltage in all three phases and note on the local HMI that the TRIP logical signal is equal to the logical 0.
3. Switch off the voltage in all three phases.
   After set *tTrip* time a TRIP signal appears on the corresponding binary output or on the local HMI.

Note that TRIP at this time is a pulse signal, duration should be according to set *tPulse*.

4. Inject the measured voltages at rated values for at least set *tRestore* time.
5. Activate the CBOPEN binary input.
6. Simultaneously disconnect all the three-phase voltages from the IED. No TRIP signal should appear.
7. Inject the measured voltages at rated values for at least set *tRestore* time.
8. Activate the VTSU binary input.
9. Simultaneously disconnect all the three-phase voltages from the IED. No TRIP signal should appear.
10. Reset the VTSU binary input.
11. Inject the measured voltages at rated values for at least set *tRestore* time.
12. Activate the BLOCK binary input.
13. Simultaneously disconnect all the three-phase voltages from the IED. No TRIP signal should appear.
14. Reset the BLOCK binary input.

6.5.4.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Voltage/LOVPTUV(27,U<)/1:LOVPTUV** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.6 Testing frequency protection functions

6.6.1 Underfrequency protection SAPTUF

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for SAPTUF are available on the local HMI under **Main menu/Tests/Function status/Frequency/SAPTUF(81,f<)/X:SAPTUF**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.6.1.1 Verifying the settings

Verification of START value and time delay to operate

1. Check that the IED settings are appropriate, especially the START value and the definite time delay.
2. Supply the IED with three-phase voltages at their rated values.
3. Slowly decrease the frequency of the applied voltage, until the START signal appears.
4. Note the operate value and compare it with the set value.
5. Increase the frequency until rated operating levels are reached.
6. Check that the START signal resets.
7. Instantaneously decrease the frequency of the applied voltage to a value about 20% lower than the operate value.
8. Measure the time delay of the TRIP signal, and compare it with the set value.

Extended testing

1. The test above can be repeated to check the time to reset.
2. The tests above can be repeated to test the frequency dependent inverse time characteristic.

Verification of the low voltage magnitude blocking

1. Check that the IED settings are appropriate, especially the *StartFrequency* and the *tDelay* and the *MinValFreqMeas* in the SMAI preprocessing function.
2. Supply the IED with three-phase voltages at rated values.
3. Slowly decrease the magnitude of the applied voltage, until the BLKDMAGN signal appears.
4. Note the voltage magnitude value and compare it with the SMAI set value *MinValFreqMeas*.
5. Slowly decrease the frequency of the applied voltage, to a value below *StartFrequency*.
6. Check that the START signal does not appear.
7. Wait for a time corresponding to *tDelay*, and check that the TRIP signal does not appear.

6.6.1.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Frequency/SAPTUF(81,f<)/X:SAPTUF** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.6.2 Overfrequency protection SAPTOF

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for SAPTOF are available on the local HMI under **Main menu/Tests/Function status/Frequency/SAPTOF(81,f>)/X:SAPTOF**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.6.2.1 Verifying the settings

Verification of START value and time delay to operate

1. Check that the settings in the IED are appropriate, especially the START value and the definite time delay.
2. Supply the IED with three-phase voltages at their rated values.
3. Slowly increase the frequency of the applied voltage, until the START signal appears.
4. Note the operate value and compare it with the set value.
5. Decrease the frequency to rated operating conditions.
6. Check that the START signal resets.
7. Instantaneously increase the frequency of the applied voltage to a value about 20% higher than the operate value.
8. Measure the time delay for the TRIP signal, and compare it with the set value.

Extended testing

1. The test above can be repeated to check the time to reset.

Verification of the low voltage magnitude blocking

1. Check that you have appropriate settings in the IED, especially the *StartFrequency*, *TtDelay* and the *MinValFreqMeas* in the SMAI preprocessing function
2. Supply the IED with three-phase voltages at their rated values.
3. Slowly decrease the magnitude of the applied voltage, until the BLKDMAGN signal appears.
4. Note the voltage magnitude value and compare it with the set value, *MinValFreqMeas*.
5. Slowly increase the frequency of the applied voltage, to a value above *StartFrequency*.
6. Check that the START signal does not appear.
7. Wait for a time corresponding to *tDelay*, and make sure that the TRIP signal does not appear.

6.6.2.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Frequency/SAPTOF(81,f>)/X:SAPTOF** for the

function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.6.3 Rate-of-change frequency protection SAPFRC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for SAPFRC are available on the local HMI under **Main menu/Tests/Function status/Frequency/SAPFRC(81,df/dt)/X:SAPFRC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

6.6.3.1 Verifying the settings

Verification of START value and time delay to operate

1. Check that the appropriate settings are available in the IED, especially the START value and the definite time delay. Set *StartFreqGrad*, to a rather small negative value.
2. Supply the IED with three-phase voltages at their rated values.
3. Slowly decrease the frequency of the applied voltage, with an increasing rate-of-change that finally exceeds the setting of *StartFreqGrad*, and check that the START signal appears.
4. Note the operate value and compare it with the set value.
5. Increase the frequency to rated operating conditions, and zero rate-of-change.
6. Check that the START signal resets.
7. Instantaneously decrease the frequency of the applied voltage to a value about 20% lower than the nominal value.
8. Measure the time delay for the TRIP signal, and compare it with the set value.

Extended testing

1. The test above can be repeated to check a positive setting of *StartFreqGrad*.
2. The tests above can be repeated to test the RESTORE signal, when the frequency recovers from a low value.

6.6.3.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Frequency/SAPFRC(81,df/dt)/X:SAPFRC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.7 Testing secondary system supervision functions

6.7.1 Current circuit supervision CCSRDIF

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for CCSRDIF are available on the local HMI under **Main menu/Tests/Function status/Secondary system supervision/ CCSRDIF(87,INd)/X:CCSRDIF**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The Current circuit supervision function CCSRDIF is conveniently tested with the same three-phase test set as used when testing the measuring functions in the IED.

The condition for this procedure is that the setting of *IMinOp* is lower than the setting of *Ip>Block*.

6.7.1.1 Verifying the settings

1. Check the input circuits and the operate value of the *IMinOp* current level detector by injecting current, one phase at a time.
2. Check the phase current blocking function for all three phases by injecting current, one phase at a time. The output signals shall reset with a delay of 1 second when the current exceeds 1.5 · *IBase*.
3. Inject a current 0.1 · *IBase* to the reference current input IREFSMPL.
4. Increase slowly the current in one of the phases current input and check that FAIL output is obtained when the current is about 0.9 · *IBase*.

6.7.1.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/ Tests/Function test modes/Secondary system supervision/CCSRDIF(87,INd)/ X:CCSRDIF** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.7.2 Fuse failure supervision SDDRFUF

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for SDDRFUF are available on the local HMI under **Main menu/Tests/Function status/Secondary system supervision/SDDRFUF/**

1:SDDRFUF. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The verification is divided in two main parts. The first part is common to all fuse failure supervision options, and checks that binary inputs and outputs operate as expected according to actual configuration. In the second part the relevant set operate values are measured.

6.7.2.1 Checking that the binary inputs and outputs operate as expected

1. Simulate normal operating conditions with the three-phase currents in phase with their corresponding phase voltages and with all of them equal to their rated values.
2. Connect the nominal dc voltage to the DISCPOS binary input.
   - The signal BLKU should appear with almost no time delay.
   - No signals BLKZ and 3PH should appear on the IED.
   - Only the distance protection function can operate.
   - Undervoltage-dependent functions must not operate.
3. Disconnect the dc voltage from the DISCPOS binary input terminal.
4. Connect the nominal dc voltage to the MCBOP binary input.
   - The BLKU and BLKZ signals should appear without any time delay.
   - All undervoltage-dependent functions must be blocked.
5. Disconnect the dc voltage from the MCBOP binary input terminal.
6. Disconnect one of the phase voltages and observe the logical output signals on the binary outputs of the IED.
   BLKU and BLKZ signals should appear simultaneously wether the BLKU and BLKZ reset depends on the setting *SealIn* “on” or “off”. If “on” no reset, if “off” reset.
7. After more than 5 seconds disconnect the remaining two-phase voltages and all three currents.
   - There should be no change in the high status of the output signals BLKU and BLKZ.
   - The signal 3PH will appear.
8. Establish normal voltage and current operating conditions simultaneously and observe the corresponding output signals.
   They should change to logical 0 as follows:
   - Signal 3PH after about 25ms
   - Signal BLKU after about 50ms
   - Signal BLKZ after about 200ms

6.7.2.2 Measuring the operate value for the negative sequence function

1. Simulate normal operating conditions with the three-phase currents in phase with their corresponding phase voltages and with all of them equal to their rated values.
2. Slowly decrease the measured voltage in one phase until the BLKU signal appears.
3. Record the measured voltage and calculate the corresponding negative-sequence voltage according to the equation.
   Observe that the voltages in the equation are phasors.

$$3 \cdot \overline{U_2} = \overline{U_{L1}} + a^2 \cdot \overline{U_{L2}} + a \cdot \overline{U_{L3}}$$

(Equation 13)

Where:

$\overline{U_{L1}}$ $\overline{U_{L2}}$ and $\overline{U_{L3}}$ = the measured phase voltages

$$a = 1 \cdot e^{j\frac{2 \cdot \pi}{3}} = -0,5 + j\frac{\sqrt{3}}{2}$$

4. Compare the result with the set value (consider that the set value *3U2>* is in percentage of the base voltage *UBase*) of the negative-sequence operating voltage.

6.7.2.3 Measuring the operate value for the zero-sequence function

1. Simulate normal operating conditions with the three-phase currents in phase with their corresponding phase voltages and with all of them equal to their rated values.
2. Slowly decrease the measured voltage in one phase until the BLKU signal appears.
3. Record the measured voltage and calculate the corresponding zero-sequence voltage according to the equation.
   Observe that the voltages in the equation are phasors.

$$3 \cdot \overline{U_0} = \overline{U_{L1}} + \overline{U_{L2}} + \overline{U_{L3}}$$

(Equation 16)

Where:

$\overline{U_{L1}}$, $\overline{U_{L2}}$ and $\overline{U_{L3}}$ = the measured phase voltages.

4. Compare the result with the set value (consider that the set value *3U0>* is in percentage of the base voltage of the zero-sequence operating voltage.

6.7.2.4 Checking the operation of the du/dt and di/dt based function

1. Simulate normal operating conditions with the three-phase currents in phase with their corresponding phase voltages and with all of them equal to their rated values.
2. Change the voltages in all three phases simultaneously.
   The voltage change must be greater than the set value for *DU>* and the current constant below the set value for *DI<*.
   - The BLKU and BLKZ signals appear without any time delay. The BLKZ signal will be activated only if the internal deadline detection is not activated at the same time.
   - 3PH should appear after 5 seconds, if the remaining voltage levels are lower than the set *UDLD<* of the DLD function.
3. Apply normal conditions as in step 1.
   The BLKU, BLKZ and 3PH signals should reset, if activated, see step 1 and 2.
4. Change the voltages in all three phases simultaneously.
   The voltage change must be greater than the set value for *DU>* and the current constant above the set value for *DI<*.
   The BLKU, BLKZ and 3PH signals should not appear.
5. Repeat step 2.
6. Connect the nominal voltages in all three phases and feed a current below the operate level in all three phases.
7. Keep the current constant. Disconnect the voltage in all three phases simultaneously.
   The BLKU, BLKZ and 3PH signals should not appear.
8. To test the internal signals *ifDeltaU* and *ifDeltaI*, change the magnitude of the voltage and current for phase 1 to a value greater than the set value for *DU>* and *DI<*.
9. Check that the start output signals STDUL1 and STDIL1 and the general start signals STDU or STDI are activated.
10. Check that the start output signals for the current and voltage phases 2 and 3 are activated by changing the magnitude of the voltage and current for phases 2 and 3.

6.7.2.5 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Secondary system supervision/SDDRFUF/1:SDDRFUF** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.8 Testing control functions

During periods of frequent counter state/value changes, if the auxiliary power to the IED is interrupted, it is possible that this information will be lost.

6.8.1 Synchrocheck, energizing check, and synchronizing SESRSYN

This section contains instructions on how to test the synchrocheck, energizing check, and synchronizing function SESRSYN for single, double and 1½ breaker arrangements.

This section contains instructions on how to test the synchrocheck and energizing check for single CB with or without the synchronizing function.

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for SESRSYN are available on the local HMI under **Main menu/Tests/Function status/Control/SESRSYN(25,SYNC)/X:SESRSYN**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

At commissioning and periodical checks, the functions shall be tested with the used settings. To test a specific function, it might be necessary to change some setting parameters, for example:

- *AutoEnerg = Off/DLLB/DBLL/Both*
- *ManEnerg = Off*
- *Operation = Off/On*
- Activation of the voltage selection function if applicable

The tests explained in the test procedures below describe the settings, which can be used as references during testing before the final settings are specified. After testing, restore the equipment to the normal or desired settings.

A secondary injection test set with the possibility to alter the phase angle and amplitude of the voltage is needed. The test set must also be able to generate different frequencies on different outputs.

The description below applies for a system with a nominal frequency of 50 Hz but can be directly applicable to 60 Hz. SESRSYN can be set to use different phases, phase to earth or phase to phase. Use the set voltages instead of what is indicated below.

Figure 19 shows the general test connection principle, which can be used during testing. This description describes the test of the version intended for one bay.

Figure 20 shows the general test connection for a 1½ breaker diameter with one-phase voltage connected to the line side.



Figure 19: General test connection with three-phase voltage connected to the line side



Figure 20: General test connection for a 1½ breaker diameter with one-phase voltage connected to the line side

6.8.1.1 Testing the synchronizing function

This section is applicable only if the synchronizing function is included.

The voltage inputs used are:

U-Line	UL1, UL2 or UL3 line 1 voltage inputs on the IED
U-Bus	Bus voltage input on the IED

Testing the frequency difference

The frequency difference is in the example set at 0.20 Hz on the local HMI, and the test should verify that operation is achieved when the *FreqDiffMax* frequency difference is lower than 0.20 Hz. The test procedure below will depend on the settings used. Input STARTSYN must be activated during the test.

1. Apply voltages
   1.1. U-Line = 100% *GblBaseSelLine* and f-Line = 50.0 Hz
   1.2. U-Bus = 100% *GblBaseSelBus* and f-Bus = 50.2Hz
2. Check that a closing pulse is submitted at a closing angle less than 2 degrees from phase equality. Modern test sets will evaluate this automatically.
3. Repeat with

3.1. U-Bus = 80% *GblBaseSelBus* and f-Bus = 50.25 Hz, to verify that the function does not operate when frequency difference is above limit.

4. Repeat with different frequency differences for example, 100 mHz with f-Bus nominal and line leading and for example 20 mHz (or just above *FreqDiffMin*) to verify that independent of frequency difference the closing pulse occurs within 2 degrees.
5. Verify that the closing command is not issued when the frequency difference is less than the set value *FreqDiffMin*.

6.8.1.2 Testing the synchrocheck check

During the test of SESRSYN for a single bay arrangement, these voltage inputs are used:

U-Line	UL1, UL2 or UL3 line 1 voltage inputs on the IED
U-Bus	Bus voltage input on the IED

Voltage inputs

At test of the SESRSYN function for a 1½ CB diameter the following alternative voltage inputs can be used for the three SESRSYN (SESRSYN 1, SESRSYN 2, SESRSYN 3) functions. These three SESRSYN functions can either be in one, two or three different IEDs. Table 10 describes the scenario when SESRSYN 1, SESRSYN 2 and SESRSYN 3 all are in the same IED. If SESRSYN 3 is in another IED, Bus1 will be considered as Bus2 and Line2 as Line1. The voltage is selected by activation of different inputs in the voltage selection logic as shown in table 10 and figure 21.

Table 10: Voltage selection logic

SESRSYN	CBConfig setting	Section to be synchronized	Activated B1QCLD input on IED from	Activated B2QCLD input on IED from	Activated LN1QCLD input on IED from	Activated LN2QCLD input on IED from	Indication from SESRSYN on IED
SESRSYN 1 (Operates on CB1QA1)	1 ½ bus CB	Bus1 – Line1			LN1QB9		B1SEL, LN1SEL
		Bus1 – Line2	CB2QA1			LN2QB9	B1SEL, LN2SEL
		Bus1 – Bus2	CB2QA1	CB3QA1			B1SEL, B2SEL
SESRSYN 2 (Operates on CB2QA1)	Tie CB	Line1 – Line2			LN1QB9	LN2QB9	LN1SEL, LN2SEL
		Bus1 – Line2	CB1QA1			LN2QB9	B1SEL, LN2SEL
		Bus2 – Line1		CB3QA1	LN1QB9		B2SEL, LN1SEL
		Bus1 – Bus2	CB1QA1	CB3QA1			B1SEL, B2SEL

Table continues on next page

SESRSYN	CBConfig setting	Section to be synchronized	Activated B1QCLD input on IED from	Activated B2QCLD input on IED from	Activated LN1QCLD input on IED from	Activated LN2QCLD input on IED from	Indication from SESRSYN on IED
SESRSYN 3 (Operates on CB3QA1)	1 ½ bus alt. CB (mirrored)	Bus2 – Line2				LN2QB9	B2SEL, LN2SEL
		Bus2 – Line1	CB2QA1		LN1QB9		B2SEL, LN1SEL
		Bus2 – Bus1	CB2QA1	CB1QA1			B1SEL, B2SEL



Figure 21: Voltage selection logic

Testing the voltage difference

Set the voltage difference to 0.15 p.u. on the local HMI, and the test should check that operation is achieved when the voltage difference *UDiffSC* is lower than 0.15 p.u.

The settings used in the test shall be final settings. The test shall be adapted to site setting values instead of values in the example below.

Test with no voltage difference between the inputs.

Test with a voltage difference higher than the set *UDiffSC*.

1. Apply voltages U-Line (for example) = 80% *GblBaseSelLine* and U-Bus = 80% *GblBaseSelBus*
2. Check that the AUTOSYOK and MANSYOK outputs are activated.
3. The test can be repeated with different voltage values to verify that the function operates within the set *UDiffSC*. Check with both U-Line and U-Bus respectively lower than the other.
4. Increase the U-Bus to 110% *GblBaseSelBus*, and the U-Line = 90% *GblBaseSelLine* and also the opposite condition.
5. Check that the two outputs for manual and auto synchronism are not activated.

Testing the phase angle difference

The phase angle differences *PhaseDiffM* and *PhaseDiffA* respectively are set to their final settings and the test should verify that operation is achieved when the phase angle difference is lower than this value both leading and lagging.

Test with no voltage difference.

1. Apply voltages U-Line (for example) = 100% *GblBaseSelLine* and U-Bus = 100% *GblBaseSelBus*, with a phase difference equal to 0 degrees and a frequency difference lower than *FreqDiffA* and *FreqDiffM*.
2. Check that the AUTOSYOK and MANSYOK outputs are activated.
   The test can be repeated with other phase difference values to verify that the function operates for values lower than the set ones, *PhaseDiffM* and *PhaseDiffA*. By changing the phase angle on the voltage connected to U-Bus, between ± dφ degrees, the user can check that the two outputs are activated for a phase difference lower than the set value. It should not operate for other values. See figure 22.



Figure 22: Test of phase difference

3. Change the phase angle between +dφ and -dφ and verify that the two outputs are activated for phase differences between these values but not for phase differences outside, see figure 22.

Testing the frequency difference

The frequency difference test should verify that operation is achieved when the *FreqDiffA* and *FreqDiffM* frequency difference is lower than the set value for manual and auto synchronizing check, *FreqDiffA* and *FreqDiffM* respectively and that operation is blocked when the frequency difference is greater.

Test with frequency difference = 0 mHz

Test with a frequency difference outside the set limits for manual and auto synchronizing check respectively.

1. Apply voltages U-Line equal to 100% *GblBaseSelLine* and U-Bus equal to 100% *GblBaseSelBus*, with a frequency difference equal to 0 mHz and a phase difference lower than the set value.
2. Check that the AUTOSYOK and MANSYOK outputs are activated.
3. Apply voltage to the U-Line equal to 100% *GblBaseSelLine* with a frequency equal to 50 Hz and voltage U-Bus equal to 100% *GblBaseSelBus*, with a frequency outside the set limit.
4. Check that the two outputs are not activated. The test can be repeated with different frequency values to verify that the function operates for values lower than the set ones. If a modern test set is used, the frequency can be changed continuously.

Testing the reference voltage

1. Use the same basic test connection as in figure 19.
   The voltage difference between the voltage connected to U-Bus and U-Line should be 0%, so that the AUTOSYOK and MANSYOK outputs are activated first.
2. Change the U-Line voltage connection to U-Line2 without changing the setting on the local HMI. Check that the two outputs are not activated.

6.8.1.3 Testing the energizing check

During the test of the energizing check function for a single bay arrangement, these voltage inputs are used:

U-Line	UL1, UL2 or UL3 line1 voltage inputs on the IED
U-Bus	Bus voltage input on the IED

General

When testing the energizing check function for the applicable bus, arrangement shall be done for the energizing check functions. The voltage is selected by activation of different inputs in the voltage selection logic.

Live voltage level is fixed to 80% *UBase* and dead voltage level to fixed 40% *UBase*.

The test shall be performed according to the settings for the station. Test the alternatives below that are applicable.

Testing the dead line live bus (DLLB)

The test should verify that the energizing check function operates for a low voltage on the U-Line and for a high voltage on the U-Bus. This corresponds to the energizing of a dead line to a live bus.

1. Apply a single-phase voltage 100% *GblBaseSelBus* to the U-Bus, and a single-phase voltage 30% *GblBaseSelLine* to the U-Line.
2. Check that the AUTOENOK and MANENOK outputs are activated after set *tAutoEnerg* respectively *tManEnerg*.
3. Increase the U-Line to 60% *GblBaseSelLine* and U-Bus to be equal to 100% *GblBaseSelBus*. The outputs should not be activated.
4. The test can be repeated with different values on the U-Bus and the U-Line.

Testing the dead bus live line (DBLL)

The test should verify that the energizing check function operates for a low voltage on the U-Bus and for a high voltage on the U-Line. This corresponds to an energizing of a dead bus to a live line.

1. Verify the settings *AutoEnerg* or *ManEnerg* to be *DBLL*.
2. Apply a single-phase voltage of 30% *GblBaseSelBus* to the U-Bus and a single-phase voltage of 100% *GblBaseSelLine* to the U-Line.
3. Check that the AUTOENOK and MANENOK outputs are activated after set *tAutoEnerg* respectively *tManEnerg*.
4. Decrease the U-Line to 60% *GblBaseSelLine* and keep the U-Bus equal to 30% *GblBaseSelBus*. The outputs should not be activated.
5. The test can be repeated with different values on the U-Bus and the U-Line.

Testing both directions (DLLB or DBLL)

1. Verify the local HMI settings *AutoEnerg* or *ManEnerg* to be *Both*.
2. Apply a single-phase voltage of 30% *GblBaseSelLine* to the U-Line and a single-phase voltage of 100% *GblBaseSelBus* to the U-Bus.
3. Check that the AUTOENOK and MANENOK outputs are activated after set *tAutoEnerg* respectively *tManEnerg*.
4. Change the connection so that the U-Line is equal to100% *GblBaseSelLine* and the U-Bus is equal to 30% *GblBaseSelBus*. The outputs should still be activated.
5. The test can be repeated with different values on the U-Bus and the U-Line.

Testing the dead bus dead line (DBDL)

The test should verify that the energizing check function operates for a low voltage on both the U-Bus and the U-Line, that is, closing of the breaker in a non-energized system. Test is valid only when this function is used.

1. Verify the local HMI setting *AutoEnerg* to be *Off* and *ManEnerg* to be *DBLL*.
2. Set the parameter *ManEnergDBDL* to *On*.
3. Apply a single-phase voltage of 30% *GblBaseSelBus* to the U-Bus and a single-phase voltage of 30% *GblBaseSelLine* to the U-Line.
4. Check that the MANENOK output is activated after set *tManEnerg*.
5. Increase the U-Bus to 80% *GblBaseSelBus* and keep the U-Line equal to 30% *GblBaseSelLine*. The outputs should not be activated.
6. Repeat the test with *ManEnerg* set to *DLLB* with different values on the U-Bus and the U-Line voltage.

6.8.1.4 Testing the voltage selection

Testing the voltage selection for single CB arrangements

This test should verify that the correct voltage is selected for the measurement in the SESRSYN function used in a double-bus arrangement. Apply a single-phase voltage of 30% *GblBaseSelLine* to the U-Line and a single-phase voltage of 100% *GblBaseSelBus* to the U-Bus.

If the UB1OK or UB2OK inputs for the fuse failure are used, they must be activated, during tests below. Also verify that deactivation prevents operation and gives an alarm.

1. Connect the signals above to binary inputs and binary outputs.
2. Connect the voltage inputs to the analog inputs used for each bus or line depending of the type of busbar arrangement and verify that correct output signals are generated.

6.8.1.5 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Control/SESRSYN(25,SYNC)/X:SESRSYN** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.8.2 Autorecloser for 3-phase operation SMBRREC

Verification of the Autorecloser for 3-phase operation function SMBRREC for three-phase reclosing attempts can be considered to consist of two parts.

- One part to verify the internal logic and timing of the function
- One part to verify its interaction with the protection system

This section deals with verification of SMBRREC itself. However, it is practical to start SMBRREC by activating a protection function, for example, by secondary injection tests.

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for SMBRREC are available on the local HMI under **Main menu/Tests/Function status/Control/SMBRREC(79,0->1)/ X:SMBRREC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The purpose of verification before commissioning is to check that entered selections, setting parameters and configuration render the intended result. The function is flexible with many options and facilities. At commissioning only the selections and settings intended for use are verified. If one chooses to reduce some time settings in order to speed up verification, be careful to set the parameters at intended operational values at the end of the verification procedure. One such parameter is the *tReclaim* time that must be timed out before a new test sequence can be performed.

The verification test is performed together with protection and trip functions. Figure 23 illustrates a suggested testing arrangement, where the circuit-breaker (CB) is simulated by an external bi-stable relay (BR), for example a relay type RXMVB2 or RXMD or Breaker Simulator of ABB. The following manual switches are used:

- Switch or push-button to close (SC)
- Switch or push-button to trip (ST)
- Switch for CB ready condition (SRY)

If no bi-stable relay or breaker simulator is available, replace it with two self-reset auxiliary relays and use a self-holding connection.

Use a secondary injection IED test set to operate the protection function. The test set shall be switched off when a trip signal is given or when the BR comes to open position to simulate real conditions.

The CB simulation can be made more elaborate, including simulation of the operating gear condition, CBREADY of either the type ready for a Close-Open (CO) cycle, or the type ready for an Open-Close -Open (OCO) cycle.

The CB condition CBREADY of a type, CO, shall be high (true) until a closing operation is performed. It then goes low (false) for a recharging time of about 5 - 10s. After that it is high again.

A CB condition CBREADY of a type, OCO shall be high (true) before and during tripping (Start reclosing). During tripping it goes low for a recharging time, for example, 10s. It may thus be low at the instant of reclosing. After each Open or Close operation it may need a recharging period before it goes high again.

In the example of CB simulation arrangement, the CBREADY condition is simulated by a manual switch, SRY.

Information and material for the verification:

- Protection or control unit, IED, configured and with settings entered.
- Configuration diagram for the IED
- Terminal diagram for the IED, or plant circuit diagram including the IED
- Technical reference manual for the IED
- IED test set for secondary injection
- Means to indicate, measure and record operation and times, for example an event recording facility
- A bi-stable relay (BR) or two auxiliary relays to simulate a CB
- Two push-buttons (SC, ST) to operate the BR and a change-over switch (SRY) to simulate CBREADY
- Possibly a switch simulation the synchronizing check SESRSYN condition



Figure 23: Simulating the CB operation by a bi-stable relay/breaker simulator and manual switches

6.8.2.1 Preparation of the verification

1. Check the function settings on the local HMI under **Main menu/Settings/ IED Settings/Control/SMBRREC(79,0->1)/1:SMBRREC**
   If any timer settings are reduced to speed up or facilitate the testing, they shall be set to normal after testing. A temporary label on the IED can be a reminder to restore normal settings after which a verification test should be performed.
2. Decide if a synchronizing check function SESRSYN shall be included in the test.

If SESRSYN as an internal function or external device is not operated by the injection, input signal SYNC must be connected as a permanent high signal or controlled by a switch.

3. Read and make notes of the reclosing operation counters on the local HMI under **Main menu/Tests/Function status/Control/SMBRREC(79,0->1)/1:SMBRREC**
   Possibly reset the counters to *Zero*. Counters are reset in the reset menu.
4. Make arrangements for the simulation of the CB, for example as in figure 23.
5. Make arrangements for indication, recording and time measurements.
   The signals for CBPOS, START, CLOSECB, READY and other relevant signals should preferably be arranged for event recording with time tagging. If that is not possible, other means of time measurement and recording should be arranged.

6.8.2.2 Switching the autorecloser for 3-phase operation function to *On* and *Off*

1. Set the *Operation* setting to *Off* and check the state.
2. Set the *Operation* setting to *On* and check the state, including SETON and READY.
   The CB should be closed and ready.
3. If external control Off/On is connected, check that it works.
   Set *Operation* to *ExternalCtrl* and use that control to switch On and Off, and check the state of the function.

6.8.2.3 Verifying the autorecloser for 3-phase operation function SMBRREC

Select the test cases to be run according to what is applicable to the particular application. It can be, for example, three-phase single-shot reclosing or two-shot reclosing. Below, a case with three-phase single-shot reclosing is described.

1. Set *Operation* = *On*.
2. If the autorecloser for 3-phase operation function SMBRREC is not to be operated, ensure that the SMBRREC input is activated. If SMBRRECis to be included, ensure that it is supplied with the appropriate AC quantities.
3. Simulate CB closed position by closing switch SC to make the BR relay start.
4. Simulate CBREADY by closing the switch SRY, and leave it closed.
5. Inject AC quantities to give a trip to the BR and to the START input.
   Observe and preferably record the operation. The BR relay shall trip and reclose (start). After reclosing, the SRY switch can be opened for about 5s and then closed again.
   The autoreclosing open time and the sequence should be checked, for example in the event recording. Check also the operation indications (disturbance report) and the operation counters on the local HMI under **Main menu/Tests/Function status/SMBRREC(79,0->1)/1:SMBRREC**

Should the operation not be as expected, this should be investigated. It could be caused by an inappropriate setting or missing condition such as CBREADY.

6. Repeat the sequence by simulating a permanent fault.
   Shortly after the reclosing shot, a new fault is applied. If a single-shot reclosing program is selected, there shall be one reclosing operation and then blocking of SMBRREC for the set Reclaim time.
   Before a new reclosing sequence can be run, the CBREADY and CBPOS (CB closed) must be set manually.

6.8.2.4 Checking the reclosing conditions

When checking the influence of a releasing condition it is suggested to first run a sequence with the condition fulfilled. When the condition signal is removed, and a new sequence is run, it indicates that the result was due to the changed condition. In case of a blocking signal the procedure should be similar. Start without the blocking or inhibit signal, and then run a sequence with the blocking or inhibit signal added.

Checking the influence of the INHIBIT signal

1. Check that the autorecloser function SMBRREC is operative, for example, by making a reclosing shot without the INHIBIT signal.
2. Apply a fault and thereby a START signal. At the same time, or during the open time, apply a signal to the input INHIBIT.
3. Check that the reclosing sequence is interrupted and no reclosing takes place.

Check closing onto a fault

1. Check that the autorecloser function SMBRREC is operative, for example by making a reclosing shot.
   Keep the CBREADY signal high.
2. Set the breaker simulating relay BR in Open position.
3. Close the BR relay and apply immediately a fault and thereby a START signal.
4. Check that no reclosing takes place.

Checking the influence of CB not ready for reclosing

1. Check that the autorecloser function SMBRREC is operative, for example by making a reclosing shot.
   Keep the CB simulator BR closed. Remove the CBREADY signal by opening SRY.
2. Apply a fault and thereby a START signal.
3. Check that no reclosing takes place.

Checking the influence of synchronizing check (at three-phase reclosing)

1. Check that the autorecloser for 3-phase operation function SMBRREC is operative, for example, by making a three-phase reclosing shot with the synchronizing check condition.
   Remove the SMBRREC signal.
2. Apply a fault causing three-phase trip and thereby a START signal.
3. Wait for the *tSync* time out limit.
   Check that no reclosing is made.

Restoring equipment

After the tests, restore the equipment to normal or desired state. Check the following items in particular:

1. Check the operation counters.
   Reset the counters to zero, if that is the user's preference. The counter reset function is found on the local HMI under **Main menu/Clear/Clear counters/ SMBRREC(79,0->1)**
2. Restore settings that may have been modified for the tests back to normal.
3. Disconnect the test switch, CB simulating arrangement and test circuits. Reconnect any links or connection terminals, which may have been opened for the tests.
4. Reset indications, alarms and disturbance recordings.
   Clearing of the disturbance report must be done via the Disturbance Handling in PCM600.

6.8.2.5 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/ Tests/Function test modes/Control/SMBRREC(79,0->1)/X:SMBRREC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.8.3 Autorecloser for 1/3-phase operation STBRREC

Verification of the automatic reclosing function STBRREC (79) for single and three-phase reclosing attempt, can be considered to consist of two parts; one part to verify the internal logic and timing of the function and one part to verify its interaction with the protection system. This section deals with verification of the auto-reclosing function itself. However, it is practical to start start the autoreclosing function by activating a protection function, for example, by secondary injection tests.

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for STBRREC are available on the local HMI under **Main menu/Tests/Function status/Control/STBRREC(79,0->1)/1:STBRREC**.

The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The purpose of verification before commissioning is to check that entered selections, setting parameters and configuration render the intended result. The function is flexible with many options and facilities. At commissioning only the selections and settings intended for use are verified. If one chooses to reduce some time settings in order to speed up verification, be careful to set the parameters at intended operational values at the end of the verification procedure. One such parameter is the reclaim Reclaim time that must be timed out before a new test can be performed.

The verification test is performed together with protection and trip functions. Figure 24 illustrates a suggested testing arrangement, where the circuit-breaker (CB) is simulated by an external bi-stable relay (BR), for example a relay type RXMVB2 or RXMD or Breaker Simulator from ABB.



Figure 24: Simulating the CB operation by a bi-stable relay/breaker simulator and manual switches

The following manual switches are used:

- Switch or push-button to close (SC)
- Switch or push-button to trip (ST)
- Switch for CB ready condition (SRY)

If no bi-stable relay or breaker simulator is available, replace it with two self-reset auxiliary relays and use a self-holding connection.

Use a secondary injection IED test set to operate the protection function. The test set shall be switched off when a trip signal is given or when the BR comes to open position to simulate real conditions.

The CB simulation can be made more elaborate, including simulation of the operating gear condition, CBREADY of either the type ready for a Close-Open (CO) cycle, or the type ready for an Open-Close -Open (OCO) cycle.

The CB condition CBREADY of a type, CO, shall be high (true) until a closing operation is performed. It then goes low (false) for a recharging time of about 5 -10 s. After that it is high again.

A CB condition CBREADY of a type, OCO shall be high (true) before and during tripping (Start start reclosing). During tripping it goes low for a recharging time, for example, 10 s. It may thus be low at the instant of reclosing. After each Open or Close operation it may need a recharging period before it goes high again.

In the example of CB simulation arrangement, the CBREADY condition is simulated by a manual switch, SRY.

Information and material for the verification:

- Protection or control unit, Intelligent electronic device (IED), configured and with settings entered
- Configuration diagram for the IED
- Terminal diagram for the IED, or plant circuit diagram including the IED
- Technical reference manual for the IED
- IED test set for secondary injection
- Means to indicate, measure and record operation and times, e.g. an event recording facility
- A bi-stable relay (BR) or two auxiliary relays to simulate a CB
- Two push-buttons (SC, ST) to operate the BR and a change-over switch (SRY) to simulate CBREADY
- Possibly a switch simulation the Synchrocheck SESRSYN condition.

6.8.3.1 Preparation of the verification

1. Check the function settings. In the HMI tree they are found under **Main menu/Settings/IED Settings/Control/STBRREC(79,0->1)/1:STBRREC** If any timer settings are reduced to speed-up or facilitate the testing, they shall be set to normal after testing. A temporary label on the unit can be a reminder to restore normal settings after which a verification test should be performed.
2. Decide if a synchronization check (SYNC) shall be included in the test.

If SYNC as an internal function or external device is not operated by the injection, it may be connected as a permanent high signal or controlled by a switch.

3. Read and make notes of the reclosing operation counters. Local HMI tree **Main menu/Tests/Function status/Control/STBRREC(79,0->1)/1:STBRREC**
   Possibly reset the counters to zero. Counters are reset in the RESET menu. Make arrangements for the simulation of the CB, for example, as in figure 13.
4. Make arrangements for indication, recording and time measurements.
   The signals for CBPOS, START, TR3P, CLOSECB, READY and other relevant signals should preferably be arranged for event recording with time tagging. If that is not possible, other means of time measurement and recording should be arranged.

6.8.3.2 Switching the auto-reclosing function *On* and *Off*

1. Set the *Operation* setting to *Off* and check the state.
2. Set the *Operation* setting to *On* and check the state, including SETON and READY.
   The CB should be closed and ready.
3. If external control *On*/*Off* is connected, check that it works.
4. Set *Operation* to *ExternalCtrl*, and use that control to switch *On* and *Off*, and check the state of the function.

6.8.3.3 Verifying the auto-reclosing function

Select the test cases to be run according to what is applicable to the particular application. It can be, for example, three-phase single-shot reclosing or two-shot reclosing. Below a case with three-phase single-shot reclosing is described.

1. Set *Operation* = *On*.
2. If SESRSYN is not to be operated, ensure that the SYNC input is activated. If the SESRSYN function is to be included, ensure that SESRSYN is supplied with the appropriate AC quantities.
3. Simulate CB closed position by closing switch SC to make the BR relay start.
4. Simulate CBREADY by closing the switch SRY, and leave it closed.
5. Inject AC quantities to give a trip to the BR and to the START input.
   Observe and preferably record the operation. The BR relay shall trip and reclose (start). After reclosing, the SRY switch can be opened for about 5 s and then closed again.
   The auto-reclosing open time and the sequence should be checked, for example in the event recording. Check also the operation indications (disturbance report) and the operation counters. **Main menu/Tests/Function status/STBRREC (79, 0->1)/1:STBRREC**

Should the operation not be as expected, this should be investigated. It could be caused by an inappropriate setting or missing condition such as CBREADY (or SYNC at three-phase reclosing).

6. Repeat the sequence by simulating a permanent fault.
   Shortly after the reclosing shot a new fault is applied. If a single-shot reclosing program is selected, there shall be one reclosing operation and then blocking of the auto-reclosing function for the set Reclaim time.
   Before a new reclosing sequence can be run, the CBREADY and CBPOS (CB closed) must be set manually.

6.8.3.4 Checking the reclosing conditions

When checking the influence of a releasing condition it is suggested to first run a sequence with the condition fulfilled. When the condition signal is removed, and a new sequence is run, it indicates that the result was due to the changed condition. In case of a blocking signal the procedure should be similar. Start without the blocking or inhibit signal, and then run a sequence with the blocking or inhibit signal added.

6.8.3.5 Checking the influence of the INHIBIT signal

1. Check that the auto-reclosing function is operative, for example, by making a reclosing shot without the INHIBIT signal.
2. Apply a fault and thereby a START signal. At the same time, or during the open time, apply a signal to the input INHIBIT.
3. Check that the reclosing sequence is interrupted and no reclosing takes place.

6.8.3.6 Check closing onto a fault

1. Check that the closing function is operative, for example by making a reclosing shot.
   Keep the CBREADY signal high.
2. Set the breaker simulating relay BR in Open position.
3. Close the BR relay and apply immediately a fault and thereby a START signal.
4. Check that no reclosing takes place.

6.8.3.7 Checking the influence of CB not ready for reclosing

1. Check that the auto-reclosing function is operative, for example by making a reclosing shot.
   Keep the CB simulator BR closed. Remove the CBREADY signal by opening SRY.
2. Apply a fault and thereby a START signal.
3. Check that no reclosing takes place.

6.8.3.8 Checking the influence of synchrocheck (at three-phase reclosing)

1. Check that the auto-reclosing function is operative, for example, by making a three-phase reclosing shot with the synchrocheck condition.
   Remove the SYNC signal.
2. Apply a fault causing three-phase trip and thereby a START and a TR3P signal.
3. Wait for the *tSync* time out limit.
   Check that no reclosing is made.

6.8.3.9 Restoring equipment

After the tests, restore the equipment to normal or desired state. Check the following items in particular.

1. Check the operation counters.
   Reset the counters to zero, if that is the user's preference. The counter reset function is found in the HMI under **Main menu/Clear/Clear counters/ STBRREC (79, 0->1)**
2. Restore settings that may have been modified for the tests back to normal.
3. Disconnect the test switch, CB simulating arrangement and test circuits.
   Reconnect any links or connection terminals, which may have been opened for the tests.
4. Reset indications, alarms and disturbance recordings.
   Clearing of the disturbance report must be done via PCM600 using the Disturbance Handling tool.

6.8.3.10 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/ Tests/Function test modes/Control/STBRREC(79,0->1)/1:STBRREC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.9 Testing scheme communication functions

6.9.1 Scheme communication logic with delta based blocking scheme signal transmit ZCPSCH

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for ZCPSCH are available on the local HMI under **Main menu/Tests/Function status/Scheme communication/ZCPSCH(85)/ 1:ZCPSCH**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

Check the scheme logic during the secondary injection test of the impedance or overcurrent protection functions.

Activating of the different zones verifies that the CS signal is issued from the intended zones. The CS signal from the independent tripping zone must have a *tSendMin* minimum time.

Check the tripping function by activating the CR and CRG inputs with the overreaching zone used to achieve the CACC signal.

It is sufficient to activate the zones with only one type of fault with the secondary injection.

6.9.1.1 Testing permissive underreaching

1. Activate the receive (CR) signal in the IED.
2. Apply healthy normal load conditions to the IED for at least two seconds.
3. Apply a fault condition within the permissive zone.
4. Check that correct trip outputs, external signals, and indications are obtained for the actual type of fault generated.
5. Check that other zones operate according to their zone timers and that the send (CS) signal is obtained only for the zone configured to generate the actual signal.
6. Deactivate the receive (CR) signal in the IED.
7. Check that the trip time complies with the zone timers and that correct trip outputs, external signals, and indications are obtained for the actual type of fault generated.

6.9.1.2 Testing permissive overreaching

1. Activate the receive (CR) signal in the IED.
2. Apply healthy normal load conditions to the IED for at least two seconds.
3. Apply a fault condition within the permissive zone.
4. Check that correct trip outputs, external signals, and indication are obtained for the actual type of fault generated.
5. Check that the other zones operate according to their zone timer and that the send (CS) signal is obtained only for the zones that are configured to give the actual signal. Also the zone connected to CS underreach is giving CS in this mode.
6. Deactivate the IED receive (CR) signal.

7. Apply healthy normal load conditions to the IED for at least two seconds.
8. Apply a fault condition within the permissive zone.
9. Check that trip time complies with the zone timers and that correct trip outputs, external signals, and indications are obtained for the actual type of fault generated.

6.9.1.3 Testing blocking scheme

1. Deactivate the receive (CR) signal of the IED.
2. Apply healthy normal load conditions to the IED for at least two seconds.
3. Apply a fault condition within the forward directed zone used for scheme communication tripping.
4. Check that correct trip outputs and external signals are obtained for the type of fault generated and that the operate time complies with the *tCoord* timer (plus relay measuring time).
5. Check that the other zones operate according to their zone times and that a send (CS) signal is only obtained for the reverse zone.
6. Activate the IED receive (CR) signal.
7. Apply a fault condition in the forward directed zone used for scheme communication tripping.
8. Check that the no trip from scheme communication occurs.
9. Check that the trip time from the forward directed zone used for scheme communication tripping complies with the zone timer and that correct trip outputs, external signals, and indications are obtained for the actual type of fault generated.

6.9.1.4 Testing delta blocking scheme

1. Deactivate the receive (CR) signal of the IED.
2. Apply healthy normal load conditions to the IED for at least two seconds.
3. Apply a fault condition within the forward directed zone used for scheme communication tripping.
4. Check that correct trip outputs and external signals are obtained for the type of fault generated and that the operate time complies with the *tCoord* timer (plus relay measuring time).
5. Check that the other zones operate according to their zone times and that a send (CS) signal is only obtained for the reverse zone.
6. Check that for a forward fault, carrier send (CS) signal is first obtained from the delta based fault inception detection (as it is not directional) , and immediately inhibited by the forward zone.
7. Activate the IED receive (CR) signal.

8. Apply a fault condition in the forward directed zone used for scheme communication tripping.
9. Check that the no trip from scheme communication occurs.
10. Check that the trip time from the forward directed zone used for scheme communication tripping complies with the zone timer and that correct trip outputs, external signals, and indications are obtained for the actual type of fault generated.

6.9.1.5 Checking of unblocking logic

Check the unblocking function (if the function is required) when checking the communication scheme.

Command function with continuous unblocking (*Unblock* = *1*)

Procedure

1. Activate the guard input signal (CRG) of the IED.
2. Using the scheme selected, check that a signal accelerated trip (TRIP) is obtained when the guard signal is deactivated.

6.9.1.6 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Scheme communication/ZCPSCH(85)/1:ZCPSCH** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.9.2 Current reversal and WEI logic for distance protection 3-phase ZCRWPSCH

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for ZCRWPSCH are available on the local HMI under **Main menu/Tests/Function status/Scheme communication/ZCRWPSCH(85)/1:ZCRWPSCH**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The current reversal logic and the weak-end infeed functions are tested during the secondary-injection test of the impedance or overcurrent protection zones together with the scheme communication logic for the distance protection function ZCPSCH.

6.9.2.1 Current reversal logic

It is possible to check the delay of the CS send signal with *tDelayRev* by changing from a reverse to a forward fault.

By continuously activating the CR input and changing from a reverse to a forward fault, the delay *tDelayRev* can be checked.

Checking of current reversal

The reverse zone timer must not operate before the forward zone fault is applied. The user might need to increase the reverse zone timer setting during testing of current reversal.

The forward zone timer must be set longer than the *tDelayRev* setting.

1. Activate the receive (CRL) signal.
2. Set the healthy condition to an impedance at 50% of the reach of the reverse zone connected to IRVL.
3. After the start condition is obtained for reverse zone, apply a fault at 50% of the reach of the forward zone connected to WEIBLK2.
4. Check that correct trip outputs and external signals are obtained for the type of fault generated.
   The operation time should be about the *tDelayRev* setting longer than the carrier accelerated trip (TRIP) previously recorded for permissive scheme communication.
5. Restore the forward and reverse zone timer to its original setting.

6.9.2.2 Weak-end infeed logic at permissive schemes

1. Check the blocking of the echo with the injection of a CRL signal >40ms after a reverse fault is applied.
2. Measure the duration of the echoed CS signal by applying a CRL receive signal.
3. Check the trip functions and the voltage level for trip by reducing a phase voltage and applying a CRL receive signal.

6.9.2.3 Testing conditions

Only one type of fault is sufficient, with the current reversal and weak-end infeed logic for distance protection function ZCRWPSCH. .. For phase L1-N fault, set these parameters:

Table 11: Phase L1-N parameter values

Phase	I (Amps)	Phase-angle (Deg)	V (Volts)	Phase-angle (Deg)
L1	0	0	Set less than *UPN<*	0
L2	0	240	63	240
L3	0	120	63	120

If wanted, change all settings cyclically for other faults (L2-N and L3-N).

Weak-end infeed set for echo and trip

1. Apply input signals according table 11.
2. Activate the receive (CR) signal.
3. After the IED has operated, turn off the input signals.
4. Check that trip, send signal, and indication are obtained.
   (note: a 200mS pulse)

6.9.2.4 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Scheme communication/ZCRWPSCH(85)/1:ZCRWPSCH** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.9.3 Current reversal and WEI logic for distance protection, phase segregated ZCWSPSCH

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for ZCWSPSCH are available on the local HMI under **Main menu/Tests/Function status/Scheme communication/ZCWSPSCH(85)/1:ZCWSPSCH**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The current reversal logic and the weak-end infeed functions are tested during the secondary injection test of the impedance or overcurrent protection zones together with the Scheme communication logic for the distance protection function ZCPSCH .

6.9.3.1 Current reversal logic

It is possible to check the delay of the CS send signal with *tDelayRev* by changing from a reverse to a forward fault.

By continuously activating the CR input and changing from a reverse to a forward fault, the delay *tDelayRev* can be checked.

Checking of current reversal

The reverse zone timer must not operate before the forward zone fault is applied. The user might need to increase the reverse zone timer setting during testing of current reversal.

The forward zone timer must be set longer than the *tDelayRev* setting.

1. Activate the receive (CRL) signal.
2. Set the healthy condition to an impedance at 50% of the reach of the reverse zone connected to IRVL.
3. After the start condition is obtained for reverse zone, apply a fault at 50% of the reach of the forward zone connected to WEIBLK2.
4. Check that correct trip outputs and external signals are obtained for the type of fault generated.
   The operation time should be about the *tDelayRev* setting longer than the carrier accelerated trip (TRIP) previously recorded for permissive scheme communication.
5. Restore the forward and reverse zone timer to its original setting.

6.9.3.2 Weak-end infeed logic at permissive schemes

1. Check the blocking of the echo with the injection of a CRL signal >40 ms after a reverse fault is applied.
2. Measure the duration of the echoed CS signal by applying a CRL receive signal.
3. Check the trip functions and the voltage level for trip by reducing a phase voltage and applying a CRL receive signal.

6.9.3.3 Testing conditions

Only one type of fault is sufficient, with the Current reversal and WEI logic for distance protection phase segregated ZCWSPSCH. Apply three faults (one in each phase). For phase *L1-N* fault, set these parameters:

Table 12: Phase L1-N parameter values

Phase	I (Amps)	Phase-angle (Deg)	V (Volts)	Phase-angle (Deg)
L1	0	0	Set less than *UPN<*	0
L2	0	240	63	240
L3	0	120	63	120

Change all settings cyclically for other faults (*L2-N* and *L3-N*).

Weak-end infeed set for echo and trip.

1. Apply input signals according to table 12.
2. Activate the receive (CR) signal of the terminal.
3. After the relay has operated, turn off the input signals.
4. Check that trip, send signal, and indication are obtained (note: a 200ms pulse).
5. Apply input signals according to table 12.
6. Activate the receive (CR) signal of the terminal.
7. After the relay has operated turn off the input signals.
8. Check that the send signal is obtained.

6.9.3.4 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Scheme communication/ZCWSPSCH(85)/1:ZCWSPSCH** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.9.4 Local acceleration logic ZCLCPLAL

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for ZCLCPLAL are available on the local HMI under **Main menu/Tests/Function status/Scheme communication/ZCLCPLAL/1:ZCLCPLAL**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The logic is checked during the secondary injection test of the impedance measuring zones.

6.9.4.1 Verifying the settings

1. Provide the IED with conditions equivalent to normal load for at least two seconds.
2. Deactivate the conditions for accelerated function.
3. Apply a phase-to-earth fault at 100% of line impedance.
4. Check that the fault is tripped with the second zone time delay.
5. Provide the IED with conditions equivalent to normal load for at least two seconds.
6. Activate the condition for accelerated function either by the autorecloser or by the loss-of-load.
7. Apply a phase-to-earth fault at 100% of line impedance.
8. Check that the fault is tripped instantaneously.

6.9.4.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Scheme communication/ZCLCPLAL/1:ZCLCPLAL** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.9.5 Scheme communication logic for residual overcurrent protection ECPSCH

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for ECPSCH are available on the local HMI under **Main menu/Tests/Function status/Scheme communication/ECPSCH(85)/1:ECPSCH**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

Before testing the communication logic for residual overcurrent protection function ECPSCH, the four step residual overcurrent protection function EF4PTOC has to be tested according to the corresponding instruction. Once this is done, continue with the instructions below.

If the current reversal and weak-end infeed logic for earth-fault protection is included, proceed with the testing according to the corresponding instruction after the testing the communication logic for residual overcurrent protection. The current reversal and weak-end-infeed functions shall be tested together with the permissive scheme.

6.9.5.1 Testing the directional comparison logic function

Blocking scheme

1. Inject the polarizing voltage 3U0 at 5% of*UBase* where the current is lagging the voltage by 65°.
2. Inject current (65° lagging the voltage) in one phase at about 110% of the set operating current, and switch the current off with the switch.
3. Switch the fault current on and measure the operating time of the communication logic.
   Use the TRIP signal from the configured binary output to stop the timer.
4. Compare the measured time with the set value *tCoord*.
5. Activate the CR binary input.
6. Check that the CRL output is activated when the CR input is activated.
7. Switch the fault current on (110% of the set operating current) and wait longer than the set value *tCoord*.

   No TRIP signal should appear.

8. Switch the fault current off.
9. Reset the CR binary input.
10. Activate the BLOCK digital input.
11. Switch the fault current on (110% of the set operating current) and wait for a period longer than the set value *tCoord*.

    No TRIP signal should appear.

12. Switch the fault current and the polarizing voltage off.
13. Reset the BLOCK digital input.

Permissive scheme

1. Inject the polarizing voltage 3U0, which is 5% of *UBase* where the current is lagging the voltage by 65°.
2. Inject current (65° lagging the voltage) into one phase at about 110% of the set operating current, and switch the current off with the switch.
3. Switch the fault current on, (110% of the set operating current) and wait longer than the set value *tCoord*.

   No TRIP signal should appear, and the CS binary output should be activated.

4. Switch the fault current off.
5. Activate the CR binary input.
6. Switch the fault current on (110% of the set operating current) and measure the operating time of the ECPSCH logic.

Use the TRIP signal from the configured binary output to stop the timer.

7. Compare the measured time with the setting for *tCoord*.
8. Activate the BLOCK digital input.
9. Switch the fault current on (110% of the set operating current) and wait for a period longer than the set value *tCoord*.

No TRIP signal should appear.

10. Switch the fault current and the polarizing voltage off.
11. Reset the CR binary input and the BLOCK digital input.

6.9.5.2 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Scheme communication/ECPSCH(85)/1:ECPSCH** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.9.6 Current reversal and weak-end infeed logic for residual overcurrent protection ECRWPSCH

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for ECRWPSCH are available on the local HMI under **Main menu/Tests/Function status/Scheme communication/ECRWPSCH(85)/1:ECRWPSCH**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

First, test the four step residual overcurrent protection function EF4PTOC and then the current reversal and weak-end infeed logic according to the corresponding instructions. Then continue with the instructions below.

6.9.6.1 Testing the current reversal logic

1. Inject the polarizing voltage 3U0 to 5% of *UBase* and the phase angle between voltage and current to 155°, the current leading the voltage.
2. Inject current (*180° — AngleRCA*) in one phase to about 110% of the set operating current of the four step residual overcurrent protection (*IN>Dir*).
3. Check that the IRVL output is activated in the disturbance recorder after the set time (*tPickUpRev*).

4. Abruptly reverse the current to *AngleRCA* setting lagging the voltage, to operate the forward directional element.
5. Check that the IRVL output still is activated after the reversal with a time delay that complies with the setting (*tDelayRev*).
6. Switch off the polarizing voltage and the current.

6.9.6.2 Testing the weak-end infeed logic

If setting *WEI = Echo*

1. Inject the polarizing voltage 3U0 to (180° — *AngleRCA*) of *UBase* and the phase angle between voltage and current to 155°, the current leading the voltage.
2. Inject current (180° — *AngleRCA*) in one phase to about 110% of the setting operating current (*IN>Dir*).
3. Activate the CRL binary input.

No ECHO and CS should appear.

4. Abruptly reverse the current to the setting of *AngleRCA* setup lagging the voltage, to operate the forward directional element.

No ECHO and CS should appear.

5. Switch off the current and check that the ECHO and CS appear on the corresponding binary output during 200ms after resetting the directional element.
6. Switch off the CRL binary input.
7. Activate the BLOCK binary input.
8. Activate the CRL binary input.

No ECHO and CS should appear.

9. Switch off the polarizing voltage and reset the BLOCK and CRL binary input.

If setting *WEI = Echo & Trip*

1. Inject the polarizing voltage 3U0 to about 90% of the setting (*3U0*) operating voltage.
2. Activate the CRL binary input.

No ECHO, CS and TRWEI outputs should appear.

3. Increase the injected voltage to about 110% of the setting (3U0) operating voltage.
4. Activate the CRL binary input.
5. Check that the ECHO, CS and TRWEI appear on the corresponding binary output or on the local HMI.
6. Reset the CRL binary input.
7. Activate the BLOCK binary input.
8. Activate the CRL binary input.

No ECHO, CS and TRWEI outputs should appear.

9. Reset the CRL and BLOCK binary input.
10. Inject the polarizing voltage 3U0 to about 110% of the setting (*3U0*) and adjust the phase angle between the voltage and current to (180° — *AnglRCA*) setting the current leading the voltage.
11. Inject current in one phase to about 110% of the setting operating current (*IN>Dir*).
12. Activate the CRL binary input.

No ECHO and TRWEI should appear.

13. Abruptly reverse the current to 65° lagging the voltage, to operate the forward directional element.

No ECHO and TRWEI should appear.

14. Switch the current off and check that the ECHO, CS and TRWEI appear on the corresponding binary output during 200ms after resetting the directional element. If EF4PTOC operates in forward direction also CS should be obtained.
15. Switch the polarizing voltage off and reset the CRL binary input.

6.9.6.3 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Scheme communication/ECRWPSCH(85)/1:ECRWPSCH** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.10 Testing logic functions

6.10.1 Tripping logic, common 3-phase output SMPPTRC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for SMPPTRC are available on the local HMI under **Main menu/Tests/Function status/Logic/SMPPTRC(94,1->0)/X:SMPPTRC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

This function is functionality tested together with other protection functions (earth-fault overcurrent protection, and so on) within the IED. It is recommended that the function is tested together with the autorecloser function, regardless of whether the autorecloser function is integrated or external.

6.10.1.1 Three-phase operating mode

1. Check that *AutoLock* and *TripLockout* are both set to *Off*.
2. Initiate a three-phase fault.
   An adequate time interval between the faults should be considered, to overcome a reclaim time caused by the possible activation of the Autorecloser function, SMBRREC. The function must issue a three-phase trip in all cases, when a trip is initiated by any protection function, either integrated or external. The functional TRIP output signal must always appear.

6.10.1.2 Circuit breaker lockout

The following tests should be carried out when the built-in lockout function is used in addition to possible other tests, which depends on the complete configuration of an IED.

1. Check that *AutoLock* and *TripLockout* are both set to *Off*.
2. Initiate a three-phase fault.
   The functional output TRIP should be active at each fault. The output CLLKOUT must not be activated.
3. Activate the automatic lockout function, set *AutoLock* = *On* and repeat.
   Besides the TRIP outputs, CLLKOUT should be set.
4. Reset the lockout signal by activating the reset lockout (RSTLKOUT) signal.
5. Activate the TRIP signal lockout function, set *TripLockout* = *On* and repeat.
   The output TRIP must be active and stay active after each fault. CLLKOUT must be activated.
6. Reset the lockout.

All functional outputs should reset.

7. Deactivate the TRIP signal lockout function, set *TripLockout* = *Off* and the automatic lockout function, set *AutoLock* = *Off* if not used.

6.10.1.3 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Logic/SMPPTRC(94,1->0)/X:SMPPTRC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.10.2 Tripping logic phase segregated output SPTPTRC

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for SPTPTRC are available on the local HMI under **Main menu/Tests/Function status/Logic/SPTPTRC(94,1->0)/1:SPTPTRC**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

This function is functionality tested together with other protection functions (earth-fault overcurrent protection, and so on) within the IED. It is recommended that the function is tested together with the autorecloser function, or when a separate external unit is used for reclosing purposes. The testing is preferable done in conjunction with the protection system and autorecloser function.

6.10.2.1 1ph/3ph operating mode

In addition to various other tests, the following tests should be performed. They depend on the complete configuration of an IED.

1. Make sure that *TripLockout* and *AutoLock* are both set to *Off*.
2. Initiate different single-phase-to-earth faults one at a time.
   Single-phase tripping will only be allowed when an auto-reclose attempt will follow. Autorecloser STBRREC has functionality such as the long trip time, CB ready and so on, which can prevent a proper single-phase tripping and auto reclose. To bypass this problem the fault initiation should be with a test set and with the auto reclose in full service with a test set connected to the distance protection function. Consider using an adequate time interval between faults, to overcome a reclaim time of which is activated by the autorecloser function. Only a single-phase trip should occur for each separate fault and only one of the trip outputs (TRLn) should be activated at a time. Functional outputs TRIP and TR1P should be active during each fault. No other outputs should be active.
3. Initiate different phase-to-phase and three-phase faults.

Consider using an adequate time interval between faults, to overcome a reclaim time which is activated by the STBRREC function. A three-phase trip should occur for each separate fault and all of the trips. Functional outputs TRIP, all TRLn and TR3P should be active at each fault. No other outputs should be active.

4. Initiate a single-phase-to-earth fault and switch it off immediately when the trip signal is issued for the corresponding phase.
5. Initiate the same fault once again within the reclaim time of the used autorecloser function.
   A single-phase fault shall be given at the first fault. A three-phase trip must be initiated for the second fault. Check that the corresponding trip signals appear after both faults. Functional outputs TRIP, TRLn and TR1P should be active during first fault. No other outputs should be active. Functional outputs TRIP, all TRLn and TR3P should be active during second fault.
6. Initiate a single-phase-to-earth fault and switch it off immediately when the trip signal is issued for the corresponding phase.
7. Initiate the second single-phase-to-earth fault in one of the remaining phases. This shall be within the time interval, shorter than *tEvolvingFault* (default setting 2.0 s) and shorter than the dead-time of the autoreclose function, when included in the protection scheme. Check that the second trip is a three-phase trip and that a three-phase autoreclosing attempt is given after the three-phase dead time. Functional outputs TRIP, TRLn and TR1P should be active during first fault. No other outputs should be active. Functional outputs TRIP, all TRLn and TR3P should be active during second fault.

6.10.2.2 Circuit breaker lockout

The following tests should be carried out when the built-in lockout function is used in addition to possible other tests, which depends on the complete configuration of an IED.

1. Check that *AutoLock* and *TripLockout* are both set to *Off*.
2. Initiate a three-phase fault
   The functional output TRIP should be active at each fault. The output CLLKOUT must not be set.
3. Activate the automatic lockout function, set *AutoLock* = *On* and repeat.
4. Reset the lockout signal by shortly thereafter activating the reset lockout (RSTLKOUT) signal.
5. Activate the TRIP signal lockout function, set *TripLockout* = *On* and repeat. The output TRIP must be active and stay active after each fault, CLLKOUT must be set.
6. Reset the lockout.
   All functional outputs should reset.
7. Deactivate the TRIP signal lockout function, set *TripLockout* = *Off* and the automatic lockout function, set *AutoLock* = *Off* if not used.

6.10.2.3 Completing the test

Continue to test another function or end the testing by setting the parameter *TestMode* to *Off* under **Main menu/Tests/IED test mode/1:TESTMODE**. If another function is tested, then set the parameter *Blocked* to *No* under **Main menu/Tests/Function test modes/Logic/SPTPTRC(94,1->0)/1:SPTPTRC** for the function, or for each individual function in a chain, to be tested next. Remember to set the parameter *Blocked* to *Yes*, for each individual function that has been tested.

6.11 Testing monitoring functions

6.11.1 Event counter CNTGGIO

The event counter function CNTGGIO can be tested by connecting a binary input to the counter under test and applying pulses to the counter. The speed of pulses must not exceed 10 per second. Normally the counter will be tested in connection with tests on the function that the counter is connected to, such as trip logic. When configured, test it together with the function that operates it. Trig the function and check that the counter result corresponds with the number of operations.

6.11.2 Fault locator LMBRFLO

Prepare the IED for verification of settings as outlined in 5.1 "Preparing the IED to verify settings".

Values of the logical signals for LMBRFLO are available on the local HMI under **Main menu/Tests/Function status/Monitoring/LMBRFLO/1:LMBRFLO**. The Signal Monitoring in PCM600 shows the same signals that are available on the local HMI.

The Fault locator function LMBRFLO depends on other functions to work properly, that is, phase selection information from distance protection function and analog information supplied by the trip value recorder function. Check that proper binary start and phase selection signals are connected and voltage and current signals are configured (parameter settings).

The fault locator LMBRFLO function, supports kilometer and mile for the line length unit. The fault distance will be presented with the same unit as the line length and is mapped to IEC61850 -8-1 communication protocol, where the fault distance is supposed to be in kilometer (km). Select the line length unit to kilometer for compliance with IEC61850.

The result is displayed on the local HMI or via PCM600. Distances to faults for the last 100 recorded disturbances can be found on the local HMI under **Main menu/ Tests/Function status/Monitoring/LMBRFLO/1:LMBRFLO/Outputs**

If PCM600 is used, the result is displayed on the recording list after upload, including loop selection information.

Table 13: Test settings

Parameter	Condition
I	Higher than 30% I_r
Healthy conditions	U = 63,5 V, I = 0 A & ZF = 0°
Impedance |Z|	Test point Note: • $Z_x \leq$ (X0 + 2 · X1)/3 For single-phase faults • $Z_x \leq$ X1 For three and two phase faults • $Z_x \leq$ (X0 + 2 · X1 XM)/3 For single-phase fault with mutual zero-sequence current
Impedance angle ZΦ	Test angle • ZΦ arctan[(X0 + 2 · X1) / (R0 + 2R1)] For single-phase faults • ZΦ arctan(X1/R1) For two-phase faults

6.11.2.1 Measuring the operate limit

1. Set the test point (|Z| fault impedance and ZΦ impedance phase angle) for a condition that meets the requirements in table 13.
2. Subject the IED to healthy normal load conditions for at least two seconds.
3. Apply a fault condition.
   Check that the distance-to-fault value displayed on the HMI complies with equations 18, 19 and 20

$$p = \frac{Z_x}{X1} \cdot 100$$

(Equation 18)

in % for two- and three-phase faults

$$p = \frac{3 \cdot Z_x}{X0 + 2 \cdot X1} \cdot 100$$

(Equation 19)

in % for single-phase-to-earth faults

$$p = \frac{3 \cdot Z_x}{X0 + 2 \cdot X1 \pm XM} \cdot 100$$

(Equation 20)

in % for single-phase-to-earth faults with mutual zero sequence current.

Where:

p = the expected value of a distance to fault in percent

Z_x = set test point on the test set

X0 = set zero-sequence reactance of a line

X1 = set positive-sequence reactance of a line

XM = set mutual zero-sequence impedance of a line

6.11.2.2 Completing the test

6.12 Testing metering functions

6.12.1 Pulse counter PCGGIO

The test of the Pulse counter function PCGGIO requires the Parameter Setting tool in PCM600 or an appropriate connection to the local HMI with the necessary functionality. A known number of pulses with different frequencies are connected to the pulse counter input. The test should be performed with settings *Operation* = *On* or *Operation* = *Off* and the function blocked or unblocked. The pulse counter value is then checked in PCM600 or on the local HMI.

6.13 Exit test mode

The following procedure is used to return to normal operation.

1. Navigate to the test mode folder.
2. Change the *On* setting to *Off*. Press the 'E' key and the left arrow key.
3. Answer *YES*, press the 'E' key and exit the menus.

Section 7 Commissioning and maintenance of the fault clearing system

7.1 Commissioning and maintenance of the fault clearing system

About this chapter

This chapter discusses maintenance tests and other periodic maintenance measures.

7.1.1 Commissioning tests

During commissioning all protection functions shall be verified with the setting values used at each plant. The commissioning tests must include verification of all circuits by green-lining the circuit diagrams and the configuration diagrams for the used functions.

Further, the settings for protection functions are tested and recorded carefully as outlined for the future periodic maintenance tests.

The final testing includes primary verification of all directional functions where load currents is checked on the local HMI and in PCM600. The amplitudes and angles of all currents and voltages should be checked and the symmetry verified.

Directional functions have information about the measured direction and, for example, measured impedance. These values must be checked and verified as correct with the export or import of power available.

Finally, final trip tests must be performed. This involves activation of protection functions or tripping outputs with the circuit breaker closed and the tripping of the breaker verified. When several breakers are involved, each breaker must be checked individually and it must be verified that the other involved breakers are not tripped at the same time.

7.1.2 Periodic maintenance tests

The periodicity of all tests depends on several factors, for example the importance of the installation, environmental conditions, simple or complex equipment, static or electromechanical IEDs, and so on.

The normal maintenance praxis of the user should be followed. However, ABB's recommendation is as follows:

Every second to third year

- Visual inspection of all equipment.
- Removal of dust on ventilation louvres and IEDs if necessary.
- Periodic maintenance test for protection IEDs of object where no redundant protections are provided.

Every four to six years

- Periodic maintenance test for protection IEDs of objects with redundant protection system.

First maintenance test should always be carried out after the first half year of service.

When protection IEDs are combined with built-in control, the test interval can be increased drastically, up to for instance 15 years, because the IED continuously reads service values, operates the breakers, and so on.

7.1.2.1 Visual inspection

Prior to testing, the protection IEDs should be inspected to detect any visible damage that may have occurred (for example, dirt or moisture deposits, overheating). Should burned contacts be observed when inspecting the IEDs, a diamond file or an extremely fine file can be used to polish the contacts. Emery cloth or similar products must not be used as insulating grains of abrasive may be deposited on the contact surfaces and cause failure.

Make sure that all IEDs are equipped with covers.

7.1.2.2 Maintenance tests

To be made after the first half year of service, then with the cycle as proposed above and after any suspected maloperation or change of the IED setting.

Testing of protection IEDs shall preferably be made with the primary circuit de-energized. The IED cannot protect the circuit during testing. Trained personnel may test one IED at a time on live circuits where redundant protection is installed and de-energization of the primary circuit is not allowed.

ABB protection IEDs are preferably tested by aid of components from the COMBITEST testing system described in information B03-9510 E. Main components are RTXP 8/18/24 test switch located to the left in each protection IED and RTXH 8/18/24 test handle, which is inserted in test switch at secondary

testing. All necessary operations such as opening of trip circuits, short-circuiting of current circuits and opening of voltage circuits are automatically performed in the right order to allow for simple and safe secondary testing even with the object in service.

Preparation

Before starting maintenance testing, the test engineers should scrutinize applicable circuit diagrams and have the following documentation available:

- Test instructions for protection IEDs to be tested
- Test records from previous commissioning and maintenance tests
- List of valid settings
- Blank test records to fill in measured values

Recording

It is of utmost importance to carefully record the test results. Special test sheets covering the frequency of test, date of test and achieved test values should be used. IED setting list and protocols from previous tests should be available and all results should be compared for differences. At component failures, spare equipment is used and set to the requested value. A note of the exchange is made and the new measured values are recorded. Test records for several years of testing should be stored in a common file for a station, or a part of a station, to give a simple overview of the period of testing and achieved test values. These test records are valuable when analysis of service disturbances shall be done.

Secondary injection

The periodic maintenance test is done by secondary injection from a portable test set. Each protection shall be tested according to the secondary injection test information for the specific protection IED. Only the setting values adopted shall be checked for each protection function. If the discrepancy between obtained value and requested set value is too big the setting should be adjusted, the new value recorded and a note should be made in the test record.

Alarm test

When inserting the test handle the alarm and event signalling is normally blocked. This is done in the IED by setting the event reporting to *Off* during the test. This can be done when the test handle is inserted or the IED is set to test mode from the local HMI. At the end of the secondary injection test it should be checked that the event and alarm signalling is correct by activating the events and performing some selected tests.

Self supervision check

Once secondary testing has been completed, it should be checked that no self-supervision signals are activated continuously or sporadically. Especially check the time synchronization system, GPS or other, and communication signals, both station communication and remote communication.

Trip circuit check

When the protection IED undergoes an operational check, a tripping pulse is normally obtained on one or more of the output contacts and preferably on the test switch. The healthy circuit is of utmost importance for the protection operation. If the circuit is not provided with a continuous trip-circuit supervision, it is possible to check that circuit is really closed when the test-plug handle has been removed by using a high-ohmic voltmeter and measuring between the plus and the trip output on the panel. The measurement is then done through the tripping magnet of the circuit breaker and therefore the complete tripping circuit is checked.

Note that the breaker must be closed.

Please observe that the test system does not provide built-in security during this test. If the instrument should be set on Amp instead of Volts, the circuit breaker naturally is tripped, therefore, great care is necessary.

Trip circuit from trip IEDs to circuit breaker is often supervised by trip-circuit supervision. It can then be checked that a circuit is healthy by opening tripping output terminals in the cubicle. When the terminal is opened, an alarm shall be achieved on the signal system after a delay of some seconds.

Remember to close the circuit directly after the test and tighten the terminal carefully.

Measurement of service currents

After a maintenance test it is recommended to measure the service currents and service voltages recorded by the protection IED. The service values are checked on the local HMI or in PCM600. Ensure that the correct values and angles between voltages and currents are recorded. Also check the direction of directional functions such as Distance and directional overcurrent functions.

For transformer differential protection, the achieved differential current value is dependent on the tap changer position and can vary between less than 1% up to perhaps 10% of rated current. For line differential functions, the capacitive charging currents can normally be recorded as a differential current.

The zero-sequence current to earth-fault protection IEDs should be measured. The current amounts normally very small but normally it is possible to see if the current circuit is "alive".

The neutral-point voltage to an earth-fault protection IED is checked. The voltage is normally 0.1 to 1V secondary. However, voltage can be considerably higher due

to harmonics. Normally a CVT secondary can have around 2.5 - 3% third-harmonic voltage.

Restoring

Maintenance is very important to improve the availability of the protection system by detecting failures before the protection is required to operate. There is however little point in testing healthy equipment and then putting it back into service with an open terminal, with a removed fuse or open miniature circuit breaker with an open connection, wrong setting, and so on.

Thus a list should be prepared of all items disturbed during test so that all can be put back into service quickly and without overlooking something. It should be put back into service item by item and signed by the responsible engineer.

Section 8 Troubleshooting

8.1 Fault tracing

8.1.1 Identifying hardware errors

1. Check the module with an error.
   - Check the general IED status in **Main menu/Diagnostics/IED status/General** for a faulty hardware module.
   - Check the history of changes in internal event list in **Main menu/Diagnostics/Internal Events**.
2. Inspect the IED visually.
   - Inspect the IED visually to find any physical error causes.
   - If you can find some obvious physical damage, contact ABB for repair or replacement actions.
3. Check whether the error is external or internal.
   - Check that the error is not caused by external origins.
   - Remove the wiring from the IED and test the input and output operation with an external test device.
   - If the problem remains, contact ABB for repair or replacement actions.

8.1.2 Identifying runtime errors

1. Check the error origin from IED's internal event list **Main menu/Diagnostics/IED status/General**.
2. Reboot the IED and recheck the supervision events to see if the fault has cleared.
3. In case of persistent faults, contact ABB for corrective actions.

8.1.3 Identifying communication errors

Communication errors are normally communication interruptions or synchronization message errors due to communication link breakdown.

- Check the IEC61850 and DNP3 communication status in internal event list in **Main menu/Diagnostics/IED Status/General**.
- In case of persistent faults originating from IED's internal faults such as component breakdown, contact ABB for repair or replacement actions.

8.1.3.1 Checking the communication link operation

There are several different communication links on the product. First check that all communication ports that are used for communication are turned on.

1. Check the front communication port RJ-45.
   1.1. Check that the uplink LED is lit with a steady green light.
   The uplink LED is located on the LHMI above the RJ-45 communication port on the left. The port is used for direct electrical communication to a PC connected via a crossed-over Ethernet cable.
   1.2. Check the communication status of the front port via the LHMI in **Main menu/Test/Function status/Communication/1:DOSFRNT/Outputs**.
   Check that the *LINKUP* value is 1, that is, the communication is working. When the value is 0, there is no communication link.

The rear port connector X0 is used for connecting an external HMI to the IED. If the *LINKUP* value is 0 for front port, there is no communication link via port X0. Do not use rear port connector X0 if the IED is equipped with an LHMI.

2. Check the communication status of the rear port X1 via the LHMI in **Main menu/Test/Function status/Communication/1:DOSLAN1/Outputs**.
   The X1 communication port on the rear side of the IED is for optical Ethernet via LC connector or electrical via RJ-45 connector of the IEC 61850-8-1 station bus communication.
   - Check that the *LINKUP* value is 1, that is, the communication is working. When the value is 0, there is no communication link.

8.1.3.2 Checking the time synchronization

- Select **Main menu/Diagnostics/IED status/General** and check the status of the time synchronization on **Time Synch**.
  The *Time synch* value is *Ready* when the synchronization is in order.

Note that the time synchronization source has to be activated. Otherwise the value is always *Ready*.

8.1.4 Running the display test

To run the display test, either use the push buttons or start the test via the menu.

- Select **Main menu/Tests/LED test**.
- Press or simultaneously and .

All the LEDs are tested by turning them on simultaneously. The display shows a set of patterns so that all the pixels are activated. After the test, the display returns to normal state.

8.2 Indication messages

8.2.1 Internal faults

When the Ready LED indicates an internal fault by flashing, the message associated with the fault is found in the internal event list in the LHMI menu **Main menu/Diagnostics/Internal events**. The message includes the date, time, description and signal state for the fault. The internal event list is not updated dynamically. The list is updated by leaving the **Internal events** menu and then selecting it again. The current status of the internal fault signals can also be checked via the LHMI in **Main menu/Diagnostics/IED status**.

Different actions are taken depending on the severity of the fault. If the fault is found to be permanent, the IED stays in internal fault mode. The IED continues to perform internal tests during the fault situation.

When a fault appears, the fault indication message is to be recorded and stated when requesting support or service.

Table 14: Internal fault indications

Fault indication	Additional information
Internal Fault Real Time Clock Error	Hardware error with the real time clock.
Internal Fault Runtime Exec. Error	One or more of the application threads are not working properly.
Internal Fault SW Watchdog Error	This signal will be activated when the terminal has been under too heavy load for at least 5 minutes.
Internal Fault Runtime App Error	One or more of the application threads are not in an expected state.
Internal Fault File System Error	A file system error has occurred.
Internal Fault TRM-Error	A TRM card error has occurred. The instance number is displayed at the end of the fault indication.
Internal Fault COM-Error	A COM card error has occurred. The instance number is displayed at the end of the fault indication.
Internal Fault PSM-Error	A PSM card error has occurred. The instance number is displayed at the end of the fault indication.

8.2.2 Warnings

The warning message associated with the fault is found in the internal event list in the LHMI menu **Main menu/Diagnostics/Internal events**. The message includes the date, time, description and signal state for the fault. The current status of the internal fault signals can also be checked via the LHMI in **Main menu/Diagnostics/IED status/General**.

When a fault appears, record the fault indication message and state it when ordering service.

Table 15: Warning indications

Warning indication	Additional information
Warning IEC 61850 Error	IEC 61850 has not succeeded in some actions such as reading the configuration file, startup etc.
Warning DNP3 Error	Error in DNP3 communication.

8.2.3 Additional indications

The additional indication messages do not activate internal fault or warning.

The messages are listed in the LHMI menu under the event list. The signal status data is found under the IED status and in the internal event list.

Table 16: Additional indications

Warning indication	Additional information
Time Synch Error	Source of the time synchronization is lost or time system has made a time reset.
BATTERY1 Error	Auxiliary power is disconnected.
Settings Changed	Settings have been changed.
Setting Groups Changed	Setting group has been changed.

8.3 Correction procedures

8.3.1 Changing and setting the password

The password can only be set with PCM600.

For more information, see PCM600 documentation.

8.3.2 Identifying IED application problems

Navigate to the appropriate menu in the LHMI to identify possible problems.

- Check that the function is on.
- Check that the correct setting group (1 to 4) is activated.
- Check the blocking.
- Check the mode.
- Check the measurement value.
- Check the connection to trip and disturbance recorder functions.
- Check the channel settings.

8.3.2.1 Inspecting the wiring

The physical inspection of wiring connections often reveals the wrong connection for phase currents or voltages. However, even though the phase current or voltage connections to IED terminals might be correct, wrong polarity of one or more measurement transformers can cause problems.

- Check the current or voltage measurements and their phase information from **Main menu/Measurements/Analog primary values** or **Analog secondary voltages**.
- Check that the phase information and phase shift between phases is correct.
- Correct the wiring if needed.
  - Change the parameter *Negation* in **Configuration/Analog modules/ 3PhaseAnalogGroup/1:SMAI_20_n** (n= the number of the SMAI used).

    Changing the *Negation* parameter is not recommended without special skills.

  - In PCM600, change the parameter *CTStarPointn* (n= the number on the current input) under the parameter settings for each current input.
- Check the actual state of the connected binary inputs.
  - In LHMI, select **Main menu/Tests/Binary input values/Binary input modules**. Then navigate to the board with the actual binary input to be checked.
  - With PCM600, right-click the product and select **Signal Monitoring**. Then navigate to the actual I/O board and to the binary input in question. The activated input signal is indicated with a yellow-lit diode.
- Measure output contacts using the voltage drop method of applying at least the minimum contact load given for the output relays in the technical data, for example 100 mA at 24 V AC/DC.

  Output relays, especially power output relays, are designed for breaking high currents. Due to this, layers of high resistance

may appear on the surface of the contacts. Do not determine proper functionality of connectivity or contact resistance by measuring with a regular hand-held ohm meter.



Figure 25: Testing output contacts using the voltage drop method

1 Contact current
2 Contact voltage drop
3 Load
4 Supply voltage



Figure 26: Testing a trip contact

1 Trip contact under test
2 Current limiting resistor

- To check the status of the output circuits driving the output relay via the LHMI, select **Main menu/Tests/Binary output values/Binary output modules** and then navigate to the board with the actual binary output to be checked.
- Test and change the relay state manually.
  1. To set the IED to test mode, select **Main menu/Tests/IED testmode1:TESTMODE/TestMode** and set the parameter to *On*.
  2. To operate or force the output relay to operate, select and then navigate to the board with the actual binary output relay to be operated/forced.
  3. Select the BOn_PO to be operated/forced and use and or to operate the actual output relay.
     In PCM600, only the result of these operations can be checked by right-clicking the product and selecting Signal Monitoring tool and then

navigating to the actual I/O-board and the binary input in question. The activated output signal is indicated with a yellow-lit diode. Each BOn_PO is represented by two signals. The first signal in LHMI is the actual value 1 or 0 of the output, and in PCM600 a lit or dimmed diode. The second signal is the status Normal or Forced. Forced status is only achieved when the BO is set to *Forced* or operated on the LHMI.

Set the parameter *TestMode* to *Off* after completing these tests. The Start LED stops flashing when the relay is no longer in test mode.

An initially high contact resistance does not cause problems as it is reduced quickly by the electrical cleaning effect of fritting and thermal destruction of layers, bringing the contact resistance back to the mOhm range. As a result, practically the full voltage is available at the load.

Section 9 Glossary

AC	Alternating current
ACT	Application configuration tool within PCM600
A/D converter	Analog-to-digital converter
ADBS	Amplitude deadband supervision
AI	Analog input
ANSI	American National Standards Institute
AR	Autoreclosing
ASCT	Auxiliary summation current transformer
ASD	Adaptive signal detection
AWG	American Wire Gauge standard
BI	Binary input
BOS	Binary outputs status
BR	External bistable relay
BS	British Standards
CAN	Controller Area Network. ISO standard (ISO 11898) for serial communication
CB	Circuit breaker
CCITT	Consultative Committee for International Telegraph and Telephony. A United Nations-sponsored standards body within the International Telecommunications Union.
CCVT	Capacitive Coupled Voltage Transformer
Class C	Protection Current Transformer class as per IEEE/ ANSI
CMPPS	Combined megapulses per second
CMT	Communication Management tool in PCM600
CO cycle	Close-open cycle
Codirectional	Way of transmitting G.703 over a balanced line. Involves two twisted pairs making it possible to transmit information in both directions
COMTRADE	Standard format according to IEC 60255-24
Contra-directional	Way of transmitting G.703 over a balanced line. Involves four twisted pairs, two of which are used for transmitting data in both directions and two for transmitting clock signals

CPU	Central processor unit
CR	Carrier receive
CRC	Cyclic redundancy check
CROB	Control relay output block
CS	Carrier send
CT	Current transformer
CVT	Capacitive voltage transformer
DAR	Delayed autoreclosing
DARPA	Defense Advanced Research Projects Agency (The US developer of the TCP/IP protocol etc.)
DBDL	Dead bus dead line
DBLL	Dead bus live line
DC	Direct current
DFC	Data flow control
DFT	Discrete Fourier transform
DHCP	Dynamic Host Configuration Protocol
DIP-switch	Small switch mounted on a printed circuit board
DI	Digital input
DLLB	Dead line live bus
DNP	Distributed Network Protocol as per IEEE/ANSI Std. 1379-2000
DR	Disturbance recorder
DRAM	Dynamic random access memory
DRH	Disturbance report handler
DSP	Digital signal processor
DTT	Direct transfer trip scheme
EHV network	Extra high voltage network
EIA	Electronic Industries Association
EMC	Electromagnetic compatibility
EMF	(Electric Motive Force)
EMI	Electromagnetic interference
EnFP	End fault protection
EPA	Enhanced performance architecture
ESD	Electrostatic discharge
FCB	Flow control bit; Frame count bit

FOX 20	Modular 20 channel telecommunication system for speech, data and protection signals
FOX 512/515	Access multiplexer
FOX 6Plus	Compact time-division multiplexer for the transmission of up to seven duplex channels of digital data over optical fibers
G.703	Electrical and functional description for digital lines used by local telephone companies. Can be transported over balanced and unbalanced lines
GCM	Communication interface module with carrier of GPS receiver module
GDE	Graphical display editor within PCM600
GI	General interrogation command
GIS	Gas-insulated switchgear
GOOSE	Generic object-oriented substation event
GPS	Global positioning system
HDLC protocol	High-level data link control, protocol based on the HDLC standard
HFBR connector type	Plastic fiber connector
HMI	Human-machine interface
HSAR	High speed autoreclosing
HV	High-voltage
HVDC	High-voltage direct current
IDBS	Integrating deadband supervision
IEC	International Electrical Committee
IEC 60044-6	IEC Standard, Instrument transformers – Part 6: Requirements for protective current transformers for transient performance
IEC 61850	Substation automation communication standard
IEC 61850–8–1	Communication protocol standard
IEEE	Institute of Electrical and Electronics Engineers
IEEE 802.12	A network technology standard that provides 100 Mbits/s on twisted-pair or optical fiber cable
IEEE P1386.1	PCI Mezzanine Card (PMC) standard for local bus modules. References the CMC (IEEE P1386, also known as Common Mezzanine Card) standard for the mechanics and the PCI specifications from the PCI SIG (Special Interest Group) for the electrical EMF (Electromotive force).

IEEE 1686	Standard for Substation Intelligent Electronic Devices (IEDs) Cyber Security Capabilities
IED	Intelligent electronic device
I-GIS	Intelligent gas-insulated switchgear
Instance	When several occurrences of the same function are available in the IED, they are referred to as instances of that function. One instance of a function is identical to another of the same kind but has a different number in the IED user interfaces. The word "instance" is sometimes defined as an item of information that is representative of a type. In the same way an instance of a function in the IED is representative of a type of function.
IP	1. Internet protocol. The network layer for the TCP/IP protocol suite widely used on Ethernet networks. IP is a connectionless, best-effort packet-switching protocol. It provides packet routing, fragmentation and reassembly through the data link layer. 2. Ingression protection, according to IEC standard
IP 20	Ingression protection, according to IEC standard, level 20
IP 40	Ingression protection, according to IEC standard, level 40
IP 54	Ingression protection, according to IEC standard, level 54
IRF	Internal failure signal
IRIG-B:	InterRange Instrumentation Group Time code format B, standard 200
ITU	International Telecommunications Union
LAN	Local area network
LIB 520	High-voltage software module
LCD	Liquid crystal display
LDD	Local detection device
LED	Light-emitting diode
MCB	Miniature circuit breaker
MCM	Mezzanine carrier module
MVB	Multifunction vehicle bus. Standardized serial bus originally developed for use in trains.
NCC	National Control Centre
OCO cycle	Open-close-open cycle
OCP	Overcurrent protection
OLTC	On-load tap changer
OV	Over-voltage

Overreach	A term used to describe how the relay behaves during a fault condition. For example, a distance relay is overreaching when the impedance presented to it is smaller than the apparent impedance to the fault applied to the balance point, that is, the set reach. The relay “sees” the fault but perhaps it should not have seen it.
PCI	Peripheral component interconnect, a local data bus
PCM	Pulse code modulation
PCM600	Protection and control IED manager
PC-MIP	Mezzanine card standard
PMC	PCI Mezzanine card
POR	Permissive overreach
POTT	Permissive overreach transfer trip
Process bus	Bus or LAN used at the process level, that is, in near proximity to the measured and/or controlled components
PSM	Power supply module
PST	Parameter setting tool within PCM600
PT ratio	Potential transformer or voltage transformer ratio
PUTT	Permissive underreach transfer trip
RASC	Synchrocheck relay, COMBIFLEX
RCA	Relay characteristic angle
RFPP	Resistance for phase-to-phase faults
RFPE	Resistance for phase-to-earth faults
RISC	Reduced instruction set computer
RMS value	Root mean square value
RS422	A balanced serial interface for the transmission of digital data in point-to-point connections
RS485	Serial link according to EIA standard RS485
RTC	Real-time clock
RTU	Remote terminal unit
SA	Substation Automation
SBO	Select-before-operate
SC	Switch or push button to close
SCS	Station control system
SCADA	Supervision, control and data acquisition
SCT	System configuration tool according to standard IEC 61850

SDU	Service data unit
SMA connector	Subminiature version A, A threaded connector with constant impedance.
SMT	Signal matrix tool within PCM600
SMS	Station monitoring system
SNTP	Simple network time protocol – is used to synchronize computer clocks on local area networks. This reduces the requirement to have accurate hardware clocks in every embedded system in a network. Each embedded node can instead synchronize with a remote clock, providing the required accuracy.
SRY	Switch for CB ready condition
ST	Switch or push button to trip
Starpoint	Neutral point of transformer or generator
SVC	Static VAr compensation
TC	Trip coil
TCS	Trip circuit supervision
TCP	Transmission control protocol. The most common transport layer protocol used on Ethernet and the Internet.
TCP/IP	Transmission control protocol over Internet Protocol. The de facto standard Ethernet protocols incorporated into 4.2BSD Unix. TCP/IP was developed by DARPA for Internet working and encompasses both network layer and transport layer protocols. While TCP and IP specify two protocols at specific protocol layers, TCP/IP is often used to refer to the entire US Department of Defense protocol suite based upon these, including Telnet, FTP, UDP and RDP.
TNC connector	Threaded Neill-Concelman, a threaded constant impedance version of a BNC connector
TPZ, TPY, TPX, TPS	Current transformer class according to IEC
UMT	User management tool
Underreach	A term used to describe how the relay behaves during a fault condition. For example, a distance relay is underreaching when the impedance presented to it is greater than the apparent impedance to the fault applied to the balance point, that is, the set reach. The relay does not “see” the fault but perhaps it should have seen it. See also Overreach.
UTC	Coordinated Universal Time. A coordinated time scale, maintained by the Bureau International des Poids et Mesures (BIPM), which forms the basis of a coordinated dissemination of standard frequencies and time signals. UTC

	is derived from International Atomic Time (TAI) by the addition of a whole number of "leap seconds" to synchronize it with Universal Time 1 (UT1), thus allowing for the eccentricity of the Earth's orbit, the rotational axis tilt (23.5 degrees), but still showing the Earth's irregular rotation, on which UT1 is based. The Coordinated Universal Time is expressed using a 24-hour clock, and uses the Gregorian calendar. It is used for aeroplane and ship navigation, where it is also sometimes known by the military name, "Zulu time." "Zulu" in the phonetic alphabet stands for "Z", which stands for longitude zero.
UV	Undervoltage
WEI	Weak end infeed logic
VT	Voltage transformer
X.21	A digital signalling interface primarily used for telecom equipment
$3I_O$	Three times zero-sequence current. Often referred to as the residual or the earth-fault current
$3U_O$	Three times the zero sequence voltage. Often referred to as the residual voltage or the neutral point voltage

Contact us

ABB AB
Substation Automation Products
SE-721 59 Västerås, Sweden
Phone +46 (0) 21 32 50 00
Fax +46 (0) 21 14 69 18

www.abb.com/substationautomation

1MRK 506 331-UEN - © Copyright 2012 ABB. All rights reserved.

Power and productivity
for a better world™