



Catalogue – 2018

Electrical installation solutions for buildings – Supplement 1

New products added 06/2018 – product description, quick and easy selection of product codes



- Command & Signalling
- Industrial plugs and sockets
- Light switches and socket outlets
- Automation boards



Electrical installation solutions for buildings



Product news – 06/2018

Index

Command & Signalling	4
Industrial plugs and sockets	6
Light switches and socket outlets	7
Automation boards	50

Command & Signalling

Busch-Dimmer®

Product	Article-No.	Order-No.	Pack/Qty
	Busch-Dimmer® ^{1) 2) 3) 4) 5)} MDRC, LED, 20-800 W Touch dimmer with local operation. Optimised for dimming of retrofit LED lamps (LEDi). For dimmable Retrofit-LEDs (LEDi). For dimmable Retrofit-LEDs (LEDi) with conventional or electronic transformers. For incandescent lamps, 230V tungsten halogen lamps and lowvoltage halogen lamps with conventional transformers or electronic transformers and dimmable halogen energy-saving lamps. Mix operation of LEDi with conventional loads possible. With the following functions: memory, snooze, wake-up, children's room, central off, cleaning light and time function. For staircase lighting control with automatic switch-off and warning function according to DIN 18015-2. Supports the adherence to the energy saving ordinance (EnEV 2014). Low-noise level by MOSFET transistors. With electronic short-circuit protection. With electronic overload protection. With manually adjustable operating mode: trailing / leading edge control. With adjustable minimum/maximum brightness. With light value storage. Operation also possible via conventional push buttons (2020 US, 2021/6 UK). Extension unit input for short switching pulses (push-button) and continuous contact (switch/timer). Extension unit input designed as wide voltage input (8-230 V; AC/DC); galvanic isolation. Nominal voltage: 110 - 230 V, +10% / -10% Rated frequency: 50 Hz/60 Hz Nominal power: 20 - 300 W/VA (leading edge control in 230 V~ networks) Nominal power: 40 - 800 W/VA (trailing edge control in 230 V~ networks) Nominal power: 20 - 150 W/VA (leading edge control in 110/127 V~ networks) Nominal power: 40 - 400 W/VA (trailing edge control in 110/127 V~ networks) Rated voltage: 110 - 230 V, +10 % / -10 % Temperature range (Device): 0 °C to 35 °C Module width: 4 MW IEC 60669-2-1, British Standard EN 60669-2-1		
			
grey	STD 6586/14	2CKA006590A0193	1

¹⁾ Illumination of the push switch is only possible with N-conductor terminal.

²⁾ In case of electronic transformers, 5 % transformer losses.

³⁾ In the case of conventional transformers, take ~20% transformer loss into account.

⁴⁾ 1 MW □ 18 mm.

⁵⁾ Recommendation: Please use loads and types of one producer..

Industrial plugs and sockets

Accessories



Plug blocker

Lockout/tagout for plugs and inlets. Can be used for any IEC 60309-1 and 60309-2 plug or inlet, both IP44 and IP67 products.

To fit	Order details		Pack qty
	Type code	Order code	pc.
Plugs 16 – 125A Panel mounted inlets 16 – 125 Surface mounted inlets 16 – 125 A	CLF 16 – 125 *	2CMA179237R1000	1

*Indicates standard product.



Protective cover 16 – 125 A, IP44/67

Material in EPDM Rubber

For inlet and plug	Order details		Pack qty
	Type code	Order code	pc.
16 A, 2P+E	GP216 *	2CMA164993R1000	1
16 A, 3P+E	GP316 *	2CMA164994R1000	1
16 A, 3P+N+E	GP416 *	2CMA164995R1000	1
32 A, 2P+E and 3P+E	GP232/332 *	2CMA164996R1000	1
32A, 3P+N+E	GP432 *	2CMA164997R1000	1
63 A, 2P+E, 3P+E and 3P+N+E	GP63 *	2CMA164998R1000	1
125 A, 2P+E, 3P+E and 3P+N+E	GP125 *	2CMA164999R1000	1

*Indicates standard product.



Padlock unit



Padlock unit suitable for all plugs and sockets with handle. Shackle for up to 6 padlocks.

To fit	Order details		Pack qty
	Type code	Order code	pc.
Plugs and sockets with handle	L6	2CMA144539R1000	10

*Indicates standard product.

Light switches and socket outlets

Multimedia / communication adapters

Product	Article-No.	Order-No.	Pack/Qty
	Busch-Radio BTconnect ^{1) 2) 3) 4)} RDS stereo radio alarm clock for flush-mounted installation. With Bluetooth interface for music replay of mobile devices. Reception frequency: 87.50 MHz - 108.00 MHz. With high resolution graphic display and background illumination. With external AUX input. For mono/stereo operation. 8 radio stations storable. With time and date display. With alarm clock and snooze function. With short-time timer. With automatic switch-off function (automatic sleep mode). With extension input to remote-controlled ON/OFF switches. With integrated antenna. With additional connection for external antenna. Permitted speaker impedance: 4 - 8 Ohm Can be installed as 1gang and in multiple combinations. Bluetooth specification: 2.1 Bluetooth profiles supported: A2DP Number of stored Bluetooth connections: max. 8 Rated voltage: 110 - 230 V~, +10 % / -10 % Rated frequency: 50 Hz - 60 Hz Protection class (Device): IP 20 Temperature range (Device): 5 °C to 40 °C Dimensions: (L x W x D): 71 mm x 71 mm x 47 mm Mounting depth: 32 mm  Bluetooth™		
	8217 U-500	2CKA008200A0194	1


¹⁾ No claw. Screw-fixing via keyholes.

²⁾ Matching loudspeaker insert 8223 U.

³⁾ Also combinable with built-in ceiling loudspeaker (8225 EB & 8226 EB) and HiFi built-in ceiling loudspeaker (8226/11 EB).

⁴⁾ Can also be combined with built-in loudspeaker (8222 EB) and moist atmosphere loudspeaker (8224 EB).

Dimmers

Product	Article-No.	Order-No.	Pack/Qty
	Busch-rotary dimmer ^{1) 2) 3) 4) 5) 6) 7)} UP, LED, 2-400 W Very small installation depth: < 20 mm Without claws. With rotary control, two-way switch and soft-catch. 2-wire connection (neutral conductor not required) Optimised for dimming of retrofit LED lamps (LEDi). For dimmable Retrofit-LEDs (LEDi). For dimmable Retrofit-LEDs (LEDi) with conventional or electronic transformers. For incandescent lamps, 230 V tungsten halogen lamps, low-voltage halogen lamps with conventional or electronic transformers and dimmable energy-saving halogen lamps. Mix operation of LEDi with conventional loads possible. With manually adjustable operating mode: trailing / leading edge control. With adjustable minimum/maximum brightness. Low-noise level by MOSFET transistors. With electronic short-circuit protection. With electronic overload protection. Without cover plate. Rated voltage: 230 V~, + 10% / - 10% Rated frequency: 50 Hz/60 Hz Nominal power: 2 - 100 W/VA (leading edge control) Nominal power: 2 - 400 W/VA (trailing edge control) Protection class (Device): IP 20 Temperature range (Device): 0 °C to 35 °C IEC 60669-2-1, British Standard EN 60669-2-1 		
	6523 UR-103-500	2CKA006512A0345	1/10

¹⁾ Illuminable with neon lamp. Neon lamp included in delivery with cover plate.

²⁾ In the case of conventional transformers, take ~20% transformer loss into account.

³⁾ In case of electronic transformers, 5 % transformer losses.

⁴⁾ Also applicable for 1gang 2way installations.


⁵⁾ Provided with terminal for net disconnection devices.

⁶⁾ Only in conjunction with standard flush-mounting boxes according to DIN 49073.


⁷⁾ Recommendation: Please use loads and types of one producer.

Light switches and socket outlets – carat®


Rocker switches / push switches

Product	Article-No.	Order-No.	Pack/Qty
	Rocker Switch Mechanism ¹⁾ Rated voltage: 250 V~ Rated current: 16 AX IEC 60669-1		
	1gang 2way 2400/6 US-500	2CKA001012A2232	10/100
	2gang 1way 2400/5 US-500	2CKA001012A2234	10
	1gang intermediate 2400/7 US-500	2CKA001012A2236	10


¹⁾ Only in conjunction with standard flush-mounting boxes according to DIN 49073. Fits to carat®, Busch-dynasty®, solo®, Busch-axcent® and future® linear.

	Rocker Switch Mechanism ¹⁾ 2gang 2way With screwless terminals. Rated voltage: 250 V~ Rated current: 16 AX IEC 60669-1		
	2400/6/6US-101-500	2CKA001022A0663	10

¹⁾ Only in conjunction with standard flush-mounting boxes according to DIN 49073. Fits to carat®, Busch-dynasty®, solo®, Busch-axcent® and future® linear.

	Rocker Switch Mechanism, control ¹⁾ 2gang 1way with LED, Rated voltage: 250 V~ Rated current: 16 AX IEC 60669-1		
	2400/5 USK-500	2CKA001012A2238	10


¹⁾ Only in conjunction with standard flush-mounting boxes according to DIN 49073. Fits to carat®, Busch-dynasty®, solo®, Busch-axcent® and future® linear.


	Rocker Switch Mechanism, control ^{1) 2) 3)} 1gang 2way with N-terminal With neon lamp. Rated voltage: 250 V~ Rated current: 16 AX IEC 60669-1		
	2400/6 USK-500	2CKA001022A0661	10


¹⁾ With 1 mA neon lamp.


²⁾ Only in conjunction with standard flush-mounting boxes according to DIN 49073.


³⁾ Illuminable by using lamps 8360, 8362, 8363, 8365, 8366, and 8367 and LED inserts. Fits to carat®, Busch-dynasty®, solo®, Busch-axcent® and future® linear.

Product	Article-No.	Order-No.	Pack/Qty
	Rocker As a cover for flush-mounted control 2gang switch.		
	anthracite	1785 K-81-500	2CKA001751A3122 10
	ivory white	1785 K-82-500	2CKA001751A3124 10
	studio white	1785 K-84-500	2CKA001751A3128 10

	Rocker with small transparent lens As cover for flush-mounted 1gang 1way, 1gang 2way switch, intermediate switch, push-button and control switch 1gang 2way.		
	anthracite	1789 N-81	2CKA001751A3147 10/100
	ivory white	1789 N-82	2CKA001751A3148 10/100
	studio white	1789 N-84-500	2CKA001751A3151 10/100


	Switch rocker with marking with small transparent lens With "Plug" icon. As cover for flush-mounted switch 1g1w DP and 3pole with neon lens and marking "I O" As cover for flush-mounted 1gang 1way, 1gang 2way switch, intermediate switch, push-button and control switch 1gang 2way.		
	anthracite	1789 ST-81	2CKA001751A3157 10/100
	ivory white	1789 ST-82	2CKA001751A3158 10/100
	studio white	1789 ST-84-500	2CKA001751A3161 10/100


	Switch rocker with marking With symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.		
	anthracite	2520 LI-81	2CKA001751A3186 10/100
	ivory white	2520 LI-82	2CKA001751A3187 10/100
	studio white	2520 LI-84-500	2CKA001751A3190 10/100

	Switch rocker with marking With key symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.		
	anthracite	2520 TR-81	2CKA001751A3196 10/100
	ivory white	2520 TR-82	2CKA001751A3197 10/100
	studio white	2520 TR-84	2CKA001751A3199 10/100

Light switches and socket outlets – carat®


Rocker switches / push switches


Product	Article-No.	Order-No.	Pack/Qty
 Switch rocker with marking With bell symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.			
anthracite	2520 KI-81	2CKA001751A3176	10/100
ivory white	2520 KI-82	2CKA001751A3177	10/100
studio white	2520 KI-84-500	2CKA001751A3180	10/100


 Rocker ^{1) 2)} with labelling field With bell symbol. With pilot lamp for uniform illumination of the labelling field. For flush-mounted push switch. Size of labelling field: 51 x 10 mm.			
anthracite	1764 NLI/KI-81	2CKA001731A3998	10/100
ivory white	1764 NLI/KI-82	2CKA001731A3999	10/100
studio white	1764 NLI/KI-84-500	2CKA001731A4002	10/100

¹⁾ For compatible lettering software, visit www.BUSCH-JAEGER-labelingtool.com.

²⁾ Illumination using neon lamp 8353 or incandescent lamp 8344-1 and LED inserts.


 Switch rocker with marking For flush-mounted switch 1g1w, 1g2w, intermediate, push switch. DO NOT DISTURB			
anthracite	1786/11-81	2CKA001751A3207	10
ivory white	1786/11-82	2CKA001751A2997	10
studio white	1786/11-84	2CKA001751A2998	10

 Switch rocker with marking For flush-mounted switch 2g 1w, 2g push switch. DO NOT DISTURB MAKE UP ROOM			
anthracite	1785/11-81	2CKA001751A3205	10
ivory white	1785/11-82	2CKA001751A2991	10
studio white	1785/11-84	2CKA001751A2992	10


 Cover plate ¹⁾ for pull switch 2610/6 UC-xx, 2610/6 UJ-xx With screw-type terminal			
anthracite	1796-81	2CKA001753A0308	10
ivory white	1796-82	2CKA001753A0309	10
studio white	1796-84	2CKA001753A0311	10


¹⁾ Exchanging the available cover/cover plate.

Movement detectors / comfort switches

Product	Article-No.	Order-No.	Pack/Qty
 Cover plate For proximity switch 6406 U.			
anthracite	6476-81	2CKA006470A0007	1/100


Blind control / timers

 Cover plate with rotary knob, with marking For Busch-Timer insert 1070 U. Running time: 15 min			
anthracite	1770-81-103	2CKA001753A0255	10
ivory white	1770-82-103	2CKA001753A0256	10
studio white	1770-84-103	2CKA001753A0258	10


 Cover plate with rotary knob, with marking For Busch-Timer insert 1071 U. Running time: 120 min			
anthracite	1771-81-103	2CKA001753A0265	10
ivory white	1771-82-103	2CKA001753A0266	10
studio white	1771-84-103	2CKA001753A0301	10

Light switches and socket outlets – carat®


Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet without claw ¹⁾ shuttered Without claws. With screwless terminals. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUCRB-81	2CKA002013A5437 10/100
	ivory white	20 EUCRB-82	2CKA002013A5438 10/100
	studio white	20 EUCRB-84-500	2CKA002013A5441 10/100


¹⁾ Increased shock protection.

	SCHUKO® socket outlet ¹⁾ shuttered With screw-type terminals. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	2300 EUCB-81	2CKA002013A5448 10
	ivory white	2300 EUCB-82	2CKA002013A5449 10/100
	studio white	2300 EUCB-84	2CKA002013A5451 10/100


¹⁾ Increased shock protection.

	Busch-Socket outlet ¹⁾ shuttered With screwless terminals. DP (2 P + E) With eject mechanism. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUCBDR-81	2CKA002013A5415 10
	ivory white	20 EUCBDR-82	2CKA002013A5416 10
	studio white	20 EUCBDR-84	2CKA002013A5418 10


¹⁾ Increased shock protection.

	SCHUKO® socket outlet ¹⁾ with labelling field Size of labelling field: 60 x 9 mm. With screwless terminals. DP (2 P + E) Shuttered. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUCNB-81	2CKA002013A5427 10
	ivory white	20 EUCNB-82	2CKA002013A5428 10
	studio white	20 EUCNB-84-500	2CKA002013A5431 10/100


¹⁾ Increased shock protection.

	SCHUKO® socket outlet ¹⁾ with LED control light Shuttered. DP (2 P + E) With transparent lens. LED colour green. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUCBL-81	2CKA002013A5457 10

¹⁾ Resistant to aggressive media, e.g. ammonia, benzene, oils, greases, alcohol, cleansing agents, in normal concentrations.

Product	Article-No.	Order-No.	Pack/Qty
	Busch-Object socket outlet ¹⁾ shuttered With screwless terminals. DP (2 P + E) Incl. Cover plate with extract mechanism. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUAB-81	2CKA002013A5404 10
	ivory white	20 EUAB-82	2CKA002013A5405 10
	studio white	20 EUAB-84	2CKA002013A5407 10


¹⁾ Increased shock protection.

	FI-SCHUKOMAT, SCHUKO® socket outlet (RCD) ^{1) 2) 3)} with earth leakage circuit breaker Shuttered. DP cut off (P,N) Without PE monitoring. With connecting conductor and protection of downstream socket outlets. Rated actuating current: 30 mA. Release time: ≤ 30 ms. Short-circuit strength: 3000 A (with 25 A GL fuse). Current surge strength: 250 A (8/20) µs. With fixing claws. Rated frequency: 45-60 Hz. Rated voltage: 230 V~ Rated current: 16 A Protection class (Device): IP 20 Temperature range (Device): -25 °C to 40 °C		
	anthracite	3120 EUCB-81	2CKA003116A0667 1/10

¹⁾ Connecting terminals approved in accordance with VDE 0620-1 as connectors.

²⁾ Protective measure according to VDE 0100; can be proven or checked using the Profitest 0100S testing device, for example.


³⁾ Increased shock protection.

	Buschmat® FI - Insert ¹⁾ with earth leakage breaker with connecting conductor Protection of downstream consumers. Rated actuating current: 30 mA. Release time: ≤ 30 ms. Short-circuit strength: 3000 A (with 25 A GL fuse). Current surge strength: 250 A (8/20) µs. DP cut off (P,N) Without claw fixation. Rated frequency: 45-60 Hz. Rated voltage: 230 V~ Rated current: 16 A Protection class (Device): IP 20 Temperature range (Device): -25 °C to 40 °C		
	anthracite	3151 UC-81	2CKA003117A0009 1/10

¹⁾ Protective measure according to VDE 0100; can be proven or checked using the Profitest 0100S testing device, for example.


Light switches and socket outlets – carat®

Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet ¹⁾ Shuttered. With screwless terminals. DP (2 P + E) with hinged lid Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUKB-81	2CKA002018A1517 10/100
	ivory white	20 EUKB-82	2CKA002018A1518 10/100
	studio white	20 EUKB-84	2CKA002018A1520 10/100
	anthracite ²⁾	20 EUKBR-81	2CKA002018A1526 10/100
	ivory white ²⁾	20 EUKBR-82	2CKA002018A1527 10/100
	studio white ²⁾	20 EUKBR-84	2CKA002018A1529 10/100


¹⁾ Increased shock protection.

²⁾ Without claws.


	SCHUKO® socket outlet ^{1) 2)} Shuttered. With screwless terminals. DP (2 P + E) with hinged lid and labelling field Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUKNB-81	2CKA002018A1537 10/100
	ivory white	20 EUKNB-82	2CKA002018A1538 10/100
	studio white	20 EUKNB-84	2CKA002018A1540 10/100

¹⁾ Increased shock protection.


²⁾ The labels are clamped under the labelling field.

	SCHUKO® socket outlet ¹⁾ with hinged lid and lock Shuttered. With screwless terminals. DP (2 P + E) With different lock mechanism. Delivery includes 2 keys. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUKNBSL-81	2CKA002018A1557 10
	ivory white	20 EUKNBSL-82	2CKA002018A1559 10
	studio white	20 EUKNBSL-84	2CKA002018A1563 10

¹⁾ Increased shock protection.


	SCHUKO® socket outlet ¹⁾ with hinged lid and lock Shuttered. With screwless terminals. DP (2 P + E) With evenly engaging lock. Delivery includes 2 keys. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUKNBSL-81-101	2CKA002018A1558 10
	ivory white	20 EUKNBSL-82-101	2CKA002018A1560 10
	studio white	20 EUKNBSL-84-101	2CKA002018A1564 10

¹⁾ Increased shock protection.

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet ^{1) 2)} with hinged lid, labelling field and LED control light Shuttered. With screwless terminals. DP (2 P + E) with hinged lid Size of labelling field: 60 x 9 mm. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUKNBL-81	2CKA002018A1548 10/100
	ivory white	20 EUKNBL-82	2CKA002018A1549 10/100
	studio white	20 EUKNBL-84	2CKA002018A1551 10/100

¹⁾ Increased shock protection.

²⁾ The labels are clamped under the labelling field.


	SCHUKO® socket outlet steplight ^{1) 2)} With night orientation light with separate connection cables for switch contact. with LED, Shuttered. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUCBLI-81	2CKA002013A5459 1

¹⁾ Connecting terminals approved in accordance with VDE 0620-1 as connectors.


²⁾ Resistant to aggressive media, e.g. ammonia, benzene, oils, greases, alcohol, cleansing agents, in normal concentrations.


Light switches and socket outlets – carat®


Data communication


Product	Article-No.	Order-No.	Pack/Qty
	Cover plate ¹⁾ socket outlet Telephone socket (TDO)		
	anthracite	1762-81-506	2CKA001710A4103 10/100
	ivory white	1762-82-506	2CKA001710A4104 10/100
	studio white	1762-84-506	2CKA001710A4106 10/100


¹⁾ Suitable insert: TDO 3x 10 OUP (for 1 telephone and 2 auxiliary devices).


	Cover plate As cover for 4gang Satellite co-axial socket outlet EVU 02 F, GEVU 15 S from Hirschmann.		
	anthracite	1743-04-81	2CKA001724A4374 10
	ivory white	1743-04-82	2CKA001724A4375 10
	studio white	1743-04-84	2CKA001724A4377 10


	Cover plate As cover for 4gang Satellite co-axial socket outlet SAT400/EAS/DC, EAS 405, 413 DAS from Ankaro.		
	anthracite	1743/10-04-81	2CKA001724A4365 10
	ivory white	1743/10-04-82	2CKA001724A4366 10
	studio white	1743/10-04-84	2CKA001724A4368 10/100


	Cover plate with metal mounting plate For 1 modular jack. Suitable for Art. Nos. 0210, 0211 and 0219-101. Without claws.		
	anthracite	2561-81	2CKA001753A0400 10
	ivory white	2561-82	2CKA001753A0401 10
	studio white	2561-84	2CKA001753A0403 10

	Cover plate with metal mounting plate For 2 modular jack inserts. Suitable for Art. No. 0210 and 0211. Without claws.		
	anthracite	2561-02-81	2CKA001753A0317 10
	ivory white	2561-02-82	2CKA001753A0392 10
	studio white	2561-02-84	2CKA001753A0394 10

	Intermediate ring For attaching cover plates from the Busch+balance® SI range.		
	anthracite	1747 BSI-81	2CKA001710A4093 10
	ivory white	1747 BSI-82	2CKA001710A4094 10
	studio white	1747 BSI-84	2CKA001710A4096 10/100

Product	Article-No.	Order-No.	Pack/Qty
	Cover plate with hinged lid For telecommunication inserts with cover plate 50 x 50 mm. With cover plate 50 x 50 mm, AMP, Brand-Rex, Rutenbeck, BTR, Telegärtner, etc.		
	anthracite	1746-81	2CKA001710A3618 10


	XLR centre plate As cover for Neutrik plug connectors, type D series. Without claws.		
	anthracite	2553-81	2CKA001724A4399 10
	ivory white	2553-82	2CKA001724A4400 10
	studio white	2553-84	2CKA001724A4402 10

	Cover plate with metal mounting plate With screw-type terminal. Fixed with central locknut. As cover for pilot devices with a diameter of 22.5 mm Without claws.		
	yellow	2533-82-15	2CKA001724A4382 10

Light switches and socket outlets – carat®

Multimedia / communication adapters

LED light

Product	Article-No.	Order-No.	Pack/Qty
 Cover plate with rotary control, with marking As a cover for volume controllers. Suitable for the "LR 15 mono BJ UP" devices of WHD.			
anthracite	1740 DR/03-81	2CKA001710A4120	10




Product	Article-No.	Order-No.	Pack/Qty
 Cover plate for indication lamp For insert 2061/2661 U. As cover for flush-mounted light signal.			
anthracite	1756-81	2CKA001753A0089	10
ivory white	1756-82	2CKA001753A0090	10
studio white	1756-84	2CKA001753A0092	10

ABB-Welcome Indoor Stations


 Cover plates For indoor audio station with display. Protection class (Device): IP 30 Temperature range (Device): -5 °C to 40 °C			
ivory white	83260-82	2CKA008300A0541	1

Light switches and socket outlets – Busch-dynasty®


Rocker switches / push switches


Product	Article-No.	Order-No.	Pack/Qty
 Rocker For flush-mounted switch 2g 1w, 2g push switch.			
anthracite	1785 K-81-500	2CKA001751A3122	10
ivory white	1785 K-82-500	2CKA001751A3124	10
antique brass ¹⁾	1785 K-840-500	2CKA001751A3131	10


¹⁾ Real metal surface refined by hand.

 Rocker With marking. For flush-mounted switch 2g 1w, 2g push switch. With Marking "DO NOT DISTURB / MAKE UP ROOM"			
anthracite	1785/11-81	2CKA001751A3205	10


Data communication

Product	Article-No.	Order-No.	Pack/Qty
 Intermediate ring For attaching cover plates with the dimensions of 55 x 55 mm.			
anthracite	1747 BSI-81	2CKA001710A4093	10
ivory white	1747 BSI-82	2CKA001710A4094	10


 XLR centre plate As cover for Neutrik plug connectors, type D series. Without claws.			
anthracite	2553-81	2CKA001724A4399	10
ivory white	2553-82	2CKA001724A4400	10

 Cover plate with metal mounting plate With screw-type terminal. Fixed with central locknut. As cover for pilot devices with a diameter of 22.5 mm Without claws.			
anthracite	2533-81	2CKA001724A4254	10
ivory white	2533-82	2CKA001724A4255	10

Socket outlets

 SCHUKO® socket outlet without claw ¹⁾ shuttered Without claws. With screwless terminals. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A			
anthracite	20 EUCRB-81	2CKA002013A5437	10/100
ivory white	20 EUCRB-82	2CKA002013A5438	10/100

¹⁾ Increased shock protection.







 SCHUKO® socket outlet ^{1) 2)} shuttered With screw-type terminals. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A			
anthracite	2300 EUCB-81	2CKA002013A5448	10
ivory white	2300 EUCB-82	2CKA002013A5449	10/100



¹⁾ Increased shock protection.

²⁾ With screw-type terminals.

Light switches and socket outlets – pure stainless steel


Rocker switches / push switches

Product	Article-No.	Order-No.	Pack/Qty
	Rocker As a cover for flush-mounted control 2gang switch.		
	stainless steel 1785 K-866-500	2CKA001751A3133	10
	Rocker with small transparent lens As cover for flush-mounted 1gang 1way, 1gang 2way switch, intermediate switch, push-button and control switch 1gang 2way. Material stainless steel. Anti fingerprint.		
	stainless steel 1789 N-866	2CKA001751A3152	10/100
	Switch rocker with marking with small transparent lens With "Plug" icon. As cover for flush-mounted switch 1g1w DP and 3pole with neon lens and marking "I O" As cover for flush-mounted 1gang 1way, 1gang 2way switch, intermediate switch, push-button and control switch 1gang 2way.		
	stainless steel 1789 ST-866	2CKA001751A3162	10/100
	Switch rocker with marking With symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch. Material stainless steel. Anti fingerprint. light		
	stainless steel 2520 LI-866	2CKA001751A3191	10/100
	Switch rocker with marking With symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch. Material stainless steel. Anti fingerprint. key		
	stainless steel 2520 TR-866	2CKA001751A3200	10/100
	Switch rocker with marking With symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch. Material stainless steel. Anti fingerprint. bell		
	stainless steel 2520 KI-866	2CKA001751A3181	10/100


Product	Article-No.	Order-No.	Pack/Qty
	Rocker ¹⁾ with labelling field With bell symbol. With pilot lamp for uniform illumination of the labelling field. For flush-mounted push switch. Size of labelling field: 51 x 10 mm. Surface painted.		
	stainless steel 1764 NLI/KI-866	2CKA001731A4003	10/100
¹⁾ Illumination using neon lamp 8353 or incandescent lamp 8344-1 and LED inserts.			
	Cover plate ¹⁾ for pull switch 2610/6 UC-xx, 2610/6 UJ-xx With screw-type terminal Surface painted.		
	stainless steel 1796-866	2CKA001753A0312	10
¹⁾ Exchanging the available cover/cover plate.			

Light switches and socket outlets – pure stainless steel

Movement detectors / comfort switches Blind control / timers


Product	Article-No.	Order-No.	Pack/Qty
 Cover plate For proximity switch 6406 U. Surface painted.			
stainless steel	6476-866	2CKA006470A0009	10

Product	Article-No.	Order-No.	Pack/Qty
 Cover plate with rotary knob, with marking For Busch-Timer insert 1070 U. Running time: 15 min Surface painted.			
stainless steel	1770-866-103	2CKA001753A0259	10


 Cover plate with rotary knob, with marking For Busch-Timer insert 1071 U. Running time: 120 min Surface painted.			
stainless steel	1771-866-103	2CKA001753A0302	10

Light switches and socket outlets – pure stainless steel


Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet without claw ¹⁾ shuttered With screwless terminals. DP (2 P + E) Material stainless steel. Anti fingerprint. Rated voltage: 250 V~ Rated current: 16 A		
stainless steel	20 EUCRB-866	2CKA002013A5442	10/100


¹⁾ Increased shock protection.

	SCHUKO® socket outlet ¹⁾ shuttered With screw-type terminals. DP (2 P + E) Material stainless steel. Anti fingerprint. Rated voltage: 250 V~ Rated current: 16 A		
stainless steel	2300 EUCB-866	2CKA002013A5452	10/100

¹⁾ Increased shock protection.


	Busch-Socket outlet ¹⁾ shuttered With screwless terminals. DP (2 P + E) With eject mechanism. Surface painted. Rated voltage: 250 V~ Rated current: 16 A		
stainless steel	20 EUCBDR-866	2CKA002013A5419	10


¹⁾ Increased shock protection.

	SCHUKO® socket outlet steplight® ^{1) 2)} With night orientation light with separate connection cables for switch contact. with LED, Shuttered. DP (2 P + E) Surface painted. Rated voltage: 250 V~ Rated current: 16 A		
stainless steel	20 EUCBLI-866	2CKA002013A5460	1


¹⁾ Connecting terminals approved in accordance with VDE 0620-1 as connectors.

²⁾ Resistant to aggressive media, e.g. ammonia, benzene, oils, greases, alcohol, cleansing agents, in normal concentrations.

	SCHUKO® socket outlet with labelling field DP (2 P + E) Size of labelling field: 60 x 9 mm. Material stainless steel. Anti fingerprint. Shuttered. Rated voltage: 250 V~ Rated current: 16 A		
stainless steel	20 EUCNB-866	2CKA002013A5432	10

Product	Article-No.	Order-No.	Pack/Qty
	Busch-Object socket outlet ¹⁾ shuttered With screwless terminals. DP (2 P + E) Incl. Cover plate with extract mechanism. Surface painted. Rated voltage: 250 V~ Rated current: 16 A		
stainless steel	20 EUAB-866	2CKA002013A5408	10


¹⁾ Increased shock protection.

	FI-SCHUKOMAT, SCHUKO® socket outlet (RCD) ^{1) 2) 3)} with earth leakage circuit breaker Shuttered. DP cut off (P,N) Without PE monitoring. With connecting conductor and protection of downstream socket outlets. Rated actuating current: 30 mA. Release time: ≤ 30 ms. Short-circuit strength: 3000 A (with 25 A GL fuse). Current surge strength: 250 A (8/20) μs. Without claw fixation. Rated frequency: 45-60 Hz. Surface painted. Rated voltage: 230 V~ Rated current: 16 A Protection class (Device): IP 21 Temperature range (Device): -25 °C to 40 °C		
stainless steel	3120 EUCB-866	2CKA003116A0669	1/10


¹⁾ Connecting terminals approved in accordance with VDE 0620-1 as connectors.

²⁾ Protective measure according to VDE 0100; can be proven or checked using the Profitest 0100S testing device, for example.

³⁾ Increased shock protection.


	Buschmat® FI - Insert ¹⁾ with earth leakage breaker with connecting conductor Protection of downstream consumers. Rated actuating current: 30 mA. Release time: ≤ 30 ms. Short-circuit strength: 3000 A (with 25 A GL fuse). Current surge strength: 250 A (8/20) μs. DP cut off (P,N) Without claw fixation. Rated frequency: 45-60 Hz. Surface painted. Rated voltage: 230 V~ Rated current: 16 A Protection class (Device): IP 21 Temperature range (Device): -25 °C to 40 °C		
stainless steel	3151 UC-866	2CKA003117A0011	1/10

¹⁾ Protective measure according to VDE 0100; can be proven or checked using the Profitest 0100S testing device, for example.

	SCHUKO® socket outlet shuttered With screwless terminals. DP (2 P + E) with hinged lid Material stainless steel. Anti fingerprint. Rated voltage: 250 V~ Rated current: 16 A		
stainless steel	20 EUKB-866	2CKA002018A1521	10/100

Light switches and socket outlets – pure stainless steel

Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	Socket outlet ^{1) 2)} with earthing pin With screwless terminals. Shuttered. DP (2 P + E) For supply and support of mobile devices via USB-cable. With USB female connector type A. With electronic short-circuit protection. With electronic overload protection. Simultaneous charging via USB connection and use of the SCHUKO® socket outlet. Suitable for the countries like Poland, Czech Republic. Surface painted. Rated voltage: 250 V~ Secondary: 5 V-, +5 % / -5 % Rated frequency: 50 Hz Suitable for: Socket outlet connection Rated current: 16 A Suitable for: USB connection Rated current: 700 mA Protection class (Device): IP 20, SELV Temperature range (Device): 5 °C to 35 °C Dimensions: (L x W x D): 71 mm x 71 mm x 53 mm Mounting depth: 35 mm		
	stainless steel	20 MUCBUSB-866-500	2CKA002017A0895 1

¹⁾ No data transfer.


²⁾ Use dust cover 2098 when cleaning the device.

	Socket outlet ^{1) 2)} with earthing pin With screwless terminals. Shuttered. Suitable for the countries like Poland, Czech Republic. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	stainless steel	20 MUCKS-866-500	2CKA002017A0900 10


¹⁾ Socket outlet with integrated child protection.

²⁾ Order-bound manufacturing.


Data communication

Product	Article-No.	Order-No.	Pack/Qty
	Cover plate ¹⁾ socket outlet Telephone socket (TDO) Surface painted.		
	stainless steel	1762-866-506	2CKA001710A4107 10/100


¹⁾ Suitable insert: TDO 3x 10 OUP (for 1 telephone and 2 auxiliary devices).

	Cover plate ¹⁾ As cover for 4gang Satellite co-axial socket outlet EVU 02 F, GEVU 15 S from Hirschmann. Surface painted.		
	stainless steel	1743-04-866	2CKA001724A4378 10

¹⁾ See adapter ring 1746/10x.


	Cover plate ¹⁾ As cover for 4gang Satellite co-axial socket outlet SAT400/EAS/DC, EAS 405, 413 DAS from Ankaro. Surface painted.		
	stainless steel	1743/10-04-866	2CKA001724A4369 10


¹⁾ See adapter ring 1746/10x.

	Cover plate ¹⁾ with metal mounting plate For 1 modular jack. Suitable for Art. Nos. 0210, 0211 and 0219-101. Without claws. Surface painted.		
	stainless steel	2561-866	2CKA001753A0404 10

¹⁾ Surface painted.

	Cover plate with metal mounting plate For 2 modular jack inserts. Suitable for Art. No. 0210 and 0211. Without claws. Surface painted.		
	stainless steel	2561-02-866	2CKA001753A0395 10


	Intermediate ring For attaching cover plates from the Busch-balance® SI range. Surface painted.		
	stainless steel	1747 BSI-866	2CKA001710A4097 10


	XLR centre plate As cover for Neutrik plug connectors, type D series. Without claws. Surface painted.		
	stainless steel	2553-866	2CKA001724A4403 10

Light switches and socket outlets – pure stainless steel

LED light

ABB-Welcome Indoor Stations


Product	Article-No.	Order-No.	Pack/Qty
 Cover plate for indication lamp For insert 2061/2661 U. As cover for flush-mounted light signal. Surface painted.			
stainless steel	1756-866	2CKA001753A0093	10

Product	Article-No.	Order-No.	Pack/Qty
 Cover plates ¹⁾ For indoor audio station with display. Protection class (Device): IP 30 Temperature range (Device): -5 °C to 40 °C			
stainless steel	83260-866	2CKA008300A0542	1


¹⁾ Surface painted.

Light switches and socket outlets – solo®


Rocker switches / push switches

Product	Article-No.	Order-No.	Pack/Qty
 Rocker As a cover for flush-mounted control 2gang switch.			
ivory white	1785 K-82-500	2CKA001751A3124	10
studio white	1785 K-84-500	2CKA001751A3128	10
grey metallic ¹⁾	1785 K-803-500	2CKA001751A3130	10


¹⁾ Surface painted.

 Rocker with small transparent lens As cover for flush-mounted 1gang 1way, 1gang 2way switch, intermediate switch, push-button and control switch 1gang 2way.			
ivory white	1789 N-82	2CKA001751A3148	10/100
studio white	1789 N-84-500	2CKA001751A3151	10/100
grey metallic ¹⁾	1789 N-803	2CKA001751A3146	10/100


¹⁾ Surface painted.

 Switch rocker with marking with small transparent lens With "Plug" icon. As cover for flush-mounted switch 1g1w DP and 3pole with neon lens and marking "I O" As cover for flush-mounted 1gang 1way, 1gang 2way switch, intermediate switch, push-button and control switch 1gang 2way.			
ivory white	1789 ST-82	2CKA001751A3158	10/100
studio white	1789 ST-84-500	2CKA001751A3161	10/100
grey metallic ¹⁾	1789 ST-803	2CKA001751A3156	10/100


¹⁾ Surface painted.

 Switch rocker with marking With symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.			
ivory white	2520 LI-82	2CKA001751A3187	10/100
studio white	2520 LI-84-500	2CKA001751A3190	10/100
grey metallic ¹⁾	2520 LI-803	2CKA001751A3185	10/100


¹⁾ Surface painted.

Product	Article-No.	Order-No.	Pack/Qty
 Switch rocker with marking With key symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.			
ivory white	2520 TR-82	2CKA001751A3197	10/100
studio white	2520 TR-84	2CKA001751A3199	10/100
grey metallic ¹⁾	2520 TR-803	2CKA001751A3195	10/100

¹⁾ Surface painted.


 Switch rocker with marking With bell symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.			
ivory white	2520 KI-82	2CKA001751A3177	10/100
studio white	2520 KI-84-500	2CKA001751A3180	10/100
grey metallic ¹⁾	2520 KI-803	2CKA001751A3175	10/100

¹⁾ Surface painted.

 Rocker ¹⁾ with labelling field With bell symbol. With pilot lamp for uniform illumination of the labelling field. For flush-mounted push switch. Size of labelling field: 51 x 10 mm.			
ivory white	1764 NLI/KI-82	2CKA001731A3999	10/100
studio white	1764 NLI/KI-84-500	2CKA001731A4002	10/100
grey metallic ²⁾	1764 NLI/KI-803	2CKA001731A3997	10/100

¹⁾ Illumination using neon lamp 8353 or incandescent lamp 8344-1 and LED inserts.


²⁾ Surface painted.

 Cover plate For card switch. For insert 2025 U. Suitable for cards sized 54 x 86 mm. The inner part of the cover plate is made of light-conducting plastic, so that the card slot is illuminated.			
grey metallic ¹⁾	1792-803	2CKA001710A4124	10


¹⁾ Surface painted.

Light switches and socket outlets – solo®


Rocker switches / push switches

Product	Article-No.	Order-No.	Pack/Qty
	Switch rocker with marking ¹⁾ For flush-mounted switch 1g1w, 1g2w, intermediate, push switch. DO NOT DISTURB		
	ivory white	1786/11-82	2CKA001751A2997 10
	studio white	1786/11-84	2CKA001751A2998 10
	grey metallic ¹⁾	1786/11-803	2CKA001751A3206 10

¹⁾ Surface painted.


	Switch rocker with marking ¹⁾ For flush-mounted switch 2g 1w, 2g push switch. DO NOT DISTURB MAKE UP ROOM		
	ivory white	1785/11-82	2CKA001751A2991 10
	studio white	1785/11-84	2CKA001751A2992 10
	grey metallic ¹⁾	1785/11-803	2CKA001751A3204 10

¹⁾ Surface painted.


	Cover plate ¹⁾ for pull switch 2610/6 UC-xx, 2610/6 UJ-xx With screw-type terminal		
	ivory white	1796-82	2CKA001753A0309 10
	studio white	1796-84	2CKA001753A0311 10
	grey metallic ²⁾	1796-803	2CKA001753A0307 10

¹⁾ Exchanging the available cover/cover plate.

²⁾ Surface painted.


	Cover plate ¹⁾ with rotary control, with marking As cover for flush mounted three-step rotary switch. With zero position. For insert 2710 U.		
	grey metallic ¹⁾	2542 DR/01-803	2CKA001710A4125 10

¹⁾ Surface painted.

	Cover plate ¹⁾ with rotary control, with marking As cover for flush mounted three-step rotary switch. Without zero position. For insert 2710/1 U.		
	grey metallic ¹⁾	2542 DR/02-803	2CKA001710A4126 10


¹⁾ Surface painted.

Movement detectors / comfort switches


Product	Article-No.	Order-No.	Pack/Qty
	Cover plate For proximity switch 6406 U.		
	grey metallic ¹⁾	6476-803	2CKA006470A0006 10

¹⁾ Surface painted.

Blind control / timers

	Cover plate with rotary knob, with marking For Busch-Timer insert 1070 U. Running time: 15 min		
	ivory white	1770-82-103	2CKA001753A0256 10
	studio white	1770-84-103	2CKA001753A0258 10
	grey metallic ¹⁾	1770-803-103	2CKA001753A0254 10


¹⁾ Surface painted.

	Cover plate with rotary knob, with marking For Busch-Timer insert 1071 U. Running time: 120 min		
	ivory white	1771-82-103	2CKA001753A0266 10
	studio white	1771-84-103	2CKA001753A0301 10
	grey metallic ¹⁾	1771-803-103	2CKA001753A0264 10

¹⁾ Surface painted.


Light switches and socket outlets – solo®

Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet without claw ¹⁾ shuttered Without claws. With screwless terminals. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	ivory white	20 EUCRB-82	2CKA002013A5438 10/100
	studio white	20 EUCRB-84-500	2CKA002013A5441 10/100
	grey metallic ²⁾	20 EUCRB-803	2CKA002013A5436 10/100


¹⁾ Increased shock protection.

²⁾ Surface painted.

	SCHUKO® socket outlet ¹⁾ shuttered With screw-type terminals. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	ivory white	2300 EUCB-82	2CKA002013A5449 10/100
	studio white	2300 EUCB-84	2CKA002013A5451 10/100
	grey metallic ²⁾	2300 EUCB-803	2CKA002013A5447 10/100


¹⁾ Increased shock protection.

²⁾ Surface painted.

	Busch-Socket outlet ¹⁾ shuttered With screwless terminals. DP (2 P + E) With eject mechanism. Rated voltage: 250 V~ Rated current: 16 A		
	ivory white	20 EUCBDR-82	2CKA002013A5416 10
	studio white	20 EUCBDR-84	2CKA002013A5418 10
	grey metallic ²⁾	20 EUCBDR-803	2CKA002013A5414 10

¹⁾ Increased shock protection.


²⁾ Surface painted.

	SCHUKO® socket outlet steplight® ^{1) 2)} With night orientation light with separate connection cables for switch contact. with LED. Shuttered. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	ivory white	20 EUAB-82	2CKA002013A5405 10
	studio white	20 EUAB-84	2CKA002013A5407 10
	grey metallic ³⁾	20 EUCBLI-803	2CKA002013A5458 1

¹⁾ Connecting terminals approved in accordance with VDE 0620-1 as connectors.


²⁾ Resistant to aggressive media, e.g. ammonia, benzene, oils, greases, alcohol, cleansing agents, in normal concentrations.

³⁾ Surface painted.

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet ¹⁾ with labelling field Size of labelling field: 60 x 9 mm. With screwless terminals. DP (2 P + E) Shuttered. Rated voltage: 250 V~ Rated current: 16 A		
	ivory white	20 EUCNB-82	2CKA002013A5428 10
	studio white	20 EUCNB-84-500	2CKA002013A5431 10/100
	grey metallic ²⁾	20 EUCNB-803	2CKA002013A5426 10


¹⁾ Increased shock protection.

²⁾ Surface painted.

	SCHUKO® socket outlet ¹⁾ with marking "EDV" With screwless terminals. DP (2 P + E) Shuttered. Rated voltage: 250 V~ Rated current: 16 A		
	ivory white	20 EUCB-82	2CKA002013A5449 10/100
	studio white	20 EUCB-84	2CKA002013A5451 10/100
	grey metallic ²⁾	20 EUCB-803	2CKA002013A5447 10/100


¹⁾ Increased shock protection.

²⁾ Surface painted.

	SCHUKO® socket outlet ¹⁾ with LED control light Shuttered. DP (2 P + E) With transparent lens. LED colour green. Rated voltage: 250 V~ Rated current: 16 A		
	ivory white	20 EUCBL-82	2CKA002013A5416 10
	studio white	20 EUCBL-84	2CKA002013A5418 10
	grey metallic ²⁾	20 EUCBL-803	2CKA002013A5414 10

¹⁾ Resistant to aggressive media, e.g. ammonia, benzene, oils, greases, alcohol, cleansing agents, in normal concentrations.

²⁾ Surface painted.


	Busch-Object socket outlet ¹⁾ shuttered With screwless terminals. DP (2 P + E) Incl. Cover plate with extract mechanism. Rated voltage: 250 V~ Rated current: 16 A		
	ivory white	20 EUAB-82	2CKA002013A5405 10
	studio white	20 EUAB-84	2CKA002013A5407 10
	grey metallic ²⁾	20 EUAB-803	2CKA002013A5403 10

¹⁾ Increased shock protection.

²⁾ Surface painted.


Light switches and socket outlets – solo®

Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	Buschmat® FI - Insert ¹⁾ with earth leakage breaker with connecting conductor Protection of downstream consumers. Rated actuating current: 30 mA. Release time: ≤ 30 ms. Short-circuit strength: 3000 A (with 25 A GL fuse). Current surge strength: 250 A (8/20) µs. DP cut off (P,N) Without claw fixation. Rated frequency: 45-60 Hz. Rated voltage: 230 V~ Rated current: 16 A Protection class (Device): IP 20 Temperature range (Device): -25 °C to 40 °C		
grey metallic ²⁾	3151 UC-803	2CKA003117A0008	1/10

¹⁾ Protective measure according to VDE 0100; can be proven or checked using the Profitest 0100S testing device, for example.

²⁾ Surface painted.


	FI-SCHUKOMAT, SCHUKO® socket outlet (RCD) ^{1) 2) 3)} with earth leakage circuit breaker Shuttered. DP cut off (P,N) Without PE monitoring. With connecting conductor and protection of downstream socket outlets. Rated actuating current: 30 mA. Release time: ≤ 30 ms. Short-circuit strength: 3000 A (with 25 A GL fuse). Current surge strength: 250 A (8/20) µs. With fixing claws. Rated frequency: 45-60 Hz. Rated voltage: 230 V~ Rated current: 16 A Protection class (Device): IP 20 Temperature range (Device): -25 °C to 40 °C		
grey metallic ⁴⁾	3120 EUCB-803	2CKA003116A0666	1/10

¹⁾ Connecting terminals approved in accordance with VDE 0620-1 as connectors.

²⁾ Protective measure according to VDE 0100; can be proven or checked using the Profitest 0100S testing device, for example.

³⁾ Increased shock protection.


⁴⁾ Surface painted.

	SCHUKO® socket outlet ¹⁾ with hinged lid Shuttered. With screwless terminals. DP (2 P + E) with hinged lid Rated voltage: 250 V~ Rated current: 16 A		
ivory white	20 EUKB-82	2CKA002018A1518	10/100
studio white	20 EUKB-84	2CKA002018A1520	10/100
grey metallic ²⁾	20 EUKB-803	2CKA002018A1516	10/100
ivory ³⁾	20 EUKBR-82	2CKA002018A1527	10/100
studio white ³⁾	20 EUKBR-84	2CKA002018A1529	10/100
grey metallic ^{2) 3)}	20 EUKBR-803	2CKA002018A1525	10/100

¹⁾ Increased shock protection.

²⁾ Surface painted.


³⁾ Without claw.

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet ^{1) 2)} with hinged lid and labelling field Shuttered. With screwless terminals. DP (2 P + E) with hinged lid Size of labelling field: 60 x 9 mm. Rated voltage: 250 V~ Rated current: 16 A		
ivory white	20 EUKNB-82	2CKA002018A1538	10/100
studio white	20 EUKNB-84	2CKA002018A1540	10/100
grey metallic ³⁾	20 EUKNB-803	2CKA002018A1536	10/100

¹⁾ Increased shock protection.


²⁾ The labels are clamped under the labelling field.

³⁾ Surface painted.

	SCHUKO® socket outlet ¹⁾ with hinged lid and lock Shuttered. With screwless terminals. DP (2 P + E) With different lock mechanism. Delivery includes 2 keys. Rated voltage: 250 V~ Rated current: 16 A		
ivory white	20 EUKNBSL-82	2CKA002018A1559	10
studio white	20 EUKNBSL-84	2CKA002018A1563	10
grey metallic ²⁾	20 EUKNBSL-803	2CKA002018A1555	10


¹⁾ Increased shock protection.

²⁾ Surface painted.

	SCHUKO® socket outlet ¹⁾ with hinged lid and lock Shuttered. With screwless terminals. DP (2 P + E) With evenly engaging lock. Delivery includes 2 keys. Rated voltage: 250 V~ Rated current: 16 A		
ivory white	20 EUKNBSL-82-101	2CKA002018A1560	10
studio white	20 EUKNBSL-84-101	2CKA002018A1564	10
grey metallic ²⁾	20 EUKNBSL-803-101	2CKA002018A1556	10

¹⁾ Increased shock protection.

²⁾ Surface painted.

	SCHUKO® socket outlet ^{1) 2)} with hinged lid, labelling field and LED control light Shuttered. With screwless terminals. DP (2 P + E) with hinged lid Size of labelling field: 60 x 9 mm. Rated voltage: 250 V~ Rated current: 16 A		
ivory white	20 EUKNBL-82	2CKA002018A1549	10/100
studio white	20 EUKNBL-84	2CKA002018A1551	10/100
grey metallic ³⁾	20 EUKNBL-803	2CKA002018A1547	10/100


¹⁾ Increased shock protection.

²⁾ The labels are clamped under the labelling field.

³⁾ Surface painted.


Light switches and socket outlets – solo®

Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	Socket outlet ¹⁾ shuttered Without claws. With screw-type terminals. DP Suitable for 1gang flush-mounted boxes. Rated voltage: 250 V~ Rated current: 16 A		
	ivory white	2300 UCRKS-82-503	2CKA002113A0510 10
	studio white	2300 UCRKS-84-503	2CKA002113A0511 10
	grey metallic ²⁾	2300 UCRKS-803-503	2CKA002113A5341 10

¹⁾ Increased shock protection.

²⁾ Surface painted.

	Socket outlet ^{1) 2)} with earthing pin With screwless terminals. Shuttered. DP (2 P + E) For supply and support of mobile devices via USB-cable. With USB female connector type A. With electronic short-circuit protection. With electronic overload protection. Simultaneous charging via USB connection and use of the SCHUKO® socket outlet. Suitable for the countries like Poland, Czech Republic. Rated voltage: 250 V~ Secondary: 5 V-, +5 % / -5 % Rated frequency: 50 Hz Suitable for: Socket outlet connection Rated current: 16 A Suitable for: USB connection Rated current: 700 mA Protection class (Device): IP 20, SELV Temperature range (Device): 5 °C to 35 °C Dimensions: (L x W x D): 71 mm x 71 mm x 53 mm Mounting depth: 35 mm		
	grey metallic ³⁾	20 MUCBUSB-803-500	2CKA002017A0892 1

¹⁾ No data transfer.


²⁾ Use dust cover 2098 when cleaning the device.

³⁾ Surface painted.

Product	Article-No.	Order-No.	Pack/Qty
---------	-------------	-----------	----------


Light switches and socket outlets – solo®

Data communication


Product	Article-No.	Order-No.	Pack/Qty
 Cover plate¹⁾ socket outlet Telephone socket (TDO)			
ivory white	1762-82-506	2CKA001710A4104	10/100
studio white	1762-84-506	2CKA001710A4106	10/100
grey metallic ²⁾	1762-803-506	2CKA001710A4102	10/100

¹⁾ Suitable insert: TDO 3x 10 OUP (for 1 telephone and 2 auxiliary devices).


²⁾ Surface painted.

 Cover plate As cover for 4gang Satellite co-axial socket outlet EVU 02 F, GEVU 15 S from Hirschmann.			
ivory white	1743-04-82	2CKA001724A4375	10
studio white	1743-04-84	2CKA001724A4377	10
grey metallic ¹⁾	1743-04-803	2CKA001724A4373	10


¹⁾ Surface painted.

 Cover plate As cover for 4gang Satellite co-axial socket outlet SAT400/EAS/DC, EAS 405, 413 DAS from Ankaro.			
ivory white	1743/10-04-82	2CKA001724A4366	10
studio white	1743/10-04-84	2CKA001724A4368	10/100
grey metallic ¹⁾	1743/10-04-803	2CKA001724A4364	10


¹⁾ Surface painted.

 Cover plate with metal mounting plate For 1 modular jack. Suitable for Art. Nos. 0210, 0211 and 0219-101. Without claws.			
ivory white	2561-82	2CKA001753A0401	10
studio white	2561-84	2CKA001753A0403	10
grey metallic ¹⁾	2561-803	2CKA001753A0399	10


¹⁾ Surface painted.

 Cover plate with metal mounting plate For 2 modular jack inserts. Suitable for Art. No. 0210 and 0211. Without claws.			
ivory white	2561-02-82	2CKA001753A0392	10
studio white	2561-02-84	2CKA001753A0394	10
grey metallic ¹⁾	2561-02-803	2CKA001753A0316	10


¹⁾ Surface painted.

Product	Article-No.	Order-No.	Pack/Qty
 Intermediate ring For attaching cover plates from the Busch-balance® SI range.			
ivory white	1747 BSI-82	2CKA001710A4094	10
studio white	1747 BSI-84	2CKA001710A4096	10/100
grey metallic ¹⁾	1747 BSI-803	2CKA001710A4092	10


¹⁾ Surface painted.

 XLR centre plate As cover for Neutrik plug connectors, type D series. Without claws.			
ivory white	2553-82	2CKA001724A4400	10
studio white	2553-84	2CKA001724A4402	10
grey metallic ¹⁾	2553-803	2CKA001724A4398	10

¹⁾ Surface painted.

 Equipotential socket outlet 2gang Without claws. For connecting wires up to 1 x 6 mm ² and 4 x 2.5 mm ² . IEC 60601-1:2005; DIN EN 60601 (VDE 0750-1): July 2007 Connection bolts German Standard DIN 42801.			
grey metallic ¹⁾	2095 UC-803	2CKA002495A0097	10

¹⁾ Surface painted.


 Cover plate with metal mounting plate With screw-type terminal. Fixed with central locknut. As cover for pilot devices with a diameter of 22.5 mm Without claws.			
yellow	2533-82-15	2CKA001724A4382	10
grey metallic ¹⁾	2533-803	2CKA001724A4407	10

¹⁾ Surface painted.


Light switches and socket outlets – solo®

Multimedia / communication adapters

LED light


Product	Article-No.	Order-No.	Pack/Qty
 Cover plate ¹⁾ with rotary control, with marking As a cover for volume controllers. Suitable for the "LR 15 mono BJ UP" devices of WHD.			
ivory white	1740 DR/03-82	2CKA001710A3807	10
studio white	1740 DR/03-84	2CKA001710A3808	10
grey metallic ¹⁾	1740 DR/03-803	2CKA001710A4119	10

¹⁾ Surface painted.

Product	Article-No.	Order-No.	Pack/Qty
 Cover plate for indication lamp For insert 2061/2661 U. As cover for flush-mounted light signal.			
ivory white	1756-82	2CKA001753A0090	10
studio white	1756-84	2CKA001753A0092	10
grey metallic ¹⁾	1756-803	2CKA001753A0088	10


¹⁾ Surface painted.

Covers for fan switch, NL

 Cover plate with rotary control, with marking As cover for fan switch. For insert 2711 U			
grey metallic ¹⁾	1740 DRL-803-503	2CKA001710A4121	10


¹⁾ Surface painted.


ABB-Welcome Indoor Stations


 Cover plates For indoor audio station with display. Protection class (Device): IP 30 Temperature range (Device): -5 °C to 40 °C			
ivory white	83260-82	2CKA008300A0541	1
grey metallic ¹⁾	83260-803	2CKA008300A0540	1


Light switches and socket outlets – Busch-axcent®


Rocker switches / push switches


Product	Article-No.	Order-No.	Pack/Qty
 Rocker As a cover for flush-mounted control 2gang switch.			
studio white	1785 K-84-500	2CKA001751A3128	10


 Rocker with small transparent lens As cover for flush-mounted 1gang 1way, 1gang 2way switch, intermediate switch, push-button and control switch 1gang 2way.			
studio white	1789 N-84-500	2CKA001751A3151	10/100

 Switch rocker with marking with small transparent lens With "Plug" icon. As cover for flush-mounted switch 1g1w DP and 3pole with neon lens and marking "I O" As cover for flush-mounted 1gang 1way, 1gang 2way switch, intermediate switch, push-button and control switch 1gang 2way.			
studio white	1789 ST-84-500	2CKA001751A3161	10/100


 Switch rocker with marking With symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.			
studio white	2520 LI-84-500	2CKA001751A3190	10/100

 Switch rocker with marking With key symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.			
studio white	2520 TR-84	2CKA001751A3199	10/100

 Switch rocker with marking With bell symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.			
studio white	2520 KI-84-500	2CKA001751A3180	10/100


 Rocker¹⁾ with labelling field With bell symbol. With pilot lamp for uniform illumination of the labelling field. For flush-mounted push switch. Size of labelling field: 51 x 10 mm.			
studio white	1764 NLI/KI-84-500	2CKA001731A4002	10/100


¹⁾ Illumination using neon lamp 8353 or incandescent lamp 8344-1 and LED inserts.

Product	Article-No.	Order-No.	Pack/Qty
 Cover plate¹⁾ for pull switch 2610/6 UC-xx, 2610/6 UJ-xx With screw-type terminal			
studio white	1796-84	2CKA001753A0311	10

¹⁾ Exchanging the available cover/cover plate.


Blind control / timers

 Cover plate with rotary knob, with marking For Busch-Timer insert 1070 U. Running time: 15 min			
studio white	1770-84-103	2CKA001753A0258	10


 Cover plate with rotary knob, with marking For Busch-Timer insert 1071 U. Running time: 120 min			
studio white	1771-84-103	2CKA001753A0301	10

Light switches and socket outlets – Busch-axcent®


Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet without claw ¹⁾ shuttered Without claws. With screwless terminals. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
studio white	20 EUCRB-84-500	2CKA002013A5441	10/100


¹⁾ Increased shock protection.

	SCHUKO® socket outlet ¹⁾ shuttered With screw-type terminals. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
studio white	2300 EUCB-84	2CKA002013A5451	10/100


¹⁾ Increased shock protection.

	Busch-Socket outlet ¹⁾ shuttered With screwless terminals. DP (2 P + E) With eject mechanism. Rated voltage: 250 V~ Rated current: 16 A		
studio white	20 EUCBDR-84	2CKA002013A5418	10


¹⁾ Increased shock protection.

	SCHUKO® socket outlet ¹⁾ with labelling field Size of labelling field: 60 x 9 mm. With screwless terminals. DP (2 P + E) Shuttered. Rated voltage: 250 V~ Rated current: 16 A		
studio white	20 EUCNB-84-500	2CKA002013A5431	10/100

¹⁾ Increased shock protection.


	Busch-Object socket outlet ¹⁾ shuttered With screwless terminals. DP (2 P + E) Incl. Cover plate with extract mechanism. Rated voltage: 250 V~ Rated current: 16 A		
studio white	20 EUAB-84	2CKA002013A5407	10

¹⁾ Increased shock protection.

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet ¹⁾ with hinged lid Shuttered. With screwless terminals. DP (2 P + E) with hinged lid Rated voltage: 250 V~ Rated current: 16 A		
studio white	20 EUKB-84	2CKA002018A1520	10/100
studio white ²⁾	20 EUKBR-84	2CKA002018A1529	10/100


¹⁾ Increased shock protection.

²⁾ Without claw.


	SCHUKO® socket outlet ^{1) 2)} with hinged lid and labelling field Shuttered. With screwless terminals. DP (2 P + E) with hinged lid Size of labelling field: 60 x 9 mm. Rated voltage: 250 V~ Rated current: 16 A		
studio white	20 EUKNB-84	2CKA002018A1540	10/100

¹⁾ Increased shock protection.


²⁾ The labels are clamped under the labelling field.

	SCHUKO® socket outlet ¹⁾ with hinged lid and lock Shuttered. With screwless terminals. DP (2 P + E) With different lock mechanism. Delivery includes 2 keys. Rated voltage: 250 V~ Rated current: 16 A		
studio white	20 EUKNBSL-84	2CKA002018A1563	10

¹⁾ Increased shock protection.

	SCHUKO® socket outlet ¹⁾ with hinged lid and lock Shuttered. With screwless terminals. DP (2 P + E) With evenly engaging lock. Delivery includes 2 keys. Rated voltage: 250 V~ Rated current: 16 A		
studio white	20 EUKNBSL-84-101	2CKA002018A1564	10

¹⁾ Increased shock protection.

	SCHUKO® socket outlet ^{1) 2)} with hinged lid, labelling field and LED control light Shuttered. With screwless terminals. DP (2 P + E) with hinged lid Size of labelling field: 60 x 9 mm. Rated voltage: 250 V~ Rated current: 16 A		
studio white	20 EUKNBL-84	2CKA002018A1551	10/100

¹⁾ Increased shock protection.

²⁾ The labels are clamped under the labelling field.

Light switches and socket outlets – Busch-axcent®

Data communication

LED light

Product	Article-No.	Order-No.	Pack/Qty
	Cover plate ¹⁾ socket outlet Telephone socket (TDO)		
	studio white	1762-84-506	2CKA001710A4106 10/100

¹⁾ Suitable insert: TDO 3x 10 OUP (for 1 telephone and 2 auxiliary devices).

	Cover plate As cover for 4gang Satellite co-axial socket outlet EVU 02 F, GEVU 15 S from Hirschmann.		
	studio white	1743-04-84	2CKA001724A4377 10

	Cover plate As cover for 4gang Satellite co-axial socket outlet SAT400/EAS/DC, EAS 405, 413 DAS from Ankaro.		
	studio white	1743/10-04-84	2CKA001724A4368 10/100

	Cover plate with metal mounting plate For 1 modular jack. Suitable for Art. Nos. 0210, 0211 and 0219-101. Without claws.		
	studio white	2561-84	2CKA001753A0403 10

	Cover plate with metal mounting plate For 2 modular jack inserts. Suitable for Art. No. 0210 and 0211. Without claws.		
	studio white	2561-02-84	2CKA001753A0394 10


	Intermediate ring For attaching cover plates from the Busch-balance® SI range.		
	studio white	1747 BSI-84	2CKA001710A4096 10/100


	XLR centre plate As cover for Neutrik plug connectors, type D series. Without claws.		
	studio white	2553-84	2CKA001724A4402 10

Product	Article-No.	Order-No.	Pack/Qty
	Cover plate for indication lamp For insert 2061/2661 U. As cover for flush-mounted light signal.		
	studio white	1756-84	2CKA001753A0092 10


Light switches and socket outlets – future® linear

Rocker switches / push switches


Product	Article-No.	Order-No.	Pack/Qty
	Rocker For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.		
	red RAL 3020	1786-12-82	2CKA001751A3145 10/100

	Rocker As a cover for flush-mounted control 2gang switch.		
	anthracite	1785 K-81-500	2CKA001751A3122 10
	ivory white	1785 K-82-500	2CKA001751A3124 10
	aluminium silver ¹⁾	1785 K-83-500	2CKA001751A3126 10
	studio white	1785 K-84-500	2CKA001751A3128 10
	studio white, matt ¹⁾	1785 K-884-500	2CKA001751A3135 10
	black matt ¹⁾	1785 K-885-500	2CKA001751A3137 10


¹⁾ Surface painted.

	Rocker with small transparent lens As cover for flush-mounted 1gang 1way, 1gang 2way switch, intermediate switch, push-button and control switch 1gang 2way.		
	anthracite	1789 N-81	2CKA001751A3147 10/100
	ivory white	1789 N-82	2CKA001751A3148 10/100
	aluminium silver ¹⁾	1789 N-83	2CKA001751A3149 10/100
	studio white	1789 N-84-500	2CKA001751A3151 10/100
	studio white, matt ¹⁾	1789 N-884	2CKA001751A3153 10/100
	black matt ¹⁾	1789 N-885	2CKA001751A3154 10/100


¹⁾ Surface painted.

	Switch rocker with marking with small transparent lens With "Plug" icon. As cover for flush-mounted switch 1g1w DP and 3pole with neon lens and marking "I O" As cover for flush-mounted 1gang 1way, 1gang 2way switch, intermediate switch, push-button and control switch 1gang 2way.		
	anthracite	1789 ST-81	2CKA001751A3157 10/100
	ivory white	1789 ST-82	2CKA001751A3158 10/100
	aluminium silver ¹⁾	1789 ST-83	2CKA001751A3159 10/100
	studio white	1789 ST-84-500	2CKA001751A3161 10/100
	studio white, matt ¹⁾	1789 ST-884	2CKA001751A3163 10/100
	black matt ¹⁾	1789 ST-885	2CKA001751A3164 10/100


¹⁾ Surface painted.

Product	Article-No.	Order-No.	Pack/Qty
	Switch rocker with marking With symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.		
	anthracite	2520 LI-81	2CKA001751A3186 10/100
	ivory white	2520 LI-82	2CKA001751A3187 10/100
	aluminium silver ¹⁾	2520 LI-83	2CKA001751A3188 10/100
	studio white	2520 LI-84-500	2CKA001751A3190 10/100
	studio white, matt ¹⁾	2520 LI-884	2CKA001751A3192 10/100
	black matt ¹⁾	2520 LI-885	2CKA001751A3193 10/100

¹⁾ Surface painted.

	Switch rocker with marking With key symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.		
	anthracite	2520 TR-81	2CKA001751A3196 10/100
	ivory white	2520 TR-82	2CKA001751A3197 10/100
	aluminium silver ¹⁾	2520 TR-83	2CKA001751A3198 10/100
	studio white	2520 TR-84	2CKA001751A3199 10/100
	studio white, matt ¹⁾	2520 TR-884	2CKA001751A3201 10/100
	black matt ¹⁾	2520 TR-885	2CKA001751A3202 10/100


¹⁾ Surface painted.

	Switch rocker with marking With bell symbol. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch.		
	anthracite	2520 KI-81	2CKA001751A3176 10/100
	ivory white	2520 KI-82	2CKA001751A3177 10/100
	aluminium silver ¹⁾	2520 KI-83	2CKA001751A3178 10/100
	studio white	2520 KI-84-500	2CKA001751A3180 10/100
	studio white, matt ¹⁾	2520 KI-884	2CKA001751A3182 10/100
	black matt ¹⁾	2520 KI-885	2CKA001751A3183 10/100

¹⁾ Surface painted.


Light switches and socket outlets – future® linear

Rocker switches / push switches

Product	Article-No.	Order-No.	Pack/Qty
 Rocker ¹⁾ with labelling field With bell symbol. With pilot lamp for uniform illumination of the labelling field. For flush-mounted push switch. Size of labelling field: 51 x 10 mm.	anthracite	1764 NLI/KI-81	2CKA001731A3998 10/100
	ivory white	1764 NLI/KI-82	2CKA001731A3999 10/100
	aluminium silver ²⁾	1764 NLI/KI-83	2CKA001731A4000 10/100
	studio white	1764 NLI/KI-84-500	2CKA001731A4002 10/100
	studio white, matt ²⁾	1764 NLI/KI-884	2CKA001731A4004 10/100
	black matt ²⁾	1764 NLI/KI-885	2CKA001731A4005 10/100


¹⁾ Illumination using neon lamp 8353 or incandescent lamp 8344-1 and LED inserts.


²⁾ Surface painted.


 Rocker ^{1) 2)} with labelling field With pilot lamp for uniform illumination of the labelling field. For flush-mounted switch 1g1w, 1g2w, intermediate, push switch. Size of labelling field: 59.7 x 11.7 mm.	Green, RAL 6032	1764 NLI-13-82	2CKA001731A4007 10/100
---	-----------------	-----------------------	------------------------

¹⁾ For compatible lettering software, visit www.BUSCH-JAEGER-labelingtool.com.

²⁾ Illumination using neon lamp 8353 or incandescent lamp 8344-1 and LED inserts.

 Switch rocker with marking For flush-mounted switch 1g1w, 1g2w, intermediate, push switch. DO NOT DISTURB	anthracite	1786/11-81	2CKA001751A3207 10
--	------------	-------------------	--------------------


 Switch rocker with marking For flush-mounted switch 2g 1w, 2g push switch. DO NOT DISTURB MAKE UP ROOM	anthracite	1785/11-81	2CKA001751A3205 10
--	------------	-------------------	--------------------

 Cover plate ¹⁾ for pull switch 2610/6 UC-xx, 2610/6 UJ-xx With screw-type terminal	anthracite	1796-81	2CKA001753A0308 10
	ivory white	1796-82	2CKA001753A0309 10
	aluminium silver ²⁾	1796-83	2CKA001753A0310 10
	studio white	1796-84	2CKA001753A0311 10
	studio white, matt ²⁾	1796-884	2CKA001753A0313 10
	black matt ²⁾	1796-885	2CKA001753A0314 10

¹⁾ Exchanging the available cover/cover plate.


²⁾ Surface painted.

Movement detectors / comfort switches

Product	Article-No.	Order-No.	Pack/Qty
 Cover plate For proximity switch 6406 U.	anthracite	6476-81	2CKA006470A0007 1/10
	aluminium silver ¹⁾	6476-83	2CKA006470A0008 10
	studio white, matt ¹⁾	6476-884	2CKA006470A0010 10
	black matt ¹⁾	6476-885	2CKA006470A0011 10


¹⁾ Surface painted.

Blind control / timers

 Cover plate with rotary knob, with marking For Busch-Timer insert 1070 U. Running time: 15 min	anthracite	1770-81-103	2CKA001753A0255 10
	ivory white	1770-82-103	2CKA001753A0256 10
	aluminium silver ¹⁾	1770-83-103	2CKA001753A0257 10
	studio white	1770-84-103	2CKA001753A0258 10
	studio white, matt ²⁾	1770-884-103	2CKA001753A0260 10
	black matt ¹⁾	1770-885-103	2CKA001753A0261 10

¹⁾ Surface painted.


²⁾ Surface lacquered in aluminium.

 Cover plate with rotary knob, with marking For Busch-Timer insert 1071 U. Running time: 120 min	anthracite	1771-81-103	2CKA001753A0265 10
	ivory white	1771-82-103	2CKA001753A0266 10
	aluminium silver ¹⁾	1771-83-103	2CKA001753A0267 10
	studio white	1771-84-103	2CKA001753A0301 10
	studio white, matt ¹⁾	1771-884-103	2CKA001753A0303 10
	black matt ¹⁾	1771-885-103	2CKA001753A0304 10

¹⁾ Surface painted.


Light switches and socket outlets – future® linear

Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet without claw ¹⁾ shuttered Without claws. With screwless terminals. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUCRB-81	2CKA002013A5437 10/100
	ivory white	20 EUCRB-82	2CKA002013A5438 10/100
	aluminium silver ²⁾	20 EUCRB-83	2CKA002013A5439 10/100
	studio white	20 EUCRB-84-500	2CKA002013A5441 10/100
	studio white, matt ²⁾	20 EUCRB-884	2CKA002013A5443 10/100
	black matt ²⁾	20 EUCRB-885	2CKA002013A5444 10/100

¹⁾ Increased shock protection.


²⁾ Surface painted.

	SCHUKO® socket outlet ^{1) 2)} shuttered With screw-type terminals. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	2300 EUCB-81	2CKA002013A5448 10
	ivory white	2300 EUCB-82	2CKA002013A5449 10/100
	aluminium silver ³⁾	2300 EUCB-83	2CKA002013A5450 10/100
	studio white	2300 EUCB-84	2CKA002013A5451 10/100
	studio white, matt ³⁾	2300 EUCB-884	2CKA002013A5453 10/100
	black matt ³⁾	2300 EUCB-885	2CKA002013A5454 10/100

¹⁾ Increased shock protection.


²⁾ With screw-type terminals

³⁾ Surface painted.

	Busch-Socket outlet ¹⁾ shuttered With screwless terminals. DP (2 P + E) With eject mechanism. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUCBDR-81	2CKA002013A5415 10
	ivory white	20 EUCBDR-82	2CKA002013A5416 10
	aluminium silver ²⁾	20 EUCBDR-83	2CKA002013A5417 10
	studio white	20 EUCBDR-84	2CKA002013A5418 10
	studio white, matt ²⁾	20 EUCBDR-884	2CKA002013A5420 10
	black matt ²⁾	20 EUCBDR-885	2CKA002013A5421 10


¹⁾ Increased shock protection.

²⁾ Surface painted.

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet steplight® ^{1) 2)} With night orientation light with separate connection cables for switch contact. with LED, Shuttered. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUCBLI-81	2CKA002013A5459 1


¹⁾ Connecting terminals approved in accordance with VDE 0620-1 as connectors.

²⁾ Resistant to aggressive media, e.g. ammonia, benzene, oils, greases, alcohol, cleansing agents, in normal concentrations.

	SCHUKO® socket outlet ¹⁾ with labelling field Size of labelling field: 60 x 9 mm. With screwless terminals. DP (2 P + E) Shuttered. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUCNB-81	2CKA002013A5427 10
	ivory white	20 EUCNB-82	2CKA002013A5428 10
	aluminium silver ²⁾	20 EUCNB-83	2CKA002013A5429 10/100
	studio white	20 EUCNB-84-500	2CKA002013A5431 10/100
	studio white, matt ²⁾	20 EUCNB-884	2CKA002013A5433 10/100
	black matt ²⁾	20 EUCNB-885	2CKA002013A5434 10/100
	red RAL 3020	20 EUCNB-12-82	2CKA002013A5423 10

¹⁾ Increased shock protection.


²⁾ Surface painted.

	SCHUKO® socket outlet ¹⁾ with LED control light Shuttered. DP (2 P + E) With transparent lens. LED colour green. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUCBL-81	2CKA002013A5457 10

¹⁾ Resistant to aggressive media, e.g. ammonia, benzene, oils, greases, alcohol, cleansing agents, in normal concentrations.


Light switches and socket outlets – future® linear

Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	Busch-Object socket outlet ¹⁾ shuttered With screwless terminals. DP (2 P + E) Incl. Cover plate with extract mechanism. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUAB-81	2CKA002013A5404 10
	ivory white	20 EUAB-82	2CKA002013A5405 10
	aluminium silver ²⁾	20 EUAB-83	2CKA002013A5406 10
	studio white	20 EUAB-84	2CKA002013A5407 10
	studio white, matt ²⁾	20 EUAB-884	2CKA002013A5409 10
	black matt ²⁾	20 EUAB-885	2CKA002013A5410 10

¹⁾ Increased shock protection.

²⁾ Surface painted.


	FI-SCHUKOMAT, SCHUKO® socket outlet (RCD) ^{1) 2) 3)} with earth leakage circuit breaker Shuttered. DP cut off (P,N) Without PE monitoring. With connecting conductor and protection of downstream socket outlets. Rated actuating current: 30 mA. Release time: ≤ 30 ms. Short-circuit strength: 3000 A (with 25 A GL fuse). Current surge strength: 250 A (8/20) μs. With fixing claws. Rated frequency: 45-60 Hz. Rated voltage: 230 V~ Rated current: 16 A Protection class (Device): IP 20 Temperature range (Device): -25 °C to 40 °C		
	anthracite	3120 EUCB-81	2CKA003116A0667 1/10
	aluminium silver ⁴⁾	3120 EUCB-83	2CKA003116A0668 1/10
	studio white, matt ⁴⁾	3120 EUCB-884	2CKA003116A0670 1/10
	black matt ⁴⁾	3120 EUCB-885	2CKA003116A0671 1/10

¹⁾ Connecting terminals approved in accordance with VDE 0620-1 as connectors.

²⁾ Protective measure according to VDE 0100; can be proven or checked using the Profitest 0100S testing device, for example.



³⁾ Increased shock protection.

⁴⁾ Surface painted.

Product	Article-No.	Order-No.	Pack/Qty
	Buschmat® FI - Insert ¹⁾ with earth leakage breaker with connecting conductor Protection of downstream consumers. Rated actuating current: 30 mA. Release time: ≤ 30 ms. Short-circuit strength: 3000 A (with 25 A GL fuse). Current surge strength: 250 A (8/20) μs. DP cut off (P,N) Without claw fixation. Rated frequency: 45-60 Hz. Rated voltage: 230 V~ Rated current: 16 A Protection class (Device): IP 20 Temperature range (Device): -25 °C to 40 °C		
	anthracite	3151 UC-81	2CKA003117A0009 1/10
	aluminium silver ²⁾	3151 UC-83	2CKA003117A0010 1/10
	studio white, matt ²⁾	3151 UC-884	2CKA003117A0012 1/10
	black matt ²⁾	3151 UC-885	2CKA003117A0013 1/10

¹⁾ Protective measure according to VDE 0100; can be proven or checked using the Profitest 0100S testing device, for example.

²⁾ Surface painted.

	xxxxxx xxx		
	anthracite	20 EUKB-81	2CKA002018A1517 10/100
	ivory white	20 EUKB-82	2CKA002018A1518 10/100
	aluminium silver ²⁾	20 EUKB-83	2CKA002018A1519 10/100
	studio white	20 EUKB-84	2CKA002018A1520 10/100
	studio white, matt ²⁾	20 EUKB-884	2CKA002018A1522 10/100
	black matt ²⁾	20 EUKB-885	2CKA002018A1523 10/100
	anthracite ³⁾	20 EUKBR-81	2CKA002018A1526 10/100
	ivory white ³⁾	20 EUKBR-82	2CKA002018A1527 10/100
	aluminium silver ^{2) 3)}	20 EUKBR-83	2CKA002018A1528 10/100
	studio white ³⁾	20 EUKBR-84	2CKA002018A1529 10/100
	studio white, matt ^{2) 3)}	20 EUKBR-884	2CKA002018A1530 10/100
	black matt ^{2) 3)}	20 EUKBR-885	2CKA002018A1531 10/100


¹⁾ Increased shock protection.

²⁾ Surface painted.

³⁾ Without claw.


Light switches and socket outlets – future® linear

Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet ¹⁾ with hinged lid and lock Shuttered. With screwless terminals. DP (2 P + E) With different lock mechanism. Delivery includes 2 keys. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUKNBSL-81	2CKA002018A1557 10
	ivory white	20 EUKNBSL-82	2CKA002018A1559 10
	aluminium silver ²⁾	20 EUKNBSL-83	2CKA002018A1561 10
	studio white	20 EUKNBSL-84	2CKA002018A1563 10
	studio white, matt ²⁾	20 EUKNBSL-884	2CKA002018A1565 10
	black matt ²⁾	20 EUKNBSL-885	2CKA002018A1567 10


¹⁾ Increased shock protection.

²⁾ Surface painted.

	SCHUKO® socket outlet ¹⁾ with hinged lid and lock Shuttered. With screwless terminals. DP (2 P + E) With evenly engaging lock. Delivery includes 2 keys. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUKNBSL-81-101	2CKA002018A1558 10
	ivory white	20 EUKNBSL-82-101	2CKA002018A1560 10
	aluminium silver ²⁾	20 EUKNBSL-83-101	2CKA002018A1562 10
	studio white	20 EUKNBSL-84-101	2CKA002018A1564 10
	studio white, matt ²⁾	20 EUKNBSL-884-101	2CKA002018A1566 10
	black matt ²⁾	20 EUKNBSL-885-101	2CKA002018A1568 10

¹⁾ Increased shock protection.

²⁾ Surface painted.


Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet ^{1) 2)} with hinged lid and labelling field Shuttered. With screwless terminals. DP (2 P + E) with hinged lid Size of labelling field: 60 x 9 mm. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUKNB-81	2CKA002018A1537 10/100
	ivory white	20 EUKNB-82	2CKA002018A1538 10/100
	red RAL 3020 ³⁾	20 EUKNB-12-82	2CKA002018A1533 10/100
	green, RAL 6032 ³⁾	20 EUKNB-13-82	2CKA002018A1534 10/100
	orange RAL 2004 ³⁾	20 EUKNB-14-82	2CKA002018A1535 10/100
	aluminium silver ⁴⁾	20 EUKNB-83	2CKA002018A1539 10/100
	studio white	20 EUKNB-84	2CKA002018A1540 10/100
	studio white, matt ⁴⁾	20 EUKNB-884	2CKA002018A1541 10/100
	black matt ⁴⁾	20 EUKNB-885	2CKA002018A1542 10/100

¹⁾ Increased shock protection.

²⁾ The labels are clamped under the labelling field.

³⁾ With continuous coloured marking of cover plate and base.

⁴⁾ Surface painted.

	SCHUKO® socket outlet ^{1) 2)} with hinged lid, labelling field and LED control light Shuttered. With screwless terminals. DP (2 P + E) with hinged lid Size of labelling field: 60 x 9 mm. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 EUKNBL-81	2CKA002018A1548 10/100
	ivory white	20 EUKNBL-82	2CKA002018A1549 10/100
	red RAL 3020 ³⁾	20 EUKNBL-12-82	2CKA002018A1544 10/100
	green, RAL 6032 ³⁾	20 EUKNBL-13-82	2CKA002018A1545 10/100
	orange RAL 2004 ³⁾	20 EUKNBL-14-82	2CKA002018A1546 10/100
	aluminium silver ⁴⁾	20 EUKNBL-83	2CKA002018A1550 10/100
	studio white	20 EUKNBL-84	2CKA002018A1551 10/100
	studio white, matt ⁴⁾	20 EUKNBL-884	2CKA002018A1552 10/100
	black matt ⁴⁾	20 EUKNBL-885	2CKA002018A1553 10/100

¹⁾ Increased shock protection.


²⁾ The labels are clamped under the labelling field.

³⁾ With continuous coloured marking of cover plate and base.

⁴⁾ Surface painted.

Light switches and socket outlets – future® linear


Socket outlets

Product	Article-No.	Order-No.	Pack/Qty
	SCHUKO® socket outlet ¹⁾ with marking Shuttered. With screwless terminals. DP (2 P + E) With continuous coloured marking of cover plate and base. Rated voltage: 250 V~ Rated current: 16 A		
	green, RAL 6032 ²⁾	20 EUCB-13-82-10	2CKA002013A5412 10/100
orange RAL 2004 ³⁾	20 EUCB-14-82-10	2CKA002013A5413	10/100


¹⁾ Increased shock protection.

²⁾ With imprint "PS"

³⁾ With imprint "CPS"


	SCHUKO® socket outlet ¹⁾ with labelling field Size of labelling field: 60 x 9 mm. With screwless terminals. DP (2 P + E) Shuttered. Rated voltage: 250 V~ Rated current: 16 A		
	green, RAL 6032	20 EUCNB-13-82	2CKA002013A5424 10
orange RAL 2004	20 EUCNB-14-82	2CKA002013A5425	10

¹⁾ Increased shock protection.

	Socket outlet ¹⁾ shuttered Without claws. With screw-type terminals. DP Suitable for 1gang flush-mounted boxes. Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	2300 UCRKS-81-503	2CKA002113A5339 10
black matt ²⁾	2300 UCRKS-885-503	2CKA002113A5340	10

¹⁾ Increased shock protection.

²⁾ Surface painted.

Product	Article-No.	Order-No.	Pack/Qty
	Socket outlet ^{1) 2)} with earthing pin With screwless terminals. Shuttered. DP (2 P + E) For supply and support of mobile devices via USB-cable. With USB female connector type A. With electronic short-circuit protection. With electronic overload protection. Simultaneous charging via USB connection and use of the SCHUKO® socket outlet. Suitable for the countries like Poland, Czech Republic. Rated voltage: 250 V~ Secondary: 5 V-, +5 % / -5 % Rated frequency: 50 Hz Suitable for: Socket outlet connection Rated current: 16 A Suitable for: USB connection Rated current: 700 mA Protection class (Device): IP 20, SELV Temperature range (Device): 5 °C to 35 °C Dimensions: (L x W x D): 71 mm x 71 mm x 53 mm Mounting depth: 35 mm		
	anthracite	20 MUCBUSB-81-500	2CKA002017A0893 1
aluminium silver ³⁾	20 MUCBUSB-83-500	2CKA002017A0894	1
studio white, matt ³⁾	20 MUCBUSB-884-500	2CKA002017A0896	1
black matt ³⁾	20 MUCBUSB-885-500	2CKA002017A0897	1

¹⁾ No data transfer.

²⁾ Use dust cover 2098 when cleaning the device.

³⁾ Surface painted.


	Socket outlet ¹⁾ with earthing pin With screwless terminals. Shuttered. Suitable for the countries like Poland, Czech Republic. DP (2 P + E) Rated voltage: 250 V~ Rated current: 16 A		
	anthracite	20 MUCKS-81-500	2CKA002017A0898 10
aluminium silver ²⁾	20 MUCKS-83-500	2CKA002017A0899	10
studio white, matt ²⁾	20 MUCKS-884-500	2CKA002017A0901	10
black matt ²⁾	20 MUCKS-885-500	2CKA002017A0902	10

¹⁾ Socket outlet with integrated child protection.

²⁾ Surface painted.


Light switches and socket outlets – future® linear

Data communication


Product	Article-No.	Order-No.	Pack/Qty
 Cover plate ¹⁾ socket outlet Telephone socket (TDO)			
anthracite	1762-81-506	2CKA001710A4103	10/100
ivory white	1762-82-506	2CKA001710A4104	10/100
aluminium silver ²⁾	1762-83-506	2CKA001710A4105	10/100
studio white	1762-84-506	2CKA001710A4106	10/100
studio white, matt ²⁾	1762-884-506	2CKA001710A4108	10/100
black matt ²⁾	1762-885-506	2CKA001710A4109	10/100

¹⁾ Suitable insert: TDO 3x 10 OUP (for 1 telephone and 2 auxiliary devices).


²⁾ Surface painted.

 Cover plate As cover for 4gang Satellite co-axial socket outlet EVU 02 F, GEVU 15 S from Hirschmann.			
anthracite	1743-04-81	2CKA001724A4374	10
ivory white	1743-04-82	2CKA001724A4375	10
aluminium silver ¹⁾	1743-04-83	2CKA001724A4376	10
studio white	1743-04-84	2CKA001724A4377	10
studio white, matt ¹⁾	1743-04-884	2CKA001724A4379	10
black matt ¹⁾	1743-04-885	2CKA001724A4380	10


¹⁾ Surface painted.

 Cover plate As cover for 4gang Satellite co-axial socket outlet SAT400/EAS/DC, EAS 405, 413 DAS from Ankaro.			
anthracite	1743/10-04-81	2CKA001724A4365	10
ivory white	1743/10-04-82	2CKA001724A4366	10
aluminium silver ¹⁾	1743/10-04-83	2CKA001724A4367	10
studio white	1743/10-04-84	2CKA001724A4368	10/100
studio white, matt ¹⁾	1743/10-04-884	2CKA001724A4370	10
black matt ¹⁾	1743/10-04-885	2CKA001724A4371	10


¹⁾ Surface painted.

Product	Article-No.	Order-No.	Pack/Qty
 Cover plate with metal mounting plate For 1 modular jack. Suitable for Art. Nos. 0210, 0211 and 0219-101. Without claws.			
anthracite	2561-81	2CKA001753A0400	10
ivory white	2561-82	2CKA001753A0401	10
aluminium silver ¹⁾	2561-83	2CKA001753A0402	10
studio white	2561-84	2CKA001753A0403	10
studio white, matt ¹⁾	2561-884	2CKA001753A0405	10
black matt ¹⁾	2561-885	2CKA001753A0406	10


¹⁾ Surface painted.

 Cover plate with metal mounting plate For 2 modular jack inserts. Suitable for Art. No. 0210 and 0211. Without claws.			
anthracite	2561-02-81	2CKA001753A0317	10
ivory white	2561-02-82	2CKA001753A0392	10
aluminium silver ¹⁾	2561-02-83	2CKA001753A0393	10
studio white	2561-02-84	2CKA001753A0394	10
studio white, matt ¹⁾	2561-02-884	2CKA001753A0396	10
black matt ¹⁾	2561-02-885	2CKA001753A0397	10

¹⁾ Surface painted.


 Intermediate ring For attaching cover plates from the Busch+balance® SI range.			
anthracite	1747 BSI-81	2CKA001710A4093	10
ivory white	1747 BSI-82	2CKA001710A4094	10
aluminium silver ¹⁾	1747 BSI-83	2CKA001710A4095	10
studio white	1747 BSI-84	2CKA001710A4096	10/100
studio white, matt ¹⁾	1747 BSI-884	2CKA001710A4098	10
black matt ¹⁾	1747 BSI-885	2CKA001710A4099	10

¹⁾ Surface painted.


 Cover plate with hinged lid For telecommunication inserts with cover plate 50 x 50 mm. With cover plate 50 x 50 mm, AMP, Brand-Rex, Rutenbeck, BTR, Telegärtner, etc.			
anthracite	1746-81	2CKA001710A3618	10

Light switches and socket outlets – future® linear


Data communication

Product	Article-No.	Order-No.	Pack/Qty
 XLR centre plate As cover for Neutrik plug connectors, type D series. Without claws.			
anthracite	2553-81	2CKA001724A4399	10
ivory white	2553-82	2CKA001724A4400	10
aluminium silver ¹⁾	2553-83	2CKA001724A4401	10
studio white	2553-84	2CKA001724A4402	10
studio white, matt ¹⁾	2553-884	2CKA001724A4404	10
black matt ¹⁾	2553-885	2CKA001724A4405	10


¹⁾ Surface painted.

 Cover plate with metal mounting plate With screw-type terminal. Fixed with central locknut. As cover for pilot devices with a diameter of 22.5 mm Without claws.			
yellow	2533-82-15	2CKA001724A4382	10

Multimedia / communication adapters


 Cover plate with rotary control, with marking As a cover for volume controllers. Suitable for the "LR 15 mono BJ UP" devices of WHD.			
anthracite	1740 DR/03-81	2CKA001710A4120	10/100
ivory white	1740 DR/03-82	2CKA001710A3807	10/100
aluminium silver ¹⁾	1740 DR/03-83	2CKA001710A3811	10/100
studio white	1740 DR/03-84	2CKA001710A3808	10/100
studio white, matt ¹⁾	1740 DR/03-884	2CKA001710A3870	10/100
black matt ¹⁾	1740 DR/03-885	2CKA001710A3892	10/100

¹⁾ Surface painted.

 Busch-Radio BTconnect ¹⁾ complete set Ready-to-install RDS Internet radio alarm clock for mono operation (set packaged). With Bluetooth interface for music replay of mobile devices. Consisting of the Busch-Radio BTconnect 8217 U. Consisting of speaker insert 8223 U. Consisting of the cover plate for the Busch-Radio. Consisting of cover plate for speaker insert 8253-84. Consisting of 2gang future® linear cover frame 1722-184K. Rated voltage: 110 - 230 V~, +10 % / -10 % Rated frequency: 50 Hz - 60 Hz Protection class (Device): IP 20 Dimensions: (L x W x D): 150 mm x 80 mm x 49 mm Mounting depth: 32 mm			
studio white	8270-84-500	2CKA008200A0197	1


¹⁾ No claw. Screw-fixing via keyholes.

LED light

Product	Article-No.	Order-No.	Pack/Qty
 Cover plate for indication lamp For insert 2061/2661 U. As cover for flush-mounted light signal.			
anthracite	1756-81	2CKA001753A0089	10
ivory white	1756-82	2CKA001753A0090	10
aluminium silver ¹⁾	1756-83	2CKA001753A0091	10
studio white	1756-84	2CKA001753A0092	10
studio white, matt ¹⁾	1756-884	2CKA001753A0251	10
black matt ¹⁾	1756-885	2CKA001753A0252	10


¹⁾ Surface painted.

Covers for fan switch, NL

 Cover plate with rotary control, with marking As cover for fan switch. For insert 2711 U			
anthracite	1740 DRL-81-503	2CKA001710A4122	10
aluminium silver ¹⁾	1740 DRL-83-503	2CKA001710A4123	10

¹⁾ Surface painted.


ABB-Welcome Indoor Stations


 Cover plates For indoor audio station with display. Protection class (Device): IP 30 Temperature range (Device): -5 °C to 40 °C			
ivory white	83260-82	2CKA008300A0541	1
studio white, matt ¹⁾	83260-884	2CKA008300A0543	1
black matt ¹⁾	83260-885	2CKA008300A0544	1


¹⁾ Surface painted.


IVIE


Rocker switches / push switches


Product	Article-No.	Order-No.	Pack/Qty
	Switch 1 way 6 A - 240 V ~ Number of modules: 1		
	white	IIS10610 BL	1SYK100001A1001 20/400
	anthracite grey	IIS10610 AN	1SYK100001A1201 20/400
	silver	IIS10610 PL	1SYK100001A1101 20/400


	Switch 2 way 6 A - 240 V ~ Number of modules: 2		
	white	IIS10620 BL	1SYK100001A1002 20/400
	anthracite grey	IIS10620 AN	1SYK100001A1202 20/400
	silver	IIS10620 PL	1SYK100001A1102 20/400


	Switch 1 way 16 A - 240 V ~ Number of modules: 1		
	white	IIS11610 BL	1SYK100001A1006 20/400
	anthracite grey	IIS11610 AN	1SYK100001A1206 20/400
	silver	IIS11610 PL	1SYK100001A1106 20/400


	Switch 1 way with indicator 16 A - 240 V ~ Number of modules: 1		
	white	IIS1161L BL	1SYK100001A1007 20/400
	anthracite grey	IIS1161L AN	1SYK100001A1207 20/400
	silver	IIS1161L PL	1SYK100001A1107 20/400

	Switch DP 32 A - 240 V ~ Number of modules: 2		
	white	IIS2321L BL	1SYK100001A1008 10/200
	anthracite grey	IIS2321L AN	1SYK100001A1208 10/200
	silver	IIS2321L PL	1SYK100001A1108 10/200

Product	Article-No.	Order-No.	Pack/Qty
	Push button with bell symbol 6A Number of modules: 1		
	white	IIS106B0 BL	1SYK100001A1003 20/400
	anthracite grey	IIS106B0 AN	1SYK100001A1203 20/400


	Push button with bell symbol 6A With indicator Number of modules: 1		
	white	IIS106BL BL	1SYK100001A1004 20/400
	anthracite grey	IIS106BL AN	1SYK100001A1204 20/400


	Mega push button with bell symbol 6A With indicator Number of modules: 2		
	white	IIS206BL BL	1SYK100001A1005 20/400
	anthracite grey	IIS206BL AN	1SYK100001A1205 20/400


	Card switch 1-gang, 1-way, DP Number of modules: 2		
	white	N2214.1 BL	2CLA221410N1102 1
	anthracite grey	N2214.1 AN	2CLA221410N1802 1
	silver	N2214.1 PL	2CLA221410N1302 1

IVIE

Socket outlets


Product	Article-No.	Order-No.	Pack/Qty
 Sockets - 240 V ~ 6A, 2+3 pin socket Number of modules: 2			
white	IHK20006 BL	1SYK100001A1021	10/200
anthracite grey	IHK20006 AN	1SYK100001A1221	10/200
silver	IHK20006 PL	1SYK100001A1121	10/200


 Sockets - 240 V ~ 6/13A universal socket Number of modules: 2			
white	IHK20613 BL	1SYK100001A1022	10/200
anthracite grey	IHK20613 AN	1SYK100001A1222	10/200
silver	IHK20613 PL	1SYK100001A1122	10/200


 Sockets - 240 V ~ 6/16A socket Number of modules: 2			
white	IHK20616 BL	1SYK100001A1023	10/200
anthracite grey	IHK20616 AN	1SYK100001A1223	10/200
silver	IHK20616 PL	1SYK100001A1123	10/200


Sockets - 240 V ~ 6/20A socket Number of modules: 2			
white	IHK20620 BL	1SYK100001A1024	10/200
anthracite grey	IHK20620 AN	1SYK100001A1224	10/200
silver	IHK20620 PL	1SYK100001A1124	10/200


Sockets - 240 V ~ 6/25A socket Number of modules: 2			
white	IHK20625 BL	1SYK100001A1025	10/200
anthracite grey	IHK20625 AN	1SYK100001A1225	10/200
silver	IHK20625 PL	1SYK100001A1125	10/200

 Sockets - 240 V ~ 6A 2 pin socket Number of modules: 1			
white	IHK10006 BL	1SYK100001A1026	20/400
anthracite grey	IHK10006 AN	1SYK100001A1226	20/400
silver	IHK10006 PL	1SYK100001A1126	20/400

Product	Article-No.	Order-No.	Pack/Qty
 Euro-American earthed socket outlet 240 V ~ Rated voltage: 125/250 Vac Rated current: 15/16A 2P+E/ NEMA 5-15R Number of modules: 2			
white	N2238 BL	2CLA223800N1102	10
anthracite grey	N2238 AN	2CLA223800N1802	10
silver	N2238 PL	2CLA223800N1302	10


 Euro-American unearthed socket outlet 240 V ~ Rated voltage: 125/250 V AC Rated current: 15/16A 2P (non-earthed)/NEMA 1-15R Number of modules: 1			
white	N2135 BL	2CLA213500N1102	20
anthracite grey	N2135 AN	2CLA213500N1802	20
silver	N2135 PL	2CLA213500N1302	20


 British standard socket outlet 240 V ~ Rated current: 13A 2 P+E Number of modules: 2			
white	N2237 BL	2CLA223700N1102	10
anthracite grey	N2237 AN	2CLA223700N1302	10
silver	N2237 PL	2CLA223700N1802	10


 Shaver Socket Number of modules: 2			
white	IIM2SVSK BL	1SYK100001A1057	5/100
anthracite grey	IIM2SVSK AN	1SYK100001A1257	5/100
silver	IIM2SVSK PL	1SYK100001A1157	5/100


IVIE

USB chargers

Product	Article-No.	Order-No.	Pack/Qty
 USB charger 750mA, 1-gang Number of modules: 1			
white	N2185 BL	2CLA218500N1102	1
anthracite grey	N2185 AN	2CLA218500N1802	1
silver	N2185 PL	2CLA218500N1302	1


 USB charger 2.000mA, 1-gang Number of modules: 1			
white	N2185.2 BL	2CLA218520N1102	1
anthracite grey	N2185.2 AN	2CLA218520N1802	1
silver	N2185.2 PL	2CLA218520N1302	1

 USB charger 1.500mA, 2-gang Number of modules: 2			
white	N2285 BL	2CLA228500N1102	1
anthracite grey	N2285 AN	2CLA228500N1802	1
silver	N2285 PL	2CLA228500N1302	1


Product	Article-No.	Order-No.	Pack/Qty
 Blank plates Number of modules: 1			
white	IIM1BLNK BL	1SYK100001A1041	20/400
anthracite grey	IIM1BLNK AN	1SYK100001A1241	20/400
silver	IIM1BLNK PL	1SYK100001A1141	20/400


IVIE


Dimmers


Product	Article-No.	Order-No.	Pack/Qty
 Dimmer & fan regulators Step fan regulator 5 step Number of modules: 2			
white	IIM2FR05 BL	1SYK100001A1042	5/100
anthracite grey	IIM2FR05 AN	1SYK100001A1242	5/100
silver	IIM2FR05 PL	1SYK100001A1142	5/100


Dimmer & fan regulators Step fan regulator 4 step Number of modules: 1			
white	IIM1FR04 BL	1SYK100001A1043	10/200
anthracite grey	IIM1FR04 AN	1SYK100001A1243	10/200
silver	IIM1FR04 PL	1SYK100001A1143	10/200

 Dimmer & fan regulators Dimmer 400 Watt Number of modules: 1			
white	IIM2D400 BL	1SYK100001A1045	10/200
anthracite grey	IIM1D400 AN	1SYK100001A1245	10/200
silver	IIM1D400 PL	1SYK100001A1145	10/200

 Universal rotatory/push dimmer Number of modules: 2 Rated voltage: 230 V AC Max. power: Incandescent: 500 W Halogen lamp with electronic transformer: 500 VA Halogen lamp with ferromagnetic transformer: 400 VA			
white	N2260.2 BL	2CLA226020N1102	1
anthracite grey	N2260.2 AN	2CLA226020N1802	1
silver	N2260.2 PL	2CLA226020N1302	1


 LED rotatory/push dimmer Number of modules: 2 Rated voltage: 230 V AC Nominal power: 250 W/VA Power (min./max load): LEDi: 2/100 W/VA (max. 10 lamps) Dimmable energy saving lamps: 2/100 W/VA (max. 10 lamps) LV LEDi with transformer (only type L or LC): 4/100 W/VA (max. 10 lamps) Incandescent lamps: 10/250 W/VA Halogen lamps: 10/250 W/VA LV halogen with transformer (only type L or LC): 10/250 W/VA (max. 10 lamps) 2 wire connection Optional: auxiliary on/off with 2-way switch N2X02			
white	N2260.3 BL	2CLA226030N1102	1
anthracite grey	N2260.3 AN	2CLA226030N1802	1
silver	N2260.3 PL	2CLA226030N1302	1


Product	Article-No.	Order-No.	Pack/Qty
 LED rotatory/push dimmer Number of modules: 2 Rated voltage: 127 V AC Frequency: 50/60 Hz (Nominal power: 140 W/VA) Power (min./max load): LEDi: 2/55 W/VA (max. 10 lamps) Dimmable energy saving lamps: 2/55 W/VA (max. 10 lamps) LV LEDi with transformer (only type L or LC): 4/55 W/VA (max. 10 lamps) Incandescent lamps: 10/140 W/VA Halogen lamps: 10/140 W/VA LV halogen with transformer (only type L or LC): 10/140 W/VA (max. 10 lamps)			
white	N2260.8 BL	2CLA226080N1102	1
anthracite grey	N2260.8 AN	2CLA226080N1802	1
silver	N2260.8 PL	2CLA226080N1302	1


 1-10V rotary dimmer Number of modules: 2 Rated voltage: 127 - 230 V AC / 50 - 60 Hz Max. power: 230 V AC: 700 VA, 127 V AC: 350 VA Max. 6 ballasts per device			
white	N2260.9 BL	2CLA226090N1102	1
anthracite grey	N2260.9 AN	2CLA226090N1802	1
silver	N2260.9 PL	2CLA226090N1302	1


IVIE


Data communication


Product	Article-No.	Order-No.	Pack/Qty
 2x RCA connection unit Number of modules: 1			
white	N2155.2 BL	2CLA215520N1102	1
anthracite grey	N2155.2 AN	2CLA215520N1802	1
silver	N2155.2 PL	2CLA215520N1302	1


 3x RCA connection unit Number of modules: 1			
white	N2155.3 BL	2CLA215530N1102	1
anthracite grey	N2155.3 AN	2CLA215530N1802	1
silver	N2155.3 PL	2CLA215530N1302	1


 Mini-Jack connection unit Number of modules: 1			
white	N2155.4 BL	2CLA215540N1102	1
anthracite grey	N2155.4 AN	2CLA215540N1802	1
silver	N2155.4 PL	2CLA215540N1302	1

 VGA connection unit Number of modules: 1			
white	N2155.5 BL	2CLA215550N1102	1
anthracite grey	N2155.5 AN	2CLA215550N1802	1
silver	N2155.5 PL	2CLA215550N1302	1

Product	Article-No.	Order-No.	Pack/Qty
 HDMI connection unit Number of modules: 1			
white	N2155.6 BL	2CLA215560N1102	1
anthracite grey	N2155.6 AN	2CLA215560N1802	1
silver	N2155.6 PL	2CLA215560N1302	1



 HDMI female-female connection unit Number of modules: 1			
white	N2155.7 BL	2CLA215570N1102	1
anthracite grey	N2155.7 AN	2CLA215570N1802	1
silver	N2155.7 PL	2CLA215570N1302	1

 USB connection unit Number of modules: 1			
white	N2155.8 BL	2CLA215580N1102	1
anthracite grey	N2155.8 AN	2CLA215580N1802	1
silver	N2155.8 PL	2CLA215580N1302	1

 USB female-female connection unit Number of modules: 1			
white	N2155.9 BL	2CLA215590N1102	1
anthracite grey	N2155.9 AN	2CLA215590N1802	1
silver	N2155.9 PL	2CLA215590N1302	1



IVIE

Data communication


Product	Article-No.	Order-No.	Pack/Qty
 Data & Voice RJ11 Tel. jack 2 pin Number of modules: 1			
white	IIM1RJ11 BL	1SYK100001A1047	20/400
anthracite grey	IIM1RJ11 AN	1SYK100001A1247	20/400
silver	IIM1RJ11 PL	1SYK100001A1147	20/400
Data & Voice RJ45 Jack cat 6 Number of modules: 1			
white	IIM1RJ45 BL	1SYK100001A1048	20/400
anthracite grey	IIM1RJ45 AN	1SYK100001A1248	20/400
silver	IIM1RJ45 PL	1SYK100001A1148	20/400
 TV Socket TV co-axial socket Number of modules: 1			
white	IIM1TVSK BL	1SYK100001A1049	20/400
anthracite grey	IIM1TVSK AN	1SYK100001A1249	20/400
silver	IIM1TVSK PL	1SYK100001A1149	20/400

IVIE

Room thermostats


Product	Article-No.	Order-No.	Pack/Qty
 Digital room thermostat Number of modules: 2 Maximum load: 3A cos = 0,5 Output relay operation modes: Hysteresis: 0.5° C Pulse-width modulation: with a ±4°C difference with the set-point temperature Variable from 100% to 0% modulation To be installed with N2240.5 cover plates			
white	8140.5	2CLA814050A1002	1
 Cover plate for digital thermostat Number of modules: 2			
white	N2240.5 BL	2CLA224050N1102	1
anthracite grey	N2240.5 AN	2CLA224050N1802	1
silver	N2240.5 PL	2CLA224050N1302	1

Multimedia





Product	Article-No.	Order-No.	Pack/Qty
 Multiroom sound module Number of modules: 1			
white	9368.1	2CLA936810A1001	1
 Remote control for multiroom sound module Number of modules: 2			
white	9368.2	2CLA936820A1001	1
 Cover plate for radio/remote control modules			
white	N2268 BL	2CLA226800N1102	1
 FM-radio and alarm module Number of modules: 2			
white	9368- FM	2CLA936800A1001	1
 Cover plate for radio/remote control modules			
white	N2268 BL	2CLA226800N1102	1
 Auxiliary module Number of modules: 2			
white	9368.3	2CLA936830A1001	1
 Cover plate for I/O + USB + Bluetooth module			
white	N2268.3 BL	2CLA226830N1102	1
 Speaker connection unit Number of modules: 2			
white	N2257.1 BL	2CLA225710N1102	1

IVIE

Movement detectors







Product	Article-No.	Order-No.	Pack/Qty
 <p>110° motion sensor Number of modules: 2 Max. power: - Incandescent: 1.800W @230V AC/1.000W @127V AC - Halogen with electronic or ferromagnetic transformer: 750VA @230V AC/400VA @127V AC - Fluorescent lamps or motors: 400VA @230V AC/200VA @127V AC For automatic switching of devices dependent on motion and brightness With integrated selector switch for automatic ON-OFF in the front side Switch-off delay: 10 sec. to 10 min. or short-time pulse 1 sec adjustable (from the front side) Detection range: 5 m radius Adjustable light set point level for activation (from the front side) Detection angle: 110° Mounting height: 1, 2 m auxiliary control with N2X04.X push-buttons</p>	white	N2241 BL	2CLA224100N1102 1
	anthracite grey	N2241 AN	2CLA224100N1802 1
	silver	N2241 PL	2CLA224100N1302 1





Buzzer / Door bell

Product	Article-No.	Order-No.	Pack/Qty
 <p>Buzzer & door bell Buzzer Number of modules: 2</p>	white	IIM2BUZR BL	1SYK100001A1054 5/100
	anthracite grey	IIM2BUZR AN	1SYK100001A1254 5/100
	silver	IIM2BUZR PL	1SYK100001A1154 5/100
 <p>Buzzer Number of modules: 1</p>	white	N2119 BL	2CLA211900N1102 1
	anthracite grey	N2119 AN	2CLA211900N1802 1
	silver	N2119 PL	2CLA211900N1302 1
 <p>Buzzer Number of modules: 2</p>	white	N2219 BL	2CLA221900N1102 1
	anthracite grey	N2219 AN	2CLA221900N1802 1
	silver	N2219 PL	2CLA221900N1302 1
 <p>Electronic door bell 230 V AC Number of modules: 2</p>	white	N2224 BL	2CLA222400N1102 1
	anthracite grey	N2224 AN	2CLA222400N1802 1
	silver	N2224 PL	2CLA222400N1302 1

IVIE



Signaling and lighting systems

Product	Article-No.	Order-No.	Pack/Qty
 Indicator Number of modules: 1			
white	IIM1INDI BL	1SYK100001A1053	20/400
anthracite grey	IIM1INDI AN	1SYK100001A1253	20/400
silver	IIM1INDI PL	1SYK100001A1153	20/400
 LED white signaling light Number of modules: 1 Lamp: white LED Luminous flux: > 2 lumen at 1 meter, white diffuser			
white	N2180 BL	2CLA218000N1102	5
 LED red signaling light Number of modules: 1 Lamp: white LED Luminous flux: > 2 lumen at 1 meter, Red diffuser			
white	N2180 RJ	2CLA218000N1602	1
 LED green signaling light Number of modules: 1 Lamp: white LED Luminous flux: > 2 lumen at 1 meter, Green diffuser			
white	N2180 VD	2CLA218000N1802	1
 LED signaling light Number of modules: 2 Lamp: white LED Luminous flux: > 2 lumen at 1 meter, White diffuser			
white	N2280 BL	2CLA228000N1102	1
 Beacon LED light Number of modules: 2 Lamp: white LED Luminous flux: > 2 lumen at 1 meter, white diffuser Autonomy: 3 hours (1 hour at maximum illumination 2 hours with lower illumination) Battery: Ni-MH (estimated lifetime: 4 years)			
white	N2281 BL	2CLA228100N1102	1

Product	Article-No.	Order-No.	Pack/Qty
 DND & MMR DND and MMR set internal & external Number of modules: 2+3			
white	IIM1DNDS BL	1SYK100001A1055	5/100
anthracite grey	IIM1DNDS AN	1SYK100001A1255	5/100
silver	IIM1DNDS PL	1SYK100001A1155	5/100
 DND/MUR 2-gang interlocked switch Number of modules: 1			
white	N2244.5 BL	2CLA224450N1102	1
anthracite grey	N2244.5 AN	2CLA224450N1802	1
silver	N2244.5 PL	2CLA224450N1302	1
 LED MUR signaling light Number of modules: 2			
white	N2180.5 BL	2CLA218050N1102	1
anthracite grey	N2180.5 AN	2CLA218050N1802	1
silver	N2180.5 PL	2CLA218050N1302	1
 LED DND signaling light Number of modules: 1			
white	N2180.4 BL	2CLA218040N1102	1
anthracite grey	N2180.4 AN	2CLA218040N1802	1
silver	N2180.4 PL	2CLA218040N1302	1


IVIE


Other products


Product	Article-No.	Order-No.	Pack/Qty
	Starters Single Phase Starter 20A Number of modules: 2		
	white	IIM2ST20 BL	1SYK100001A1051 5/100
	Starters Single Phase Starter 25A Number of modules: 2		
	white	IIM2ST25 BL	1SYK100001A1052 5/100
	Down lighter Number of modules: 3		
	white	IIM3DOWN BL	1SYK100001A1059 5/100
	anthracite grey	IIM3DOWN AN	1SYK100001A1259 5/100
	silver	IIM3DOWN PL	1SYK100001A1159 5/100

IVIE

Cover frames

Product	Article-No.	Order-No.	Pack/Qty
 Plate with frame 1M plate Number of modules: 1			
white	IIP0133 BL	1SYK100001A1071	15/360
anthracite grey	IIP0133 AN	1SYK100001A1271	15/360
silver	IIP0133 PL	1SYK100001A1171	15/360

 Plate with frame 2M plate Number of modules: 2			
white	IIP0233 BL	1SYK100001A1072	15/360
anthracite grey	IIP0233 AN	1SYK100001A1272	15/360
silver	IIP0233 PL	1SYK100001A1172	15/360

 Plate with frame 3M plate power Number of modules: 3			
white	IIPP343 BL	1SYK100001A1073	10/240
anthracite grey	IIPP343 AN	1SYK100001A1273	10/240
silver	IIPP343 PL	1SYK100001A1173	10/240


 Plate with frame 3M plate Number of modules: 3			
white	IIP0343 BL	1SYK100001A1074	10/240
anthracite grey	IIP0343 AN	1SYK100001A1274	10/240
silver	IIP0343 PL	1SYK100001A1174	10/240

Plate with frame 4M plate Number of modules: 4			
white	IIP0453 BL	1SYK100001A1075	10/190
anthracite grey	IIP0453 AN	1SYK100001A1275	10/190
silver	IIP0453 PL	1SYK100001A1175	10/190

Plate with frame 6M plate Number of modules: 6			
white	IIP0683 BL	1SYK100001A1076	5/120
anthracite grey	IIP0683 AN	1SYK100001A1276	5/120
silver	IIP0683 PL	1SYK100001A1176	5/120


 Plate with frame 8M plate Number of modules: 8			
white	IIP0893 BL	1SYK100001A1077	5/120
anthracite grey	IIP0893 AN	1SYK100001A1277	5/120
silver	IIP0893 PL	1SYK100001A1177	5/120

Plate with frame 8M plate square Number of modules: 8			
white	IIP0855 BL	1SYK100001A1078	5/95
anthracite grey	IIP0855 AN	1SYK100001A1278	5/95
silver	IIP0855 PL	1SYK100001A1178	5/95







 Plate with frame 12M plate Number of modules: 12			
white	IIP1286 BL	1SYK100001A1079	5/95
anthracite grey	IIP1286 AN	1SYK100001A1279	5/95
silver	IIP1286 PL	1SYK100001A1179	5/95

Plate with frame 18M plate Number of modules: 18			
white	IIP1888 BL	1SYK100001A1080	5/40
anthracite grey	IIP1888 AN	1SYK100001A1280	5/40
silver	IIP1888 PL	1SYK100001A1180	5/40

IVIE

Installation boxes

Product	Article-No.	Order-No.	Pack/Qty
	Flush boxes 1-2 M Metal Box Number of modules: 1/2		
	IAB0233W	1SYK100001A1441	24
	Flush boxes 3 M Metal Box Number of modules: 3		
	IAB0343W	1SYK100001A1442	18
	Flush boxes 4 M Metal Box Number of modules: 4		
	IAB0453W	1SYK100001A1443	18
	Flush boxes 6 M Metal Box Number of modules: 6		
	IAB0683W	1SYK100001A1444	12

Product	Article-No.	Order-No.	Pack/Qty
	Flush boxes 8 M Metal Box Number of modules: 8		
	IAB0893W	1SYK100001A1445	12
	Flush boxes 8 M Metal Box Square Number of modules: 8		
	IAB0855W	1SYK100001A1446	7
	Flush boxes 12M Metal Box Number of modules: 12		
	IAB1286W	1SYK100001A1447	5
	Flush boxes 18 M Metal Box Number of modules: 18		
	IAB1888W	1SYK100001A1448	5

Automation boards – SR1 enclosures

Painted steel enclosures for automation applications

The range of SR1 enclosures provides a complete offer of monobloc enclosures for small and medium-size automation, command and distribution applications. They are available with blind door in 22 different sizes and with a maximum height of 1000 mm.

- 01 SR1 enclosure
- 02 120° opening door angle and stable door hinge
- 03 Ample cable entry flange and solid galvanized mounting plate

The SR1 is part of the System pro E control series of automation boards, which also includes large free-standing floor-mounted enclosures IS2 and SR2.

Construction characteristics

The construction characteristics of the series guarantee practical installation and versatility, as well as highly technical features, such as the IP65 degree of protection. The enclosure structure is fitted with one ample cable entry flange (top or bottom side) and with a reversible door. The SR1 is delivered with an internal galvanized mounting plate and has common accessories with the SR2 range.

Range

The range is available with blind door in 22 different sizes with a maximum height of 1000 mm and maximum width of 800mm. The enclosures can be installed on the wall using special brackets or on the floor.

All of the products in the range conform to the international standards in force in particular with IEC 62208. All data needed to comply with the IEC 61439-1-2 are provided.

Technical characteristics


Description	Value
Standards	IEC 62208 - IEC61439-1-2
Degree of protection	IP65
Degree of mechanical strength	IK10
Type of material	Metal
Installation site	Indoor/Outdoor
Fixing method	Floor/wall
Paint	Epoxy poliester
Environmental temperature limits	Operating -5° +40° Storage -25° +55°
Rated service voltage Un	1000Vac - 1500Vdc
Rated frequency	50 - 60 Hz
Door opening angle	120° reversible



Automation boards – SR1 enclosures

Ordering codes: the enclosures

Rapid selection table




The enclosures are already fitted with the internal galvanized mounting plate.

Overall dimensions			Static Load (kg)		Global ID ABB	Customer code
H (mm)	W (mm)	D (mm)	Mounting plate	Door		
250	200	150	15	5	1SZR000001A0001	SRY2215K
300	200	150	25	10	1SZR000001A0002	SRY3215K
300	250	150	25	10	1SZR000001A0003	SRY32515K
300	300	150	25	10	1SZR000001A0004	SRY3315K
300	400	200	25	10	1SZR000001A0005	SRY3420K
400	300	150	35	10	1SZR000001A0006	SRY4315K
400	300	200	35	10	1SZR000001A0007	SRY4320K
400	400	200	35	10	1SZR000001A0008	SRY4420K
500	300	200	35	15	1SZR000001A0009	SRY5320K
500	400	150	35	15	1SZR000001A0010	SRY5415K
500	400	200	35	15	1SZR000001A0011	SRY5420K
500	400	250	35	15	1SZR000001A0012	SRY5425K
500	500	200	35	15	1SZR000001A0013	SRY5520K
600	400	200	50	20	1SZR000001A0014	SRY6420K
600	400	250	50	20	1SZR000001A0015	SRY6425K
600	600	250	50	20	1SZR000001A0016	SRY6625K
700	500	200	50	20	1SZR000001A0017	SRY7520K
700	500	250	50	20	1SZR000001A0018	SRY7525K
800	600	250	50	20	1SZR000001A0019	SRY8625K
800	600	300	50	20	1SZR000001A0020	SRY8630K
800	800	300	50	20	1SZR000001A0021	SRY8830K
1000	800	300	80	25	1SZR000001A0022	SRY10830K

Automation boards – SR1 enclosures

Ordering codes: the accessories




Inner doors

The inner doors guarantees degree of protection of IP20. Made of galvanized and painted steel, color RAL 7035 orange peel, complete with the EV1008 handle with double bit lock.

Blind Counterdoor


Dimensions mm			Package/ No. of pieces
H	W	Code	
500	400	KC504OK	1/1
600	400	KC604OK	1/1
700	500	KC705OK	1/1
800	600	KC806OK	1/1
1000	600	KC106OK	1/1
1000	800	KC108OK	1/1



Spacer kit for adjusting the depth of the back plates

Kit consisting of 12 spacers for fixing the back plate with the possibility of adjusting the depth with 25 mm pitch.


Description	Code	
Spacers 25 mm long	AA8025	1/12
Spacers 50 mm long	AA8050	1/12



Brackets for wall fixing


These brackets allow the wall installation of the enclosures and are mounted by using the special holes provided on the enclosures.

Description	Code	
Brackets for wall fixing	AA1201	1/4



Accessories for stacking

IP65 gasket			
Dimensions (mm)			Package/ No. of pieces
W	D	Code	
400	200	GZ4020	1/1
	250	GZ4025	1/1
600	200	GZ6020	1/1
	250	GZ6025	1/1
	300	GZ6030	1/1
800	300	GZ8030	1/1




Plinth

Steel plinth 25/10 thick grey RAL 7012 color.

Plinth				
Dimensions mm				Package/ No. of pieces
W	D	H	Code	
400	200	100	ZA4020	
	250	100	ZA4025	
600	250	100	ZA6025	
	300	100	ZA6030	
800	300	100	ZA8030	

Automation boards – SR1 enclosures


Ordering codes: the accessories



Frame for DIN rail

Internal supports for fixing modular panels and DIN rails, color RAL 7035 orange peel.

Description	Dimensions mm		Code	Package/ No. of pieces
	H	W		
Supports 14 mod. DIN x 2 rows	500	400	KD5040K	1/1
Supports 14 mod. DIN x 3 rows	600	400	KD6040K	1/1
Supports 25 mod. DIN x 4 rows	800	600	KD8060K	1/1
Supports 25 mod. DIN x 5 rows	1000	600	KD1060K	1/1
Supports 36 mod. DIN x 5 rows	1000	800	KD1080K	1/1



Modular panels

Modular panels made of sheet steel painted RAL 7035 color orange peel. The modular hinged panels can be mounted on the enclosures by using the special kit (KD...) consisting of functional uprights and a compensation panel. The hinges patented by ABB allow automatic earthing for panel contact when it is closed and are also prepared for conventional earthing (with a cable). Each modular panel (PM) has a DIN rail provided (depth-adjustable), the fixing brackets and the relative small items. Modular and circuit breakers and Tmax moulded-case circuit breakers up to T3/XT3 can be placed side by side on the same DIN rail using the special depth adapter AP 6001. To install moulded-case circuit breakers, it is necessary to fix the DIN rail in a position towards the back. The fixing brackets of the DIN rail allow the wiring duct to be mounted up to a maximum size of 60 x 60 mm.

Modular hinged panels for modular apparatus (DIN rail and fixing brackets included)


Description	Dimensions mm		Code	Package/ No. of pieces
	H	W		
14 mod. DIN + fixing brackets	185	400	PM1414K	1/1
25 mod. DIN + fixing brackets	185	600	PM1625K	1/1
36 mod. DIN + fixing brackets	185	800	PM1836K	1/1

Modular hinged panels for measuring instruments

Description	Dimensions mm		Code	Package/ No. of pieces
	H	W		
2 instruments 72 x 72 mm	185	400	PS2476K	1/1
2 instruments 72 x 72 mm	185	600	PS2676K	1/1
2 instruments 72 x 72 mm	185	800	PS2876K	1/1

Modular hinged blind panels

Description	Dimensions mm		Code	Package/ No. of pieces
	H	W		
Blind panel	185	400	PC1406K	1/1
Blind panel	185	600	PC1606K	1/1
Blind panel	185	800	PC1806K	1/1
Blind panel	370	600	PC2606K	1/1
Blind panel	370	800	PC2806K	1/1




DIN rail and fixing brackets

Description	No. modules	W (mm)	Code	Package/ No. of pieces
DIN rail and fixing brackets	14	400	GD4006	1/1
DIN rail and fixing brackets	25	600	GD6006	1/1
DIN rail and fixing brackets	36	800	GD8006	1/1
Depth adapter				
No.1 depth adapter for Tmax T1-T2-T3-XT1-XT3 W=600mm			AP6001	1/4

Polished flange for DIN rail mounting

Description	Code	Package/ No. of pieces
Polished flange for XT1 3P mounted on DIN rail	AD3301	1/1
Polished flange for XT1 4P mounted on DIN rail	AD3302	1/1
Polished flange for XT3 3P mounted on DIN rail	AD3303	1/1
Polished flange for XT3 4P mounted on DIN rail	AD3304	1/1

Already supplied with the DIN rail mounting kit for breakers (in the breakers' catalogue)




Neutral or earthing busbars

The busbars made of electrolytic copper with M6 threaded holes with 25 mm pitch, can be mounted on the back plates by means of the special supports. They must be sized according to the enclosure and the position they are installed in.

Description	W (mm)	Code	Package/ No. of pieces
No. 4 busbars sect. 20 x 5 mm	1000	AA8010	1/4
No. 5 support for busbar		AA8011	1/5

Automation boards – SR1 enclosures


Ordering codes: the accessories



Spray protection roof

To improve protection against entry of liquids and rain. Made of sheet steel, painted RAL 7035 color orange peel.


Spray protection roof			
Dimensions mm			Package/ No. of pieces
W	D	Code	
200	150	TT2015K	1/1
300	150	TT3015K	1/1
400	150	TT4015K	1/1
300	200	TT3020K	1/1
400	200	TT4020K	1/1
500	200	TT5020K	1/1
400	250	TT4025K	1/1
500	250	TT5025K	1/1
600	250	TT6025K	1/1
600	300	TT6030K	1/1
800	300	TT8030K	1/1




Shaped profiles for accessories

These allow the fixing of some accessories (e.g.: wiring ducts) inside the blind doors. They consist of a pair of vertical profiles made of 15/10 mm thick white galvanised sheet, pre-drilled with 25 mm pitch.

Description	Dimensions H	Code	Package/ No. of pieces
No. 2 shaped profiles for door	600	TS6009	1/1
No. 2 shaped profiles for door	700	TS7009	1/1
No. 2 shaped profiles for door	800	TS8009	1/1
No. 2 shaped profiles for door	1000	1SLM400000A9000	1/1



AA8002



AA8003




EV1008

Locking systems

These can replace the standard closures of the external doors. The inserts are interchangeable and easily replaced by loosening a single nut.


Description	Temporary codes	Package/ No. of pieces
Box Ø19 mm with security insert and Yale type key	AA8002	1/1
Box Ø19 mm with Yale type key	AA8003	1/1
Box Ø19 mm with triangular insert	AA5200	1/1
Ergonomic box complete with double bit lock (without tongue)	EV1008	1/1
Ronis 455 insert	EV1037	1/1



Document pocket RAL7035

Made of plastic RAL 7035 color, A4 size. The pocket can be glued inside the blind door with a width of more than 400 mm, using the adhesives provided.


Description	Code	Package/ No. of pieces
Plastic document pocket for A4	EV1075K	1/1



Accessories for DIN panel

Hole covering strip RAL 7035 color.


Description	Dimensions mm W	Code	Package/ No. of pieces
No. 10 hole covers, grey	2000	AD1086	1/10
No. 3 hole covers, 24 DIN modules	600	AD1088	1/3
No. 3 hole covers, 36 DIN modules	800	AD1089	1/3



Adhesive label holders.

Description	Dimensions mm W	Code	Package/ No. of pieces
No. 20 label holders 18 DIN mod.	325	EH2118	1/20
No. 20 label holders 29 DIN mod.	525	EH2129	1/20
No. 20 label holders 24 DIN mod.	432	AD1600	1/20
No. 20 label holders 36 DIN mod.	534	AD1800	1/20

AD1101-AD1102
AD1103-AD1104




EH2118-EH2129
AD1600-AD1800

Labels for label holder.

Description	No. of DIN mod.	Code	Package/ No. of pieces
No. 288 labels 1 DIN mod.	1	AD1101	1/288
No. 192 labels 2 DIN mod.	2	AD1102	1/192
No. 96 labels 3 DIN mod.	3	AD1103	1/96
No. 96 labels 4 DIN mod.	4	AD1104	1/96



Hinges and rapid closures for panels

Description	Code	Package/ No. of pieces
No. 10 hinges for panels	EH1889	1/10
No. 5 rapid closures for front panels	EH1890	1/5





Automation boards – SR1 enclosures

Overall dimensions




Customer code	A	B	C	D	E	F*	G	H	I	L	R	S
SRY2215K	260	210	150	88	138	130	172	296	246	222	120	44
SRY3215K	310	210	150	88	138	155	172	346	246	272	120	44
SRY32515K	310	260	150	88	138	155	222	346	296	272	170	44
SRY3315K	310	310	150	88	138	155	272	346	346	272	220	44
SRY3420K	310	410	200	138	188	155	372	346	446	272	320	94
SRY4315K	410	310	150	88	138	205	272	446	346	372	220	44
SRY4320K	410	310	200	138	188	205	272	446	346	372	220	94
SRY4420K	410	410	200	138	188	205	372	446	446	372	320	94
SRY5320K	510	310	200	138	188	255	272	546	346	472	220	94
SRY5415K	510	410	150	88	138	255	372	546	446	472	320	44
SRY5420K	510	410	200	138	188	255	372	546	446	472	320	94
SRY5425K	510	410	250	188	238	255	372	546	446	472	320	144
SRY5520K	510	510	200	138	188	225	472	546	546	472	420	94
SRY6420K	610	410	200	138	188	105	372	646	446	572	320	94
SRY6425K	610	410	250	188	238	105	372	646	446	572	320	144
SRY6625K	610	610	250	188	238	105	572	646	646	572	520	144
SRY7520K	710	510	200	138	188	105	472	746	546	672	420	94
SRY7525K	710	510	250	188	238	105	472	746	546	672	420	144
SRY8625K	810	610	250	188	238	145	572	846	646	772	520	144
SRY8630K	810	610	300	238	288	145	572	846	646	772	520	194
SRY8830K	810	810	300	238	288	145	772	846	846	772	720	194
SRY10830K	1010	810	300	238	288	145	772	1046	846	972	720	194

Modular panels and internal counter door



Fairlead flange



(*) Locks (F)

n. 1 central for enclosures with A from 303 to 510 mm
 n. 2 for enclosures with A from 603 to 703 mm (F = 105 mm)
 n. 2 for enclosures with A from 803 to 1003 (F = 145 mm)

() Copper plated stud on rear**


Only for enclosures with A = 1003 mm

(*) M6 Copper plated stud on door**

n. 1 for enclosures with A from 303 to 503 mm
 n. 4 for enclosures with A from 603 to 803 mm
 n. 6 for enclosures with A = 1003 mm

(**) Flange mounting holes**

n. 4 for enclosures with B = 203 mm
 n. 6 for enclosures with B from 303 to 403 mm
 n. 8 for enclosures with B from 503 to 1003 mm



Inner doors

Code	M	N
KC5040K*	456	360
KC6040K*	556	360
KC7050K*	656	460
KC8060K	756	560
KC1060K	956	560
KC1080K	956	760

* These inner doors have only one hole in the center-right for the lock installation.

Internal plates

For the enclosure code	P	P1	O	O1
SRY2215K	207	182	154	132
SRY3215K	257	232	154	132
SRY32515K	257	232	204	182
SRY3315K	257	232	254	232
SRY3420K	257	232	354	332
SRY4315K	257	232	354	332
SRY4320K	257	232	354	332
SRY4420K	357	332	354	332
SRY5320K	457	432	254	232
SRY5415K	457	432	354	332
SRY5420K	457	432	354	332
SRY5425K	457	432	354	332
SRY5520K	457	432	545	432
SRY6420K	573	532	370	332
SRY6425K	573	532	370	332
SRY6625K	573	532	570	532
SRY7520K	673	632	470	432
SRY7525K	673	632	470	432
SRY8625K	773	732	570	532
SRY8630K	773	732	570	532
SRY8830K	773	732	770	732
SRY10830K	973	932	770	732

** Only for enclosures with A = 1003 mm

All measurements are in mm.



—

new.abb.com/low-voltage