

LEGACY		RGME/RGWM						
Tranquell	RGMESP/RGWMSP	Voltage	Enclosure	Disconnect	Type	kA	Data Sheet	IOM Reference
TME120S065WM	RGMESP120S08T2	120/240 Split	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME120S080WM	RGMESP120S08T2	120/240 Split	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME120S100WM	RGMESP120S10T2	120/240 Split	Nema 4	No Disconnect	Type 2	100	9AKK108472A3745	9AKK108472A3746
TME120Y065WM	RGMESP120Y08T2	120Y/208	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME120Y080WM	RGMESP120Y08T2	120Y/208	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME120Y100WM	RGMESP120Y10T2	120Y/208	Nema 4	No Disconnect	Type 2	100	9AKK108472A3745	9AKK108472A3746
TME220Y065WM	RGMESP220Y08T2	220Y/380	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME220Y080WM	RGMESP220Y08T2	220Y/380	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME220Y100WM	RGMESP220Y10T2	220Y/380	Nema 4	No Disconnect	Type 2	100	9AKK108472A3745	9AKK108472A3746
TME240D065WM	RGMESP240D08T2	240 Delta	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME240D100WM	RGMESP240D10T2	240 Delta	Nema 4	No Disconnect	Type 2	100	9AKK108472A3745	9AKK108472A3746
TME240H065WM	RGMESP240H08T2	120/240 Delta HL	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME240H080WM	RGMESP240H08T2	120/240 Delta HL	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME240H100WM	RGMESP240H10T2	120/240 Delta HL	Nema 4	No Disconnect	Type 2	100	9AKK108472A3745	9AKK108472A3746
TME240Y065WM	RGMESP240Y08T2	240Y/415	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME240Y080WM	RGMESP240Y08T2	240Y/415	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME240Y100WM	RGMESP240Y10T2	240Y/415	Nema 4	No Disconnect	Type 2	100	9AKK108472A3745	9AKK108472A3746
TME277Y065WM	RGMESP277Y08T2	277Y/480	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME277Y080WM	RGMESP277Y08T2	277Y/480	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME277Y100WM	RGMESP277Y10T2	277Y/480	Nema 4	No Disconnect	Type 2	100	9AKK108472A3745	9AKK108472A3746
TME480D065WM	RGMESP480D08T2	480 Delta	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME480D080WM	RGMESP480D08T2	480 Delta	Nema 4	No Disconnect	Type 2	80	9AKK108472A3745	9AKK108472A3746
TME480D100WM	RGMESP480D10T2	480 Delta	Nema 4	No Disconnect	Type 2	100	9AKK108472A3745	9AKK108472A3746
TPME120S06WMN1T1	RGWMSP120S08T11D	120/240 Split	Nema 1	Disconnect	Type 1	80	9AKK108472A3743	9AKK108472A3747
TPME120S08WMN1T1	RGWMSP120S08T11D	120/240 Split	Nema 1	Disconnect	Type 1	80	9AKK108472A3743	9AKK108472A3747
TPME120S06WMN4ST1	RGWMSP120S08T14D	120/240 Split	Nema 4x	Disconnect	Type 1	80	9AKK108472A3743	9AKK108472A3747
TPME120S08WMN4ST1	RGWMSP120S08T14D	120/240 Split	Nema 4x	Disconnect	Type 1	80	9AKK108472A3743	9AKK108472A3747
TPME120S08WMN4T1	RGWMSP120S08T14D	120/240 Split	Nema 4x	Disconnect	Type 1	80	9AKK108472A3743	9AKK108472A3747
TPME120S08WMN4XT1	RGWMSP120S08T14D	120/240 Split	Nema 4x	Disconnect	Type 1	80	9AKK108472A3743	9AKK108472A3747
TPME120S06WMN4XT1	RGWMSP120S08T1XD	120/240 Split	Nema 4x	Disconnect	Type 1	80	9AKK108472A3743	9AKK108472A3747
TPME120S06WMN1	RGWMSP120S08T21D	120/240 Split	Nema 1	Disconnect	Type 2	80	9AKK108472A3743	9AKK108472A3747
TPME120S08WMN1	RGWMSP120S08T21D	120/240 Split	Nema 1	Disconnect	Type 2	80	9AKK108472A3743	9AKK108472A3747
TPME120S06WMN4	RGWMSP120S08T24D	120/240 Split	Nema 4x	Disconnect	Type 2	80	9AKK108472A3743	9AKK108472A3747
TPME120S06WMN4S	RGWMSP120S08T24D	120/240 Split	Nema 4x	Disconnect	Type 2	80	9AKK108472A3743	9AKK108472A3747
TPME120S08WMN4S	RGWMSP120S08T24D	120/240 Split	Nema 4x	Disconnect	Type 2	80	9AKK108472A3743	9AKK108472A3747
TPME120S06WMN4X	RGWMSP120S08T2XD	120/240 Split	Nema 4x	Disconnect	Type 2	80	9AKK108472A3743	9AKK108472A3747
TPME120S08WMN4	RGWMSP120S08T2XD	120/240 Split	Nema 4x	Disconnect	Type 2	80	9AKK108472A3743	9AKK108472A3747
TPME120S08WMN4X	RGWMSP120S08T2XD	120/240 Split	Nema 4x	Disconnect	Type 2	80	9AKK108472A3743	9AKK108472A3747
TPHE120S12WMN1T1	RGWMSP120S15T11D	120/240 Split	Nema 1	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPHE120S15WMN1T1	RGWMSP120S15T11D	120/240 Split	Nema 1	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPHE120S12WMN4ST1	RGWMSP120S15T14D	120/240 Split	Nema 4x	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPHE120S15WMN4ST1	RGWMSP120S15T14D	120/240 Split	Nema 4x	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPHE120S15WMN4T1	RGWMSP120S15T14D	120/240 Split	Nema 4x	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPHE120S15WMN4XT1	RGWMSP120S15T14D	120/240 Split	Nema 4x	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPME120S10WMN4ST1	RGWMSP120S15T14D	120/240 Split	Nema 4x	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPME120S10WMN4T1	RGWMSP120S15T14D	120/240 Split	Nema 4	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPHE120S12WMN4T1	RGWMSP120S15T1XD	120/240 Split	Nema 4x	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPHE120S12WMN4XT1	RGWMSP120S15T1XD	120/240 Split	Nema 4x	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPME120S10WMN4XT1	RGWMSP120S15T1XD	120/240 Split	Nema 4x	Disconnect	Type 1	150	9AKK108472A3743	9AKK108472A3747
TPHE120S10WMN1	RGWMSP120S15T21D	120/240 Split	Nema 1	Disconnect	Type 2	150	9AKK108472A3743	9AKK108472A3747

Tranquell	RGMESP/RGWMSP	Voltage	Enclosure	Disconnect	Type	kA	Data Sheet	IOM Reference
TPHE480D12WMN4X	RGWMSP480D15T2XD	480 Delta	Nema 4x	Disconnect	Type 2	150	9AKK108472A3743	9AKK108472A3747
TPME480D10WMN4	RGWMSP480D15T2XD	480 Delta	Nema 4x	Disconnect	Type 2	150	9AKK108472A3743	9AKK108472A3747
TPME480D10WMN4X	RGWMSP480D15T2XD	480 Delta	Nema 4x	Disconnect	Type 2	150	9AKK108472A3743	9AKK108472A3747
TPHE480D20WMN4ST1	RGWMSP480D22T14D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D20WMN4T1	RGWMSP480D22T14D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D20WMN4XT1	RGWMSP480D22T14D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D25WMN4ST1	RGWMSP480D22T14D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D25WMN4T1	RGWMSP480D22T14D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D25WMN4XT1	RGWMSP480D22T14D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D20WMN1T1	RGWMSP480D22T24D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D20WMN4	RGWMSP480D22T24D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D20WMN4S	RGWMSP480D22T24D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D25WMN4	RGWMSP480D22T24D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D25WMN4S	RGWMSP480D22T24D	480 Delta	Nema 4	Disconnect	Type 1	225	9AKK108472A3743	9AKK108472A3747
TPHE480D20WMN4X	RGWMSP480D22T2XD	480 Delta	Nema 4x	Disconnect	Type 2	225	9AKK108472A3743	9AKK108472A3747
TPHE480D25WMN4X	RGWMSP480D22T2XD	480 Delta	Nema 4x	Disconnect	Type 2	225	9AKK108472A3743	9AKK108472A3747
TPHE480D25WMN1T1	RGWMSP480D30T14D	480 Delta	Nema 4	Disconnect	Type 1	300	9AKK108472A3743	9AKK108472A3747
TPHE480D30WMN1T1	RGWMSP480D30T14D	480 Delta	Nema 4	Disconnect	Type 1	300	9AKK108472A3743	9AKK108472A3747
TPHE480D30WMN4ST1	RGWMSP480D30T14D	480 Delta	Nema 4	Disconnect	Type 1	300	9AKK108472A3743	9AKK108472A3747
TPHE480D30WMN4T1	RGWMSP480D30T14D	480 Delta	Nema 4	Disconnect	Type 1	300	9AKK108472A3743	9AKK108472A3747
TPHE480D30WMN4XT1	RGWMSP480D30T14D	480 Delta	Nema 4	Disconnect	Type 1	300	9AKK108472A3743	9AKK108472A3747
TPHE480D25WMN1	RGWMSP480D30T24D	480 Delta	Nema 4	Disconnect	Type 2	300	9AKK108472A3743	9AKK108472A3747
TPHE480D30WMN1	RGWMSP480D30T24D	480 Delta	Nema 4	Disconnect	Type 2	300	9AKK108472A3743	9AKK108472A3747
TPHE480D30WMN4	RGWMSP480D30T24D	480 Delta	Nema 4	Disconnect	Type 2	300	9AKK108472A3743	9AKK108472A3747
TPHE480D30WMN4S	RGWMSP480D30T24D	480 Delta	Nema 4	Disconnect	Type 2	300	9AKK108472A3743	9AKK108472A3747
TPHE480D30WMN4X	RGWMSP480D30T2XD	480 Delta	Nema 4x	Disconnect	Type 2	300	9AKK108472A3743	9AKK108472A3747