ABB PROPRIETARY AND CONFIDENTIAL INFORMATION

The information contained in the document has to be kept strictly confidential.
Any unauthorized use, reproduction, distribution or disclosure to third parties is strictly forbidden.
ABB reserves all rights regarding intellectual Property Rights.
Copyright 2018 ABB. All rights reserved.

SIZE	DRAWING NO.	REV	SHEET
C	M354CP6M02	1	1

REVISIONS

REV.	DESCRIPTION	DATE	APPROVED
A	CN CI23933 DH	12/03/2021	WILL L
B	ECN ECN000253823	12/01/2022	WILL L



FRONT VIEW INTERIOR



FRONT VIEW EXTERNAL



FRONT VIEW EXTERNAL



SIDE VIEW

CONFIGURATION M354CP6



WIRE RANGE TABLE:

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRANDED	SOLID	STRANDED
LINE	---	6-1/0	---	6-1/0
LOAD	---	---	---	---
NEUTRAL (LARGE HOLE)	12-8	12-1/0	10-8	10-1/0
NEUTRAL (SIDE HOLE)	14-8	14-4	12-8	12-4
POST LINE CONNECTORS SUITABLE FOR LOOP FEED	#6-350 KCMIL		#6-350 KCMIL	
EQUIP. GRND. POST	14-2/0	14-2/0	14-2/0	14-2/0

RECEPTACLES
BR54UWR

CIRCUIT PROTECTION
THQL2150

THIRD ANGLE PROJECTION

Part must conform to SI 900000 Sect. 4, Toxicity Procedure

FOR ADDITIONAL INFO REFER TO: APPLIED PRACTICES

DIMENSIONS ARE IN INCHES

UNLESS OTHERWISE SPECIFIED IN DRAWING

TOLERANCE ON:
1 PL DECIMALS ± 0.1
2 PL DECIMALS ± 0.02
3 PL DECIMALS ± 0.005
ANGLES ± 1.0
FRACTIONS ±
FINISH √

◇ CRITICAL TO QUALITY CHARACTERISTIC

SIGNATURES	DATE
MODEL	
DETAIL	
CHECKED	
ENGRG	
MFG	
QUALITY	
ISSUED	

DRAWING FILE: M354CP6M02_OD

SOLID MODEL: M132CP6M03

Midwest Electric Products

TITLE
MIDWEST SERVICE EQUIP 100 A METERED INLINE EARTH BURIAL POST 120/240V 50A RECPT 3 SPACES N3R UL LISTED

SIZE	DRAWING	REV
C	M354CP6	1

SCALE: 7:100 SHEET 1 OF 1