

PRODUCT SPECIFICATION

DLSTF3LS60

Aqualux Self-Contained IP65 DALI Test Surface

Catalogue Number **DLSTF3LS60**
 GID **7TCA091180R0375**
 Warranty **3 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Self-Contained (individual battery)**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **Aluminium/Plastic**
 Colour **White/Silver**
 Dimensions (LxWxD) **381 x 170 x 75 mm**
 Temperature Range **-25 to +30°C**
 Weight **1.7 Kg**

Nominal Voltage **220-240v AC 50Hz**
 Emergency Duration (Hours) **3 Hours**
 Battery **NiCd**
 Monitoring Equipment **DALI test**
 Lamp **1 x 3W LED**
 Light output in Emergency Operation **119 Lumens**
 Average Lifespan light source (hours) **50000 Hours**
 Light Colour/Temperature/CRI **White / 6500 / 73**
 Degree of Protection **IP 65 IK 10**

Wiring System **Maintained / non-maintained circuit**
 Type of Legend **Single Sided (Order separate)**
 Exit Sign Viewing/Recognition Distance (m) **25**
 Power Consumption **9.9 VA / 5.1 Watts**
 Nominal Current **42.5 (mA)**
 Inrush Current **18 A to 0.1 ms**

Accessories

- XEN2W** Down ISO7010 Legend for Backlit Exit Sign
- XEN3W** Left ISO7010 Legend for Backlit Exit Sign
- XEN6W** Right ISO7010 Legend for Backlit Exit Sign
- XEN5W** Up ISO7010 Legend for Backlit Exit Sign
- XLF802W** Fire Extinguisher Legend for Backlit Exit Sign
- XLF803W** Hose Reel Legend for Backlit Exit Sign
- OW/BCM** Ceiling Bracket for Vertical Mount
- OW/BWA** Wall Bracket for Angled Mount
- OW/BWM** Cantilever Bracket for End to Wall Mount
- OW/BCR** Recessing Kit
- OW/DSC** Blank double sided diffuser for Edgelite Exit Sign

- RSEN2W** Down ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN3W** Left ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN6W** Right ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN5W** Up ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN3W/RSEN6W** Left+Right ISO7010 Legend for Edgelit Exit Sign (Double Sided)



Edgelit Exit Sign
DLSTF3LS60 + RSEN5W + OW/DSC



Backlit Exit Sign
DLSTF3LS60 + XEN5W



Bulkhead
DLSTF3LS60

