








General Purpose Enclosures










ARIA - Universal polyester cabinets - Accessories


Product	Type	Order code	Pack
Locks			
With interchangeable cylinders (Supplied with 1 key)			
3mm			
	AR831008	4TBA831008C0100	1
8mm			
	AR831005	4TBA831005C0100	1
8mm			
	AR831006	4TBA831006C0100	1
11mm			
	AR831007	4TBA831007C0100	1
Other locks: please contact us.			

Product	Type	Order code	Pack
Handles			
Neutral handle (without lock)			
	AR831003	4TBA831003R0100	1
With lock and 2 keys V2432E			
	AR831004	4TBA831004R0100	1
With lock and 2 keys 1242E			
	AR831180	4TBA831180R0100	1
With lock and 2 keys 405E			
	AR831152	4TBA831152C0100	1
With lock and 2 keys 455E			
	AR831153	4TBA831153C0100	1
Handle for lock, 45 mm semi-cylindrical profile			
	AR831821	4TBA831821C0100	1
For replacing a double-bit lock or other locks for Aria 54, a mechanical adaptation of the door openings is required.			
Handle for lock with semi-cylindrical profile and locking by padlock			
	AR831822	4TBA831822C0100	1
For replacing a double-bit lock or other locks for Aria 54, a mechanical adaptation of the door openings is required.			

Product	Type	Order code	Pack
Fixing lugs⁽¹⁾			
In 304 grade stainless steel			
Set of 4 pieces			
	ARACCB03	4TBA831000C0100	1
Set of 4 polyamide pieces			
	ARACCB13	4TBA831001C0100	1
(1) not supplied as standard			


Product	Type	Order code	Pack
Hinge supports for inner door			
Set of 2 pieces, for front plate			
	AR831010	4TBA831010C0100	1
A lower door may be installed together with a closed front plate.			


Product	Type	Order code	Pack
Profile half cylinder locks			
Standard: D = 40 mm - L = 30.5 mm			
With 2 keys V2432-E			
	PS832030	4TBP832030C0100	1
Replacement keys for 832030			
	PS832741	4TBP832741R0100	2
With 2 keys 1242-E			
	PS832031	4TBP832031C0100	1
With 2 keys 455-E			
	PS832465	4TBP832465C0100	1
With 2 keys 405-E			
	PS832466	4TBP832466R0100	1
With a replacement key, 8 mm			
	PS832032	4TBP832032C0100	1
With an 8 mm triangular key			
	PS832033	4TBP832033C0100	1
With an 11 mm triangular key			
	PS832034	4TBP832034C0100	1
With 3 mm double-bit key			
	PS832029	4TBP832029C0100	1


Product	Type	Order code	Pack
Vents			
(IP44 if fitting in the double corner)			
Set of 2 ventilation grilles.			
Bore hole Ø 34.9 mm			
	AR831009	4TBA831009C0100	1
See Sect. Cabinet ventilation for additional ventilation options.			

General Purpose Enclosures


ARIA - Universal polyester cabinets - Accessories


Product	Type	Order code	Pack
Metal frame			
For ARIA 75 and 86, for temporary connection enclosures			
H x W x D = 1400 x 750 x 400 mm			
	AR891854	4TBA891854C0100	1


Product	Type	Order code	Pack
Module covers			
Sectionable by 1/2 module			
12 modules			
	ZA3P5	2CPX062385R9999	5
4 modules			
	FORSTBP500	4TBR610484C0200	500


Product	Type	Order code	Pack
Label holders			
Adhesive			
	APLB1M	4TBC851321C0100	1m


Product	Type	Order code	Pack
Pedestal mounting assembly			
For ARIA 54/64			
	AR891608	4TBA891608C0100	1
Fixing lugs in stainless steel included. Steel strips not included.			

Product	Type	Order code	Pack
Document pocket			
DIN A4 - LxH = 325x180 mm			
	AR811516	4TBC811516C0100	1
DIN A5 - LxH = 155x225 mm			
	PS832000	4TBP832000C0100	1

Product	Type	Order code	Pack
Connection busbars			
6 x 10 mm ² + 2 x 16 mm ² clip onto 12 x 2 mm rail			
Phase busbar - black			
	FORSTTL	4TBR610185C0200	4
Ground busbar - green			
	FORSTTPE	4TBR610186C0200	4
Neutral busbar - blue			
	FORSTTN	4TBR610187C0200	4

Product	Type	Order code	Pack
Slide nuts			
For perforated mounting plate			
M4			
	AR831328	4TBA831328C0100	50
M5			
	AR831329	4TBA831329C0100	50
M6			
	AR831330	4TBA831330C0100	50

Product	Type	Order code	Pack
Self-adhesive drip molding profile			
Length 415 mm for ARIA 54 and 64			
	AR831530	4TBA831530C0100	1
May also be used for ARIA 32 and 43 after cutting out.			
Length 835 mm for ARIA 108			
	AR831533	4TBA831533C0100	1
May also be used for ARIA 75 and 86 after cutting out.			

Product	Type	Order code	Pack
Hinge pins			
Length 66 mm for ARIA 32			
	AR831653	4TBA831653C0100	20
Length 100.5 mm for ARIA 43, 54 and 64			
	AR831652	4TBA831652C0100	20
Length 131.5 mm for ARIA 75, 86 and 108			
	AR831953	4TBA831953C0100	10