

Recommended stock list

Electronic timers, monitors, interface relays and power supplies



Timing relays

CT-D

1SVR 500 020 R0000	CT-MFD.12 Time relay, multifunction, 1c/o, 24-240VAC 24-48VDC
1SVR 500 020 R1100	CT-MFD.21 Time relay, multifunction, 2c/o, 12-240VAC/DC
1SVR 500 100 R0000	CT-ERD.12 Time relay, ON-delay, 1c/o, 24-240VAC 24-48VDC
1SVR 500 100 R0100	CT-ERD.22 Time relay, ON-delay, 2c/o, 24-48VDC, 24-240VAC

CT-E

1SVR 550 029 R8100	CT-MFE Time relay, multifunction, 1c/o, 0.05s-100h, 24-240VAC/DC
1SVR 550 100 R1100	CT-ERE Time relay, ON-delay, 1c/o, 0.1-10s, 110-130VAC

CT-S

1SVR 730 010 R0200	CT-MFS.21S Time relay, multifunction, 2c/o, 24-240VAC/DC
1SVR 730 100 R0300	CT-ERS.21S Time relay, ON-delay, 2c/o, 24-240VAC/DC
1SVR 730 100 R3100	CT-ERS.12S Time relay, ON-delay, 1c/o, 24-48VDC, 24-240VAC
1SVR 730 030 R3300	CT-MXS.22S Time relay, multifunction, 2c/o, 24-48VDC, 24-240VAC



Measuring and monitoring relays

Three-phase monitors

1SVR 730 824 R9300	CM-PFS.S Three-phase monitoring relay, 2c/o, L1-L2-L3=200-500VAC 50/60Hz
1SVR 730 884 R3300	CM-MPS.41S Three-phase monitoring relay, 2c/o, 0,0.1-30s, L1-L2-L3=3x300-500VAC
1SVR 750 487 R8300	CM-MPN.52S Three-phase monitoring relay, 2c/o, 0,0.1-30s, L1-L2-L3=3x350-580VAC

Single-phase current and voltage monitors

1SVR 730 830 R0500	CM-ESS.MS Voltage monitoring relay, 2c/o, B-C=3-600VRMS, 24-240VAC/DC
1SVR 730 840 R0600	CM-SRS.M1S Current monitoring relay, 2c/o, B-C=3mA-1A RMS, 24-240VAC/DC
1SVR 730 840 R0700	CM-SRS.M2S Current monitoring relay, 2c/o, B-C=0.3-15A RMS, 24-240VAC/DC

Thermistor motor protection relays

1SVR 430 720 R0300	CM-MSS Thermistor motor protection relay, 2c/o, 24-240VAC/DC
--------------------	--



Primary switch mode power supplies

CP-E

1SVR 427 030 R0000	CP-E 24/0.75 Power supply, In:100-240VAC Out: 24VDC/0.75A
1SVR 427 031 R0000	CP-E 24/1.25 Power supply, In:100-240VAC Out: 24VDC/1.25A
1SVR 427 032 R0000	CP-E 24/2.5 Power supply, In:100-240VAC Out: 24VDC/2.5A
1SVR 427 034 R0000	CP-E 24/5.0 Power supply, In:115/230VAC Out: 24VDC/5A
1SVR 427 035 R0000	CP-E 24/10.0 Power supply, In:115/230VAC Out: 24VDC/10A
1SVR 427 036 R0000	CP-E 24/20.0 Power supply, In:115/230VAC Out: 24VDC/20A

CP-D

1SVR 427 041 R0000	CP-D 24/0.42 Power supply, In: 100-240VAC Out: 24VDC/0.42A
1SVR 427 043 R0100	CP-D 24/1.3 Power supply, In: 100-240VAC Out: 24VDC/1.3A
1SVR 427 044 R0200	CP-D 24/2.5 Power supply, In: 100-240VAC Out: 24VDC/2.5A
1SVR 427 045 R0400	CP-D 24/4.2 Power supply, In: 100-240VAC Out: 24VDC/4.2A




Analog signal converters

CC-E

1SVR 011 700 R0000	CC-E/STD Signal converter, univers., V/I / V/I, 24VDC
1SVR 011 705 R2100	CC-E/STD Signal converter, univers., V/I / V/I, 110-240VAC
1SVR 010 201 R0300	CC-E I/I-2 Current / current isolator, 2 channel, loop-powered

CC-U

1SVR 040 000 R1700	CC-U/STD Universal signal converter, 24VAC 50/60Hz / 24-48VDC
1SVR 040 003 R0600	CC-U/RTD Universal signal converter, 110-240VAC 50/60Hz / 100-300VDC
1SVR 040 005 R0000	CC-U/TC Universal signal converter, 110-240VAC 50/60Hz / 100-300VDC
1SVR 040 007 R0200	CC-U/I Universal signal converter, 110-240VAC 50/60Hz / 100-300VDC
1SVR 040 009 R1400	CC-U/V Universal signal converter, 110-240VAC 50/60Hz / 100-300VDC



Interface relays and optocouplers

CR-P

1SVR 405 600 R1000	CR-P024DC1 Pluggable interface relay, 1c/o, A1-A2=24VDC, 250V/16A
1SVR 405 600 R2000	CR-P120AC1 Pluggable interface relay, 1c/o, A1-A2=120VAC, 250V/1
1SVR 405 601 R1000	CR-P024DC2 Pluggable interface relay, 2c/o, A1-A2=24VDC, 250V/8A
1SVR 405 601 R2000	CR-P120AC2 Pluggable interface relay, 2c/o, A1-A2=120VAC, 250V/8A
1SVR 405 650 R0000	CR-PLS Logical socket, for 1c/o or 2c/o CR-P relays
1SVR 405 650 R1000	CR-PSS Standard socket, for 1c/o or 2c/o CR-P relays
1SVR 405 659 R0000	CR-PH Holder for CR-P socket
1SVR 405 654 R1000	CR-P/M 62V Pluggable module, LED green, 6-24VAC/DC
1SVR 405 654 R1100	CR-P/M 92V Pluggable module, LED green, 110-230VAC/DC

CR-M

1SVR 405 613 R1100	CR-M024DC4L Pluggable interface relay, 4c/o, A1-A2=24VDC, 250V/6A, LED
1SVR 405 613 R2100	CR-M120AC4L Pluggable interface relay, 4c/o, A1-A2=120VAC, 250V/6A, LED
1SVR 405 651 R3100	CR-M4LS Logical socket, for 2c/o or 4c/o CR-M relay
1SVR 405 651 R3000	CR-M4SS Standard socket, for 2c/o or 4c/o CR-M relay
1SVR 405 659 R1000	CR-MH Holder for CR-M socket

R600

1SNA 645 064 R0100	RB121-24VDC Interface relay R600, 1c/o, A1-A2=24VDC, 250V/10mA-6A, LED
1SNA 645 007 R0100	RB121A-115VAC/DC Interface relay R600, 1c/o, A1-A2=115VAC/DC, 250V/1mA, 6A, LED

ABB Inc.

Low Voltage Products
16250 W. Glendale Drive
New Berlin, WI 53151

Technical Support & Customer Service
Phone: 888-385-1221, Option 4
Email: lvps.support@us.abb.com
Web: www.abb.us/lowvoltage

Note:

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document. We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

© Copyright 2014 ABB Inc. All rights reserved

1SXU110002L0201 March 2014

Power and productivity
for a better world™

