



EVA-DIP-32/DALI

Self-contained 4 watt, aluminium recess 32 meter led luminaire, including DALI control module, series Evago, including the pictogram PP 320/51

Product Information

| | |
|-----------------|--|
| Type | EVA-DIP-32/DALI |
| Catalog number | 4510216963 |
| Category_ | Escape route signalisation |
| GTIN | 08713812769462 |
| GID | 7TCA091180R0317 |
| Serie | Evago |
| Warranty (Year) | 5 |
| Other | Including round and square decorative covers. Including DALI communication module, conform EN62386 |



Characteristics

| | |
|---------------------------------------|-------------------------------------|
| Power supply system | Self-contained individual battery |
| Continuous operation | Yes |
| Mounting Method | Ceiling |
| Mounting form | Recess |
| Material housing | Aluminium / plastic |
| Colour housing | Aluminium |
| Material | Aluminium / polycarbonate |
| Colour | Aluminium |
| Length (mm) | 335 |
| Width (mm) | 84 |
| Height/depth (mm) | 184 |
| Maximum outer diameter (mm) | 84 |
| Built-in length (mm) | 300 |
| Built-in width (mm) | 68 |
| Built-in diameter (mm) | 68 |
| Built-in depth (mm) | 48 |
| Nominal voltage (V) | 230 |
| Voltage type | AC |
| Duration (hours) | 1 |
| Battery | NiMH |
| Monitoring equipment | Safety module for monitoring |
| With lamp | Yes |
| Lamp Type | Led |
| Lamp holder | Other |
| Lamp power (W) | 4 |
| Number of lamps | 1 |
| Average lifespan light source (hours) | 100.000 |
| Colour of light | White |
| Colour temperature (K) | 5000 |
| CRI | 80 |
| Protection class | II |
| Degree of protection (IP) | 40 |
| With remote switch connection | No |
| Wiring system | Maintained / non-maintained circuit |
| Type of indicator | Single / double-sided |
| Labelling type | Insert sheet/plate |
| Recognition distance (m) | 32 |

| | |
|---|---------|
| Circuit | Other |
| Power consumption maintained mode (W) | 6,5 |
| Apparent power consumption maintained mode (VA) | 7,1 |
| Nominal current (mA) | 31 |
| Powerfactor | > 0,9 |
| Temperature range (°C) | 5 ~ +35 |

Article Details

| | |
|-----------------|---------------------|
| Product class | Emergency luminaire |
| E-code | EC001957 |
| Discount group | 30502 |
| Harmonized code | 9405408440 |
| GLN | 8713812000008 |

Ordering information

| | |
|------------------------|--------|
| Orderable | Yes |
| Order-Unit | Pieces |
| Minimum order quantity | 1 |
| Order Increment | 1 |

Supply Information

| | |
|-----------------------------------|----------------|
| Weight (kg) | 1,398 |
| Packaging | Cardboard box |
| Packaging dimensions (LxWxH) (mm) | 400 x 250 x 88 |