



中国国家强制性产品认证证书

证书编号: 2018010304129267

委托人名称、地址

ABB France

2 rue d'Arsonval 69680 Chassieu France

生产者(制造商)名称、地址

ABB France

2 rue d'Arsonval 69680 Chassieu France

生产企业名称、地址

ABB Bulgaria E00D - Rakovski branch

BULGARIA, 4142 Village of Stryama, Region of Plovdiv, Municipality of Rakovski, Rakovski Industrial Zone, 14 Industrial Road 1, nr, 14-18

产品名称和系列、规格、型号

交流接触器

A45, A50, A63, A75; 详情见附件

产品标准和技术要求

GB/T 14048.4-2010

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求,
特发此证。

发证日期: 2020 年 08 月 07 日有效期至: 2023 年 11 月 06 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2018 年 11 月 06 日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询

经中国合格评定国家认可委员会认可 CNAS G001-P



主任:

陆楠



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2018010304129267

NAME AND ADDRESS OF THE APPLICANT

ABB France
2 rue d'Arsonval 69680 Chassieu France

NAME AND ADDRESS OF THE MANUFACTURER

ABB France
2 rue d'Arsonval 69680 Chassieu France

NAME AND ADDRESS OF THE FACTORY

ABB Bulgaria EOOD – Rakovski branch
BULGARIA, 4142 Village of Stryama, Region of Plovdiv, Municipality of Rakovski, Rakovski
Industrial Zone, 14 Industrial Road 1, nr.14-18

PRODUCT NAME, MODEL AND SPECIFICATION

AC Contactor
A45, A50, A63, A75; See the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.4-2010

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification (REFNO.CNCA-C03-02:2014).

Valid from: Aug.07,2020 **Valid until:** Nov.06,2023

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Nov.06,2018

The certificate information is available through CNCA's website: www.cnca.gov.cn

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

附 录

第 1 页 共 3 页

证书编号: 2018010304129267

纸 号: 2658602

A45, A50, A63, A75

U_{imp} : 8kV;

U_i : 1000V;

I_{th} : A45/A50: 100A, A63: 125A, A75: 125A;

A45-22/40:

AC-1: U_e/I_e : 690V/70A;

AC-3/AC-4: U_e/I_e : 220-230-240V/40A, 380-440V/37A, 415V/37A, 440V/37A, 500V/33A, 690V/25A;

A50-30:

AC-1: U_e/I_e : 690V/100A;

AC-3/AC-4: U_e/I_e : 220-230-240V/53A, 380-440V/50A, 415V/50A, 440V/45A, 500V/45A, 690V/35A;

AC-8a: U_e/I_e : 400V/63A;

A50-40:

AC-1: U_e/I_e : 690V/100A;

AC-3/AC-4: U_e/I_e : 220-230-240V/53A, 380-440V/50A, 415V/50A, 440V/45A, 500V/45A, 690V/35A;

A63-30:

AC-1: U_e/I_e : 690V/115A;

AC-3/AC-4: U_e/I_e : 220-230-240V/65A, 380-440V/65A, 415V/65A, 440V/65A, 500V/55A, 690V/43A;

AC-8a: U_e/I_e : 400V/85A;

A75-30:

AC-1: U_e/I_e : 690V/125A;

AC-3/AC-4: U_e/I_e : 220-230-240V/75A, 380-440V/75A, 415V/75A, 440V/70A, 500V/65A, 690V/46A;

AC-8a: U_e/I_e : 400V/95A;

注: 此附录与证书同时使用时有效。



主 任:

陆 楠



中国质量认证中心



中国国家强制性产品认证证书

附 录

第 2 页 共 3 页

证书编号: 2018010304129267

纸 号: 2658602

A75-22/40:

AC-1: U_e/I_e : 690V/125A;

AC-3/AC-4: U_e/I_e : 220-230-240V/75A, 380-440V/75A, 415V/75A, 440V/70A, 500V/65A, 690V/46A;

U_s : 24V 50/60Hz, 42V 50/60Hz, 110V 50Hz /110-120V 60Hz, 220-230 50Hz/230-240V 60Hz, 380-400 50Hz/400-415V 60Hz, 400-415 50Hz/415-440V 60Hz;

极数: 3P, 4P;

IP10;

配用的辅助触头: (CAL5, CA5)

I_{th} : 16A;

AC-15: U_e/I_e : 24-127V/6A, 220-240V/4A, 380-440V/3A, 500-690V/2A;

DC-13: U_e/I_e : 24V/6A, 48V/2.8A, 72V/1A, 110-125V/0.55A, 220-250V/0.3A;

CAL5-11: 1N01NC;

CA5: 4NO, 3N01NC, 2N02NC, 4NC, 1N01NC, 1N03NC

型号解释:

注: 此附录与证书同时使用时有效。



主 任:

陆 楠



中国质量认证中心



中国国家强制性产品认证证书

附 录

第 3 页 共 3 页

证书编号: 2018010304129267

纸 号: 2658602

Example 例如: A75-30-11-85				
A	75	-30	-11	-85
I	II	III	IV	V

I - Name of series 系列名称

A series A 系列

II - Size of contactor 大小

45, 50, 63, 75

III - Number of main contacts 主触头数量

22 = 2 NO- and 2 NC-contacts

30 = 3 NO- and 0 NC-contacts

40 = 4 NO- and 0 NC-contacts

IV - Number of auxiliary contacts 辅助触头数量

00 = No auxiliary pole provided.

11 = 1 NO- and 1 NC-contacts

40 = 4 NO- and 0 NC-contacts

31 = 3 NO- and 1 NC-contacts

22 = 2 NO- and 2 NC-contacts

13 = 1 NO- and 3 NC-contacts

04 = 0 NO- and 4 NC-contacts

V - Coil code 线圈代号

Control voltage 控制电压		Coil code 线圈代号
50Hz	60Hz	
24	24	81
42	42	82
110	110-120	84
220-230	230-240	80
380-400	400-415	85
400-415	415-440	86

注: 此附录与证书同时使用时有效。



主 任: 陆 楠



中国质量认证中心