


## FurseWELD

### Cable to earth rod CR1

#### Cable to earth rod CR1 - FurseWELD



Earth rod A ø (mm)	Earth rod B ø (")	Stranded/solid circular conductor size C (mm <sup>2</sup> )	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
14.2	5/8	16 *	CR1-4-14216	7TCA083910R1619	65P10	HCPK4
14.2	5/8	25	CR1-4-14225	7TCA083910R1623	65P10	HCPK4
14.2	5/8	35	CR1-4-14235	7TCA083910R1625	65P10	HCPK4
14.2	5/8	50	CR1-4-14250	7TCA083910R1627	90P10	HCPK4
14.2	5/8	Ø 8	CR1-4-1428SC	7TCA083910R1629	90P10	HCPK4
14.2	5/8	70	CR1-4-14270	7TCA083910R1628	90P10	HCPK4
14.2	5/8	70	CR1-4-14270-IU	-	90P10	HCPK4
14.2	5/8	95	CR1-4-14295	7TCA083910R1630	90P10	HCPK4
14.2	5/8	185	CR1-4-14295-IU	-	115P10	HCPK4
14.2	5/8	120	CR1-4-142120	7TCA083910R1617	90P10	HCPK4
14.2	5/8	120	CR1-4-142120-IU	-	90P10	HCPK4
14.2	5/8	150	CR1-4-142150	7TCA083910R1618	115P10	HCPK4
14.2	5/8	150	CR1-4-142150-IU	-	115P10	HCPK4
14.2	5/8	185	CR1-4-142185	7TCA083910R1620	115P10	HCPK4
14.2	5/8	240	CR1-4-142240	7TCA083910R1622	150P10	HCPK4
17.2	3/4	16 *	CR1-4-17216	7TCA083910R1645	65P10	HCPK4
17.2	3/4	25	CR1-4-17225	7TCA083910R1648	65P10	HCPK4
17.2	3/4	35	CR1-4-17235	7TCA083910R1650	65P10	HCPK4
17.2	3/4	50	CR1-4-17250	7TCA083910R1651	90P10	HCPK4
17.2	3/4	Ø 8	CR1-4-1728SC	7TCA083910R2300	90P10	HCPK4
17.2	3/4	70	CR1-4-17270	7TCA083910R1652	90P10	HCPK4
17.2	3/4	95	CR1-4-17295	7TCA083910R1653	90P10	HCPK4
17.2	3/4	120	CR1-4-172120	7TCA083910R1642	90P10	HCPK4
17.2	3/4	150	CR1-4-172150	7TCA083910R1644	115P10	HCPK4
17.2	3/4	185	CR1-4-172185	7TCA083910R1646	115P10	HCPK4
17.2	3/4	240	CR1-4-172240	7TCA083910R1647	150P10	HCPK4
17.2	3/4	300	CR1-4-172300	7TCA083910R1649	200P10	HCPK4

Suitable for connections to copperbond rods - for connections to solid copper and stainless steel rods please contact our sales office

Threaded portion of copperbond rods must be removed prior to welding

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

\*1 x S103 Sleeve required when joining conductors 16 mm<sup>2</sup> or smaller

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection