


On-load tap-changer type (V)UCGD./F, (V)UCLD./F, UCCD./F,
 31 tap positions, coarse/fine switching.
 Min. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 16,
 the preceding pos. was 15.

Lindningskopplare typ (V)UCGD./F, (V)UCLD./F, UCCD./F.
 31 lägen, grov/fin koppling.
 Min antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 16,
 föregående läge var 15.



The tap-changer is shown in pos. 16,
 the preceding pos. was 15.
 The tap selector and the change-over selector
 are seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 16,
 föregående läge var 15.
 Väljaren och grov/fin-omkopplaren sedda uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
 tap-changer. Dashed lines show leads belonging
 to the cleats and leads.

Heldragna linjer visar ledare som ingår i
 lindningskopplaren. Streckade linjer visar
 ledare som tillhör anslutningsdonet.

Pos. Läge	R connects in direction R förbinder i riktning	Tap selector and diverter switch connect Väljaren och lastkopplaren förbinder
1		15-V-x
2		14-H-v
3		13-V-x
4		12-H-v
5		11-V-x
6		10-H-v
7		9-V-x
8	20-22	8-H-v
9		7-V-x
10		6-H-v
11		5-V-x
12		4-H-v
13		3-V-x
14		2-H-v
15		1-V-x
16		16-H-v
17		15-V-x
18		14-H-v
19		13-V-x
20		12-H-v
21		11-V-x
22		10-H-v
23		9-V-x
24	20-21	8-H-v
25		7-V-x
26		6-H-v
27		5-V-x
28		4-H-v
29		3-V-x
30		2-H-v
31		1-V-x

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB '19

Sheet	Cont				
Year	Week				
Dept					
Rev Ind	Revision	Appd	Year	Week	
Accepted by qual control	Accepted for prod by	Description (English)		DATAORIGINAL	
L.Oberg	M.Haggmar	CONNECTION DIAGRAM			
Design checked by	Drawn by	Description (own language)		File name	
H.Sundberg	A.Wang	KOPPLINGSSHEMA			
Drawing checked by	Issued by Dept	Year	Week	Lang	Sheet
N.Gustavsson	CO/TK	14	02		1
				1ZSC004312-AAM	
				Rev Ind	Cont