

PRODUCT-DETAILS

4533216153BT

EVA-DOW-32/BT/ZWART



General Information

| | |
|-----------------------|---|
| Extended Product Type | 4533216153BT |
| Product ID | 7TCA305020R0305 |
| EAN | 8713812776491 |
| Catalog Description | EVA-DOW-32/BT/ZWART |
| Long Description | Self-contained 4 watt, black aluminium surface wall mounted 32 meter led luminaire, including control module, series Evago. The luminaire is including the pictogram PP 320/51 (escape route straight forward) - wireless - bluetooth |

Technical

| | |
|---------------------------------|---|
| Function | Escape route signage |
| Rated Voltage (U _r) | 230...240 V |
| Input Voltage Type | AC |
| Power Supply Type | 1.15 W Peripheral (Individual Battery) |
| Number of Poles | 4 |
| Number of Lamps | 1 |
| Number of Lighting Heads | 1 |
| Functional Testing Capability | Safety Module for Monitoring (Central Fedded System) |
| Wiring Configuration | Continuous circuit/emergency circuit Suitable for through wiring |

| | |
|------------------------------|----------------------|
| Ballast Type | Current Controlled |
| Connection Type | Screw |
| Lamp Type | LED not exchangeable |
| Marking Type | InsertSheet Plate |
| Mounting Type | Wall surface mounted |
| Type of Indicator | Single-sided |
| Cover Material | Plastic, Transparent |
| Housing Material | Aluminium |
| Housing Color | Black |
| Battery Chemical Composition | Nickel-Metal Hydride |
| Battery Type | Industrial |
| Battery Weight | 52 g |
| Number of Batteries | 2 |
| | 5000 K |

Environmental

| | |
|----------------------|---------------------|
| Ambient Temperature | 5 ... 35 °C |
| Degree of Protection | IP40 |
| Protection Class | Isolated (Class II) |

Dimensions

| | |
|----------------------------|----------|
| Product Net Width | 184 mm |
| Product Net Height | 66 mm |
| Product Net Depth / Length | 335 mm |
| Product Net Weight | 1.225 kg |

Ordering

| | |
|------------------------------|--------------|
| Minimum Order Quantity | 1 piece |
| Package Level 1 Units | box 1 piece |
| Package Level 1 Gross Weight | 1.530 kg |
| UPC | 075114442596 |

Certificates and Declarations

| | |
|--------------------------------|-----------------|
| Declaration of Conformity - CE | 9AKK108468A7159 |
|--------------------------------|-----------------|

Installation

| | |
|--------------------------|-----------------|
| Instructions and Manuals | 9AKK107992A4815 |
|--------------------------|-----------------|

Popular Downloads

| | |
|-----------------------|--------------|
| Data Sheet, Technical | 4533216153BT |
|-----------------------|--------------|

Information

Classifications

| | |
|----------------|--|
| ETIM 8 | EC001957 - Emergency luminaire |
| ETIM 9 | EC001957 - Emergency luminaire |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |
| WEEE B2C / B2B | Business To Business |
| CN8 | 9405490000 |

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Emergency Lighting

