

Exit LED edgelit Signature exit LED edgelit recessed Nexus[®], original style square diffuser



! Please note that the diffuser needs to be ordered separately.

Range

Signature range

Product group

Exit LED edgelit

Features

- 3 year warranty
- LED technology 100,000 hours lamp life
- Advanced pulsetime dual rate battery charger with high temperature NiMH batteries
- Nexus[®] monitored, either cabled or wireless
- Slim and elegant
- Surface ceiling mounted
- Easy installation and maintenance
- 2m flex and plug included
- All pictograph diffuser options available (order separately)



Nexus products

Catalogue no.	Description
PLRONXSLED	LED legend recessed Nexus LX pictograph exit, original style square diffuser
PLRONRFLED	LED legend recessed Nexus RF pictograph exit, original style square diffuser

Accessories

Catalogue no.	Description
31-PL1	Diffuser single sided picto
31-PL2	Diffuser single sided <picto
31-PL3	Diffuser single sided picto>
31-PL5	Diffuser double sided picto
31-PL6	Diffuser double sided picto AOW

Spare parts

Catalogue no.	Description
03-01213P	Battery 4 cell NiMH 4.8V 1.25Ah

Dimensions

Item	Length	Width
Face plate	464mm	121mm
Ceiling cutout	422mm	93mm

Weight

Model	Body	Diffuser
Nexus LX/RF	1.5kg	1.6kg

Construction

Part	Construction
Body and gear tray	White powder coated zinc steel
Fascia cover	White powder coated zinc steel
Diffuser	Acrylic

Light source

Model	Light source
Nexus LX/RF	Multiple LED 1.0W

Power consumption

Model	Power consumption
Nexus LX	2.71W
Nexus RF	2.84W

Photometrics

Model	Class	Classification
Standard	C0	D2
	C90	E1.6

Note: Preliminary results

Note: Designed to comply with AS2293 and meet relevant Australian EMC standards

For more information please contact:

ABB Australia Pty Limited

Phone: 1300 666 595

Fax: 1300 666 594

E-mail: AU-ABB-Stanilite@abb.com

www.stanilite.com.au

Note: We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright © 2016 ABB
All rights reserved