

TY-RAP®

Fastening products




—
01

—
01 Dimensions
Frame: 24 in. W x 54 in. H x 24 in. D
Header: 24 in. W x 6 in. H



1. Innovative wire management solutions
2. Cable management

Plan-O-Gram Display unit



Side A

	Cat. No.	Description	Qty/ Pkg	Order Qty
A1	TC5345A	Mounting Base, Natural 1.125 x 1.125 in., Adhesive Back	100	1000
A2	TY23M	Cable Tie, Natural, 18 lb. 3.62 in. Long, 0.63 in. dia. bundle	1000	10000
A3	TY24M	Cable Tie, Natural, 40 lb. 5.5 in. Long, 1.38 in. dia. bundle	1000	10000
	TY-TOTE23	Cable Tie Dispenser 4 in. cable Ties	1	Option
	TY-TOTE25	Cable Tie Dispenser 7 in. cable Ties	1	Option
	WT-1TB	Cable Tie Tool 18-50 lb.	1	Option
	WT-2TB	Cable Tie Tool 50-120 lb.	1	Option
	ERG50	Cable Tie Tool 18 - 50 lb.	1	Option
	ERG120	Cable Tie Tool 50-120 lb.	1	Option
A4	TY25M	Cable Tie, Natural, 50 lb. 7.3 in. Long, 1.89 in. dia. bundle	1000	10000
A5	TY26M	Cable Tie, Natural, 30 lb. 11.1 in. Long, 3.0 in. dia. bundle	1000	10000
A6	TY27M	Cable Tie, Natural, 120 lb. 13.4 in. Long, 4.0 in. dia. bundle	500	10000
A7	TY28M	Cable Tie, Natural, 50 lb. 14.2 in. Long, 4.0 in. dia. bundle	1000	20000
	TY275M	Cable Tie, Natural, 120 lb. 18.0 in. Long, 5.0 in. dia. bundle	500	Option



Side B

	Cat. No.	Description	Qty/ Pkg	Order Qty
B1	TY23MX	Cable Tie, UV Black, 18 lb. 3.62 in. Long, 0.63 in. dia. bundle	1000	10000
B2	TY24MX	Cable Tie, UV Black, 40 lb. 5.5 in. Long, 1.38 in. dia. bundle	1000	10000
B3	TC5345AX	Mounting Base, UV Black 1.125 x 1.125 in., Adhesive back	100	1000
	TY525M-CLRS	Cable Tie, Colour, 50 lb. 7.3 in. Long, 1.89 in. dia. bundle	100	Option
	WM-0-45	E-Z-Code® Wire Markers Legend: 0 - 45	10	Option
	WM-A-Z	E-Z-Code® Wire Markers Legend: A - Z	10	Option
	WT-1TB	Cable Tie Tool 18-50 lb.	1	Option
	WT-2TB	Cable Tie Tool 50-120 lb.	1	Option
	ERG50	Cable Tie Tool 18-50 lb.	1	Option
	ERG120	Cable Tie Tool 50-120 lb.	1	Option
B4	TY25MX	Cable Tie, UV Black, 50 lb. 7.3 in. Long, 1.89 in. dia. bundle	1000	10000
B5	TY26MX	Cable Tie, UV Black, 30 lb. 11.1 in. Long, 3.0 in. dia. bundle	1000	10000
B6	TY27MX	Cable Tie, UV Black, 120 lb. 13.4 in. Long, 4.0 in. dia. bundle	500	10000
B7	TY28MX	Cable Tie, UV Black, 50 lb. 14.2 in. Long, 4.0 in. dia. bundle	1000	20000
	TY275MX	Cable Tie, UV Black, 120 lb. 18.0 in. Long, 5.0 in. dia. bundle	500	Option