


# Tamperproof Ex d Stopping Plug



## Features

- Suitable for use in Zones 1, 2, 21, 22

## Approvals



## Certification & Standards

<b>Approved to:</b>	EN/IEC 60079-0, 60079-1
<b>EC TYPE Examination Certificate:</b>	Baseefa 08ATEX0324, IECEx BAS 08.0109 Ex d I Mb Ex d IIC Gb Ex tb IIIC Db UL1203 (Nickel Plated Brass and Stainless Steel only) Class I Div. 1 ABCD Class II Div. 1 EFG
<b>Temperature:</b>	-20°C bis +200°C

Nickel Plated Brass Part No.	Metric Thread	GID Code	Stainless Steel Part No.	Metric Thread	GID Code	Brass Part No.	Metric Thread	GID Code
EXN/M16/TSP	M16 x 1.5	7TCA297140R0091	EXS/M16/TSP	M16 x 1.5	7TCA297140R0159	EX/M16/TSP	M16 x 1.5	7TCA297140R0037
EXN/M20/TSP	M20 x 1.5	7TCA297140R0095	EXS/M20/TSP	M20 x 1.5	7TCA297140R0161	EX/M20/TSP	M20 x 1.5	7TCA297140R0044
EXN/M25/TSP	M25 x 1.5	7TCA297140R0099	EXS/M25/TSP	M25 x 1.5	7TCA297140R0170	EX/M25/TSP	M25 x 1.5	7TCA297140R0052
EXN/M32/TSP	M32 x 1.5	7TCA297140R0103	EXS/M32/TSP	M32 x 1.5	7TCA297140R0160	EX/M32/TSP	M32 x 1.5	7TCA297140R0060
EXN/M40/TSP	M40 x 1.5	7TCA297140R0106	EXS/M40/TSP	M40 x 1.5	7TCA297140R0167	EX/M40/TSP	M40 x 1.5	7TCA297140R0066
EXN/M50/TSP	M50 x 1.5	7TCA297140R0109	EXS/M50/TSP	M50 x 1.5	7TCA297140R0162	EX/M50/TSP	M50 x 1.5	7TCA297140R0070
EXN/M63/TSP	M63 x 1.5	7TCA297140R0112	EXS/M63/TSP	M63 x 1.5	7TCA297140R0165	EX/M63/TSP	M63 x 1.5	7TCA297140R0073

Nickel Plated Brass Part No.	NPT Thread	GID Code	Stainless Steel Part No.	NPT Thread	GID Code	Brass Part No.	NPT Thread	GID Code
EXN/038/TSP	3/8"	7TCA297140R0076	EXS/038/TSP	3/8"	7TCA297140R0169	EX/038/TSP	3/8"	7TCA297140R0020
EXN/050/TSP	1/2"	7TCA297140R0078	EXS/050/TSP	1/2"	7TCA297140R0152	EX/050/TSP	1/2"	7TCA297140R0023
EXN/075/TSP	3/4"	7TCA297140R0080	EXS/075/TSP	3/4"	7TCA297140R0153	EX/075/TSP	3/4"	7TCA297140R0026
EXN/100/TSP	1"	7TCA297140R0082	EXS/100/TSP	1"	7TCA297140R0154	EX/100/TSP	1"	7TCA297140R0028
EXN/125/TSP	1 1/4"	7TCA297140R0084	EXS/125/TSP	1 1/4"	7TCA297140R0155	EX/125/TSP	1 1/4"	7TCA297140R0030
EXN/150/TSP	1 1/2"	7TCA297140R0086	EXS/150/TSP	1 1/2"	7TCA297140R0156	EX/150/TSP	1 1/2"	7TCA297140R0032
EXN/200/TSP	2"	7TCA297140R0088	EXS/200/TSP	2"	7TCA297140R0158	EX/200/TSP	2"	7TCA297140R0034

CMG House, Station Road, Coleshill, Birmingham, B46 1HT United Kingdom  
 Tel: +44 (0) 1675 468 213 | Email: sales@kopex.co.uk  
[www.tnb-hazardous.com](http://www.tnb-hazardous.com)

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.

Power and productivity  
for a better world™

