

PRODUCT SPECIFICATION

# DLOW3LS60

## Aqualux Self-Contained IP65 DALI Test Surface

Catalogue Number **DLOW3LS60**  
 GID **7TCA091180R0346**  
 Warranty **3 Year/s Refer to ABB warranty terms & conditions**  
 Power Supply System **Self-Contained (individual battery)**  
 Mounting Method/Form **Ceiling, Wall Surface**  
 Housing Material **Aluminium/Plastic**  
 Colour **White/Silver**  
 Dimensions (LxWxD) **381 x 170 x 75 mm**  
 Temperature Range **0 to 25°C**  
 Weight **1.7 Kg**

Nominal Voltage **220-240v AC 50Hz**  
 Emergency Duration (Hours) **3 Hours**  
 Battery **NiCd**  
 Monitoring Equipment **DALI test**  
 Lamp **1 x 3W LED**  
 Light output in Emergency Operation **119 Lumens**  
 Average Lifespan light source (hours) **50000 Hours**  
 Light Colour/Temperature/CRI **White / 6500 / 73**  
 Degree of Protection **IP 65 IK 10**

Wiring System **Maintained / non-maintained circuit**  
 Type of Legend **Single Sided (Order separate)**  
 Exit Sign Viewing/Recognition Distance (m) **25**  
 Power Consumption **9.9 VA / 5.1 Watts**  
 Nominal Current **42.5 (mA)**  
 Inrush Current **18 A to 0.1 ms**

### Accessories

- XEN2W** Down ISO7010 Legend for Backlit Exit Sign
- XEN3W** Left ISO7010 Legend for Backlit Exit Sign
- XEN6W** Right ISO7010 Legend for Backlit Exit Sign
- XEN5W** Up ISO7010 Legend for Backlit Exit Sign
- XLF802W** Fire Extinguisher Legend for Backlit Exit Sign
- XLF803W** Hose Reel Legend for Backlit Exit Sign

- OW/BCM** Ceiling Bracket for Vertical Mount
- OW/BWA** Wall Bracket for Angled Mount
- OW/BWM** Cantilever Bracket for End to Wall Mount
- OW/BCR** Recessing Kit
- OW/DSC** Blank double sided diffuser for Edgelite Exit Sign

- RSEN2W** Down ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN3W** Left ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN6W** Right ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN5W** Up ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN3W/RSEN6W** Left+Right ISO7010 Legend for Edgelit Exit Sign (Double Sided)



**Edgelit Exit Sign**  
 DLOW3LS60 + RSEN5W + OW/DSC



**Backlit Exit Sign**  
 DLOW3LS60 + XEN5W



**Bulkhead**  
 DLOW3LS60

