


FurseWELD

Cable to cable CC4

Cable to cable CC4 - FurseWELD

	Stranded/solid circular conductor size A (mm ²)	Stranded/solid circular conductor size B (mm ²)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	16 *	16 *	CC4-4-1616	7TCA083910R1455	65P10	HCPK4
	25	25	CC4-4-2525	7TCA083910R1466	45P10	HCPK4
	35	35	CC4-4-3535	7TCA083910R1470	65P10	HCPK4
	35	25	CC4-4-3525	7TCA083910R2956	65P10	HCPK4
	Ø 8	Ø 8	CC4-4-885C	7TCA083910R1479	90P10	HCPK4
	50	50	CC4-4-5050	7TCA083910R1473	90P10	HCPK4
	50	35	CC4-4-5035	7TCA083910R1472	90P10	HCPK4
	50	25	CC4-4-5025	7TCA083910R2957	90P10	HCPK4
	Ø 10	Ø 10	CC4-4-1010SC	7TCA083910R2958	115P10	HCPK4
	70	70	CC4-4-7070	7TCA083910R1477	115P10	HCPK4
	70	50	CC4-4-7050	7TCA083910R1476	115P10	HCPK4
	70	35	CC4-4-7035	7TCA083910R1475	115P10	HCPK4
	70	25	CC4-4-7025	7TCA083910R1474	115P10	HCPK4
	95	95	CC4-4-9595	7TCA083910R1485	150P10	HCPK4
	95	70	CC4-4-9570	7TCA083910R1484	150P10	HCPK4
	95	50	CC4-4-9550	7TCA083910R1483	115P10	HCPK4
	95	35	CC4-4-9535	7TCA083910R1482	115P10	HCPK4
	120	120	CC4-4-120120	7TCA083910R1442	200P10	HCPK4
	120	95	CC4-4-12095	7TCA083910R1448	200P10	HCPK4
	120	70	CC4-4-12070	7TCA083910R1447	150P10	HCPK4
	120	50	CC4-4-12050	7TCA083910R1446	150P10	HCPK4
	150	150	CC4-4-150150	7TCA083910R1450	250P10	HCPK4
	150	120	CC4-4-150120	7TCA083910R1449	250P10	HCPK4
	150	95	CC4-4-15095	7TCA083910R1454	200P10	HCPK4
	150	70	CC4-4-15070	7TCA083910R1453	150P10	HCPK4
	185	185	CC4-4-185185	7TCA083910R1461	2 x 150P10	HCPK4
	185	150	CC4-4-185150	7TCA083910R1459	250P10	HCPK4
	185	120	CC4-4-185120	7TCA083910R1458	250P10	HCPK4
	185	95	CC4-4-18595	7TCA083910R1463	200P10	HCPK4
	185	70	CC4-4-18570	7TCA083910R1462	200P10	HCPK4
	240	240	CC4-5-240240	7TCA083910R1491	2 x 250P10	HCPK5
	240	185	CC4-5-240185	7TCA083910R1490	2 x 200P10	HCPK5
240	150	CC4-5-240150	7TCA083910R1489	2 x 200P10	HCPK5	
240	120	CC4-5-240120	7TCA083910R1488	2 x 150P10	HCPK5	
300	300	CC4-5-300300	7TCA083910R1499	3 x 200P10	HCPK5	

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

*4 x S103 Sleeve required when joining conductors 16 mm² or smaller

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection