


# FurseWELD

## Cable to earth rod CR2

### Cable to earth rod CR2 - FurseWELD



Earth rod A ø (mm)	Earth rod B ø (")	Stranded/solid circular conductor size C (mm <sup>2</sup> )	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
14.2	5/8	16 *	CR2-4-14216	7TCA083910R1712	90P10	HCPK4
14.2	5/8	25	CR2-4-14225	7TCA083910R1717	90P10	HCPK4
14.2	5/8	35	CR2-4-14235	7TCA083910R1718	90P10	HCPK4
14.2	5/8	50	CR2-4-14250	7TCA083910R1720	90P10	HCPK4
14.2	5/8	Ø 8	CR2-4-1428SC	7TCA083910R1722	90P10	HCPK4
14.2	5/8	70	CR2-4-14270	7TCA083910R1721	115P10	HCPK4
14.2	5/8	95	CR2-4-14295	7TCA083910R1723	115P10	HCPK4
14.2	5/8	120	CR2-4-142120	7TCA083910R1708	150P10	HCPK4
14.2	5/8	120	CR2-4-142120-IU	-	150P10	HCPK4
14.2	5/8	150	CR2-4-142150	7TCA083910R1711	200P10	HCPK4
14.2	5/8	185	CR2-4-142185	7TCA083910R1714	200P10	HCPK4
14.2	5/8	240	CR2-4-142240	7TCA083910R1716	250P10	HCPK4
17.2	3/4	16 *	CR2-4-17216	7TCA083910R1737	90P10	HCPK4
17.2	3/4	25	CR2-4-17225	7TCA083910R1740	90P10	HCPK4
17.2	3/4	35	CR2-4-17235	7TCA083910R1742	90P10	HCPK4
17.2	3/4	50	CR2-4-17250	7TCA083910R1743	115P10	HCPK4
17.2	3/4	Ø 8	CR2-4-1728SC	7TCA083910R2315	115P10	HCPK4
17.2	3/4	70	CR2-4-17270	7TCA083910R1744	115P10	HCPK4
17.2	3/4	95	CR2-4-17295	7TCA083910R1745	115P10	HCPK4
17.2	3/4	120	CR2-4-172120	7TCA083910R1734	150P10	HCPK4
17.2	3/4	150	CR2-4-172150	7TCA083910R1736	200P10	HCPK4
17.2	3/4	185	CR2-4-172185	7TCA083910R1738	200P10	HCPK4
17.2	3/4	240	CR2-4-172240	7TCA083910R1739	250P10	HCPK4
17.2	3/4	300	CR2-5-172300	7TCA083910R1761	2 x 150P10	HCPK5

Suitable for connections to copperbond rods - for connections to solid copper and stainless steel rods please contact our sales office

Threaded portion of copperbond rods must be removed prior to welding

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

\*2 x S103 Sleeve required when joining conductors 16 mm<sup>2</sup> or smaller

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection