



EC DECLARATION OF CONFORMITY

(supplier's name) We ABB SACE S.p.A

(address) VIALE VICENZA, 61

36063 - MAROSTICA (VI)

declare under our sole responsibility that the product : _____

CABLE TRUNKINGS AND CABLE TRAYS - 08 SERIES

(name,type or model,lot,batch or serial number,possibly sources and numbers of items)

ARTICLES : IN ATTACHED

to which this declaration relates is in conformity with the following standard(s) or other
normative/documents CEI 23-32 , EN50085-1 AND EN 61537

(title and/or number and date of issue of the standard(s) or other normative document(s))

following the provisions of the Directive(s) 73/23 CEE MODIFIED BY 93/68 CEE

MAROSTICA, 11/03/2002

(Place and date of issue)

02

(last two digits of the year in which the mark was affixed)

ABB SACE S.p.A
TECHNICAL MANAGER
ENZO RIZZI

(seal, name and signature of authorized person)

Mod. 379 - 12/94 - 900

1SLT000007D00

Industrial plastic trunkings

Cable trunkings and cable trays



Article	Dimensions WxH (mm)	Weight (kg/m)	Unit/pack-metres
---------	---------------------	---------------	------------------

Cable trunkings IP40*

08 101	100x60	1.00	12
08 102	150x60	1.27	6
08 103	200x60	1.74	6
08 105	300x60	2.15	6
08 106	300x100	2.70	6
08 107	400x100	3.70	6

Cable trays IP20*

08 111	100x60	0.90	12
08 112	150x60	1.21	6
08 113	200x60	1.56	6
08 115	300x60	2.00	6
08 116	300x100	2.55	6
08 117	400x100	3.20	6

* The degree of protection refers to the trunking fitted with cover

Article	Trunking base (mm)	Weight (kg/m)	Unit/pack - metres
---------	--------------------	---------------	--------------------

Cover

Snaps onto trunkings.

08 121	100	0.43	12
08 122	150	0.70	6
08 123	200	0.80	6
08 125	300	1.38	6
08 126	400	2.18	6

Article	Trunking dimensions WxH (mm)	Unit/pack - Pieces
---------	------------------------------	--------------------

Flat 90° corner

Complete with cover.

08 131	100x60	1
08 132	150x60	1
08 133	200x60	1
08 135	300x60	1
08 136	300x100	1
08 137	400x100	1

Flat tee

Complete with cover.

08 141	100x60	1
08 142	150x60	1
08 143	200x60	1
08 145	300x60	1
08 146	300x100	1
08 147	400x100	1

Industrial plastic trunkings

Cable trunkings and cable trays

5



FLCP8111

Article	Trunking dimensions WxH (mm)	Unit/pack-Pieces
---------	------------------------------	------------------

Flat cross

Complete with cover.

08 161	100x60	1
08 162	150x60	1
08 163	200x60	1
08 165	300x60	1
08 166	300x100	1
08 167	400x100	1



FLCP8112

Article	Trunking height (mm)	Pack/metres
---------	----------------------	-------------

Divider

Fixed with screws.
Standard 3-metre length.

08 171	60	30
08 172	100	30



FLCP8113

Article	Material	Pack/metres
---------	----------	-------------

Screw and nut

08 190	Techno-polymer	100
08 192	Stainless steel	100



FLCP8114

Article	Trunking dimensions WxH (mm)	Unit/pack-metres
---------	------------------------------	------------------

End cap

If a hole is made in the end it can be used as a reducer (concentric, left and right).

08 151	100x60	4
08 152	150x60	4
08 153	200x60	4
08 155	300x60	4
08 156	300x100	4
08 157	400x100	4



FLCP8115

Branch connection element

For tee, vertical and cross branch connections and tee reducers.

08 164	trunking height 60/100	1/10
--------	------------------------	------

Industrial plastic trunkings

Cable trunkings and cable trays



Article	Trunking dimensions WxH (mm)	Unit/pack-Pieces
---------	------------------------------	------------------

Straight joint

2 pieces – complete with screws and nuts.

08 175	100/400x60	1/10
08 176	300/400x100	1/10

Adjustable joint

2 pieces – complete with screws and nuts.

08 179	100/400x60	1/10
08 180	300/400x100	1/10

Wall plastic bracket

08 181	Base 100	1/12
08 182	Base 150	1/12
08 183	Base 200	1/12
08 185	Base 300	1/12
08 187	Base 400	1/10

