

—
PRODUCT BROCHURE

Steel City[®] made in USA steel EMT fittings

High-quality steel construction —
made in the USA



Steel City® made in USA steel EMT fittings

High-quality steel construction — made in the USA



TC724US TC722US
Insulated EMT set-screw connectors



TK114US TK111US
EMT compression couplings



Insulated EMT set-screw connector (TC729US)

Insulated EMT compression connector (TC7110US)



EMT set-screw coupling (TK128US)

High-quality steel construction — made in the USA

- Available in sizes for ½" to 4" electrical metallic tubing (EMT)
- Steel construction for strength and durability
- Electroplated zinc finish for corrosion protection
- Use couplings to join two lengths of EMT
- Use connectors (insulated or non-insulated) to join EMT to a box or enclosure
- Set-screw couplings and connectors are for use in dry locations and are concrete-tight when taped
- Compression couplings and connectors are concrete-tight
- Made in USA

Made in USA steel EMT fittings



Cat. no.	Hub size (in.)	UPC no.
EMT compression connectors, non-insulated		
TC111US	½	785991-05020
TC112US	¾	785991-05021
TC113US	1	785991-05022
TC114US	1¼	785991-05023
TC115US	1½	785991-05024
TC116US	2	785991-05025
TC117US	2½	785991-05026
TC118US	3	785991-05027
TC119US	3½	785991-05028
TC1110US	4	785991-05029
EMT compression connectors, insulated		
TC711US	½	785991-05040
TC712US	¾	785991-05041
TC713US	1	785991-05042
TC714US	1¼	785991-05043
TC715US	1½	785991-05044
TC716US	2	785991-05045
TC717US	2½	785991-05046
TC718US	3	785991-05047
TC719US	3½	785991-05048
TC7110US	4	785991-05049

Cat. no.	Hub size (in.)	UPC no.
EMT set-screw connectors, non-insulated		
TC121US	½	785991-05030
TC122US	¾	785991-05031
TC123US	1	785991-05032
TC124US	1¼	785991-05033
TC125US	1½	785991-05034
TC126US	2	785991-05035
TC127US	2½	785991-05036
TC128US	3	785991-05037
TC129US	3½	785991-05038
TC1210US	4	785991-05039
EMT set-screw connectors, insulated		
TC721US	½	785991-05050
TC722US	¾	785991-05051
TC723US	1	785991-05052
TC724US	1¼	785991-05053
TC725US	1½	785991-05054
TC726US	2	785991-05055
TC727US	2½	785991-05056
TC728US	3	785991-05057
TC729US	3½	785991-05058
TC7210US	4	785991-05059

Cat. no.	Hub size (in.)	UPC no.
EMT compression couplings		
TK111US	½	785991-05060
TK112US	¾	785991-05061
TK113US	1	785991-05062
TK114US	1¼	785991-05063
TK115US	1½	785991-05064
TK116US	2	785991-05065
TK117US	2½	785991-05066
TK118US	3	785991-05067
TK119US	3½	785991-05068
TK1110US	4	785991-05069
EMT set-screw couplings		
TK121US	½	785991-05070
TK122US	¾	785991-05071
TK123US	1	785991-05072
TK124US	1¼	785991-05074
TK125US	1½	785991-05073
TK126US	2	785991-05076
TK127US	2½	785991-05083
TK128US	3	785991-05084
TK129US	3½	785991-05085
TK1210US	4	785991-05086

ABB Inc.
Electrification Products
860 Ridge Lake Blvd.
Memphis, TN 38120

Customer Service: 800-816-7809
Technical Support: 888-862-3289

abb.com/lowvoltage

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc.
Copyright © 2018 ABB
All rights reserved