ABB PROPRIETARY AND CONFIDENTIAL INFORMATION

The information contained in the document has to be kept strictly confidential.
Any unauthorized use, reproduction, distribution or disclosure to third parties is strictly forbidden.
ABB reserves all rights regarding intellectual Property Rights.
Copyright 2018 ABB. All rights reserved.

SIZE	DRAWING NO.	REV	SHEET
D	M354C	1	1

REVISIONS

REV.	DESCRIPTION	DATE	APPROVED
A	CN C123933 DH	09-21-21	WILL L
B	ECN ECN000253823	12-01-22	WILL L













CONFIGURATION
M354C





KNOCKOUT TABLE:

G= 1/2", 3/4", 1" KO
D= 3/4", 1", 1-1/4" KO
B= 1", 1-1/4", 1-1/2" KO
H= 9/32" KO

RECEPTACLES
BR54UWR

CIRCUIT PROTECTION
THQL2150

WIRE RANGE TABLE:

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRANDED	SOLID	STRANDED
LINE	---	6-350	---	6-350
LOAD	---	---	---	---
NEUTRAL-LARGE HOLE	12-8	12-1/0	10-8	10-1/0
NEUTRAL-SMALL HOLE	14-8	14-4	12-8	12-4
EQUIP. GRND.	12-8	12-2	12-8	12-2

THIRD ANGLE PROJECTION

Part must conform to SI 900000 Sect. 4, Toxicity Procedure

FOR ADDITIONAL INFO REFER TO: APPLIED PRACTICES

DIMENSIONS ARE IN INCHES

UNLESS OTHERWISE SPECIFIED IN DRAWING

TOLERANCE ON:
1 PL DECIMALS ± 0.1
2 PL DECIMALS ± 0.02
3 PL DECIMALS ± 0.005
ANGLES ± 1.0
FRACTIONS ±
FINISH

◇ CRITICAL TO QUALITY CHARACTERISTIC

SIGNATURES	DATE
MODEL M354C	
DETAIL	
CHECKED	
ENGRG	
MFG	
QUALITY	
ISSUED	

DRAWING FILE: M354CM02.0D

SOLID MODEL: U061CPGM02

Midwest Electric Products

TITLE
MIDWEST SERVICE EQUIP 100A METERED SURFACE MT OVERHEAD/UNDERGROUND FEED 120/240V 50A RECEPT 3 SPACES N3R UL LISTED

SIZE	DRAWING	REV
D	M354C	1

SCALE: 3:50 SHEET 1 OF 1