
PRODUCT SHEET

Kindorf® modular half-slot channel

Flexible half-slot configuration with modular 1½" design



Kindorf® modular half-slot channel



01

01 Kindorf half-slot makes bolted connections fast and easy.


02 Make 1½" connections with Kindorf half-slot and fittings like the Kindorf B-917 angle connector shown.

03 Kindorf half-slot is available in a variety of sizes and finishes.

04 Make connections with Kindorf half-slot and typical 1½" fittings like the Superstrut AB-219 shown.



02



03



04

The labor-saving Kindorf modular design is available with half-slot holes that provide the latitude to make adjustments during installations. The half-slot design also allows the flexibility to use either 1½" or 1⅝" accessories.

Flexible half-slot configuration

The Kindorf half-slot hole pattern is ⅝" x 7/8" slots on 1½" centers for flexibility and adjustability on installations of racks, trapezes — almost any strut application.

Modular 1½" spacing

Designed on 1½" centers, the Kindorf half-slot channel continues to provide modular, labor-saving connections between channel, fittings, post bases and other accessories, but in an easy-to-use half-slot format.

Scribe marks for easy fabrication

Field cutting and layout are simple with convenient scribe marks. Every 1½" has a scribe mark and every 6" has a mid-point mark. Simply count the marks and make your cut.

Available in a variety of sizes and finishes

Kindorf half-slot is available in a wide range of finishes, including Galv-Krom®, SilverGalv®, hot-dip galvanized, stainless steel and 316 stainless steel. This hole configuration is available in popular B903, B905, B907 and B909 sizes, as well as back-to-back.

Accommodates 1⅝" accessories

In addition to the modular 1½" connections that can be made with the Kindorf system, the Kindorf half-slot also accommodates 1⅝" accessories. With the ⅝" x 7/8" slot configuration, connections can be made with the hole spacing for fittings, post bases and other accessories in 1⅝" strut systems like Superstrut®.

Kindorf half-slot, Galv-Krom® finish



Cat. no.	Description	Steel thickness (ga.)	Std. pkg. qty.	UPC no.
B 905HS 10	1½" x 1½" Channel	12	600	785991-04424
B 907HS 10	1½" x ¾" Channel	14	600	785991-04425
B 903HS 10	1½" x 3" Channel	12	160	785991-04428
B 905HS M 10	1½" x 1½" Channel	14	600	785991-04438
B 909HS 10	1½" x 1⅝" Channel	12	600	785991-04435

Also available in the following finishes: SilverGalv (-EG), hot-dip galvanized (-HD), stainless steel (-SS), type 316 stainless steel (-SS316)

ABB Installation Products Inc.
Electrification Products Division
860 Ridge Lake Blvd.
Memphis, TN 38120

tnb.abb.com

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc.
Copyright© 2018 ABB
All rights reserved