


On-load tap-changer type (V)UCGR./F, (V)UCLR./F, UCCR./F,
 27 tap positions, plus/minus switching.
 Min. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 14,
 the preceding pos. was 13.

Lindningskopplare typ (V)UCGR./F, (V)UCLR./F, UCCR./F,
 27 lägen, plus/minus koppling.
 Min antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 14,
 föregående läge var 13.



Pos. Läge	R connects in direction R förbinder i riktning	Tap selector and diverter switch connect Väljaren och lastkopplaren förbinder
1		1-V-x
2		2-H-v
3		3-V-x
4		4-H-v
5		5-V-x
6		6-H-v
7	20-21	7-V-x
8		8-H-v
9		9-V-x
10		10-H-v
11		11-V-x
12		12-H-v
13		13-V-x
14	20-21	14-H-v
15		1-V-x
16		2-H-v
17		3-V-x
18		4-H-v
19		5-V-x
20		6-H-v
21	20-22	7-V-x
22		8-H-v
23		9-V-x
24		10-H-v
25		11-V-x
26		12-H-v
27	20-22	13-V-x

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB '19

The tap-changer is shown in pos. 14,
 the preceding pos. was 13.
 The tap selector and the change-over selector
 are seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 14,
 föregående läge var 13.
 Väljaren och plus/minus-omkopplaren sedda uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
 tap-changer. Dashed lines show leads belonging
 to the cleats and leads.

Heldragna linjer visar ledare som ingår i
 lindningskopplaren. Streckade linjer visar
 ledare som tillhör anslutningsdonet.

Drawn by Form No.	Sheet	Cont				
	Year	Week				
	Dept					
	Rev Ind	Revision	Appd	Year	Week	
Design checked by	Accepted by qual control	Accepted for prod by	Description (English)		DATAORIGINAL	
	L.Oberg	M.Haggmar	CONNECTION DIAGRAM			
	Design checked by	Drawn by	Description (own language)		File name	
Design checked by	H.Sundberg	A.Wang	KOPPLINGSSHEMA			
	Drawing checked by	Issued by Dept	Year	Week	Lang	Sheet
	N.Gustavsson	CO/TK	14	02		1
					1ZSC004310-AAK	
					Rev Ind	Cont
						-