



**GE PowerMark Gold™ Auxillary Gutter**



LISTED CONTROL NO. 48PA AUXILIARY GUTTER

Type 1 Indoor Enclosure  
Cat. No.: **TMAGB39**

Use only GE type Tap Kits: **TMGT250** or **TMGT500** or **TMGT750**

1 PHASE OR 3 PHASE 240 VOLT MAXIMUM

SUITABLE FOR USE ON A CIRCUIT CAPABLE OF DELIVERING NOT MORE THAN 65,000 RMS SYMMETRICAL AMPERES AT 240 V.A.C. MAXIMUM.

ONLY FEED-THRU AND PARALLEL TAP CONNECTORS LISTED BELOW ARE TO BE ACCOMODATED IN THIS ENCLOSURE. SUITABLE FOR USE IN ALL GE LOAD CENTERS. TAP KIT ASSEMBLIES ARE ORDERED SEPARATELY.

ACCEPTABLE GUTTER TAP KITS:	MAIN	TAP
TMGT250	250-1/0	250-6
TMGT500	500-350	500-02
TMGT750	750-500	500-02

**TAP KIT INSTRUCTIONS:**

TAP LUGS TERMINATIONS REQUIRED WITHIN 18 INCHES OF THE FEED-IN SIDE OF THE AUXILIARY GUTTER.

1. STRIP WIRE PER GAUGE ON PROTECTIVE COVER, SPACING CUTS A MINIMUM OF 2 1/2 INCHES APART. MAKE MAIN AND TAP CONNECTIONS.
2. TORQUE REQUIREMENTS:  
TMGT250 - 325 IN.LBS.; TMGT500 & TMGT750 - 375 IN.LBS.
3. PLACE CONNECTOR WITH WIRES INTO THE PROTECTIVE COVER.
4. SNAP PROTECTIVE COVER CLOSED.

NOTE: BUSHING COUPLER AND MOUNTING BOLTS MUST BE INSTALLED PER INSTRUCTION SHEET PRIOR TO WIRE INSTALLATION.

10080802P4

Plainville, CT 06062

ASSEMBLED IN MEXICO

REVISIONS


REV	DESCRIPTION	DATE	APPROVED
1	9800240C	6-22-98	
2	9800240I	7-29-98	
3	R0814582	MSM 03-31-08	



MAT'L: C50HD15A  
SIZE: 5.00 X 5.00

GE (USA) CONFIDENTIAL AND PROPRIETARY  
THIS GE DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF GE ELECTRICAL DISTRIBUTION & CONTROL (ED&C). IT IS LOANED ON CONDITION THAT IT AND THE INFORMATION THEREIN SHALL NOT BE USED BY RECIPIENT NOR DISCLOSED TO OTHERS EXCEPT AS EXPRESSLY APPROVED BY ED&C. ANY DOCUMENT CONTAINING SUCH INFORMATION SHALL BE RETURNED ON REQUEST.

THIRD ANGLE PROJECTION



FOR ADDITIONAL INFO REFER TO	SIGNATURES	DATE
APPLIED PRACTICES	DRAWN JFN	6-22-98
UNLESS OTHERWISE SPECIFIED	CHECKED	
DIMENSIONS ARE IN INCHES	ENGRG	
TOLERANCES ON:	MFG	
PL DECIMALS ±	QUALITY	
PL DECIMALS ±	ISSUED	
ANGLES ±		
FRACTIONS ±		



**GE Consumer & Industrial**

TITLE

RATING LABEL

FIRST MADE FOR

DRAWING FILE 10080802P4.tif  
REFERENCE

SIZE A CAGE CODE

DWG NO

10080802

⊖ CRITICAL TO QUALITY CHARACTERISTIC

SCALE

NTS

SHEET 1 OF 1