



中国国家强制性产品认证证书

证书编号: 2018010304128277

委托人名称、地址

ABB France

2 rue d'Arsonval 69680 Chassieu France

生产者(制造商)名称、地址

ABB France

2 rue d'Arsonval 69680 Chassieu France

生产企业名称、地址

ABB Bulgaria E00D - Rakovski branch

BULGARIA, 4142 Village of Stryama, Region of Plovdiv, Municipality of Rakovski, Rakovski Industrial Zone, 14 Industrial Road 1, nr,14-18

产品名称和系列、规格、型号

切换电容器接触器

UA50...RA,UA63...RA,UA75...RA: 详情见附件

产品标准和技术要求

GB/T 14048.4-2010

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求,
特发此证。

发证日期: 2020 年 08 月 07 日有效期至: 2023 年 11 月 05 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2018 年 11 月 05 日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询

经中国合格评定国家认可委员会认可 CNAS C001-P



主 任:

陆梅



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2018010304128277

NAME AND ADDRESS OF THE APPLICANT

ABB France
2 rue d'Arsonval 69680 Chassieu France

NAME AND ADDRESS OF THE MANUFACTURER

ABB France
2 rue d'Arsonval 69680 Chassieu France

NAME AND ADDRESS OF THE FACTORY

ABB Bulgaria EOOD – Rakovski branch
BULGARIA, 4142 Village of Stryama, Region of Plovdiv, Municipality of Rakovski, Rakovski
Industrial Zone, 14 Industrial Road 1, nr.14-18

PRODUCT NAME, MODEL AND SPECIFICATION

Contactors for capacitor switching
UA50...RA,UA63...RA,UA75...RA: See the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.4-2010

This is to certify that the above mentioned product(s) complies with therequirements of implementation rules for compulsory certification(REFNO.CNCA-C03-02:2014).

Valid from: Aug.07,2020**Valid until:**Nov.05,2023

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Nov.05,2018

The certificate information is available through CNCA's website: www.cnca.gov.cn

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

附 录

第 1 页 共 2 页

证书编号: 2018010304128277

纸 号: 2658601

UA50...RA, UA63...RA, UA75...RA

U_{imp} : 8kV;

U_i : 1000V;

UA50...RA:

I_{th} : 100A;

AC-6b: U_e/Q_e : 220-230-240V/25kvar, 400-415V/40kvar, 440V/50kvar,
500-550V/55kvar, 660-690V/72kvar;

I_e : 66A;

UA63...RA:

I_{th} : 125A;

AC-6b: U_e/Q_e : 220-230-240V/30kvar, 400-415V/50kvar, 440V/55kvar,
500-550V/65kvar, 660-690V/80kvar;

I_e : 76A;

UA75...RA:

I_{th} : 125A;

AC-6b: U_e/Q_e : 220-230-240V/35kvar, 400-415V/60kvar, 440V/65kvar,
500-550V/75kvar, 660-690V/100kvar;

I_e : 88A;

U_s : 24V 50/60Hz, 42V 50/60Hz, 110V 50Hz/110-120V 60Hz,

220-230V 50Hz/230-240V 60Hz, 380-400V 50Hz/400-415V 60Hz,

400-415V 50Hz/415-440V 60Hz;

IP10;

极数: 3P

型号解释:

注: 此附录与证书同时使用时有效。



主 任:

陆 楠



中国质量认证中心



中国国家强制性产品认证证书

附 录

第 2 页 共 2 页

证书编号: 2018010304128277

纸 号: 2658601

Example 例如: UA50-30-00RA-85					
UA	50	-30	-00	RA	-85
I	II	III	IV	V	VI

I - Name of series 系列名称

UA series UA 系列

II - Size of contactor 大小

50, 63, 75

III - Number of main contacts 主触头数量

30 = 3 NO- and 0 NC-contacts

IV - Number of auxiliary contacts 辅助触头数量

00 = No auxiliary pole provided.

V - RA means with insertion of damping resistors 带电阻模块

VI - Coil code 线圈代号

Control voltage 控制电压		Coil code 线圈代号
50Hz	60Hz	
24	24	81
42	42	82
110	110-120	84
220-230	230-240	80
380-400	400-415	85
400-415	415-440	86

注: 此附录与证书同时使用时有效。



主 任:

陆 楠



中国质量认证中心