

SAFETY PRODUCTS

# Safe door monitoring with interlock for low risk

## Sentry, MKey5 and contactor

- Simple solution
- Easy to install
- Cost effective



### Application

For low risk machines (where the risk assessment shows that the possible injuries are minor or reversible), simpler solutions are often enough. For instance an interlock (monitoring) function supervising a single door or hatch using a safety key switch and safety relay.

MKey5 is a simple and cost-effective solution if a safety level up to PL c/SIL 1 is required, see below. The safety relay can be configured for manual or automatic reset. (For manual reset a reset button is required, see illustration.)

Using a single contactor to cut power to the machine is sufficient for reaching PL c/SIL 1.

### Functional safety level

This is a one-channel solution that fulfills up to Category 1, PL c according to EN ISO 13849-1 and up to SIL 1 according to EN 62061. MKey5 meets the low-level coding requirements according to EN ISO 14119 regarding manipulation protection. Measures to prevent tampering must be considered.



\* The reset button is only required if the safety relay is set to manual reset.



**Sentry SSR10P**

—  
**Sentry safety relay**  
 Choose between standard screw terminals or push-in terminals

Description	Type	Order code
Single function safety relay with screw terminals	Sentry SSR10	2TLA010050R0000
Single function safety relay with push-in terminals	Sentry SSR10P	2TLA010050R0001



**MKey5**

—  
**MKey safety switch**

Description	Type	Order code
Safety interlock switch, plastic body and head. 2NO+1NC guard open. 3xM20 conduit entries. Delivered with standard key.	MKey5	2TLA050003R0100

Note that alternative models are available both for the switch and the key (see [Safety Products catalog](#)).



**Smile 11 RA**

—  
**Reset button**

Description	Type	Order code
Reset button in Smile enclosure, 1xNO button, 1x Blue LED, 1x M12-5 male connector	Smile 11 RA	2TLA030053R0000



**M12-C61**

—  
**Cables for reset button**  
 Choose suitable cable length

Description	Type	Order code
M12-5 cable length 3 meter	M12-C31	2TLA020056R0500
M12-5 cable length 6 meter	M12-C61	2TLA020056R0000

Note that alternative cable lengths are available (see [Safety Products catalog](#)).



**AFS09**

—  
**Safety contactors**  
 The AFS contactors are dedicated for safety applications. See [product sheet](#) for range and selection.

## Links

Product sheets	<a href="#">Sentry flyer</a> <a href="#">AF contactors for safety applications</a>
Web pages	<a href="#">Sentry SSR10</a> <a href="#">MKey5</a> <a href="#">Smile 11 RA</a> <a href="#">Contactors for safety applications - Motor protection and control</a>
Connection diagrams	<a href="#">Sentry connection diagrams with most safety devices</a> See SSR10 General E)
Manuals	<a href="#">Sentry SSR10</a> <a href="#">MKey5</a>