








6.18 Suction Cup Attachment

<p>Type: Suction Cup Attachment R 1/4" Female Thread Spring</p> <p>Part number: 91110230 Thread: R 1/4" Weight: 290 g Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment R 3/8" Female Thread Spring</p> <p>Part number: 91110231 Thread: R 3/8" Weight: 260 g Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment R 1/4" Male Thread Spring</p> <p>Part number: 91110232 Thread: R 1/4" Weight: 310 g Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment R 3/8" Male Thread Spring</p> <p>Part number: 91110233 Thread: R 3/8" Weight: 280 g Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment Female Thread</p> <p>Part number: 91110234 Thread: R 1/4" Weight: 216 g Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment Female Thread</p> <p>Part number: 91110235 Thread: R 3/8" Weight: 180 g Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment Male Thread</p> <p>Part number: 91110236 Thread: R 1/4" Weight: 210 g Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment Male Thread</p> <p>Part number: 91110237 Thread: R 3/8" Weight: 218 g Material: Aluminum/Steel</p>		






Filename: Kap6.fm, Mod date: 2005 04 07



<p>Type: Suction Cup Attachment R 1/4" Female Thread Spring</p> <p>Part number: 91110238</p> <p>Thread: R 1/4"</p> <p>Weight: 440 g</p> <p>Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment R 3/8" Female Thread Spring</p> <p>Part number: 91110239</p> <p>Thread: R 3/8"</p> <p>Weight: 420 g</p> <p>Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment R 1/4" Male Thread Spring</p> <p>Part number: 91110240</p> <p>Thread: R 1/4"</p> <p>Weight: 470 g</p> <p>Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment R 3/8" Male Thread Spring</p> <p>Part number: 91110241</p> <p>Thread: R 3/8"</p> <p>Weight: 450 g</p> <p>Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment R 1/4" Female Thread</p> <p>Part number: 91110242</p> <p>Thread: R 1/4"</p> <p>Weight: 265 g</p> <p>Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment R 3/8" Female Thread</p> <p>Part number: 91110243</p> <p>Thread: R 3/8"</p> <p>Weight: 275 g</p> <p>Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment R 1/4" Male Thread</p> <p>Part number: 91110244</p> <p>Thread: R 1/4"</p> <p>Weight: 285 g</p> <p>Material: Aluminum/Steel</p>		
<p>Type: Suction Cup Attachment R 3/8" Male Thread</p> <p>Part number: 91110245</p> <p>Thread: R 3/8"</p> <p>Weight: 295 g</p> <p>Material: Aluminum/Steel</p>		








6.35 Suction cups

<p>Main type: SAB circular bellow</p> <p>Type: Circular Suction cup Bellow SAB 40 -1/4" Female Thread</p> <p>Part number: 91206336</p> <p>Material: Perbunan (NBR)</p> <p>Dimension: 1/4" - Ø40 mm</p> <p>Weight: 14,3 g</p>	
<p>Type: Circular Suction cup Bellow SAB 40 -1/4" Male Thread</p> <p>Part number: 91207632</p> <p>Material: Perbunan (NBR)</p> <p>Dimension: 1/4" - Ø52 mm</p> <p>Weight: 19,6 g</p>	
<p>Type: Circular Suction cup Bellow SAB 50 -3/8" Female Thread</p> <p>Part number: 91207599</p> <p>Material: Perbunan (NBR)</p> <p>Dimension: 3/8" - Ø52 mm</p> <p>Weight: 32,3 g</p>	
<p>Type: Circular Suction cup Bellow SAB 50 -3/8" Male Thread</p> <p>Part number: 91207633</p> <p>Material: Perbunan (NBR)</p> <p>Dimension: 3/8" - Ø52 mm</p> <p>Weight: 45 g</p>	
<p>Type: Circular Suction cup Bellow SAB 60 -3/8" Female Thread</p> <p>Part number: 91206337</p> <p>Material: Perbunan (NBR)</p> <p>Dimension: 3/8" - Ø60 mm</p> <p>Weight: 40,0 g</p>	
<p>Type: Circular Suction cup Bellow SAB 60 -3/8" Male Thread</p> <p>Part number: 91207634</p> <p>Material: Perbunan (NBR)</p> <p>Dimension: 3/8" - Ø60 mm</p> <p>Weight: 50 g</p>	
<p>Type: Circular Suction cup Bellow SAB 80 -3/8" Female Thread</p> <p>Part number: 91206338</p> <p>Material: Perbunan (NBR)</p> <p>Dimension: 3/8" - Ø80 mm</p> <p>Weight: 63,0 g</p>	

Filename: Kap6.fm, Mod date: 2005 04 07

<p>Type: Circular Suction cup Bellow SAB 80 -3/8" Male Thread Part number: 91207635 Material: Perbunan (NBR) Dimension: 3/8" - Ø80 mm Weight: 75 g</p>	
<p>Type: Circular Suction cup Bellow SAB 100 -3/8" Female Thread Part number: 91206339 Material: Perbunan (NBR) Dimension: 3/8" - Ø100 mm Weight: 88,2 g</p>	
<p>Type: Circular Suction cup Bellow SAB 100 -3/8" Male Thread Part number: 91207636 Material: Perbunan (NBR) Dimension: 3/8" - Ø100 mm Weight: 100 g</p>	
<p>Type: Circular Suction cup Bellow SAB 125 -3/8" Female Thread Part number: 91206340 Material: Perbunan (NBR) Dimension: 3/8" - Ø125 mm Weight: 170,2 g</p>	
<p>Type: Circular Suction cup Bellow SAB 125 -3/8" Male Thread Part number: 91207640 Material: Perbunan (NBR) Dimension: 3/8" - Ø125 mm Weight: 182 g</p>	

<p>Main type: FSGA soft</p> <p>Type: Circular Suction cup Bellow FSGA 30 VU -1/4" Female Thread</p> <p>Part number: 91206341</p> <p>Material: Vulkollan (VU)</p> <p>Dimension: 1/4" - Ø30 mm</p> <p>Weight: 14,2 g</p>	
<p>Type: Circular Suction cup Bellow FSGA 50 VU -3/8" Female Thread</p> <p>Part number: 91206342</p> <p>Material: Vulkollan (VU)</p> <p>Dimension: 3/8" - Ø50 mm</p> <p>Weight: 30 g</p>	
<p>Type: Circular Suction cup Bellow FSGA 85 VU -3/8" Female Thread</p> <p>Part number: 91206343</p> <p>Material: Vulkollan (VU)</p> <p>Dimension: 3/8" - Ø85 mm</p> <p>Weight: 113 g</p>	


Main type: SAF circular flat		
Type: Circular Suction cup SAF 30 -1/4" Female Thread Part number: 91207600 Material: Perbunan (NBR) Dimension: 1/4" - Ø32 mm Weight: 25,5 g		
Type: Circular Suction cup SAF 40 -1/4" Female Thread Part number: 91207601 Material: Perbunan (NBR) Dimension: 1/4" - Ø42 mm Weight: 27,5 g		
Type: Circular Suction cup SAF 50 -3/8" Female Thread Part number: 91207602 Material: Perbunan (NBR) Dimension: 3/8" - Ø52 mm Weight: 30,7 g		
Type: Circular Suction cup SAF 60 -3/8" Female Thread Part number: 91206821 Material: Perbunan (NBR) Dimension: 3/8" - Ø60 mm Weight: 37,3 g		
Type: Circular Suction cup SAF 80 -3/8" Female Thread Part number: 91206822 Material: Perbunan (NBR) Dimension: 3/8" - Ø80 mm Weight: 50,0 g		
Type: Circular Suction cup SAF 100 -3/8" Female Thread Part number: 91206823 Material: Perbunan (NBR) Dimension: 3/8" - Ø100 mm Weight: 67,2 g		
Type: Circular Suction cup SAF 125 -3/8" Female Thread Part number: 91206824 Material: Perbunan (NBR) Dimension: 3/8" - Ø125 mm Weight: 146,0 g		

Filename: Kap6.fm, Mod date: 2005 04 07

<p>Main type: SAOB oval bellow</p>	
<p>Type: Oval Suction cup Bellow SAOB 30x60 -1/4" Female Thread Part number: 91207300 Material: Perbunan (NBR) Dimension: 1/4" - 30 x 60 mm Weight: 47,9 g</p>	
<p>Type: Oval Suction cup Bellow SAOB 30x60 -3/8" Female Thread Part number: 91207607 Material: Perbunan (NBR) Dimension: 3/8" - 30 x 60 mm Weight: 56,7 g</p>	
<p>Type: Oval Suction cup Bellow SAOB 40x80 -1/4" Female Thread Part number: 91206868 Material: Perbunan (NBR) Dimension: 1/4" - 40 x 80 mm Weight: 55,2 g</p>	
<p>Type: Oval Suction cup Bellow SAOB 40x80 -3/8" Female Thread Part number: 91207608 Material: Perbunan (NBR) Dimension: 3/8" - 40 x 80 mm Weight: 64,0 g</p>	
<p>Type: Oval Suction cup Bellow SAOB 40x80 -3/8" Male Thread Part number: 91207638 Material: Perbunan (NBR) Dimension: 3/8" - 40 x 80 mm Weight: 72 g</p>	
<p>Type: Oval Suction cup Bellow SAOB 55x110 -3/8" Female Thread Part number: 91207609 Material: Perbunan (NBR) Dimension: 3/8" - 55 x 110 mm Weight: 111,3 g</p>	
<p>Type: Oval Suction cup Bellow SAOB 70x140 -3/8" Female Thread Part number: 91207610 Material: Perbunan (NBR) Dimension: 3/8" - 70 x 140 mm Weight: 146,3 g</p>	

Main type: SAOF oval flat	
Type: Oval Suction cup SAOF 16x50 -1/4" Female Thread Part number: 91207639 Material: Perbunan (NBR) Dimension: 1/4" - 16 x 50 mm Weight: 33,4 g	
Type: Oval Suction cup SAOF 23x60 -3/8" Female Thread Part number: 91207603 Material: Perbunan (NBR) Dimension: 3/8" - 23 x 60 mm Weight: 29,3 g	
Type: Oval Suction cup SAOF 30x90 -1/4" Female Thread Part number: 91207298 Material: Perbunan (NBR) Dimension: 1/4" - 30 x 90 mm Weight: 51,5 g	
Type: Oval Suction cup SAOF 30x90 -3/8" Female Thread Part number: 91207598 Material: Perbunan (NBR) Dimension: 3/8" - 30 x 90 mm Weight: 60,3 g	
Type: Oval Suction cup SAOF 40x80 -1/4" Female Thread Part number: 91207299 Material: Perbunan (NBR) Dimension: 1/4" - 40 x 80 mm Weight: 47,0 g	
Type: Oval Suction cup SAOF 40x80 -3/8" Female Thread Part number: 91207597 Material: Perbunan (NBR) Dimension: 3/8" - 40 x 80 mm Weight: 55,8 g	
Type: Oval Suction cup SAOF 40x80 -3/8" Male Thread Part number: 91207637 Material: Perbunan (NBR) Dimension: 3/8" - 40 x 80 mm Weight: 63 g	
Type: Oval Suction cup SAOF 50x100 -3/8" Female Thread Part number: 91207604 Material: Perbunan (NBR) Dimension: 3/8" - 50 x 100 mm Weight: 85,3 g	

Filename: Kap6.fm, Mod date: 2005 04 07

<p>Type: Oval Suction cup SAOF 60x120 -3/8" Female Thread Part number: 91207605 Material: Perbunan (NBR) Dimension: 3/8" - 60 x 120 mm Weight: 99,4 g</p>	
<p>Type: Oval Suction cup SAOF 70x140 -3/8" Female Thread Part number: 91207606 Material: Perbunan (NBR) Dimension: 3/8" - 70 x 140 mm Weight: 107,3 g</p>	