



中国国家强制性产品认证证书

证书编号：2013010304646608

委托人名称、地址

ABB France

3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

生产者（制造商）名称、地址

ABB France

3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

生产企业名称、地址

ABB 新会低压开关有限公司

广东省江门市新会区今古洲工业开发区

产品名称和系列、规格、型号

接触器

AX06-30-□□-□□、AX09-30-□□-□□、AX12-30-□□-□□、AX18-30-□□-□□、 AX25-30-□□-□□；

详细型号解释见附录

产品标准和技术要求

GB/T14048. 4-2010

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求，
特发此证。

发证日期：2018 年 05 月 17 日 有效期至：2023 年 05 月 17 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书，证书首次颁发日期：2013 年 09 月 30 日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询



主任：



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2013010304646608

NAME AND ADDRESS OF THE APPLICANT

ABB France
3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

NAME AND ADDRESS OF THE MANUFACTURER

ABB France
3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

NAME AND ADDRESS OF THE FACTORY

ABB Xinhui Low Voltage Switchgear Co., Ltd.
Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province,
P.R.China

PRODUCT NAME, MODEL AND SPECIFICATION

contactor
AX06-30-□□-□□、AX09-30-□□-□□、AX12-30-□□-□□、AX18-30-□□-□□、 AX25-30-□□-□□
□; See the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T14048.4-2010

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO.CNCA-C03-02:2014).

Valid from: May.17,2018

Valid until: May.17,2023

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Sep.30,2013

The certificate information is available through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

附录:

第 1 页 共 4 页

证书编号: 2013010304646608

纸号: 1931905

型号: AX06-30-□□-□□、AX09-30-□□-□□、

AX12-30-□□-□□、AX18-30-□□-□□、AX25-30-□□-□□;

I_{th} : AX06: 22A, AX09: 24A, AX12: 26A, AX18: 28A, AX25: 32A;

U_i : 690V;

U_s :

频率	U_s (V~)									
50Hz	24	48	105	110	190	200	220-230	230-240	380-400	400-415
60Hz	24	48	110-127	110-120	220	200-220	230-240	240-260	400-415	415-440

极数: 3P;

使用类别、 U_c 、 I_c :

使用类别	U_c (V~)	I_c (A)				
		AX06	AX09	AX12	AX18	AX25
AC-3	220-230-240V	7A	9A	12A	18A	25A
AC-3	380-400V	7A	9A	12A	18A	25A
AC-3	415V	7A	9A	12A	18A	25A
AC-3	440V	7A	9A	9A	12A	16A
AC-3	500V	6A	9A	9A	12A	14A
AC-3	690V	5A	7A	7A	9A	10A
AC-8a	400V	9A	12A	16A	22A	30A
AC-1	690V	20A	22A	25A	27A	32A

注: 此附录与证书同时使用时有效。



主任:



中国质量认证中心



中国国家强制性产品认证证书

附录:

第 2 页 共 4 页

证书编号: 2013010304646608

纸号: 1931905

内置式辅助触头: 1NO, 1NC; I_{th} : 16A;
使用类别、 U_c 、 I_c :

使用类别	$U_c(V)$	$I_c(A)$
AC-15	24-127VAC	6
AC-15	220-240VAC	4
AC-15	380-440VAC	3
AC-15	500VAC	2
AC-15	690VAC	2
DC-13	24VDC	6
DC-13	48VDC	2.8
DC-13	72VDC	2
DC-13	125VDC	1.1
DC-13	250VDC	0.55

注: 此附录与证书同时使用时有效。



主任:



中国质量认证中心



中国国家强制性产品认证证书

附录:


第 3 页 共 4 页

证书编号: 2013010304646608

纸号: 1931905

型号解释

AX □□ - 3 0 - □□ - □□



注: 此附录与证书同时使用时有效。



主任:



中国质量认证中心



中国国家强制性产品认证证书

附录:

第 4 页 共 4 页

证书编号: 2013010304646608

纸号: 1931905

表一

额定工作电压 (Vac)		线径	匝数	线圈代号
50Hz	60Hz			
24	24	0.425	520	81
48	48	0.28	1040	83
105	110-127	0.19	2380	26
110	110-120	0.19	2380	84
190	220	0.14	4210	36
200	200-220	0.14	4250	75
220-230	230-240	0.125	4960	80
230-240	240-260	0.125	5150	88
380-400	400-415	0.095	8500	85
400-415	415-440	0.095	8780	86

注: 此附录与证书同时使用时有效。



主任:



中国质量认证中心