

PRODUCT HIGHLIGHTS

Color-Keyed® COLORKIT-PLUS

Everything you need to strip and crimp connections for #8 to #2 AWG.

Color-Keyed®



Value proposition

The COLORKIT-PLUS offers you 275 genuine Color-Keyed connectors for wire sizes #8 to #2 AWG, plus heat-shrink tubing, wire stripper and premium, ergonomic Comfort Crimp® compression tool — all in one convenient, portable kit.




Key differentiating features

- Everything you need to strip, crimp and protect connections, including the TBM1-WS wire stripping tool, TMB45S crimp tool, heat-shrink tubing and assorted connectors for #8–#2 AWG wire.
- Uses the T&B Color-Keyed long-barrel method of installing compression connectors, designed to provide a high degree of reliability and considerable time savings.
- TBM45S Comfort Crimp compression tool is color-coded to match and crimp the included connectors with the lowest handle force of any tool in its class, providing a UL listed crimp.
- Kit includes assortment of 17 different part numbers, including one-hole lugs, C-taps, long-barrel two-way splices and heat-shrink tubing.

- Durable black plastic carrying case with clear lid and handle.
- Foam insert keeps products and tools in place when case is closed, regardless of orientation.
- Metal latches hold lid closed.
- Includes extra-long splices for the most reliable crimp connections.
- Included C-tap connectors are ideal for pig tailing, two-way splicing or tapping unbroken continuous mains, and are UL approved for direct burial.
- Protect your connections from the elements with included heavy-wall heat-shrink tubing (heat source not included).

Applicable industries



— COLORKIT-PLUS contains:

Included connectors and heat-shrink tubing

Part no.	Description	Color code	No. of crimps	Bolt size	Qty	Wire size range (AWG)
54130	One-hole lug — Standard barrel	Red ■	2	¼	25	#8 Cu
54132	One-hole lug — Standard barrel	Red ■	2	⅜	25	#8 Cu
54105	One-hole lug — Standard barrel	Blue ■	2	¼	25	#6 Cu
54136	One-hole lug — Standard barrel	Blue ■	2	⅜	25	#6 Cu
54106	One-hole lug — Standard barrel	Gray ■	2	¼	10	#4 Cu
54140	One-hole lug — Standard barrel	Gray ■	2	⅜	10	#4 Cu
54143-TB	One-hole lug — Standard barrel	Brown ■	2	⅜	5	#2 Cu
54705	C-Tap	Red ■	2	—	25	Main 14–12 / Branch 16–14
54710	C-Tap	Blue ■	2	—	20	Main 10–8 / Branch 10–12
54715	C-Tap	Gray ■	2	—	20	Main 6–8 / Branch 8–12
54720	C-Tap	Brown ■	4	—	10	Main 8–4 / Branch 8–12
54725	C-Tap	Green ■	4	—	10	Main 5–3 / Branch 6–12
54804	Two-way splice — Long barrel	Red ■	4	—	25	#8 Cu
54805	Two-way splice — Long barrel	Blue ■	4	—	25	#6 Cu
54806	Two-way splice — Long barrel	Gray ■	4	—	10	#4 Cu
54807	Two-way splice — Long barrel	Brown ■	4	—	5	#2 Cu
HS12-6	Heat Shrink-3 black heavy-wall	—	—	—	20	#12–#6

Note: Product must be installed in accordance with applicable national and local electrical codes.

Included tools

Part no.	Description
TBM45S	Insulated crimp tool
TBM1-WS	Cable stripper

ABB Installation Products Inc.
Electrification Business
860 Ridge Lake Blvd.
Memphis, TN 38120

ABB Inc. has made every attempt to ensure the accuracy and reliability of the contents of this document. However, all content is provided for general informational purposes only, and ABB Inc. makes no guaranty or warranty, express or implied, as to the accuracy of any technical content, or that the information contained in this publication will be error free and all such guarantees or warranties are expressly

disclaimed. ABB Inc. may change or modify the contents at any time, without prior notice. We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction or utilization of its contents — in whole or in parts — is forbidden without prior written consent of ABB Inc.
© 2024 ABB Inc. All rights reserved