


■ DP/PA linking device LD 800P

■ Accessories for LD 800P



Ordering information

DP/PA linking device LD 800P		Catalog No.			
HS 810	1) Head Station to connect a PROFIBUS DP line up to 12 Mbit/s, 1 channel links up to 5 Power Link Modules for PROFIBUS PA	(63637)	3BDH000305R0101		
HS 820	2) Head Station to connect a PROFIBUS DP line up to 12 Mbit/s, 2 channels links up to 2 x 5 Power Link Modules for PROFIBUS PA	(63637)	3BDH000306R0101		
HS 840	3) Head Station to connect a redundant PROFIBUS DP line up to 12 Mbit/s, 4 channels links up to 4 x 5 Power Link Modules for PROFIBUS PA	(63637)	3BDH000307R0101		
PL 810	4) Power Link Module connect one single PROFIBUS PA line with 31.25 kBit/s Each Power Link Module needs at least a Head Station for the DP connection PA supply: U _s 24 ... 26 V DC, I _s ≤ 400 mA Incl. a fixed PA bus termination	(63637)	3BDH000311R0101		
PL 890	5) Power Link Mod. conn. one single PROFIBUS PA line [EE _x i] with 31.25 kBit/s Each Power Link Module needs at least a Head Station for the DP connection PA supply: U _s 12.8 ... 13.4 V DC, I _s ≤ 100 mA Incl. a fixed PA bus termination	(63637)	3BDH000312R0101		
<p>All particular modules of LD 800P are approved for installation in Ex zone 2 / Div. 2. Head Stations and Power Link Modules are certified to: - ATEX, Industrial IT enabled (FM, CSA pending)</p>					
LD 800P Media CD-ROM		(63638)	3BDS009466R0101		
<ul style="list-style-type: none"> - GSD conversion tool to optimize the GSD files of underlying PA slave devices, English and German - User Instructions in pdf-format, English and German - Service tool 					
LD 800P User Instruction, printed		(63638)	3BDD011704R0103		
		(63638)	3BDD011704R0101		
Accessories for LD 800P					
PF 900-NR	6) Power Feed Module Module for power rail mounting, supplies the PR 900-N with 24 V DC / 4A (redundant) Cable termination via plugable screw terminations	(63637)	3BDH000357		
PR 900-N	7) Power Rail, For devices type PF 9xx, PC 9xx, HS 8xx or PL 8xx etc., length 50 cm	(63637)	3BDH000355		
EP 900-N	7) Extension Plug, for power rail type PR 900-N, for connection of two PR 900-N	(63637)	3BDH000356		

- 1) Data sheet Doc-No.: 3BDD011713R0101
- 2) Data sheet Doc-No.: 3BDD011714R0101
- 3) Data sheet Doc-No.: 3BDD011715R0101
- 4) Data sheet Doc-No.: 3BDD011711R0201
- 5) Data sheet Doc-No.: 3BDD011712R0201
- 6) Data sheet Doc-No.: 3BDD011868R101
- 7) Data sheet Doc-No.: 3BDD011869R101

ABB has Sales & Customer Support
expertise in over 100 countries worldwide.

www.abb.com/fieldbus

The Company's policy is one of continuous product
improvement and the right is reserved to modify the
information contained herein without notice.

Printed in the Fed. Rep. of Germany (12.2005)

© ABB 2005



ABB Automation Products GmbH

Borsigstr. 2
63755 Alzenau
Germany
Tel: +49 551 905-534
Fax: +49 551 905-555
CCC-support.deapr@de.abb.com