

Industrial plugs and sockets Off the shelf



It is all about service and simplicity, availability and efficiency, plug and play. Some things should just be there when you need them. Like when you can not find the charger for your phone while the battery is low and you have to make an important call, the same feeling of crisis appears when you do not have the correct plug and socket for the equipment you need to use to your job.

On the following pages we have gathered the industrial plugs and sockets that we think needs to be available off the shelf from the wholesaler for the installer or end-user, of course we hold inventory of a much larger range at our central warehouses.



216-P6



432-C6

Terminals/ Poles	Voltage V	Frequency Hz	Type	Order code	Pack qty	Weight kg/ea
Plugs 16 A, IP44, Splashproof						
2P+E	200-250	50 and 60	216-P6	2CMA193501R1000	1	0.11
3P+E	380-415		316-P6	2CMA193506R1000		0.16
3P+N+E	346-415		416-P6	2CMA193511R1000		0.17
Plug 32 A, IP44 Splashproof						
3P+N+E	346-415	50 and 60	432-P6	2CMA193519R1000	1	0.23
Plug 63 A, IP44 Splashproof						
3P+N+E	346-415	50 and 60	463-P6	2CMA166764R1000	1	0.75
Connectors 16 A, IP44, Splashproof						
2P+E	200-250	50 and 60	216-C6	2CMA193521R1000	1	0.16
3P+E	380-415		316-C6	2CMA193523R1000		0.21
3P+N+E	346-415		416-C6	2CMA193526R1000		0.23
Connector 32 A, IP44, Splashproof						
3P+N+E	346-415	50 and 60	432-C6	2CMA193531R1000	1	0.30
Connector 63 A, IP44, Splashproof						
3P+N+E	346-415	50 and 60	463-C6	2CMA166862R1000	1	0.88


Ordering details



416RS6



463MHS6



416T6



CUE 416-6+R/UJP



UJ 110/2

Surface socket outlets 16 A, IP44 Splashproof

Terminals/ Poles	Voltage V	Frequency Hz	Type	Order code	Pack qty	Weight kg/ea
2P+E	200-250	50 and 60	216RS6	2CMA193098R1000	1	0.22
3P+E	380-415		316RS6	2CMA193106R1000		0.24
3P+N+E	346-415		416RS6	2CMA193115R1000		0.26

Surface socket outlets 32 A, IP44 Splashproof

Terminals/ Poles	Voltage V	Frequency Hz	Type	Order code	Pack qty	Weight kg/ea
2P+E	200-250	50 and 60	232RS6	2CMA193122R1000	1	0.30
3P+E	380-415		332RS6	2CMA193130R1000		0.32
3P+N+E	346-415		432RS6	2CMA193139R1000		0.34

Surface socket outlet 63 A, IP44 Splashproof

Terminals/ Poles	Voltage V	Frequency Hz	Type	Order code	Pack qty	Weight kg/ea
3P+N+E	346-415	50 and 60	463RS6	2CMA167484R1000	1	1.05

Switched interlocked socket outlets 16 A, IP44, Splashproof

Terminals/ Poles	Voltage V	Frequency Hz	Type	Order code	Pack qty	Weight kg/ea
2P+E	200-250	50 and 60	216MHS6	2CMA167623R1000	1	0.55
3P+N+E	346-415		416MHS6	2CMA167640R1000		0.61

Switched interlocked socket outlet 32 A, IP44, Splashproof

Terminals/ Poles	Voltage V	Frequency Hz	Type	Order code	Pack qty	Weight kg/ea
3P+N+E	346-415	50 and 60	432MHS6	2CMA167686R1000	1	0.66

Switched interlocked socket outlet 63 A, IP44, Splashproof

Terminals/ Poles	Voltage V	Frequency Hz	Type	Order code	Pack qty	Weight kg/ea
3P+N+E	346-415	50 and 60	463MHS6	2CMA167727R1000	1	2.10

Terminals/ Poles	Voltage V	Frequency Hz	Type	Order code	Pack qty	Weight kg/ea
------------------	-----------	--------------	------	------------	----------	--------------

Three way adaptor, 16 A, Splashproof

Terminals/ Poles	Voltage V	Frequency Hz	Type	Order code	Pack qty	Weight kg/ea
23P++NE	346-415	50 and 60	416T6	2CMA168124R1000	1	0.89

Surface socket outlet with schuko, 16 A, IP44, Splashproof

Terminals/ Poles	Voltage V	Frequency Hz	Type	Order code	Pack qty	Weight kg/ea
3P+N+E	400/230	50 and 60	CUE 416-6+R/UJP	2C2CMA178301R1000	1	0.34

Terminals/ Poles	Number of outlets	Conductor area, mm ²	Cable entry Hz	Type	Order code	Pack qty	Weight kg/ea
------------------	-------------------	---------------------------------	----------------	------	------------	----------	--------------

Schuko outlets, 10/16 A, 250 V, IP 44, Splashproof

Terminals/ Poles	Number of outlets	Conductor area, mm ²	Cable entry Hz	Type	Order code	Pack qty	Weight kg/ea
1P+E	1	2.5	2xM20	UJ 210/2	2CMA178339R1000	1	0.30
	2			UJ 110/2	2CMA178338R1000		0.60
	4		2xM20+2xM25	UJ 410	2CMA178341R1000		0.90

For more information, please contact:

ABB AB
Electrification Products
 Box 1005
 SE-611 29 NYKÖPING, Sweden
 Phone: +46 155 29 50 00
 Fax: +46 155 28 81 10
www.abb.com

© Copyright 2016 ABB. All rights reserved
 Specification subject to change without notice



Below QR-code is linked to our web site www.abb.com/lowvoltage. You will have to download a QR-code reader app to your phone in order to use it.