

---

PRODUCT BROCHURE

## **Steel City<sup>®</sup> adjustable mud ring**

Inner ring adjusts ½" to 1½" in depth —  
before or after drywall installation



---

# Steel City® adjustable mud ring

## Finally, a quick, easy solution for a common rough-in problem

Now there's a quick, easy and economical way to ensure that stud-mounted outlet boxes fit flush with finished drywall, plaster or ceramic tile. The Steel City adjustable mud ring features an inner ring that adjusts from  $\frac{1}{2}$ " to  $1\frac{1}{2}$ " in depth to accommodate various drywall thicknesses. Marked with a measured rule and equipped with two adjustment screws, the inner ring can be set to the anticipated depth prior to installation and then easily adjusted after drywall installation to accommodate any variation in depth ( $\frac{1}{2}$  to  $1\frac{1}{2}$ ). Rely on the Steel City adjustable mud ring for a code-compliant finish in many applications.



**Typical applications:**

- Outside firewalls in hotel, casino and residential high-rise structures
- Hospital construction, where drywall depth often varies
- Ceramic-tile walls
- Any other application in which a stud-mounted box and mud ring may require depth adjustment prior to final trim work



## Steel City® adjustable mud ring

Adjustability enables flush fit with drywall every time



### Adjustable mud ring installation/adjustment steps:

#### Rough-in phase:

- Install mud ring to box with the inner ring in the extended position
- Set the depth of the inner ring to the anticipated drywall/tile thickness and lock into place by tightening adjustment screws

Note: Mud ring is shipped assembled with the inner ring not preset.

#### Problem: Ring is set too far back/forward

#### Solution:

- 1 Loosen...**  
The 2 adjustment screws located in opposing corners of the mud ring.
- 2 Adjust...**  
Inner ring to be flush with wall surface.
- 3 Re-tighten...**  
Adjustment screws.

- Patent-pending design, rugged steel construction similar to standard mud ring but with greater flexibility
- Quick-release locking mechanism enables fast and easy adjustment of inner ring
- Locking mechanism located behind outer ring remains safe from router damage or excess mudding
- Adjustment screws located outside inner ring leave maximum capacity for devices — won't take up crucial box area
- Measured rule on inner ring for simple pre-fab setting in pre-drywall installs
- Mounts to any standard 4"-square 2 1/8" deep outlet box such as Steel City 521711234E
- Accepts industry-standard devices, including GFCIs
- UL® Listed component
- Not intended for 1 1/2" deep boxes



### Steel City adjustable mud ring



Cat. no.	Description	Std. pkg. qty.	UPC no.
52-C-ADJ	Single-gang adjustable mud ring, 1/2" to 1 1/2"	25	785991-04454



---

**ABB Inc.**

Electrification Products  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Customer Service: 800-816-7809  
Technical Support: 888-862-3289

**[abb.com/lowvoltage](http://abb.com/lowvoltage)**