

PRODUCT SPECIFICATION

# IR2OW3L261

## Aqualux Self-Contained IP65 IR2 Surface

Catalogue Number **IR2OW3L261**  
 GID **7TCA091170R0008**  
 Warranty **3 Year/s Refer to ABB warranty terms & conditions**  
 Power Supply System **Self-Contained (individual battery)**  
 Mounting Method/Form **Ceiling, Wall Surface**  
 Housing Material **Aluminium/Plastic**  
 Colour **White/Silver**  
 Dimensions (LxWxD) **381 x 170 x 75 mm**  
 Temperature Range **0 to 25°C**  
 Weight **1.7 Kg**

Emergency Duration (Hours) **3 Hours**  
 Battery **NiCd**  
 Monitoring Equipment **IR2 test**  
 Lamp **2 x 2W LED**  
 Emergency Light Output (Lumens) **89**  
 Average Lifespan light source (Hours) **100000 Hours**  
 Light Colour/Temperature/CRI **White / 6350 / 73**  
 Degree of Protection **IP65 IK10**

Type of Legend **Single Sided (Order separate)**  
 Exit Sign Viewing/Recognition Distance (m) **25**  
 Nominal Voltage **220-240v AC 50Hz**  
 Power Consumption **9.9 VA / 5.1 Watts**  
 Current **Nominal: 42.5mA (mA) Inrush: 18A**

### Accessories

**XEN2W** Down ISO7010 Legend for Backlit Exit Sign  
**XEN3W** Left ISO7010 Legend for Backlit Exit Sign  
**XEN6W** Right ISO7010 Legend for Backlit Exit Sign  
**XEN5W** Up ISO7010 Legend for Backlit Exit Sign  
**XLF802W** Fire Extinguisher Legend for Backlit Exit Sign  
**XLF803W** Hose Reel Legend for Backlit Exit Sign

**OW/BCM** Ceiling Bracket for Vertical Mount  
**OW/BWA** Wall Bracket for Angled Mount  
**OW/BWM** Cantilever Bracket for End to Wall Mount  
**OW/BCR** Recessing Kit  
**OW/DSC** Blank double sided diffuser for Edgelite Exit Sign

**RSEN2W** Down ISO7010 Legend for Edgelit Exit Sign (Single Sided)  
**RSEN3W** Left ISO7010 Legend for Edgelit Exit Sign (Single Sided)  
**RSEN6W** Right ISO7010 Legend for Edgelit Exit Sign (Single Sided)  
**RSEN5W** Up ISO7010 Legend for Edgelit Exit Sign (Single Sided)  
**RSEN3W/RSEN6W** Left+Right ISO7010 Legend for Edgelit Exit Sign (Double Sided)



**Edgelit Exit Sign**  
 IR2OW3L261 + RSEN5W + OW/DSC



**Backlit Exit Sign**  
 IR2OW3L261 + XEN5W



**Bulkhead**  
 IR2OW3L261

