


FurseWELD

Cable to cable CC7

Cable to cable CC7 - FurseWELD



Stranded/solid circular conductor size A (mm ²)	Stranded/solid circular conductor size B (mm ²)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
16 *	16 *	CC7-4-1616	7TCA083910R1566	65P10	HCPK4
25	25	CC7-4-2525	7TCA083910R1575	45P10	HCPK4
35	35	CC7-4-3535	7TCA083910R1577	65P10	HCPK4
35	25	CC7-4-3525	7TCA083910R1576	65P10	HCPK4
50	50	CC7-4-5050	7TCA083910R1581	90P10	HCPK4
50	35	CC7-4-5035	7TCA083910R1580	90P10	HCPK4
50	25	CC7-4-5025	7TCA083910R1579	65P10	HCPK4
70	70	CC7-4-7070	7TCA083910R1585	115P10	HCPK4
70	50	CC7-4-7050	7TCA083910R1584	115P10	HCPK4
70	35	CC7-4-7035	7TCA083910R1583	90P10	HCPK4
70	25	CC7-4-7025	7TCA083910R1582	90P10	HCPK4
95	95	CC7-4-9595	7TCA083910R1589	150P10	HCPK4
95	70	CC7-4-9570	7TCA083910R1588	115P10	HCPK4
95	50	CC7-4-9550	7TCA083910R1587	115P10	HCPK4
95	35	CC7-4-9535	7TCA083910R1586	115P10	HCPK4
120	120	CC7-4-120120	7TCA014980R0101	200P10	HCPK4
120	95	CC7-4-12095	7TCA083910R1561	200P10	HCPK4
120	70	CC7-4-12070	7TCA083910R1560	150P10	HCPK4
120	50	CC7-4-12050	7TCA083910R1559	150P10	HCPK4
150	150	CC7-5-150150	7TCA083910R1590	2 x 150P10	HCPK5
150	120	CC7-4-150120	7TCA083910R1563	250P10	HCPK4
150	95	CC7-4-15095	7TCA083910R1565	200P10	HCPK4
150	70	CC7-4-15070	7TCA083910R1564	150P10	HCPK4
185	185	CC7-5-185185	7TCA083910R1591	2 x 150P10	HCPK5
185	150	CC7-5-185150	7TCA083910R2962	2 x 150P10	HCPK5
185	120	CC7-4-185120	7TCA083910R1568	250P10	HCPK4
185	95	CC7-4-18595	7TCA083910R1572	200P10	HCPK4
240	240	CC7-5-240240	7TCA083910R1593	2 x 200P10	HCPK5
240	185	CC7-5-240185	7TCA083910R2963	2 x 200P10	HCPK5
240	150	CC7-5-240150	7TCA083910R1592	2 x 150P10	HCPK5
240	120	CC7-4-240120	7TCA083910R1573	250P10	HCPK4
300	300	CC7-5-300300	7TCA083910R1596	2 x 250P10	HCPK5
300	240	CC7-5-300240	7TCA083910R1595	2 x 250P10	HCPK5
300	185	CC7-5-300185	7TCA083910R2964	2 x 200P10	HCPK5
300	150	CC7-5-300150	7TCA083910R1594	2 x 150P10	HCPK5

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

*4 x S103 Sleeve required when joining conductors 16 mm² or smaller

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection