

PCV z pionowymi szczelinami

Kanały grzebienione



Kanały grzebienione 8/12 mm

Numer Ref.	Numer GID	Wymiary		Dł. Całk. w Opk. [m]	Ilość sztuk w opakowaniu [sztuk po 2 m]
		Szer.W [mm]	Wys.H [mm]		
05 019	M050190000	15	17	46	23
05 033	M050330000	25	30	58	29
05 035	M050350000	40	30	38	19
05 037	M050370000	60	30	52	26
05 043	M050430000	25	40	48	24
05 045	M050450000	40	40	30	15
05 047	M050470000	60	40	40	20
05 049	M050490000	80	40	32	16
05 051	M050510000	100	40	24	12
05 053	M050530000	120	40	20	10
05 063	M050630000	25	60	34	17
05 065	M050650000	40	60	22	11
05 067	M050670000	60	60	32	16
05 069	M050690000	80	60	24	12
05 071	M050710000	100	60	20	10
05 073	M050730000	120	60	14	7
05 083	M050830000	25	80	28	14
05 085	M050850000	40	80	36	18
05 087	M050870000	60	80	24	12
05 089	M050890000	80	80	16	8
05 091	M050910000	100	80	16	8
05 093	M050930000	120	80	12	6
05 094	M050940000	25	100	20	10
05 095	M050950000	40	100	28	14
05 096	M050960000	60	100	20	10
05 097	M050970000	80	100	14	7
05 098	M050980000	100	100	8	4
05 099	M050990000	150	100	8	4

Kanały grzebienione 4/6 mm

Numer Ref.	Numer GID	Wymiary		Dł. Całk. w Opk. [m]	Ilość sztuk w opakowaniu [sztuk po 2 m]
		Szer.W [mm]	Wys.H [mm]		
05 119	M051190000	15	17	46	23
05 133	M051330000	25	30	58	29
05 135	M051350000	40	30	38	19
05 137	M051370000	60	30	52	26
05 143	M051430000	25	40	48	24
05 145	M051450000	40	40	30	15
05 147	M051470000	60	40	40	20
05 149	M051490000	80	40	32	16
05 151	M051510000	100	40	24	12
05 153	M051530000	120	40	20	10
05 163	M051630000	25	60	34	17
05 165	M051650000	40	60	22	11
05 167	M051670000	60	60	32	16
05 169	M051690000	80	60	24	12
05 171	M051710000	100	60	20	10
05 173	M051730000	120	60	14	7
05 183	M051830000	25	80	28	14
05 185	M051850000	40	80	36	18
05 187	M051870000	60	80	24	12
05 189	M051890000	80	80	16	8
05 191	M051910000	100	80	16	8
05 193	M051930000	120	80	12	6
05 194	M051940000	25	100	20	10
05 195	M051950000	40	100	28	14
05 196	M051960000	60	100	20	10
05 197	M051970000	80	100	14	7
05 198	M051980000	100	100	8	4
05 199	M051990000	150	100	8	4