

PANEL MARKS:

RNSB08B7245A

TECHNICAL SPECIFICATIONS

PANEL TYPE: ReliaGear neXT SuperBox
 QUANTITY: 1
 AMPS: 800A
 VOLTAGE: Up to 600V
 SYSTEM: 3P3W or 3P4W
 KAIC: Up to 200 KAIC SC FULLY RATED
 MATERIAL: COPPER BUS
 PLATE: SILVER PLATE
 ENCLOSURE: NEMA 1
 MOUNTING: SURFACE

MAIN DISCONNECT DEVICE

FEED DIR. Bottom
 TYPE: Breaker
 AMPS: 800A
 POLES: 3

INTERIOR X-VALUES



TOTAL X BUS AVAILABLE X BUS
 24 24

OPTIONS INCLUDED

QTY	DESCRIPTION
1	Copper Bus Heat Rated
1	47 Ckt bonded grd

BOM

QTY	CAT #	DESCRIPTION
1	GDBG47AL	Ground
1	IN2408NN3H2	Bus
1	NL12I0NSTNDAL	Neutral
1	ER7245A	Enclosure
1	IF2445F	Frame
1	FT45S00135	Front 1 of 2
1	FT45S00215	Front 2 of 2
1	GC45F24NNA	Gutter
6	SR03BF	Spacer
6	SR03BB	Spacer
2	SR02BF	Spacer
2	SR02BB	Spacer
2	SR01BF	Spacer
2	SR01BB	Spacer



PANEL INFORMATION	
INTERNAL DIMENSIONS	72"X45"X11"
NOTES	
EXTERNAL DIMENSIONS	72.3"X45.7"X11"

1. FML - FRAME MOUNTING LOCATION.
2. DRAWING NOT TO SCALE.
3. DIMENSIONS ARE IN INCHES[mm].

NEUTRAL ARE PRESSURE LUGS.

PROJECT NAME :	ABB	PANEL ID:	PRODUCT NAME:	DRAWING NO:
CUSTOMER:		CREATED BY:	ReliaGear neXT	ITEM NO:
		DATE:	PANELBOARD	MARKS:
		REVISION NO.		QUOTE NO:
				SHEET: