



Test Report				Date of issue: 13.6.2014					
				Serial No.: 3GP11027636					
				Tag No.:					
				Order No.: 596143-20 / 30171211-1					
				Type: M3GP 355SMC 4 B3					
				Product Code: 3GGP352230-ADG					
				Protection type: Ex nA IIC T3 Gc					
				Cert. No.: LCIE 12 ATEX 1008X IECEX LCI 07.0001X					
Rating:									
3~Motor Insul.cl.F IP55		V	Hz	kW	r/min	A	cos φ	Duty	
		400	D 50	355	1487	616	0,86	S1	
Resistance			Ambient: 21,5 °C		Insulation resistance at 41,5 °C				
Line					3000 MΩ		1000 V		
U ₁ - V ₁			0,00434 Ω						
U ₁ - W ₁			0,00434 Ω						
V ₁ - W ₁			0,00434 Ω						
High-voltage test winding					1800 V		60 s		
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]
No load test		399,9 D	50	168,0	5,03		1500	0,04	
Locked rotor test		75,8 D	50	615,8	23,5		0	0,29	
Thermal test (100% load)	2280,0	400,3 D	50	616,4	370,1	355,0	1487	0,87	95,9
Partial load points:									
~75% load	1716,1	400,3 D	50	470,6	276,8	266,3	1491	0,85	96,2
~50% load	1142,6	400,7 D	50	337,2	185,1	177,5	1494	0,79	95,9
~25% load	569,7	400,9 D	50	224,4	94,6	88,8	1497	0,61	93,8
Temperature rise at rated load.		[°C]		[K]	Method		Measurement method		
Stator winding :				79,4	1		1 Resistance		
Frame :				31,1	2		2 Thermometer		
Bearing D-end :				53,9	2		3 Thermocouples		
Ambient Temperature :		25,0			2				
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.									
On behalf of customer									
On behalf of manufacturer		Date of test		13.1.2012					
Tested by ABB Oy, Motors and Generators, Vaasa, Finland						Telephone +358 10 2211 Telefax +358 10 22 47372			

Computer print-out valid without signature.