

Contact us

ABB Oy

P.O. Box 622
FI-65101 Vaasa
Finland



abb.com/lowvoltage

© Copyright 2023 ABB. All rights reserved.
Specifications subject to change without notice.


34OT_G3-34 rev. A/ 1SCC301127M0201 # 11.12.2023




OT Plus OT30...160G3-




Mounting




Padlock



Adjustable neutral pole timing



Clearances per UL98



Minimum enclosure size or equivalent volume

| | H | W | D | A | B | C |
|----------|---------|--------|--------|---|---|--------|
| OT30G3- | 203 mm | 152 mm | 102 mm | 0 | 0 | 13 mm |
| OT60G3- | 8 in | 6 in | 4 in | | | 0.5 in |
| OT100G3- | 300 mm | 200 mm | 135 mm | 0 | 0 | 13 mm |
| | 11.8 in | 7.9 in | 5.3 in | | | 0.5 in |

| Wire type | 1 Wire (mm ²) | 2 Wire (mm ²) | Stripping length | Tightening torque |
|------------------------------------|---------------------------|---------------------------|------------------|-------------------|
| Class 5-Flexible | 4-70 | 4-25 | | |
| Class 2-Stranded | 4-70 | 4-25 | | |
| Class 6-Very flexible with ferrule | 2.5-4 | 2.5-4 | | |
| Class 1-Solid | 2.5-6 | 2.5-6 | | |
| UL - CU wire size (AWG) | 12-2/0 | 12-4 | | |



Warning! Hazardous voltage! Installation by person with electrotechnical expertise only.

