


## UniMotor

### Motor control center air insulated metal-clad switchboards


- Internal arc-proof construction
- Compact dimension
- Takes up to three contactors in one panel
- Connection and withdrawal of the contactor with the door closed
- Possibility of constructing all types of motor starting
- Can be coupled with UniSafe switchboards
- Wide use of recyclable material
- Production cycle certified ISO 14001



## Technical data

Switchboard	UniMotor+UniSafe		
Type of construction	Metal-clad	•	
Rated voltage	[kV]	12	
Insulation levels	[kV]	12/28/75	
Rated main busbar current (40 °C)	[A]	2500	
Rated branch connection current (40 °C)	[A]	630	
Rated short-time current	[kA]	31,5	
Arc proof withstand current	[kA]	31,5	
Tested according to	IEC Standards		
Overall dimensions of basic cubicle		H [mm]	2250
		W [mm]	900
		D [mm]	1850
Design includes:			
Vacuum contactors with fuses		•	
Integrated capacitor banks		•	
Earthing switch		•	
Bay computer		•	
Measuring transformers		•	
Measuring sensors		•	
Technical catalogue	No.	601347	

## Basic cubicle



For more information please contact:

### ABB S.p.A.

#### Power Products Division Unità Operativa Sace-MV

Via Friuli, 4  
I-24044 Dalmine  
Tel.: +39 035 6952 111  
Fax: +39 035 6952 874  
E-mail: sacetms.tipm@it.abb.com

### ABB AG

#### Calor Emag Medium Voltage Products

Oberhausener Strasse 33 Petzower Strasse 8  
D-40472 Ratingen D-14542 Glindow  
Phone: +49(0)2102/12-1230, Fax: +49(0)2102/12-1916  
E-mail: calor.info@de.abb.com

[www.abb.com](http://www.abb.com)

The data and illustrations are not binding. We reserve the right to make changes without notice in the course of technical development of the product.

Copyright 2009 ABB.  
All rights reserved.