


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB '19

On-load tap-changer type (V)UCGL./F, (V)UCLL./F, UCCL./F,  
 5 tap positions, linear switching.  
 Min. effective No. of turns in pos. 1.  
 The tap-changer is delivered set in pos. 3,  
 the preceding pos. was 2.

Lindningskopplare typ (V)UCGL./F, (V)UCLL./F, UCCL./F,  
 5 lägen, linjär koppling.  
 Min antal effektiva varv i läge 1.  
 Lindningskopplaren levereras inställd i läge 3,  
 föregående läge var 2.

Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	



The tap-changer is shown in pos. 3,  
 the preceding pos. was 2.  
 The tap selector is seen from above.  
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 3,  
 föregående läge var 2.  
 Väljaren sedd uppifrån.  
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the  
 tap-changer. Dashed lines show leads belonging  
 to the cleats and leads.

Heldragna linjer visar ledare som ingår i  
 lindningskopplaren. Streckade linjer visar  
 ledare som tillhör anslutningsdonet.

Drawn by Form No.	Sheet	Cont									
	Year	Week	Dept								
	Rev Ind	Revision	Appd	Year	Week						
	Design checked by	Accepted by qual control	Accepted for prod by	Description (English)		DATA ORIGINAL					
Drawing checked by	L.Oberg	M.Haggmar	Description (own language)		KOPPLINGSSCHEMA		File name				
Design checked by	H.Sundberg	A.Wang	Issued by Dept		Year	Week	Lang		Sheet		
Design checked by	N.Gustavsson	CO/TK	14	02			Rev Ind		Cont		
				1ZSC004308-AAA							