

Tmax molded case circuit-breakers

Tmax T7

Compliance with Standards

UL489
 CSA C22.2 No. 5.1
 IEC 60947-2
 EC Directive:
 - "Low voltage directives" (LVD) no. 73/23 EEC
 - "Electromagnetic compatibility directive" (EMC) no. 89/336 EEC




Type of circuit-breaker		Tmax T7		
Frame		1000/1200		
Rated ultimate short-circuit breaking capacity, Icu		S	H	L
(AC) 50-60 Hz 240 V	[kA]	65	100	150
(AC) 50-60 Hz 277 V	[kA]	-	-	-
(AC) 50-60 Hz 347 V	[kA]	-	-	-
(AC) 50-60 Hz 480 V	[kA]	50	65	100
(AC) 50-60 Hz 600V/347 V	[kA]	-	-	-
(AC) 50-60 Hz 600 V	[kA]	25	50	65
(DC) 250 V-2 poles in series	[kA]	-	-	-
(DC) 500 V-2 poles in series	[kA]	-	-	-
(DC) 500 V-3 poles in series	[kA]	-	-	-
(DC) 600 V-3 poles in series	[kA]	-	-	-
Trip units:				
T fixed, M fixed (10xIn) TMF		-		
T adj., M fixed (10xIn) TMD		-		
Thermomagnetic	T adj., M adj. (5...10xIn) TMA	-		
	T adj., M fixed (3xIn) TMG	-		
Magnetic only	T adj., M adj. (2.5...5xIn) TMG	-		
	M adjustable (6...12xIn) MA	-		
Electronic	PR231/P	•		
	PR232/P	•		
	PR331/P	•		
	PR332/P	•		
Versions		F-W		
Terminals	Fixed (F)	F-FC CuAl HR/VR		
	Plug-in (P)	-		
Withdrawable (W)		HR/VR		
Fixing on DIN rail		-		
Mechanical life	[No. operations /hourly oper.]	10000/60		
Electrical life	[No. operations /hourly oper.]	2000/60		
Basic fixed dimensions	3/4 pole	W [mm]	210/280	
		D [mm]	154/154 Manual 178/178 Motorized	
		H [mm]	268/268	
Weights	fixed	3/4 pole	[kg]	9.7/12.5 Manual 11/14 Motorized
	plug-in	3/4 pole	[kg]	-
	Withdrawable	3/4 pole	[kg]	29.7/39.6 Manual 32/42 Motorized

Tmax molded case circuit-breakers

Dimensions T7/T7M series


Overall dimensions T7



- 1 Front terminals for flat connection
- 2 Busbars
- 3 Flange for the compartment door
- 4 Flange fixing screws
- 7 Tightening torque: 18 Nm
- 8 Key lock (optional)
- 9 Padlock (optional)
- 10 Tightening torque: 2.5 Nm
- 13 Terminal for auxiliary contacts

	With flange	Without flange
A (mm)	125...141	147
A (in)	4.92...5.55	5.79

Drilling template for support sheet



Contact us

Canada

ABB Inc.

Low Voltage Products

2117 – 32nd Avenue

Lachine, QC, CANADA H8T 3J1

Tel.: 514-420-3100

Fax: 514-420-3137

Toll Free: 1-800-567-0283

www.abb.ca

While all care has been taken to ensure that the information contained in this publication is correct, no responsibility can be accepted for any inaccuracy. The Company reserves the right to alter or modify the information contained herein at any time in the light of technical or other developments. Technical specifications are valid under normal operating conditions only. The Company does not accept any responsibility for any misuse of the product and cannot be held liable for indirect or consequential damages.

© Copyright 2011 ABB Inc. All rights reserved.

