


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
ABB 09

On-load tap-changer type UCGL./C, VUCGL./C, 17 tap positions, linear switching.
Max. effective No. of turns in pos. 1.
The tap-changer is delivered set in pos. 9, the preceding pos. was 8.

Lindningskopplare typ UCGL./C, VUCGL./C, 17 lägen, linjär koppling.
Max antal effektiva varv i läge 1.
Lindningskopplaren levereras inställd i läge 9, föregående läge var 8.



Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	
15	15-V-x	
16	16-H-v	
17	17-V-x	

The tap-changer is shown in pos. 9, the preceding pos. was 8.
The tap selector is seen from above.
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 9, föregående läge var 8.
Väljaren sedd uppifrån.
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the tap-changer. Dashed lines show leads belonging to the cleats and leads.

Heldragna linjer visar ledare som ingår i lindningskopplaren. Streckade linjer visar ledare som tillhör anslutningsdonet.

Drawn by Form No.	Sheet	Cont
	Year	Week
	Dept	
	Revind	
Design checked by	Design checked by	Cont
	Design checked by	Cont
	Design checked by	Cont

Rev Ind	Revision	Appd	Year	Week	
	Accepted by qual control L Öberg	Accepted for prod by M Häggmar			Description (English) CONNECTION DIAGRAM
	Design checked by H Sundberg	Drawn by C Arnborg			Description (own language) KOPPLINGSSHEMA
	Drawing checked by P Sundqvist	Issued by Dept CO/TKD 09	Year 37	Week	File name 0373-13
ABB Asea Brown Boveri					Lang 82
					Sheet 1
					RevInd -
					Cont -

54920373-13