

CERTIFICATE OF COMPLIANCE

Certificate Number E48139
Report Reference E48139-20090126
Date 2020-November-18

Issued to: ABB Stotz-Kontakt GmbH
Eppelheimer Str 82
Heidelberg69123 DE

**This is to certify that
representative samples of** AUXILIARY DEVICES
See Addendum Page for Product Designation(s).

Have been investigated by UL in accordance with the
Standard(s) indicated on this Certificate.

Standard(s) for Safety: UL 60947-1, C22.2 No. 60947-1, LOW-VOLTAGE SWITCHGEAR AND
CONTROLGEAR – PART 1: GENERAL RULES,
UL 60947-4-1, C22.2 No. 60947-4-1, LOW-VOLTAGE SWITCHGEAR
AND CONTROLGEAR — PART 4-1: CONTACTORS AND MOTOR-
STARTERS — ELECTROMECHANICAL CONTACTORS AND
MOTOR-STARTERS.

Additional Information: See the UL Online Certifications Directory at
<https://iq.ulprospector.com> for additional information

This Certificate of Compliance does not provide authorization to apply the UL Mark. Only the UL Follow-Up
Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's
Follow-Up Services.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please
contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>

CERTIFICATE OF COMPLIANCE

Certificate Number E48139
Report Reference E48139-20090126
Date 2020-November-18

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements

Overload relays, open type Class 10 device, Cat Nos.

T16, followed by -0.13, -0.17, -0.23, -0.31, -0.41, -0.55, -0.74, -1.0, -1.3, -1.7, -2.3, -3.1, -4.2, -5.7, -7.6, -10, -13, -16, -20, -24, -29, -35 or -38.

B05N, followed by -0.13, -0.17, -0.23, -0.31, -0.41, -0.55, -0.74, -1.0, -1.3, -1.7, -2.3, -3.1, -4.2, -5.7, -7.6, -10, -13, -16.

TA40 or TF42, followed by -0.13, -0.17, -0.23, -0.31, -0.41, -0.55, -0.74, -1.0, -1.3, -1.7, -2.3, -3.1, -4.2, -5.7, -7.6, -10, -13, -16, -20, -24, -29, -35 or -38, may additionally be followed by B.

B18N, followed by -0.13, -0.17, -0.23, -0.31, -0.41, -0.55, -0.74, -1.0, -1.3, -1.7, -2.3, -3.1, -4.2, -5.7, -7.6, -10, -13, -16, -20, -24, -29, -35 or -38.

Accessory - Single mounting Kits, Cat. Nos. DB16 and DB42.

Accessory - Single mounting Kits, Cat. Nos. VST05N or VST18N.

Accessory – Wire Reset Button, Cat. Nos. WRB-400, WRB-600, WRB-1000



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>